

Tumble dryers with heat-pump and hot water heating

Drying laundry efficiently, economically and sustainable – with the latest Professional technology from Miele

Gütersloh/Nuremberg, April 25, 2017. – Dryers from Miele Professional now adopt new approaches to heating in a bid to reduce costs. Large mountains of laundry are ready to be returned to the cupboard or perfectly prepared for finishing on a flatwork ironer in next to no time – combined with low consumption and highest efficiency.

The first heat-pump dryer for clients with limited space and large volumes of laundry to process slashes energy costs by half and, thanks to a width of only 71 cm, fits through doors and into confined spaces with ease. The PT 8203 WP from the SlimLine series features a new heat-pump module which is fully housed inside the dryer. With a load capacity of up to 10 kg and a drum volume of 200 l, this model complements the existing range of Miele commercial heat-pump dryers now catering for loads of 6.5, 10 and 13 kg of laundry. The blue-fronted SlimLine dryer has an open plinth, making it easy to manoeuvre into place with a palletiser, and is therefore ideal for smaller laundries. The heat-pump module requires no wall gap at the rear: It is now conveniently located below the drum and can be withdrawn easily for servicing. And there's another important benefit: Thanks to its good sound insulation, it is extremely quiet in operation, producing emissions of no more than 63 dB(A).

Like all heat-pump dryers from Miele Professional, this model from the SlimLine range also features a closed-circuit air path. This dispenses with the need for vent ducting and thereby reduces installation costs to a minimum. Warm, moisture-laden air from the dryer is passed into the heat pump and cooled and dried through contact with a heat exchanger. The dry air is then reheated in a second heat exchanger, ready to pass through the laundry load once again. As the air is cooled and dehumidified, it releases energy which can then be used in re-heating the colder, dry air. In contrast to vented and condenser dryers, this technology recuperates a good deal of the energy, returning it to the drying process.

>>>

Free for editorial use

Please submit copies to
Miele & Cie. KG
Press/Public Relations

Postal address
P.O.B.
33325 Gütersloh
Germany

Phone
+49 5241 89-1953

Fax
+49 5241 89-1950

www.miele.de
presse@miele.de

As alternative sources of heat such as solar-thermal energy, district heating or the use of unit-type co-generation plants gain traction on a worldwide scale, Miele Professional offers a range of specially designed dryers which drastically cut energy costs. Miele's H₂O dryers can be heated by an economical, alternative central heating source. If the water used to cool a co-generation plant is used, dryer operation is virtually cost-free. These dryers are available in a variety of sizes with drum volumes ranging from 325 l to 800 l and load capacities between 10 and 32 kg.

(461 words, 2,769 characters, incl. spaces)

Media contact:

Anke Schläger

Phone: +49 5241 89-1949

Email: anke.schlaeger@miele.de

Company profile: Miele is the world's leading manufacturer of premium domestic appliances including cooking, baking and steam-cooking appliances, refrigeration products, coffee makers, dishwashers and laundry and floor care products. This line-up is augmented by dishwashers, washer-extractors and tumble dryers for commercial use as well as washer-disinfectors and sterilisers for use in medical and laboratory applications (Miele Professional).

The Miele company, founded in 1899, has 8 production plants in Germany as well as one plant each in Austria, the Czech Republic, China and Romania. 2015/16 turnover amounted to approx. EUR 3.71 bn with sales outside Germany accounting for around 70%. Miele is represented with its own sales subsidiaries and via importers in almost 100 countries. The Miele company, now in the fourth generation of family ownership, employs a workforce of around 19,100, 10,800 thereof in Germany. The company headquarters are located in Gütersloh/Westphalia, Germany.

There are two photographs with this text

Photo 1: Takes up only the smallest of footprints and uses merely half as much energy as a vented dryer: The new heat-pump dryer PT 8203 WP from Miele Professional's SlimLine series. (Photo: Miele)

Photo 2: To facilitate maintenance, the heat-pump module can be pulled out on runners for greater accessibility. During operation, the unit is hidden from sight as it is completely integrated into the machine.

(Photo: Miele)

Text and photo download: www.miele-presse.de

Follow us on Twitter: www.twitter.com/Miele_Press 