

**Press Release  
No. 4a/2019**

## **Brief H 7860 BP portrait, a flagship 60 cm wall oven**

### Design

Available in the PureLine design line with a striking stainless-steel handle and trim; in VitroLine design with a handle in the same colour as the glass front, hence in graphite grey, brilliant white or obsidian black; available as an alternative model with a handleless ArtLine design as the H 7860 BPX in all three colours

### Oven functions

20, including various functions in combination with Moisture Plus, low-temperature cooking; more than 100 automatic programmes (in part country-specific); 20 own programmes can be saved; soiling-dependent pyrolytic cleaning

### User convenience

TasteControl prevents food from overcooking; MotionReact responds in a context-sensitive manner to a person approaching the unit, for example by automatically switching the unit on; a built-in camera monitors cooking (FoodView); wireless food probe for roasting to a core temperature; connectivity-ready with numerous further convenience features (WiFi on board)

### Further technical specifications

76 l oven volume with five rack levels, A+ energy efficiency, temperature range 30°C - 300°C, BrilliantLight with fluorescent side lightbars

### Accessories

Baking sheet and multi-purpose rack with PerfectClean; roasting rack, FlexiClip fully telescopic runners and side racks able to withstand pyrolytic cleaning (PyroFit); cookery book (depending on country)

### **Media contact:**

Michael Prempert

Phone: +49 5241 89-1957

Email: michael.prempert@miele.com

Text and photo download: [www.miele-presse.de](http://www.miele-presse.de)