

Press Release
No. 16/2019

New tank dishwashers provide sparkling results and are more efficient than ever before

- ▶ Versatile and even easier to operate
- ▶ Optimised washing system with redesigned spray arms

Gütersloh/Hamburg, March 15, 2019. – Four new undercounter tank dishwashers from Miele offer greater convenience than ever before. The user interface with its high-resolution touch display is child's play to use and is simple to the point of virtually eliminating operating mistakes. In addition, operating costs are cut significantly by an optimised washing system. These dishwashers produce perfect results – and thanks to their innovative add-on features dispense with the need for manual polishing as glasses leave the dishwasher without stains. The new models are due to be launched in the second quarter of 2019.

Economies are particularly noticeable in the 46 cm wide glass washer: Standard programmes get by with only two litres of water, and in the Eco programme, water consumption is even as low as 1.8 l. Compared with the previous model generation, this represents savings of 17% and 25% respectively. In the other three models, consumption has been reduced by between 8% and 17%. These excellent values are achieved through an optimised water circuit and completely redesigned spray arms. Reduced water consumption also automatically results in lower energy and detergent requirements.

The new hard glass touch display makes all undercounter tank dishwashers even simpler to use than previously, even when wearing gloves. Self-explanatory pictogrammes guide users to the three standard and three special-purpose programmes. Individual functions are intuitively selected. An integrated reverse osmosis system on selected models provides additional convenience, giving stemware a sparkling finish without the need for manual polishing.

With a capacity of up to 77 baskets per hour, these undercounter tank dishwashers are capable of washing large mountains of crockery per hour. The programmes are geared specifically to the needs of different load types and degrees of soiling, such as glassware, mixed loads or plates. Variable pressure levels and cycle durations as well as flexible dispensing ensure optimum cleaning combined with the best possible protection of loads. Short programmes are completed in 47 or 55 seconds. Safety functions such as integrated

Free for
editorial use

Please submit
copies to
Miele & Cie. KG
Public Relations

Postal address
P.O.B.
33325 Gütersloh
Germany

Phone
+49 5241 89-1953
Fax
+49 5241 89-1950

www.miele.de
presse@miele.de

spray arm and filter monitoring detect possible problems at an early stage and relay their findings to the display.

Thanks to a chamber depth of more than 60 cm, the PTD 704 also lends itself to washing large and bulky items such as trays or EN containers. As previously, all models can be used as free-standing units or installed below a worktop.

Media contact:

Anke Schläger

Phone +49 5241 89-1949

Email: anke.schlaeger@miele.com

Company profile: Miele is the world's leading manufacturer of premium domestic appliances including cooking, baking and steam-cooking appliances, refrigeration products, coffee makers, dishwashers and laundry and floor care products. This line-up is augmented by dishwashers, washer-extractors and tumble dryers for commercial use as well as washer-disinfectors and sterilisers for use in medical and laboratory applications (Professional Business Unit). The Miele company, founded in 1899, has eight production plants in Germany as well as one plant each in Austria, the Czech Republic, China and Romania. These are joined by the two plants belonging to Miele's Italian medical technology subsidiary Steelco. 2017/18 turnover amounted to approx. EUR 4.1 bn, with sales outside Germany accounting for 70%. Miele is represented with its own sales subsidiaries and via importers in almost 100 countries. Throughout the world, the family-run enterprise, now in its fourth generation, employs a workforce of around 20,100, whereof 11,200 are employed in Germany. The company headquarters are located in Gütersloh/Westphalia, Germany.

There are three photographs with this text



Photo 1: Easy to operate, not only behind the bar: A new undercounter tank dishwasher from Miele. (Photo: Miele)



Photo 2: Perfect results: Thanks to their innovative add-on features dispense with the need for manual polishing as glasses leave the dishwasher without stains. (Photo: Miele)



Photo 3: With up to 77 baskets per hour, these new machines are able to cope with large large loads – from glasses to mixed loads.
(Photo: Miele)

Text and photo download: www.miele-presse.de

Follow us on:

 @Miele_Press

 @Miele

 @Miele_com

 Miele | Miele Professional