

Press release  
No. 047/2020

## **Maximum convenience in a small package – the new 45 cm dishwashers from Miele**

- ▶ The G 5000 SL generation is powerful, flexible and elegant
- ▶ QuickPowerWash delivers clean dishes in less than an hour

**Gütersloh, August 31, 2020. – As more and more people move to expensive urban accommodation, they have to make the most out of every available centimetre – and that includes the space in their kitchens. Luckily, Miele's new slim dishwashers are the perfect fit. Measuring just 45 centimetres wide, the G 5000 SL generation offers a host of high-quality, convenient features that have so far been the preserve of larger appliances: extremely convenient loading, top performance and, of course, networking. The appliances are being launched on the market in September.**

At the heart of this new range is EcoPower technology, which makes use of an improved circulation pump, new spray arms and a highly effective filter system. This means that water consumption is reduced to six litres in the automatic programme and energy efficiency is able to achieve standards of up to A+++ -10%, with outstanding cleaning results. Not only that, but Miele's exclusive QuickPowerWash programme is available as an option when time is scarce: combined with the ultra-quick-dissolving Miele UltraTabs All in 1 , it gets dishes, glasses and cutlery clean in less than an hour.

The patented AutoOpen drying feature ensures outstanding drying results by opening the door slightly at the end of the programme to allow moist air to escape. A special flow of air and a function that heats the underside of the countertop prevents any adverse effects of condensation harming the countertop.

### **Smart through and through**

For the first time, Miele's slim 45 cm dishwashers are network-enabled with WiFiConn@ct, making it possible for users to see the appliance status on their smartphone or tablet – and even order more detergent – while they're on the go. The appliance can also be voice-controlled with Amazon Alexa.

The FlexLine baskets make the G 5000 SL even more flexible and convenient, with wide handles that ensure the baskets are easy to pull out. The MultiFlex tray in the 45 cm models can be adapted to different situations thanks to a row of spikes that can be lowered. In the

Free for  
editorial use

Please submit  
copies to  
Miele & Cie. KG  
Public Relations

Postal address  
P.O.B.  
33325 Gütersloh  
Germany

Phone  
+49 5241 89-1953  
Fax  
+49 5241 89-1950

[www.miele.de](http://www.miele.de)  
[presse@miele.de](mailto:presse@miele.de)

upper basket, the height-adjustable FlexCare cup rack features a pimpled surface that holds cups securely in place. As well as this, there are high-quality silicone holders that are designed to protect wine and champagne glasses.

As the rows of spikes in the lower basket can be moved down, even large pans and other extensive items can be placed inside. The adjustable FlexCare glass holders with silicone cushioning allow wine glasses to be held safely in place. Meanwhile, an additional MultiClip keeps small and lightweight dishes secure during cleaning. All the removable parts and handles are marked in yellow, making them instantly identifiable.

Four power LEDs (BrilliantLight) evenly illuminate the interior and the baskets when they are pulled out, making loading and unloading easier. Another convenient bonus for open-plan kitchens in particular is the ExtraQuiet programme, which reaches a noise level of just 40 dB(A).

The design and intuitive operation of the G 5000 SL dishwashers make these appliances perfectly in tune with Generation 7000 built-in appliances. They are available as integrated or fully integrated models, or as built-under or freestanding appliances. Miele offers up to three colour options for models with a fascia panel: CleanSteel, Obsidian black and Brilliant white.

**Media contact:**

Julia Cink

Phone: +49 5241 89-1962

Email: [julia.cink@miele.com](mailto:julia.cink@miele.com)

**Company profile:** Miele is the world's leading manufacturer of premium domestic appliances including cooking, baking and steam-cooking appliances, refrigeration products, coffee makers, dishwashers and laundry and floor care products. This line-up is augmented by dishwashers, washing machines and tumble dryers for commercial use as well as washer-disinfectors and sterilisers for use in medical and laboratory applications (Miele Professional). The Miele company, founded in 1899, has eight production plants in Germany as well as one plant each in Austria, the Czech Republic, China, Romania and Poland. These are joined by the two plants belonging to Miele's Italian medical technology subsidiary Steelco. Turnover in the 2018/19 business year was around € 4.16 bn, with a share of business outside Germany of approx. 71%. Miele is represented with its own sales subsidiaries and via importers in almost 100 countries/regions. Throughout the world, the family-run enterprise, now in its fourth generation, employs a workforce of around 20,500, whereof 11,050 are employed in Germany. The company has its headquarters in Gütersloh in Westphalia.


There are three photographs with this text



**Photo 1:** The proven QuickPowerWash function and compatible Miele UltraTabs All in 1 get dishes and cutlery clean in just 58 minutes. (Photo: Miele)



**Photo 2:** The new G 5000 SL 45 cm dishwashers deliver appealing features that ensure maximum convenience in a small package: these include BrilliantLight illumination in the fully integrated G 5890 SCVi model. (Photo: Miele)



**Photo 3:** A new basket design makes these dishwashers highly flexible and easy to load. (Photo: Miele)

Text and photo download: [www.miele-presse.de](http://www.miele-presse.de)

Follow us on:

 @Miele\_Press

 @Miele

 @Miele\_com

 Miele