

Press release
No. 033/2021

Washing reusable bottles in a dishwasher – now possible with all commercial models from Miele

- ▶ Bottle basket now for the first time available for fresh water and ProfiLine dishwashers
- ▶ Injector nozzles enable thorough internal cleaning

Gütersloh, May 11, 2021. – Reusable glass bottles and decanters are becoming increasingly popular – whether at home, in offices, in cafés and restaurants or in nursing homes and child care. Now, the insides of these bottles can be washed fast and thoroughly in all Miele commercial dishwashers. The matching basket is available both for fresh water dishwashers and for models from the ProfiLine series.

As the bottle basket has now stood the test of time on undercounter tank dishwashers, a similar basket will now be made available for the other model series. The new basket is fitted in place of the lower basket and connects directly to the water supply. It features injector nozzles for 16 bottles. Hence, vessels are cleaned reliably on the inside. ProfiLine models can safely accommodate bottles with a height of up to 27.5 cm; fresh water dishwashers even up to a height of 50 cm (with upper basket removed).

The bottle basket is fitted in only a few simple moves, allowing crockery, pots and pans, and glassware to be washed in the same machine – under particularly hygienic conditions as this type of model takes in fresh water multiple times during a programme cycle. The 'Glassware' programme is recommended for bottles and decanters, although the other programmes can also be used. On fresh water models, the shortest relevant cycle time is 8 minutes; 17 minutes on ProfiLine models.

Media contact:

Anke Schläger

Phone: +49 5241 89-1949

Email: anke.schlaeger@miele.com

Free for
editorial use

Please submit
copies to
Miele & Cie. KG
Public Relations

Postal address
P.O.B.
33325 Gütersloh
Germany

Phone
+49 5241 89-1953
Fax
+49 5241 89-1950

www.miele-professional.com
presse@miele.de

Company profile: Miele is the world's leading manufacturer of premium domestic appliances including cooking, baking and steam-cooking appliances, refrigeration products, coffee makers, dishwashers and laundry and floor care products. Their product portfolio also includes dishwashers, air purifiers, washing machines and tumble dryers for commercial use as well as washer-disinfectors and sterilisers for use in medical and laboratory applications (Miele Professional). Founded in 1899, the company has eight production plants in Germany, one each in Austria, the Czech Republic, China, Romania and Poland as well as two production plants belonging to its Italian medical technology subsidiary Steelco. Sales in the 2020 business year amounted to around € 4.5 bn (thereof 29.5% in Germany). Miele is represented with its own sales subsidiaries and via importers in almost 100 countries/regions. Throughout the world, the family-run enterprise, now in its fourth generation, employs a workforce of around 20,900, of which approx. 11,050 employees work in Germany. The company has its headquarters in Gütersloh in Westphalia.

There is one photograph with this text



Photo 1: A secure hold for 16 reusable glass bottles: In the new basket for commercial dishwashers and ProfiLine models from Miele, glassware is thoroughly washed both inside and out. (Photo: Miele)

Text and photo download: www.miele-press.com

Follow us on:

 @Miele_Press

 @Miele

 @Miele_com

 Miele | Miele Professional

Further information on this topic is available to users on www.miele-professional.com