

Press release
No. 068/2021

Strong performance and even smarter: The new Miele Scout RX3 robovac

- ▶ Cleaning performance increased by up to 25%*
- ▶ Comfortable mobile control
- ▶ HD camera delivers pin-sharp live images to smartphone

Gütersloh, September 3, 2021. – The floor under the dining table is to be cleaned after every meal and the living room vacuumed once a day? Or just drop in remotely to see if everything is OK at home? Neither is a problem for the new Miele Scout RX3. The new generation of robotic vacuum cleaners excels thanks to innovative functions, excellent user convenience – and a considerable improvement in suction power. The Scout RX3 has been available in Germany since June and is now also available across Europe.

Thanks to a completely revamped Miele Scout app, the robotic vacuum cleaner can be conveniently controlled from a smartphone, including such useful functions as time and status queries. A further highlight: Scout RX3 Home Vision HD models sport an HD camera which transmits high-resolution images straight to an end device. As with all other Miele appliances featuring connectivity, the robovac, linked via WiFi, responds to Amazon's voice assistant Alexa. An 'Alexa, tell Miele to clean the kitchen' is sufficient for the Scout to set to work on pre-defined areas.

With the launch of its third generation, Miele has further perfected the Scout's navigation. Thanks to two front cameras, the Scout RX3 cleans in the very last corner and systematically vacuums every square centimeter of the home. The stereo camera system sees rooms and objects in 3D and is able to calculate sizes and distances. As a result, steps, furniture and other obstacles are detected and reliably circumnavigated – even when it is completely dark. With a height of only 8.5 cm, the robotic vacuum cleaner fits effortlessly below cupboards and sofas for thorough cleaning. And should the Scout become trapped on the way, an optimised error processing routine precisely reports the problem and how to resolve it.

The rechargeable 5200 mAh lithium ion battery provides 120 minutes of cleaning, equating to an area of up to 120 square meters. When the battery is flat, the Scout RX3 finds its own way to the recharging station, which can now be securely fixed to the floor. Once recharged, work is resumed at the precise spot where the appliance last finished.

Free for
editorial use

Please submit
copies to
Miele & Cie. KG
Public Relations

Postal address
P.O.B.
33325 Gütersloh
Germany

Phone
+49 5241 89-1953
Fax
+49 5241 89-1950

www.miele.de
presse@miele.de

With its tried-and-tested Quattro Cleaning Power 4-stage system, the Scout RX3 can achieve much higher suction power on any surface. Technical optimisation of the motor, increased air performance and a beater bar with harder bristles ensure that the robovac is better at removing fine dust in particular from carpets. Corner cleaning on hard floors and short-pile carpets is even more effective thanks to the new 20-arm side brushes.

The Scout RX3 is available in three model versions: Whilst the entry-line obsidian black Scout RX3 has a battery runtime of up to 60 minutes, the Scout RX3 Runner (bronze pearl finish) vacuums for up to twice as long. The same applies to the Scout RX3 Home Vision HD in rosé gold pearl finish, which also relays live images to an end device with its HD camera. The entry-line and flagship models are already on sale; the Scout RX3 Runner will follow in October 2021.

*compared with the Miele Scout RX2 on carpeting in accordance with IEC 62929:2015 Section 6.4.

Media contact:

Hilal Kalafat

Phone: +49 5241 89-1011

Email: hilal.kalafat@miele.com

Company profile: Miele is the world's leading manufacturer of premium domestic appliances including cooking, baking and steam-cooking appliances, refrigeration products, coffee makers, dishwashers and laundry and floor care products. Their product portfolio also includes dishwashers, air purifiers, washing machines and tumble dryers for commercial use as well as washer-disinfectors and sterilisers for use in medical and laboratory applications (Miele Professional). Founded in 1899, the company has eight production plants in Germany, one each in Austria, the Czech Republic, China, Romania and Poland as well as two production plants belonging to its Italian medical technology subsidiary Steelco. Sales in the 2020 business year amounted to around € 4.5 bn (thereof 29.5% in Germany). Miele is represented with its own sales subsidiaries and via importers in almost 100 countries/regions. Throughout the world, the family-run enterprise, now in its fourth generation, employs a workforce of around 20,900, of which approx. 11,050 employees work in Germany. The company has its headquarters in Gütersloh in Westphalia.

There are three photographs with this text



Photo 1: The Miele Scout RX3 Home Vision HD is also equipped with an HD camera. This allows you to check that everything is OK back at home while on the move, end-to-end encryption included!
(Photo: Miele)



Photo 2: Thanks to its intelligent navigation, Miele's robotic vacuum cleaner recognises and negotiates objects in its path. (Photo: Miele)



Photo 3: The new Miele Scout app is easy to use, even remotely – for a cleaner home when you return from work. (Photo: Miele)

Text and photo download: www.miele-press.com

Follow us on:

 @Miele_Press

 @Miele

 @Miele_com

 Miele