

Press release
No. 076/2022

Quiet and powerful: Miele TwoInOne induction hob with new extraction concept

- ▶ New Silence motor reduces perceived sound emissions by around 30%
- ▶ Plug&Play for simple installation

Gütersloh/Berlin, August 31, 2022. – TwoInOne - Nomen est omen: The induction hob with an integrated extractor combines the best from the two Miele competence centres in Bünde and Arnsberg. These elegant multitalents have been in particularly big demand for several years in the design of open-plan kitchens. The company is now augmenting its portfolio with the inclusion of two very powerful yet quiet models with a new fan system.

The two newcomers, the KMDA 7272 Silence and the KMDA 7473 Silence, draw in moisture, grease and odours via a centrally positioned downdraught extractor far more forcefully than previously the case. If the highest available power output is needed, for instance when all rings are in use, the booster can be activated to transport up to 610 m³ of air per hour (vented mode). Despite this, the new models have perceived sound emissions during operation which are around 30% lower than on their predecessors. 'This makes them the quietest on the market', says Till Deutschmann, Head of Category Marketing Hobs and Hoods with Miele, 'and the ideal proposition for modern living styles'.

The technical centrepiece of the new extraction system is a Silence motor with a streamlined cross-section and a reduced building-in depth. In both cooking zones on either side of the downdraught extractor, individual pans or larger dishes are automatically detected (permanent pan recognition). On the KMDA 7473 Silence, two zones (FlexZones) can be joined to give two racetrack burners with an output of 3.7 kW, for example for casserole dishes, a Gourmet griddle or Teppan Yaki.

The elegant design of the products is largely the result of the striking extraction grille in the centre. The grille is set in the ceramic screen and, thanks to its bevelled frame, is now even more streamlined. Depending on the model, the grille is either completely black (KMDA 7272 Silence) or has discreet brushed stainless-steel slats (KMDA 7473 Silence). The ComfortSelect Plus controls are located directly in front of the extractor, with an indicator each for the cooking zones and the extractor (depending on the model, the run of numbers is either printed on the surface or back-lit). New, too, are the minimalistic ring graphics. With the proven Con@ctivity* function, suction power is automatically adjusted to what is actually

happening on the hob. Shortly after cooking ends, the extractor automatically switches itself off again.

Greater flexibility and simpler installation with Plug&Play

TwoInOne hob units offer a choice between air venting and recirculation. In vented mode, steam and vapours are drawn in and filtered by the grease filter and blown outside the building via flat ducting and a wall vent. This rids the kitchen entirely of odours and moisture. At the same time, fresh air must be admitted, for instance via an open window.

In recirculation mode, the TwoInOne passes air first through a grease filter and an active charcoal filter. New on this model is that the latter is now located next to the grease filter for easy and fast replacement when needed. The air then passes through ducting with a rectangular cross-section and returns to the kitchen via a recirculation box (ducted recirculation). What is also new is the fine dust filter on the active charcoal version. The Sensitive AirClean filter removes not only odours but also cleans the room air using an additional random-spun filter: Fine dust particles such as pollen, spores, bacteria and tobacco smoke (with a size of 0.3 to 2.5 µm) are reduced by more than 50% (the random-spun filter subscribes to Class ePM 2.5 filtration efficiency, tested according to ISO 16890).

With this new approach to extraction, Miele is now offering its customers an additional Plug&Play recirculation version which guarantees even greater flexibility regarding planning and installation. With this type of installation, it is also possible to achieve shorter plinths than previously. This method of installation requires neither flat ducting nor a plinth box. Instead, an adapter connects the air discharge on the unit with a round cut-out in rear panel of the housing unit. This allows filtered air to be returned to the room via a gap between the housing unit and the wall and from there via the kitchen plinth. The active charcoal filter and the grease filter are located, as on models with ducted recirculation, at the top of the unit from where they can be removed conveniently. Thanks to the slim design of the new Silence motor and a building-in depth of only 20 cm, only the top drawer below the unit is sacrificed with Plug&Play installation. All other drawers below can be used to their full extent as storage space.

The new TwoInOne hob units will be available in two versions from December 2022: one model with four individual rings and a black grille (KMDA 7272 Silence) and a 'racetrack burner' version (KMDA 7473 Silence) with WiFi functionality for connection to the Miele App*. Both models are available either as frameless units or with an all-round stainless-steel frame. Furthermore, these hob units are available as recirculation and vented versions. Both models achieve an A+ energy efficiency rating.

*The applications for domestic appliances mentioned in the text are additional digital services from Miele & Cie. KG. All smart applications are enabled by the Miele@home system. The range of functions may vary depending on the model and the country.

Media contact

Julia Cink

Phone: +49 5241 89-1962

Email: julia.cink@miele.com

Company profile: Miele is the world's leading manufacturer of premium domestic appliances including cooking, baking and steam-cooking appliances, refrigeration products, coffee makers, dishwashers and laundry and floor care products. Their product portfolio also includes dishwashers, air purifiers, washing machines and tumble dryers for commercial use as well as washer-disinfectors and sterilisers for use in medical and laboratory applications. Founded in 1899, the company has eight production plants in Germany, one each in Austria, the Czech Republic, China, Romania and Poland as well as two production plants belonging to its Italian medical technology subsidiary Steelco. Sales in the 2021 business year amounted to around €4.84 bn. Miele is represented with its own sales subsidiaries and via importers in almost 100 countries/regions. Throughout the world, the family-run enterprise, now in its fourth generation, employs a workforce of around 22,300, of which approx. 11,200 employees work in Germany. The company has its headquarters in Gütersloh in Westphalia.

There are four photographs with this text



Photo 1: The new TwoInOne hob units KMDA 7272 Silence and KMDA 7473 Silence count among the quietest models on the market. This makes them ideal propositions for modern open-plan kitchens. (Photo: Miele)



Photo 2: Thanks to the slim design of the new Silence motor and simple Plug&Play installation, only the top drawer below the unit is sacrificed. All other drawers below can be used to their full extent as storage space. (Photo: Miele)



Photo 3: Depending on cooking needs, two rings on the KMDA 7473 Silence model can be joined together to accommodate a Gourmet griddle for example. (Photo: Miele)



Photo 4: The striking extraction grille in the centre is the hallmark of the elegant design of these units. In front are the convenient controls with an indicator each for the cooking zones and the extractor (depending on the model, the run of numbers is either printed on the surface or back-lit). (Photo: Miele)

Text and photo download: www.miele-press.com

Follow us on:  @Miele_Press

 @Miele

 @Miele_com

 Miele