

Press release
No. 077/2023

Award-winning – Three Miele induction hobs net design prizes

- ▶ Experts laud the flexibility of TwoInOne models for modern kitchen design
- ▶ Full-surface induction hob offering ample space and elegance

Gütersloh, August 9, 2023. – Miele induction hobs are exceptional in terms of both functionality and design. This has been confirmed by the jury of the iF Design Award and the RedDot Design Award. Two hobs with an integrated extractor (TwoInOne) and a full-surface induction hob were each double winners. Both awards count among the world's most coveted prizes of their kind.

The elegant TwoInOnes, highly sought-after products when designing open-plan kitchens, are both powerful and quiet in operation. Their reduced design is characterised by the central air intake with a grille set in the ceramic glass screen. This feature, in particular, convinced the jury of the Red Dot Award and allows pots and pans to slide freely. The grille on the rectangular air intake blends in seamlessly with the design of the hob. Depending on the model, the grille is either completely black (KMDA 7272 Silence) or has discreet brushed stainless-steel slats (KMDA 7473 Silence).

Both hobs feature 4 rings, whereby two rings (Flex zone) on the KMDA 7473 Silence can be joined to give a racetrack burner, for example for an oven dish, a Gourmet griddle or a Teppan Yaki. The TwoInOne hobs offer maximum flexibility in contemporary kitchen design according to the iF Design Award assessment. This is further supported by the shallow installation depth of the units which means that only the top drawer in the base unit below is sacrificed as well as by simple and fast Plug&Play installation. As a result, these induction hobs meet the highest demands placed on aesthetics and functionality, the jurors continue.

Further information on the TwoInOne induction hobs KMDA 7272 Silence and KMDA 7473 Silence are provided by the following link: [Press release](#).

A further recipient of the iF and the Red Dot design prize was the KM 7897-1 FL Diamond full-surface induction hob. As many as 6 pots, pans and oven dishes can be placed anywhere on the 90 cm wide hob unit and move around freely. This guarantees untold freedom during cooking. Moreover, the ceramic screen on the hob unit features a special coating: DiamondFinish is one of the hardest surfaces on the market and hence particularly scratch-resistant. The Red Dot jury took a particular fancy to the unit's low-key appearance: 'When the frameless hob unit is not in use, the controls are invisible. This results in a

subdued and uniform look'. The iF team of jurors highlights the restrained radiance which lends these hobs an additional touch of elegance.

For all details on the KM 7897-1 FL Diamond full-surface induction hob, see [here](#).

Alongside the three hob units for domestic use, commercial machines from Miele were also awarded the two prizes: MasterLine dishwashers, the PDW 909 washer-dryer stack and the PDR 510/910 series of dryers. Further information on these products is provided by [this press release](#).

Media contact

Julia Cink

Phone: +49 5241 89-1962

Email: julia.cink@miele.com

Company profile: Miele is the world's leading manufacturer of premium domestic appliances including cooking, baking and steam-cooking appliances, refrigeration products, coffee makers, dishwashers and laundry and floor care products. Their product portfolio also includes dishwashers, washing machines and tumble dryers for commercial use as well as washer-disinfectors and sterilisers for use in medical and laboratory applications. Founded in 1899, the company has eight production plants in Germany, one each in Austria, the Czech Republic, China, Romania and Poland as well as two production plants belonging to its Italian medical technology subsidiary Steelco. Sales in the 2022 business year amounted to around € 5.43 bn. Miele is represented with its own sales subsidiaries and via importers in almost 100 countries/regions. Throughout the world, the family-run enterprise, now in its fourth generation, employs a workforce of around 23,300, of which approx. 11,900 employees work in Germany. The company has its headquarters in Gütersloh in Westphalia.

There are three photographs with this text



Photo 1: Miele's KMDA 7272 Silence induction hob received the 2023 iF Design Award for its striking yet discreet design and was the 2023 reddot winner. (Photo: Miele)



Photo 2: Recipient of the iF Design Award 2023 and reddot winner 2023: The KMDA 7473 Silence on which two rings can be joined to give a casserole zone which can also be used with Miele's Gourmet griddle. (Photo: Miele)



Photo 3: The KM 7897-1 FL Diamond full-surface induction hob offers ample space for up to 6 pots and pans. DiamondFinish reduces scratches and adds elegance thanks to its discreet radiance. Reason enough for commendation with the coveted iF and Red Dot awards. (Photo: Miele)

Text and photo download: www.miele-press.com

Follow us on:



@Miele



@Miele_com



Miele