

Press release
No. 107/2024

125 Gala Edition: ArtLine handleless kitchen appliances in elegant Obsidian black matt

- ▶ Free 125-week extended warranty to mark Miele's anniversary
- ▶ Induction hobs with unique ceramic glass surface

Gütersloh/Rödinghausen, September 20, 2024. – Whether it's blending harmoniously into a dark kitchen design concept or standing out against a light backdrop, the ArtLine range of built-in appliances in elegant Obsidian black matt opens up a whole host of design options. These appliances come with an extra incentive to mark Miele's anniversary year: the 125 Gala Edition is eligible for a free 125-week extended warranty – added onto the standard warranty.

The promotional range includes ovens, compact microwave combination ovens, warming and vacuum drawers, built-in coffee machines and a wine unit, plus induction hobs with a special matt black ceramic glass surface. Completing the 125 Gala Edition are a cooker hood and a freestanding fridge-freezer.

A standout feature of the Obsidian matt black ArtLine models is their handleless design: appliances open at the touch of a sensor control, allowing oven doors, for example, to slide down smoothly. The new colour is also in full display on the door. The glass surface has a fine texture, giving it a different look and feel from conventional glass fronts.

MattFinish ceramic glass on hobs repels scratches and fingerprints

Miele offers two induction hobs with MattFinish ceramic glass to go with its ArtLine range in Obsidian black matt, using a material that not only enhances the minimalist hob design but is also highly scratch-resistant. It reduces scratches from sand by some 80 percent, for example, helping hobs hold onto their high-quality looks for years to come. The textured surface also has the advantage of virtually hiding any fingerprints impressed on it. What's more, the model featuring integrated vapour extraction (KMDA 7876 FL 125 Gala Edition) and a second hob with PowerFlex cooking zones (KM 7576 FL 125 Gala Edition) have been honoured with the iF Design Award 2024, with the jury praising their minimalist design. Discreet white lines indicate where to position cookware and griddle plates, while the power level displays are also designed in white.



New angled cooker hood delivers efficient ventilation technology and customisable lighting

Customers seeking out an angled cooker hood need look no further than the model featuring a glass panel in Obsidian black matt. The body of the canopy has a shallower depth and lower height than previous models, lending it an elegant, discreet appearance, while the steeper angle of the glass gives taller people more room to move around during cooking.

The new DynamicWhite feature allows the hood lighting to blend beautifully into the kitchen environment with a colour temperature selection option that can be adjusted in the Miele app. This makes it possible to cast LED lighting onto the kitchen in a colour temperature range from warm white (2700 kelvins) to cool white (6500 kelvins) – and the intensity can be adjusted too. Meanwhile, the energy-saving ECO motor achieves outstanding performance values and meets the criteria of energy efficiency class A++. Not only that, but this model creates sound emissions that are around 20 percent* lower than other angled cooker hoods from Miele, while still delivering exceptional air throughput. The matt black appliance option is available in a width of 90 centimetres.

Wine unit and freestanding fridge-freezer round off the range

The new matt black KWT 7112 iG built-in wine unit is able to accommodate a small yet sophisticated collection of favourite wines: made for 45 cm niches, the appliance provides space for 18 bottles and is equipped with an Active AirClean filter, flexible beechwood shelves (FlexiFrame) and LED lighting. This model is also handleless and is opened using a Push2open mechanism.

Model KFN 4799 AD in Obsidian black matt is available for customers who want a freestanding fridge-freezer combination – plus, its elegant design has no visible handles either. The model is also a highly sustainable option, meeting the criteria of energy efficiency class A and featuring the PerfectFresh Pro system.

With every model in the 125 Gala Edition promotional range, Miele is including a free 125-week extended warranty that can be activated easily in the Miele app.

*DAH 4980 compared to DA 6498 W extracted air, level 3

Media contact

Julia Cink

Phone: +49 5241 89-1962

E-Mail: julia.cink@miele.com

Company profile: Miele is recognised as the world's leading supplier of Premium domestic appliances, with an inspiring portfolio for the kitchen, laundry and floor care. The company also offers machines, systems and services for use in hotels, offices, care and medical technology. Since its foundation in 1899, Miele has lived up to its brand promise of "Immer Besser" in terms of quality, innovation, performance and timeless elegance. With its durable and energy-saving appliances, Miele helps its customers to make their everyday lives as sustainable as possible. The company is still owned by the two founding families Miele and Zinkann and has 15 production plants, eight of which are in Germany. Around 22,700 people work for Miele worldwide and the company's most recent turnover was 4,96 billion Euro. The company has its headquarters in Gütersloh in Westphalia.

There are three photographs with this text



Photo 1: To mark its 125th anniversary, Miele is launching an elegant Obsidian black matt option for its handleless ArtLine series, plus induction hobs and an angled cooker hood. A free 125-week extended warranty is available on top of the standard Miele warranty. (Photo: Miele)



Photo 2: The induction hob with integrated TwoInOne vapour extraction (KMDA 7876 FL) and MattFinish has an elegant look and feel, and is even resistant to scratches. The textured surface also has the advantage of virtually hiding any fingerprints impressed on it. Available as an extra bonus with the 125 Gala Edition is a free 125-week extended warranty. (Photo: Miele)



Photo 3: The angled cooker hood gives taller people more room to move around during cooking. With its new DynamicWhite feature, the hood lighting fits perfectly into the kitchen surroundings – and the colour temperature can be changed at any time in the Miele app. (Photo: Miele)

Text and photo download: www.miele-press.com

Follow us on:

 @Miele

 @Miele_com

 Miele