

Press release
No. 048/2025

Fire-fighting equipment is quickly available from Miele drying cabinets

- ▶ Drying helmets, boots and other kit items all at the same time
- ▶ Maximum load capacity of 6 or 15 kg

Gütersloh/Fulda, May 14, 2025 – For the protective equipment of fire-fighters, many manufacturers recommend drying cabinets – both for drying operational jackets and trousers which are suitable for drying, but especially for utensils made from materials which may suffer damage in a tumble dryer. This includes, for example, boots, gloves, belts, wetsuits and cut-proof trousers. Miele is therefore now offering drying cabinets in two sizes and, consequently, a complete portfolio for reprocessing personal equipment from one single source.

The cabinets are available in widths of 60 and 120 cm and, depending on the model, are designed for up to 15 kg loads. Items of clothing and accessories are placed in them either on hangers or racks. There are suitable programmes for clothing, helmets, respirators and gloves, which are significantly faster than simply airing. Reproofing agent is also sustainably activated. If necessary, the cabinet can be opened at any time to add more items.

The 60 cm wide Easy Dryer 1900 Extreme model is a compact, flexible unit for drying personal protective equipment and temperature-sensitive apparatus. In it, the programme temperature and running time can be set in three stages - up to 65°C and over a maximum duration of six hours. Helmets, breathing apparatus and similar items can be placed on extendible racks, and there are also six double clothes hooks and two rows of glove holders on the inside of the door. An additional rack for jacket hangers is also available.

For drying and impregnation of protective clothing and rescue wear on hangers, the 120 cm wide DC 120 WW unit is particularly well suited. It offers the two residual moisture-controlled programmes "Normal" (up to 60°C) and "Impregnate" (up to 75°C), which are selected via touch keys. The display shows the programme names in the selected language. An efficient system combining recirculation and exhaust air heating ensures short heat-up and drying phases. Warm air is fed directly into the hanging garments via four ventilation connections, while two side cabinet vents also provide airflow on the outside of garments. As a result, the "Normal" programme is completed in only 95 minutes. Instead of the ventilation connections, holders for boots or gloves are also available as accessories, which can then be dried effectively from the inside in larger quantities.

Apart from the regular cleaning of the filters, no further maintenance is required when operating the drying cabinets. Both models are made from high-quality zinc-plated steel, which is corrosion-resistant, robust and durable - an environmentally friendly and highly recyclable product.

Media contact

Anke Schläger

Phone: +49 5241 89-1949

Email: anke.schlaeger@miele.com

About Miele: For more than 125 years, Miele has lived up to its brand promise of “Immer Besser” in terms of quality, innovation and timeless elegance. Founded in 1899, the globally active company for premium domestic appliances inspires customers with pioneering solutions for the connected home. In addition, Miele offers appliances, systems and services for commercial use, such as in hotels or care facilities as well as in medical technology. With its durable and energy-saving appliances, Miele helps its customers make their daily lives as sustainable as possible. The company is owned by the two founding families, Miele and Zinkann. In the 2024 business year, Miele generated a turnover of 5.04 billion Euros with approximately 23,500 employees. Its global network comprises 19 production plants and around 50 service and sales subsidiaries (as of February 2025). The company has its headquarters in Gütersloh, North Rhine-Westphalia.

There are two photographs with this text



Photo 1: With a width of 120 cm, the DC 120 WW drying cabinet offers space for protective suits, gloves and other items of personal protective equipment. (Photo: Miele)



Photo 2: The 60 cm wide Easy Dryer 1900 Extreme model combines recirculation and exhaust air heating - for drying protective suits and other accessories. (Photo: Miele)

Text and photo download: www.miele-press.com

Follow us on:



Miele



miele



Miele | Miele Professional

Further information on this topic is available to users on www.miele-professional.com