

Information on Critical Substances

Disclosure requirement pursuant to Article 33 of European Regulation (EC) No. 1907/2006 (REACH) regarding substances on the so-called "REACH Candidate List" (SVHC—Substances of Very High Concern).

Please refer to the PDF to determine whether any materials in our products contain a substance on the so-called "REACH Candidate List" in concentrations exceeding 0.1% w/w (weight percent).

Miele's compliance with all European regulatory requirements restricting the use of substances ensures that, when our products are used as intended and handled properly, there are no risks to the environment or human health during their use or disposal.

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10565481	Timeclock EZT 7664 400V 50Hz	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
7884426	Timeclock EZT 7654 220-240V	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396770	Viewing screen EW 5661	Viewing screen EW 5661	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
7884486	Timeclock EZT 7664 400V 50Hz	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
9966020	Timeclock EZT 7661 400V/50Hz	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
9966011	Timeclock EZT 7651 200-240V	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
7883965	Timeclock EZT 7660 400V/50Hz	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
7883945	Timeclock EZT 7650 200-240V	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396770	Viewing screen EW 5661	Viewing screen EW 5661	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396790	Viewing screen EWX 5662-B	Viewing screen EWX 5662-B	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396790	Viewing screen EWX 5662-B	Viewing screen EWX 5662-B	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396790	Viewing screen EWX 5662-B	Viewing screen EWX 5662-B	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396790	Viewing screen EWX 5662-B	Viewing screen EWX 5662-B	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
9461794	Viewing screen I/O EW 5662-B	Viewing screen I/O EW 5662-B	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
9461794	Viewing screen I/O EW 5662-B	Viewing screen I/O EW 5662-B	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
9259392	Viewing screen EWX 5664-A	Viewing screen EWX 5664-A	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
9259392	Viewing screen EWX 5664-A	Viewing screen EWX 5664-A	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396660	Viewing screen EWX 5662-A	Viewing screen EWX 5662-A	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396660	Viewing screen EWX 5662-A	Viewing screen EWX 5662-A	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396660	Viewing screen EWX 5662-A	Viewing screen EWX 5662-A	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10490970	Timeclock EZT 7651-CN 200-240V	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10396660	Viewing screen EWX 5662-A	Viewing screen EWX 5662-A	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
11172600	Power-/Control unit ELPW 5672-R 200-240V	Viewing screen EW 5661	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10565491	Timeclock EZT 7654 220-240V	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10549030	Timeclock EZT 7661 400V/50Hz	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
10549010	Timeclock EZT 7651 200-240V	Casing EZT 7650/7654	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
9259374	Viewing screen EW 5662-A	Viewing screen EW 5662-A	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
9259374	Viewing screen EW 5662-A	Viewing screen EW 5662-A	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulfonate	29420-49-3
11567152	Built-in frame DAD4840	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
12949450	Built-in frame DADX3X0	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
12948370	Built-in frame DADX9X0	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083710	DAD6884 XD1/D MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083770	DAD6984 XD1/D MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083740	DAD6884 XS1/CH MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083800	DAD6984 XS1/CH MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083720	DAD6884 XG1/GB MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083780	DAD6984 XG1/GB MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
11805362	Built-in frame DAD4940	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083810	DAD6984 C XC2/CN MASW 220/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083750	DAD6884 C XC2/CN MASW 220/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083790	DAD6984 XA1/AUS MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083730	DAD6884 XA1/AUS MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083820	DAD6984 XR1/OER MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
12679430	Built-in frame DADX8X0	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
13083760	DAD6884 XR1/OER MASW 230/50 TLK	Seal Built-in frame	Bis(alpha,alpha-dimethylbenzyl) peroxide	80-43-3
12341870	DAH1850 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12342470	DAH1650 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
9340560	Casing Front facing	Casing Front facing	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12533990	DAH2960EXTA D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12533960	DAH2960 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12533940	DAH2860 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12341910	DAH2660 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12342350	DAH2960 XG1/GB OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12533920	DAH2660 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12341850	DAH1650 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12533900	DAH1950 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12503241	LED lamp Cornered HV DAH BLACK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12533880	DAH1850 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12555210	DAH1650 TR OBSW 230/50 TL	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12591560	DAH1650 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12555220	DAH1950 TR OBSW 230/50 TL	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12591570	DAH1950 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12533860	DAH1650 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12591580	DAH2960 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12503241	LED lamp Cornered HV DAH BLACK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12555650	DAH1852 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12342570	DAH2960 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12342510	DAH1950 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12343440	DAH1950 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12342000	DAH2960 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12341980	DAH2860 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12343460	DAH2660 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12343480	DAH2860 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12343500	DAH2960 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12679140	DAH1950 KZ OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12343420	DAH1850 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12679130	DAH1650 KZ OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12786270	DAH2960 XO1/ROK OBSW 220/60 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12623210	DAH2960 ROK OBSW 220/60 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12341890	DAH1950 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12343400	DAH1650 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12545640	DAH2960 GB OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12534190	DAH1950 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12534180	DAH1650 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12534200	DAH2960 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
12342160	DAH2960EXTA XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	4,4'-Dihydroxydiphenyldimethylmethane	80-05-7
11471350	KM2012 USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
11592520	KMDA7476 FL ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
8287380	Burner tap 0,42	Burner tap 0,42	Lead	7439-92-1
8287280	Burner tap 0,42	Burner tap 0,42	Lead	7439-92-1
11276540	KM7594 FR BR 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
8122760	Jet 0,80MM	Jet 0,80MM	Lead	7439-92-1
11276510	KM7575 FR BR 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11408350	CS1011 C JZT-10T	Sealing ring 7,65x1,78	Lead	7439-92-1
8122760	Jet 0,80MM	Jet 0,80MM	Lead	7439-92-1
7738070	ETD Double Olympus	Sensor	Lead	7439-92-1
8287290	Burner tap 0,39	Burner tap 0,39	Lead	7439-92-1
8597130	Oven cavity DGM 6301-6805 vorm.	Drive top	Lead	7439-92-1
11408360	CS1014 C JZT-10T	Sealing ring 7,65x1,78	Lead	7439-92-1
11604640	H7260BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11604650	H7260BP F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11507760	KM7629 FX NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11293050	KM3465LP BR EDST	Sealing ring 7,65x1,78	Lead	7439-92-1
11604630	H7260BP F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11503460	KMDA7634 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11484100	H2269-1B EXP EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11593570	H7264B CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11593570	H7264B CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11484100	H2269-1B EXP EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11491520	KMDA7634 FR NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11552920	KM7404 FX NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11593570	H7264B CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11580950	H7262B D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11370710	KM3014 SGP EDST 230/50	Holder	Lead	7439-92-1
11581190	H7262BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11370710	KM3014 SGP EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11491510	KMDA7634 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11581200	H7262B D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11581250	H7262B D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11581230	H7262BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11426960	KMDA7633 FR UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11598870	H7262B B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11598880	H7262B B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11614640	H7162BP IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11614720	H7262BP SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11598840	H7162B B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11614740	H7262BP IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11599010	H7262BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11598910	H7262BP B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11599000	H7262BP B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11598860	H7162BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11587990	H7262BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11587970	H7262BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11587980	H7262BP NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11614630	H7162B IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11614670	H7262B SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11614660	H7262B SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11614690	H7262B IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11580980	H2265-1B J EDST/CLST 200/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
11582550	H7162BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11582560	H7162BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11582440	H7262B RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11582470	H7262BP RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11582450	H7262B RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11582460	H7262BP RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11582480	H7262BP RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11582430	H7262B RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11592530	KMDA7476 FR ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11686150	H7162-1BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11686920	H2269-1E D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11686920	H2269-1E D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11687420	H2455EP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11687420	H2455EP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11687460	H2455BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11687460	H2455BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11687450	H2455B ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11276510	KM7575 FR BR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11687450	H2455B ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11650050	H2266-1BP NER EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11581260	H7262BP D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11650050	H2266-1BP NER EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11276370	KM7464 FR BR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11612940	H7262BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11599870	H7262BP I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11612930	H7162BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11588090	H7262BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11293040	KM3475LP BR EDST	Sealing ring 7,65x1,78	Lead	7439-92-1
11588080	H7162BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
1159820	H7262B I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11598890	H7262B B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11595950	H7262BP UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11595940	H7262B UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11614710	H7262BP SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10831650	H6860BPX C CN OBSW 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10773320	H6281BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10773320	H6281BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10773320	H6281BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
8534850	Conv.kit nozzle Natural gas H 20mbar/CS	Jet 0,54MM	Lead	7439-92-1
8534850	Conv.kit nozzle Natural gas H 20mbar/CS	Jet 0,42MM	Lead	7439-92-1
10009380	H2661-1B ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10009380	H2661-1B ANL EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
9863620	H6280BP USA OBSW 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9863620	H6280BP USA OBSW 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9863620	H6280BP USA OBSW 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
9863640	H6680BP USA OBSW 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9863640	H6680BP USA OBSW 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9863640	H6680BP USA OBSW 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
9863750	H6680BP USA BRWS 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9863750	H6680BP USA BRWS 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9863750	H6680BP USA BRWS 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
9863740	H6280BP USA BRWS 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9863740	H6280BP USA BRWS 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9863740	H6280BP USA BRWS 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
9646260	H6860BP J EDST/CLST 200/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9646260	H6860BP J EDST/CLST 200/60	Heater element Bottom heat	Lead	7439-92-1
9646090	H6860BP J EDST/CLST 200/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9646090	H6860BP J EDST/CLST 200/50	Heater element Bottom heat	Lead	7439-92-1
9646230	H6461BP J BRWS 200/60	Heater element Bottom heat	Lead	7439-92-1
9646110	H6461BP J BRWS 200/50	Heater element Bottom heat	Lead	7439-92-1
9646240	H6461BP J EDST/CLST 200/60	Heater element Bottom heat	Lead	7439-92-1
9646100	H6461BP J EDST/CLST 200/50	Heater element Bottom heat	Lead	7439-92-1
9646290	H6260B J EDST/CLST 200/60	Heater element Bottom heat	Lead	7439-92-1
9646190	H6260B J EDST/CLST 200/50	Heater element Bottom heat	Lead	7439-92-1
9782480	H6860BP TW EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9622860	H6860BP C CN BRWS 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9622910	H6860BP C CN EDST/CLST 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9632340	H6860BP ROK EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9682530	H6860BP SA EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9769460	H6680BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9769460	H6680BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9769460	H6680BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
9769450	H6580BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9769450	H6580BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9769450	H6580BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10831590	H6860BPX C CN GRGR 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10752150	H6880-2BP USA OBSW 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10752070	H6880-2BP USA BRWS 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10752070	H6880-2BP USA BRWS 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10752070	H6880-2BP USA BRWS 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10752160	H6880-2BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10752160	H6880-2BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10752160	H6880-2BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10751970	H6780-2BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10751970	H6780-2BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10751970	H6780-2BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10725160	Drain valve DGD7000 kpl.,vormont	Rundmessing D 15,0 MS 58-hartgezogen	Lead	7439-92-1
10869120	DA4298W PAC EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10869020	DA4228W PAC EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10863280	DA4298W RU EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10842690	DA4298W CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10842680	DA4288W CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10869060	DA6698W PAC OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10869050	DA6698W PAC BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10869040	DA6698W PAC EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10863340	DA6698W RU OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10863330	DA6698W RU BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10863350	DA6698W RU EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10863310	DA5798W RU EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10851450	DA5798W GB EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10842700	DA5798W CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10750330	DA6698W D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10750300	DA6698W D BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10749650	DA6698W D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10749620	DA5798W D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10749600	DA4288W D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10749560	DA4228W D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
8592510	Drain valve DGD46*5 kpl.,vormont	Rundmessing D 15,0 MS 58-hartgezogen	Lead	7439-92-1
10276890	PG8583CD EXE AE-WW-ADP-CM 3 AC 220-230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10138790	H2561B IB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10138790	H2561B IB EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
10109610	H2661-1B D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10109610	H2661-1B D BRWS 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10109600	H2661-1B D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10109600	H2661-1B D OBSW 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
10109590	H2661-1B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10109590	H2661-1B D EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
11136700	H2860BP RU BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11136680	H2860B RU BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11136680	H2860B RU BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11124010	H2860BP RU GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11124010	H2860BP RU GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11124000	H2860BP RU OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11124000	H2860BP RU OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11124030	H2860BP RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11124030	H2860BP RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11123960	H2760BP RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11123960	H2760BP RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11123980	H2860B RU GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11123980	H2860B RU GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11123970	H2860B RU OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11123970	H2860B RU OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11123990	H2860B RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11123990	H2860B RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11123950	H2760B RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11123950	H2760B RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11123940	H2265-1BP RU EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11123940	H2265-1BP RU EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11123930	H2265-1B RU EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11123930	H2265-1B RU EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
10170340	PG8056 U LV AE m.K.	Circulation pump S35 PP (00-53)	Lead	7439-92-1
10179650	PG8056 U CN AE m.K.	Circulation pump S35 PP (00-53)	Lead	7439-92-1
7913180	PG8056 U D AE m.K.	Circulation pump S35 PP (00-53)	Lead	7439-92-1
7130410	Conv.kit nozzle Liquid gas 30mbar	Jet 0,32MM	Lead	7439-92-1
7130410	Conv.kit nozzle Liquid gas 30mbar	Jet 0,27MM	Lead	7439-92-1
8535100	Conv.kit nozzle Natural gas H 20mbar/KM	Jet 0,39MM	Lead	7439-92-1
8535100	Conv.kit nozzle Natural gas H 20mbar/KM	Jet 0,54MM	Lead	7439-92-1
8535100	Conv.kit nozzle Natural gas H 20mbar/KM	Jet 0,42MM	Lead	7439-92-1
8535040	Conv.kit nozzle Natural gas H 20mbar/KM	Jet 0,39MM	Lead	7439-92-1
8535040	Conv.kit nozzle Natural gas H 20mbar/KM	Jet 0,54MM	Lead	7439-92-1
8535040	Conv.kit nozzle Natural gas H 20mbar/KM	Jet 0,42MM	Lead	7439-92-1
7130130	Conv.kit nozzle Liquid gas 30mbar	Jet 0,54MM	Lead	7439-92-1
7130130	Conv.kit nozzle Liquid gas 30mbar	Jet 0,32MM	Lead	7439-92-1
7130130	Conv.kit nozzle Liquid gas 30mbar	Jet 0,27MM	Lead	7439-92-1
7138030	Conv.kit nozzle Liquid gas 30mbar	Jet 0,32MM	Lead	7439-92-1
7138030	Conv.kit nozzle Liquid gas 30mbar	Jet 0,27MM	Lead	7439-92-1
11172600	Power-/Control unit ELPW 5672-R 200-240V	Power-/Control unit ELPW 5672-R 200-240V	Lead	7439-92-1
11172600	Power-/Control unit ELPW 5672-R 200-240V	Power-/Control unit ELPW 5672-R 200-240V	Lead	7439-92-1
11136700	H2860BP RU BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
9769440	H6280BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9769440	H6280BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9769440	H6280BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
9769420	H6180BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9769420	H6180BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9769420	H6180BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11569760	H7660BP AN3 GRGR 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11569760	H7660BP AN3 GRGR 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11569740	H7660BP AN3 OBSW 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11569740	H7660BP AN3 OBSW 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11569720	H7263BP AN3 GRGR 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11569720	H7263BP AN3 GRGR 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11569710	H7263BP AN3 BRWS 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11569710	H7263BP AN3 BRWS 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
8286740	Burner tap 0,88	Burner tap 0,88	Lead	7439-92-1
8286750	Burner tap 0,74	Burner tap 0,74	Lead	7439-92-1
8126201	Burner tap 0,88/0,42	Burner tap 0,88/0,42	Lead	7439-92-1
11164270	H2860BP UA GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11164270	H2860BP UA GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11164250	H2860BP UA OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11164250	H2860BP UA OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11167160	H2860BP UA BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11167160	H2860BP UA BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11164280	H2860BP UA EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11164280	H2860BP UA EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11164200	H2265-1BP UA EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11164200	H2265-1BP UA EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11164230	H2860B UA GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11164230	H2860B UA GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11164210	H2860B UA OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11164210	H2860B UA OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11167150	H2860B UA BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11167150	H2860B UA BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11164240	H2860B UA EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11164240	H2860B UA EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11164180	H2265-1B UA EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11164180	H2265-1B UA EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11164310	H7260BP UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11164290	H7260B UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124420	H7260BP RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124410	H7260B RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
7329870	CS1014 CN EDST 230/50	Burner tap 0,52	Lead	7439-92-1
7329870	CS1014 CN EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7488140	KM3464 CN EDST 220/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10650520	KM7575 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10650520	KM7575 FR R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
7359700	B995 D CN 220-240/50-60 3,2-3,8kW	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
7135490	CS1011 CN EDST 220/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7135510	CS1112 CN EDST 220/50	Heater plate 1,2KW 230V	Lead	7439-92-1
7263620	Trough 2,775KW 230V	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
7256530	Trough 2,10KW 230V	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
7256390	Trough 2,775KW 230V	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
10750370	DA6798W D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10842720	DA6798W CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10866610	DA6698W C CN EDST 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10866600	DA6698W C CN OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10866590	DA6698W C CN BRWS 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10866570	DA4248VD C CN EDST 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10866550	DA4208D C CN EDST 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10866560	DA4228W C CN EDST 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10866580	DA4298W C CN EDST 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11073340	CS7612 FL C CN 220/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11073340	CS7612 FL C CN 220/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11166750	JZT-10T-KM3464 CN	Sealing ring 7,65x1,78	Lead	7439-92-1
7227370	Trough 3,00KW 230V	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
11118930	H2860-55B CH EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11118950	H2860-55B CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
11118950	H2860-55B CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11118950	H2860-55B CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
11118960	H2860-55B CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
11118960	H2860-55B CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11118960	H2860-55B CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
11118970	H2860-55BP CH EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
11118970	H2860-55BP CH EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11118970	H2860-55BP CH EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11118980	H2860-55BP CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
11118980	H2860-55BP CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11118980	H2860-55BP CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
11101900	DGM7440 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101910	DGM7440 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101920	DGM7440 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101930	DGM7640 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101940	DGM7840 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101950	DGM7840 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101960	DGM7840 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11119000	H2860-55BP CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
11119000	H2860-55BP CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11119000	H2860-55BP CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
11127670	H2265-1B AUS EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11127690	H2267-1B AUS EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127690	H2267-1B AUS EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11127680	H2265-1BP AUS EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127680	H2265-1BP AUS EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11127760	H2860B AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127760	H2860B AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127710	H2760B AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127710	H2760B AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127730	H2850B AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127730	H2850B AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127700	H2267-1BP AUS EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127700	H2267-1BP AUS EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11127810	H2860BP AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127810	H2860BP AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127770	H2860BP AUS BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127770	H2860BP AUS BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127780	H2860BP AUS OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127780	H2860BP AUS OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127790	H2860BP AUS GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127790	H2860BP AUS GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127720	H2760BP AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127720	H2760BP AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127670	H2265-1B AUS EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11119990	H2267-1B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11119990	H2267-1B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11119620	H2266-1B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11119620	H2266-1B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11119630	H2265-1BP I EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11119630	H2265-1BP I EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11120000	H2267-1BP I EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11120000	H2267-1BP I EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11120020	H2268-1BP I EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11120020	H2268-1BP I EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11120060	H2840B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11120030	H2760B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11120030	H2760B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11120070	H2860B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11120070	H2860B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11120050	H2760BP I EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11120050	H2760BP I EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11120080	H2860BP I EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11120080	H2860BP I EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127650	H2265-1E AUS EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127650	H2265-1E AUS EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11127660	H2265-1I AUS EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11127660	H2265-1I AUS EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11118930	H2860-55B CH EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11110810	H2265-1E CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110810	H2265-1E CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110790	H2265-1E CH HVBR 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11110790	H2265-1E CH HVBR 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110790	H2265-1E CH HVBR 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110860	H2265-1EP CH EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11110860	H2265-1EP CH EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110860	H2265-1EP CH EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110830	H2265-1EP CH BRWS 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11110830	H2265-1EP CH BRWS 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110830	H2265-1EP CH BRWS 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110850	H2265-1EP CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11110850	H2265-1EP CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110850	H2265-1EP CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110880	H2265-1B CH EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11110880	H2265-1B CH EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110880	H2265-1B CH EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110890	H2265-1BP CH EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11110890	H2265-1BP CH EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110890	H2265-1BP CH EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110920	H2860B CH EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
11110920	H2860B CH EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11110920	H2860B CH EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11110810	H2265-1E CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11135530	DGM7640 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135550	DGM7640 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135560	DGM7640 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133570	DGM7440 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133710	DGM7640 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133700	DGM7840 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11111040	H7264B CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111040	H7264B CH EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11111040	H7264B CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111030	H7244BP CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111030	H7244BP CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111000	H7244BP CH BRWS 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111000	H7244BP CH BRWS 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111010	H7244BP CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111010	H7244BP CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111020	H7244BP CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111020	H7244BP CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11110820	H2265-1E CH EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11110820	H2265-1E CH EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110820	H2265-1E CH EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110800	H2265-1E CH BRWS 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11110800	H2265-1E CH BRWS 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11110800	H2265-1E CH BRWS 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11117550	H2265-1-55E CH HVBR 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11117550	H2265-1-55E CH HVBR 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11117550	H2265-1-55E CH HVBR 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11111120	H7640BP CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111120	H7640BP CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111110	H7640BP CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111110	H7640BP CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11118880	H2265-1-55EP CH EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11118880	H2265-1-55EP CH EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11118880	H2265-1-55EP CH EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11117590	H2265-1-55EP CH BRWS 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11117590	H2265-1-55EP CH BRWS 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11117590	H2265-1-55EP CH BRWS 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11118860	H2265-1-55EP CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11118860	H2265-1-55EP CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11118860	H2265-1-55EP CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11118900	H2265-1-55B CH EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11118900	H2265-1-55B CH EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11118900	H2265-1-55B CH EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11118920	H2265-1-55BP CH EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11118920	H2265-1-55BP CH EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11118920	H2265-1-55BP CH EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11118930	H2860-55B CH EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11117570	H2265-1-55E CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11110900	H2860B CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
11110900	H2860B CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11110900	H2860B CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
11110910	H2860B CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
11110910	H2860B CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11110910	H2860B CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
11110950	H2860BP CH EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
11110950	H2860BP CH EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11110950	H2860BP CH EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11110930	H2860BP CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
11110930	H2860BP CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11110930	H2860BP CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
11110940	H2860BP CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
11110940	H2860BP CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11110940	H2860BP CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
11117580	H2265-1-55E CH EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11117580	H2265-1-55E CH EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11117580	H2265-1-55E CH EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11117560	H2265-1-55E CH BRWS 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11117560	H2265-1-55E CH BRWS 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11117560	H2265-1-55E CH BRWS 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11117570	H2265-1-55E CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11117570	H2265-1-55E CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11127740	H2850BP AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10897060	KM7164 FR R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10974800	KMDA7774-1 FL N 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974790	KMDA7774-1 FR N 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974810	KMDA7774-1 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974840	KMDA7774-1 FR ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974850	KMDA7774-1 FR RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974860	KMDA7774-1 FL C CN 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11022890	KM7464 FR D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11022920	KM7464 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11022950	KM7564 FR D 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11022960	KM7564 FL D 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11022970	KM7575 FR D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11022970	KM7575 FR D 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11022980	KM7575 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11022980	KM7575 FL D 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144180	KM7164 FR NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144230	KM7464 FR NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144240	KM7464 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144250	KM7465 FR NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144260	KM7465 FL NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144290	KM7564 FR NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144300	KM7564 FL NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144310	KM7575 FR NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10897070	KM7174 FR R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10517770	KMDA7774 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10517760	KMDA7774 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10604220	KMDA7774 FR N 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10604240	KMDA7774 FL N 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10603870	KMDA7774 FR RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10666420	KMDA7774 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10650420	KM7464 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10650410	KM7464 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10650430	KM7465 FL R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10650440	KM7465 FR R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10650510	KM7575 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10650510	KM7575 FL R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10650530	KM7594 FL R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10650540	KM7594 FR R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10650550	KM7684 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10650550	KM7684 FL R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10776530	KM6329 RU FL.BDG. 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10800260	KMDA7774 FL C CN 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10787580	KM6329 AUS FL.BDG. 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10897100	KM7004 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10897110	KM7005 FR R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10974770	KMDA7774-1 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974780	KMDA7774-1 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11221240	KM7465 FR ROK 220/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
11221290	KM7684 FL ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
11221290	KM7684 FL ROK 220/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
11249320	KM7464 FR J 200/50-60	Induction coil G5 Octa OL L100	Lead	7439-92-1
11249340	KM7564 FL J 200/50-60	Induction coil G5 Octa OL L250	Lead	7439-92-1
11249360	KM7684 FL J 200/50-60	Induction coil G5 Octa OL L100	Lead	7439-92-1
11249360	KM7684 FL J 200/50-60	Induction coil G5 Octa OL L250	Lead	7439-92-1
11296660	KMDA7633 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11296650	KMDA7633 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11345350	KMDA7633 FR D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11345390	KMDA7633 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11358880	KMDA7634 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11358870	KMDA7634 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11325900	KMDA7633 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11325610	KMDA7633 FR N 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11325620	KMDA7633 FL N 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11390360	KMDA7634 FR D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11390370	KMDA7634 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11325850	KMDA7633 FR RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11384260	KMDA7633 FR ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
11325600	KMDA7633 FL C CN 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11427460	KMDA7634 FR R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11427470	KMDA7634 FL R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11221210	KM7464 FR ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144310	KM7575 FR NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144320	KM7575 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144320	KM7575 FL NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144330	KM7684 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144330	KM7684 FL NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11127290	KM7004 FR D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11127300	KM7005 FR D 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11206040	KM7174 FR RU 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11206080	KM7464 FR RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11206090	KM7465 FL RU 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11206100	KM7564 FL RU 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11206120	KM7575 FR RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11206120	KM7575 FR RU 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11206130	KM7684 FL RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11206130	KM7684 FL RU 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11230310	KM7684 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11230310	KM7684 FL AUS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11230350	KM7464 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11230370	KM7564 FL AUS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11230390	KM7575 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11230390	KM7575 FL AUS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11230400	KM7594 FL AUS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11221280	KM7564 FR ROK 220/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
10414780	KM6329 R01 FL.BDG. 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11288120	H2567BP NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11288120	H2567BP NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11306060	H2765BP NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11306060	H2765BP NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11306270	H7165BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11328620	DA6999W D BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10975170	KM2312 C CN EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10975170	KM2312 C CN EDST 230/50	Holder	Lead	7439-92-1
10975200	KM2356-1 C CN EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10975210	KM3014 C CN EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10975210	KM3014 C CN EDST 230/50	Holder	Lead	7439-92-1
10975230	KM3054-1 C CN EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
11344690	H2567B B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11344690	H2567B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11344700	H2567BP B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11344700	H2567BP B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11146110	H7263BP AN3 EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11146110	H7263BP AN3 EDST/CLST 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11146120	H7660BP AN3 EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11146120	H7660BP AN3 EDST/CLST 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11258920	KM7564 FL C CN 220/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11258930	KM7684 FL C CN 220/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11258930	KM7684 FL C CN 220/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11281720	H2567E D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11127740	H2850BP AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11128380	H7260BP AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128370	H7164BP AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128420	H7264BP AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128390	H7264BP AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128400	H7264BP AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128410	H7264BP AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11258040	H2860B EU1 BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11258040	H2860B EU1 BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129060	H7264B GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129040	H2860B HK EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129040	H2860B HK EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11229560	H2266-1BP F EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11229560	H2266-1BP F EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11229570	H2268-1BP F EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11229570	H2268-1BP F EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11073290	CS7101 FLC CN 220/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11073310	CS7102 FLC CN 220/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11281690	H2567B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11281690	H2567B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11281700	H2567BP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11281700	H2567BP D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11281720	H2567E D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11366550	H2265-11 CDN EDST/CLST 240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11366510	H2265-1I CDN EDST/CLST 208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
11369870	DA6999W RU BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11435240	H7260B D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11435250	H7260B D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11435260	H7260B D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11435270	H7260BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11435280	H7260BP D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11435290	H7260BP D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11384600	H2765BP F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11384600	H2765BP F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11410470	H7261BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11455590	H2765BP EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11455590	H2765BP EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11160130	DGM7440 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160140	DGM7440 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160150	DGM7440 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160160	DGM7640 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160170	DGM7640 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160180	DGM7640 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160200	DGM7840 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160210	DGM7840 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160220	DGM7840 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11366430	H2265-1E CDN EDST/CLST 208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
11323480	H2860BP EU1 BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11323480	H2860BP EU1 BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11292910	H7264B TW EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11146320	H7264B ROK EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11136550	H2265-1B J EDST/CLST 200/50 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
11136560	H7264B J EDST/CLST 200/50	Heater element Bottom heat	Lead	7439-92-1
11136560	H7264B J EDST/CLST 200/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11136570	H7264B J EDST/CLST 200/60	Heater element Bottom heat	Lead	7439-92-1
11136570	H7264B J EDST/CLST 200/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11327980	H2860B AUS BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11327980	H2860B AUS BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11327990	H2860B AUS OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11327990	H2860B AUS OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11328000	H2860B AUS GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11328000	H2860B AUS GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11281870	H2265-1B BR EDST/CLST 220/60	Heater element Top heat 230V	Lead	7439-92-1
11226260	HR1924-3 G DF AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11226260	HR1924-3 G DF AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11226260	HR1924-3 G DF AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11419390	HM16-80 D SOM AC 220-240V 50-60Hz	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
11366610	H2265-1B CDN EDST/CLST 240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11366580	H2265-1B CDN EDST/CLST 208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
11366410	H2265-1E CDN EDST/CLST 240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
10752150	H6880-2BP USA OBSW 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11512310	KM7689 FL RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11520720	KM7699 FR IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11507820	KM7899 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11564890	KMDA7634 FR B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11564900	KMDA7634 FL B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11491400	KMDA7634 FR I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11491390	KMDA7634 FL I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11491350	KMDA7634 FL NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11491340	KMDA7634 FR NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11402820	CS7101-1 FL E 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11576240	H6560B BR EDST/CLST 127/220/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11560190	DG2840 TW EDST/CLST 220/50-60	SMD- Diode STTH1R04A	Lead	7439-92-1
10921028	Power-/Control unit ELP 7752 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10921048	Power-/Control unit ELP 7753 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10921068	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10921116	Power-/Control unit ELP 7755 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11730524	Power electron.unit EL 7712	SMD- Diode STTH1R04A	Lead	7439-92-1
11715060	H2269-1I D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11715060	H2269-1I D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11754200	KMDA7633 FR BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11754210	KMDA7633 FL BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11396930	CS7101-1 FL R01 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11408180	CS7102-1 FL IB 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11396960	CS7102-1 FL R01 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11476590	DA7378D IB BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11421440	DA7378D NL BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11425590	KMDA7633 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11416420	DA7378D GR BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11410550	DA7378D TR BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11273730	HR1936-2 LP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11273730	HR1936-2 LP BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11273730	HR1936-2 LP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11410100	DA7378D B BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11410070	DA7378D F BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11409580	DA7378D CH BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11409230	DA7378D GB BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11408960	DA7378D NER BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11408820	DA7378D CZ BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11408240	DA7378D UA BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11283040	HR1956-2 LP BR EDST/CLST 127/220/60	Heater element Catalyst 208-240V	Lead	7439-92-1
11273700	HR1934-2 LP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11273700	HR1934-2 LP BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11273700	HR1934-2 LP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11712770	KMDA7476 FL R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11804810	H7660BP USA EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11804780	H7263BP USA GRGR 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11804780	H7263BP USA GRGR 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11804750	H7263BP USA BRWS 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11804750	H7263BP USA BRWS 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11804760	H7263BP USA EDST/CLST 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11804760	H7263BP USA EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11901201	Operating module TT-HA-A-double	Operating module Lifting mechanism 1	Lead	7439-92-1
11687480	H2455EP AN1 EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11687480	H2455EP AN1 EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11687480	H2455EP AN1 EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
11687470	H2455BP AN1 EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11687470	H2455BP AN1 EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11687470	H2455BP AN1 EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
11816730	PW6321 RH ZER 3N AC 380-415V 50/60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11814100	PW6321 EL ZER 3 220-240/50-60 MF	Control electr.unit EW 235-A	Lead	7439-92-1
11814090	PW6321 EL SOM WEK MF 3AC 220-240/50-60	Control electr.unit EW 235-A	Lead	7439-92-1
11814000	PW6321 EL SOM WEK MF 3AC 440V 60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11814110	PW6321 EL SOM WEK MF 3AC 400V 50-60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11813970	PW6321 EL SOM WEK MF 3NAC 380-415/50-60	Control electr.unit EW 235-A	Lead	7439-92-1
11813790	PW6241 EL SOM WEK MF 3AC 220-240/50-60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11813730	PW6241 EL SOM WEK MF 3AC 440V 60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11813830	PW6241 EL SOM WEK MF 3AC 400V 50-60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11813670	PW6241 EL SOM WEK MF 3NAC 380-415/50-60	Control electr.unit EW 235-A	Lead	7439-92-1
11761780	H2860-2B D EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11761780	H2860-2B D EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11761770	H2760-2B D EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11761770	H2760-2B D EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11761760	H2267-2E D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11761760	H2267-2E D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11763800	CS1012-2 G USA EDST 120/60	Burner tap 0,52	Lead	7439-92-1
11763800	CS1012-2 G USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
11763810	CS1012-2 LP USA EDST 120/60	Burner tap 0,52	Lead	7439-92-1
11763810	CS1012-2 LP USA EDST 120/60	Jet 0,32MM	Lead	7439-92-1
11763810	CS1012-2 LP USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
11763790	CS1011-1 G USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
11798830	KMDA7476 FL ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
11786360	KMDA7476 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11874401	Operating module TT-HA-A-single	Operating module Lifting mechanism 1	Lead	7439-92-1
11791030	H2755B EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11791030	H2755B EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11782440	KMDA7476 FL F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11789940	KMDA7476 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11388410	KMDA7633 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11146170	DG2840 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146160	DG2840 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146180	DG2840 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133940	DO7860 NER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11133940	DO7860 NER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11133940	DO7860 NER GRGR 230/50	Supply cable DO	Lead	7439-92-1
11085780	HR1956-1 G B EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
11085700	HR1936-1 G B EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11085700	HR1936-1 G B EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086230	HR1936-1 G GB EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086230	HR1936-1 G GB EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086070	HR1936-1 G DK EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086070	HR1936-1 G DK EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086050	HR1924-1 G DK EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086050	HR1924-1 G DK EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086100	HR1956-1 G E EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
10939190	KM2356-1 E EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10939190	KM2356-1 E EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10939190	KM2356-1 E EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10939190	KM2356-1 E EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10939190	KM2356-1 E EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940150	KM2356-1 R01 EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10940150	KM2356-1 R01 EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10940150	KM2356-1 R01 EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10940150	KM2356-1 R01 EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10940150	KM2356-1 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10939070	KM3054-1 P EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
10939900	KM3054-1 R01 EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
11086150	HR1956-1 G F EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
11086140	HR1936-1 G F EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086140	HR1936-1 G F EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086130	HR1924-1 G F EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086130	HR1924-1 G F EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11086120	HR1622-1 F EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086120	HR1622-1 F EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086090	HR1936-1 G E EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086090	HR1936-1 G E EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086110	HR1622-1 FIN EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086110	HR1622-1 FIN EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086260	HR1924-1 G I EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086260	HR1924-1 G I EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086250	HR1622-1 I EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086250	HR1622-1 I EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11146200	DG7240 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11388400	KMDA7633 FR DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11393750	KMDA7633 FL I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11393740	KMDA7633 FR I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11389260	KMDA7633 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11389170	KMDA7633 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11325860	KMDA7633 FR IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11389070	KMDA7633 FL NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11389060	KMDA7633 FR NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11388990	KMDA7633 FL B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11388970	KMDA7633 FR B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11389040	KMDA7633 FR F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11389030	KMDA7633 FL F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11281860	H6560BP BR EDST/CLST 127/220/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11985104	Power-/Control unit ELP 7755 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11361830	DA7378D D BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11331770	KM7684 FL IB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11331770	KM7684 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11258710	KMDA7774-1 FL I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11258700	KMDA7774-1 FR I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11028420	KM6520 FR J 200/50-60	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11218270	KM7564 FL IB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11218170	KM7594 FL IB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11218160	KM7465 FL IB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11218150	KM7464 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11218120	KM7404 FX IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10650380	KM7404 FX R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11215650	KM7174 FR IB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11145800	DGM7840 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11145850	DGM7840 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11145840	DGM7840 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11145830	DGM7440 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11145810	DGM7440 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11145820	DGM7440 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11190270	DA6698W ROK EDST 220/60 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11099690	DG2840 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099670	DG2840 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099640	DG2840 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134200	DG2840 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11137810	DG2840 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11115300	DG2840 TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094400	DG2840 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146230	DG7440 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146210	DG7440 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11804810	H7660BP USA EDST/CLST 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12105840	H2765B GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12125340	H7165BP GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12106290	KMDA7476 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12044330	DA9298W F BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12088700	PW6321 EL NAM SST MF 3AC 208/240V 60Hz D	Control electr.unit EW 235-A	Lead	7439-92-1
12088670	PW6241 EL NAM SST MF 3AC 208/240V 60Hz D	Control electr.unit EW 235-A	Lead	7439-92-1
12060640	KM6523 FL IB 230/50	Heater plate 2,6-1,5KW 230V	Lead	7439-92-1
12060640	KM6523 FL IB 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
12060640	KM6523 FL IB 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060640	KM6523 FL IB 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11327600	KM6523 FL R01 230/50	Heater plate 2,6-1,5KW 230V	Lead	7439-92-1
11327600	KM6523 FL R01 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
11327600	KM6523 FL R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11327600	KM6523 FL R01 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12060630	KM6521 FR IB 230/50	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
12060630	KM6521 FR IB 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
12060630	KM6521 FR IB 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060630	KM6521 FR IB 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11327590	KM6521 FR R01 230/50	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
11327590	KM6521 FR R01 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
11327590	KM6521 FR R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11327590	KM6521 FR R01 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12050610	DA6698W GB EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12050600	DA6698W GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12011690	DA9298W TR BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12027540	DA9298W NER BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12011700	DA9298W NL BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12011680	DA9298W IB BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
11816560	HR1936-3 LP DF GD AB2EDST/CLST127/240/60	Heater element Hot air 208V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11816560	HR1936-3 LP DF GD AB2EDST/CLST127/240/60	Heater element Top heat 208V	Lead	7439-92-1
11816560	HR1936-3 LP DF GD AB2EDST/CLST127/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
12028540	KM7575 FL IB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12028540	KM7575 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11955090	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11737812	Power-/Control unit EPL 8810-U	SMD- Diode STTH1R04A	Lead	7439-92-1
11955910	H2760-2BP IB EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11955910	H2760-2BP IB EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11955890	H2760-2B IB EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11955890	H2760-2B IB EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11955930	H2860-2BP SER OBSW 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11955930	H2860-2BP SER OBSW 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11955920	H2860-2B SER OBSW 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11955920	H2860-2B SER OBSW 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
12105840	H2765B GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12100690	DGC7845 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100680	DGC7845 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100670	DGC7845 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100660	DGC7845 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100650	DGC7840 HCX Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100640	DGC7840 HCX Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100630	DGC7840 HCX Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100620	DGC7840 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100610	DGC7840 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100600	DGC7840 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100590	DGC7840 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100400	DGC7640 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100370	DGC7640 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100360	DGC7465 HCX Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100340	DGC7465 HCX Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100330	DGC7465 HCX Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100320	DGC7465 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100240	DGC7465 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100230	DGC7465 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100220	DGC7465 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100210	DGC7460 HCX Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100200	DGC7460 HCX Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100140	DGC7460 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100130	DGC7445 HCX Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100120	DGC7445 HCX Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100100	DGC7445 HCX Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100090	DGC7445 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100000	DGC7445 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099980	DGC7445 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099960	DGC7445 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099950	DGC7440 HCX Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099940	DGC7440 HCX Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099920	DGC7440 HCX Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099690	DGC7460 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099700	DGC7460 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12173500	H2860B GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12173500	H2860B GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12102230	H2765BP D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12102230	H2765BP D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12102220	H2765B D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12102220	H2765B D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12105850	H2765BP GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12105850	H2765BP GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11955950	H2860-2BP IB EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11933780	H2860-2BP D EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11933580	H2760-2BP D EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11933580	H2760-2BP D EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11933650	H2860-2B D GRGR 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11933650	H2860-2B D GRGR 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11933640	H2860-2B D OBSW 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11933640	H2860-2B D OBSW 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11791560	HR1924-3 LP DF USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11791560	HR1924-3 LP DF USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791560	HR1924-3 LP DF USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11451091	Power-/Control unit ELP 7442-A 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11681363	Power-/Control unit EPL 8760	SMD- Diode STTH1R04A	Lead	7439-92-1
11876310	DGC7885 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876470	DGC7680 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876450	DGC7685 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876440	DGC7880 USA BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876420	DGC7880 USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876370	DGC7880 USA GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876350	DGC7880 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876020	DGC7580 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11875850	DGC7585 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11875830	DGC7780 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11875810	DGC7785 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11877020	DGC7865 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11877010	DGC7860 USA BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11877000	DGC7860 USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876990	DGC7860 USA GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876980	DGC7860 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11844915	Power-/Control unit ELP 7442-A 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11791570	HR1934-3 G DF USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11791570	HR1934-3 G DF USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791570	HR1934-3 G DF USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11797310	CS7612 FL ROK 220/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
11797310	CS7612 FL ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
11791610	HR1936-3 G DF GD USA EDST/CLST120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11791610	HR1936-3 G DF GD USA EDST/CLST120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791610	HR1936-3 G DF GD USA EDST/CLST120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11804840	H7660BP USA GRGR 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11804840	H7660BP USA GRGR 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11804800	H7660BP USA BRWS 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11804800	H7660BP USA BRWS 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11804860	H7660BP USA OBSW 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11804860	H7660BP USA OBSW 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11933780	H2860-2BP D EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11955950	H2860-2BP IB EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11955940	H2860-2B IB EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11955940	H2860-2B IB EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11977970	B4847 AUS	Electronic unit	Lead	7439-92-1
11977960	B4847 RU	Electronic unit	Lead	7439-92-1
11916360	KM7464 FL ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
11977950	B4312 RU	Electronic unit	Lead	7439-92-1
11978010	B4847 GB	Electronic unit	Lead	7439-92-1
11977940	B4826 GB	Electronic unit	Lead	7439-92-1
11977920	B43-12 CH	Electronic unit	Lead	7439-92-1
11977930	B48-26 CH	Electronic unit	Lead	7439-92-1
11916370	KM7465 FL ROK 220/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
11977990	B4847 CN	Electronic unit	Lead	7439-92-1
11945990	H2760-2BP GB EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11945990	H2760-2BP GB EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11947960	H2760-2BP I EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11947960	H2760-2BP I EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11947950	H2760-2B I EDST/CLST230/50<3KW PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11947950	H2760-2B I EDST/CLST230/50<3KW PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11948640	H2760-2BP F EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11948640	H2760-2BP F EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11942780	H2860-2BP TR EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11942780	H2860-2BP TR EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11942770	H2860-2B TR EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11942770	H2860-2B TR EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11945370	H2860-2BP NER OBSW 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11945370	H2860-2BP NER OBSW 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11945380	H2860-2BP NER EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11945380	H2860-2BP NER EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11945310	H2760-2BP NER EDST/CLST 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11945310	H2760-2BP NER EDST/CLST 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11041490	KM6565 FR SA 220/60	Heater plate 3,2-2,05-1,05KW 230V	Lead	7439-92-1
11041490	KM6565 FR SA 220/60	Heater plate 2,6-1,5KW 230V	Lead	7439-92-1
11041490	KM6565 FR SA 220/60	Heater plate 1,2KW 230V	Lead	7439-92-1
11041490	KM6565 FR SA 220/60	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11681364	Power-/Control unit EPL 8760	SMD- Diode STTH1R04A	Lead	7439-92-1
11977910	B4847 D	Electronic unit	Lead	7439-92-1
11977900	B4826 D	Electronic unit	Lead	7439-92-1
11977890	B4312 D	Electronic unit	Lead	7439-92-1
11933770	H2860-2BP D GRGR 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11933770	H2860-2BP D GRGR 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
11933660	H2860-2BP D OBSW 230/50 PizzaPlus	Heater element Top heat 230V	Lead	7439-92-1
11933660	H2860-2BP D OBSW 230/50 PizzaPlus	Heater element Unterhitze 230-240V	Lead	7439-92-1
9769410	H6560BP USA EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
9937980	KM6367-1 AUS FL.BDG. 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
9872990	H6660BP USA EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
9862880	H6660BP USA BRWS 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
9862850	H6660BP USA OBSW 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
8122981	Operating unit 6-fold	Operating unit 6-fold	Lead	7439-92-1
8122981	Operating unit 6-fold	Operating unit 6-fold	Lead	7439-92-1
9775930	KM6377 USA EDST 240/60	power supply unit Induktion G5	Lead	7439-92-1
9775920	KM6375 USA FL.BDG. 240/60	power supply unit Induktion G5	Lead	7439-92-1
9775910	KM6370 USA EDST 240/60	power supply unit Induktion G5	Lead	7439-92-1
10250050	H6290B SA EDST/CLST 220/60	Temperature regul. Sub-assembly	Lead	7439-92-1
11985094	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12511992	Power-/Control unit ELP 7753 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12511892	Power-/Control unit ELP 7752 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10921089	Power-/Control unit ELP 7792 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10920989	Power-/Control unit ELP 7751 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10445990	H6860BPX D GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10445990	H6860BPX D GRGR 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10445980	H6860BPX D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10445980	H6860BPX D OBSW 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10463130	H6860BPX NL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9775900	KM6365 USA FL.BDG. 240/60	power supply unit Induktion G5	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
9775890	KM6360 USA EDST 240/60	power supply unit Induktion G5	Lead	7439-92-1
9810800	CS1013-1 NG EDST 230/50	Jet 0,42MM	Lead	7439-92-1
9810800	CS1013-1 NG EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9810830	CS1018 NG EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9391550	CS1013-1 LPG EDST 230/50	Jet 0,32MM	Lead	7439-92-1
9391550	CS1013-1 LPG EDST 230/50	Jet 0,27MM	Lead	7439-92-1
9391550	CS1013-1 LPG EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9391540	CS1018 LPG EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9233820	KM3014 HK EDST 230/50	Holder	Lead	7439-92-1
9233820	KM3014 HK EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9272050	KM3010 G USA EDST 120/60	Holder	Lead	7439-92-1
9272050	KM3010 G USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
9209870	KM3014 AUS EDST 230/50	Holder	Lead	7439-92-1
9209870	KM3014 AUS EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9265870	KM3010 RU EDST 230/50	Burner tap 0,42	Lead	7439-92-1
9265870	KM3010 RU EDST 230/50	Burner tap 0,39	Lead	7439-92-1
9265870	KM3010 RU EDST 230/50	Holder	Lead	7439-92-1
9265870	KM3010 RU EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9101190	KM3010 GB EDST 230/50	Burner tap 0,42	Lead	7439-92-1
9101190	KM3010 GB EDST 230/50	Burner tap 0,39	Lead	7439-92-1
9101190	KM3010 GB EDST 230/50	Holder	Lead	7439-92-1
10463130	H6860BPX NL GRGR 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
7077470	KM6003 D EDST/LPT 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
7111190	KM2034 E EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7054080	KM2034 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7111180	KM2012 E EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7053550	KM2012 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7001710	KM6023 D EDST 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
7001710	KM6023 D EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
7001680	KM6024 D EDST/LPT 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
7001650	KM6013 D EDST/LPT 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
7001650	KM6013 D EDST/LPT 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6910590	KM6031 D EDST 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
6910590	KM6031 D EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6910580	KM6024 D EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6910520	KM6017 D fl.bdg. 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
6910520	KM6017 D fl.bdg. 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6910460	KM6013 D EDST 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
6910460	KM6013 D EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6910440	KM6012 D EDST 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
6910440	KM6012 D EDST 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
6910440	KM6012 D EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12602380	OGD1232L XD1 BL	Socket food probe GP	Lead	7439-92-1
12602380	OGD1232L XD1 BL	Supply cable G32	Lead	7439-92-1
12602380	OGD1232L XD1 BL	Distributor kpl	Lead	7439-92-1
12602380	OGD1232L XD1 BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
12602380	OGD1232L XD1 BL	Adapter Gas connection	Lead	7439-92-1
12602380	OGD1232L XD1 BL	Ignitiontransformer	Lead	7439-92-1
12729760	Ignitiontransformer	Ignitiontransformer	Lead	7439-92-1
11612858	Power-/Control unit ELP 7757 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12649310	G5455 Vi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649300	G5450 Vi D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649130	G5455 SCVi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649120	G5450 SCVi D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12048010	KM6521 FR D 230/50	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
12048010	KM6521 FR D 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
12048010	KM6521 FR D 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12048010	KM6521 FR D 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
9628720	Connection hose 4,0x2,5x350mm FEP	Connection hose 4,0x2,5x350mm FEP	Lead	7439-92-1
9628720	Connection hose 4,0x2,5x350mm FEP	Connection hose 4,0x2,5x350mm FEP	Lead	7439-92-1
10778710	Door Lock	Door Lock	Lead	7439-92-1
10778710	Door Lock	Door Lock	Lead	7439-92-1
10921009	Power-/Control unit ELP 7794 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10813520	K36683IDF EU1	K36683IDF EU1	Lead	7439-92-1
10813520	K36683IDF EU1	K36683IDF EU1	Lead	7439-92-1
9101190	KM3010 GB EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12511891	Power-/Control unit ELP 7752 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12511891	Power-/Control unit ELP 7753 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
9894040	H6166E D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9834530	H6167E D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9769400	H6560B USA EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
9624130	H6461B HK EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9542020	H6260B NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9523810	H6260B GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9518900	H6461B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
8307500	Spacer D 18,0 x 0,5mm/MS	Blech-Tafel-Messing 0,50 x 1000 x 2000	Lead	7439-92-1
8287150	Residual heat ind. 5-fold 3034	Residual heat ind. 5-fold 3034	Lead	7439-92-1
8287150	Residual heat ind. 5-fold 3034	Residual heat ind. 5-fold 3034	Lead	7439-92-1
8579400	Distributor KM 3012	Rundmessing D 17,0 MS 58-hartgezogen	Lead	7439-92-1
8249260	power supply unit Induktion G5	power supply unit Induktion G5	Lead	7439-92-1
8249260	power supply unit Induktion G5	power supply unit Induktion G5	Lead	7439-92-1
7187740	KM2010 P EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7053540	KM2010 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
8392390	Threaded bushing 57mm	Rundmessing D 15,0 MS 58-hartgezogen	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
8239930	Heater plate 2,2-1,0KW 230V	Heater plate 2,2-1,0KW 230V	Lead	7439-92-1
8239930	Heater plate 2,2-1,0KW 230V	Heater plate 2,2-1,0KW 230V	Lead	7439-92-1
8236720	Heater plate 2,2KW 230V	Heater plate 2,2KW 230V	Lead	7439-92-1
8236720	Heater plate 2,2KW 230V	Heater plate 2,2KW 230V	Lead	7439-92-1
8239890	Heater plate 1,8KW 230V	Heater plate 1,8KW 230V	Lead	7439-92-1
8239920	Heater plate 2,2-0,75KW 230V	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
4771040	Heater plate 2,2-0,75KW 230V	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
8230650	Regulator 230V 50.55021.105	Regulator 230V 50.55021.105	Lead	7439-92-1
8230650	Regulator 230V 50.55021.105	Regulator 230V 50.55021.105	Lead	7439-92-1
4771010	Heater plate 1,8KW 230V	Heater plate 1,8KW 230V	Lead	7439-92-1
4771000	Heater plate 2,3KW 230V	Heater plate 2,3KW 230V	Lead	7439-92-1
8038765	Regulator 230V 50.57021.010	Regulator 230V 50.57021.010	Lead	7439-92-1
8038765	Regulator 230V 50.57021.010	Regulator 230V 50.57021.010	Lead	7439-92-1
8512300	Burner tap 0,32	Jet 0,32MM	Lead	7439-92-1
8508070	Burner DualWok	Rundmessing D 15,0 MS 58-hartgezogen	Lead	7439-92-1
7564810	Harness Regulator vormontiert	Regulator 230V 50.57021.155	Lead	7439-92-1
7564810	Harness Regulator vormontiert	Regulator 230V 50.55021.155	Lead	7439-92-1
6850913	Regulator 230V 50.57021.155	Regulator 230V 50.57021.155	Lead	7439-92-1
6850913	Regulator 230V 50.57021.155	Regulator 230V 50.57021.155	Lead	7439-92-1
6850923	Regulator 230V 50.55021.155	Regulator 230V 50.55021.155	Lead	7439-92-1
6850923	Regulator 230V 50.55021.155	Regulator 230V 50.55021.155	Lead	7439-92-1
10904390	H6880-2BP USA GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10904390	H6880-2BP USA GRGR 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10904390	H6880-2BP USA GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10752150	H6880-2BP USA OBSW 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10395870	H6880BP2 USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
7789280	CS1013-1 HK EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7131020	CS1112 GB EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
7142120	CS1018 G HK EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
6980830	CS1134 R01 EDST 230/50	Heater plate 1,8-0,7KW 230V	Lead	7439-92-1
6980830	CS1134 R01 EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6980820	CS1122 R01 EDST 230/50	Regulator 230V 50.55021.117/+Z	Lead	7439-92-1
6980820	CS1122 R01 EDST 230/50	Regulator 230V 50.57021.052	Lead	7439-92-1
6980810	CS1112 R01 EDST 230/50	Heater plate 1,8-0,7KW 230V	Lead	7439-92-1
6980810	CS1112 R01 EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
9858470	H6167EP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
7840252	Heater element Bottom heat	Heater element Bottom heat	Lead	7439-92-1
7840252	Heater element Bottom heat	Heater element Bottom heat	Lead	7439-92-1
9519090	H6890BP D EDST/CLST 3N AC230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9542300	H6860BP EU1 OBSW 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9542300	H6860BP EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9542180	H6461BP NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9523970	H6860BP GB BRWS 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9523970	H6860BP GB BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9523820	H6260BP GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9456920	KM2355 LP USA EDST 120/60	Jet 0,54MM	Lead	7439-92-1
9456920	KM2355 LP USA EDST 120/60	Jet 0,32MM	Lead	7439-92-1
9456920	KM2355 LP USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
9450190	KM2355 G USA EDST 120/60	Burner tap 0,52	Lead	7439-92-1
9450190	KM2355 G USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
9518990	H6660BP D OBSW 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9518990	H6660BP D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9519080	H6860BP D EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9519080	H6860BP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9519070	H6860BP D OBSW 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9519070	H6860BP D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9519060	H6860BP D BRWS 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9519060	H6860BP D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
9323230	KM2354 AUS EDST 230/50	Burner tap 0,52	Lead	7439-92-1
9323230	KM2354 AUS EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9289880	KM2354 GB EDST 230/50	Jet 0,39MM	Lead	7439-92-1
9289880	KM2354 GB EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9110800	KM2355 R01 EDST 230/50	Jet 0,39MM	Lead	7439-92-1
9110800	KM2355 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9110790	KM2354 R01 EDST 230/50	Jet 0,39MM	Lead	7439-92-1
9110790	KM2354 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12594720	Power-/Control unit ELP 7482	SMD- Diode STTH1R04A	Lead	7439-92-1
10395870	H6880BP2 USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10395870	H6880BP2 USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
7077470	KM6003 D EDST/LPT 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10902430	HR1954-2 G USA EDST/CLST 120/240/60	Heater element Catalyst 208-240V	Lead	7439-92-1
10902420	HR1936-2 LP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10902420	HR1936-2 LP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10902420	HR1936-2 LP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10902410	HR1936-2 G USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10902410	HR1936-2 G USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10902410	HR1936-2 G USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10902400	HR1935-2 G USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10902400	HR1935-2 G USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10902400	HR1935-2 G USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10902390	HR1934-2 LP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10902390	HR1934-2 LP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10902390	HR1934-2 LP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10902380	HR1934-2 G USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10902380	HR1934-2 G USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10902380	HR1934-2 G USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10902370	HR1924-2 LP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10902370	HR1924-2 LP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10902370	HR1924-2 LP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10902360	HR1924-2 G USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10902360	HR1924-2 G USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10902360	HR1924-2 G USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10752020	H6880-2BP2 USA OBSW 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10752020	H6880-2BP2 USA OBSW 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10752020	H6880-2BP2 USA OBSW 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10752010	H6880-2BP2 USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10752010	H6880-2BP2 USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10752010	H6880-2BP2 USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10751980	H6780-2BP2 USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10751980	H6780-2BP2 USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10751980	H6780-2BP2 USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10902350	HR1622-2 USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10902350	HR1622-2 USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10902350	HR1622-2 USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
12384021	Power-/Control unit ELP 7202 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10983730	KM6542 FR ROK 220/60	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10983730	KM6542 FR ROK 220/60	Heater plate 1,2kW 230V	Lead	7439-92-1
10983720	KM6527 FR ROK 220/60	Heater plate 1,8kW 230V	Lead	7439-92-1
10983720	KM6527 FR ROK 220/60	Heater plate 1,5kW 230V	Lead	7439-92-1
10983710	KM6520 FR ROK 220/60	Heater plate 1,2kW 230V	Lead	7439-92-1
10983710	KM6520 FR ROK 220/60	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12594721	Power-/Control unit ELP 7482	SMD- Diode STTH1R04A	Lead	7439-92-1
10941510	KM6565 FR RU 230/50	Heater plate 1,2kW 230V	Lead	7439-92-1
10902440	HR1954-2 LP USA EDST/CLST 120/240/60	Heater element Catalyst 208-240V	Lead	7439-92-1
11086390	HR1622-1 S EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086390	HR1622-1 S EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086420	HR1956-1 G TR EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
11086410	HR1936-1 G TR EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086410	HR1936-1 G TR EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086310	HR1956-1 G N EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
11086300	HR1936-1 G N EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086300	HR1936-1 G N EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086290	HR1924-1 G N EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086290	HR1924-1 G N EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086270	HR1622-1 N EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086270	HR1622-1 N EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086040	HR1956-1 G D EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
10938820	CS1021-1 E EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940430	CS1021-1 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10938800	CS1012-2 E EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10938800	CS1012-2 E EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10938800	CS1012-2 E EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940410	CS1012-2 R01 EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10940410	CS1012-2 R01 EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10940410	CS1012-2 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11086030	HR1936-1 G D EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086030	HR1936-1 G D EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
11086020	HR1622-1 D EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
11086020	HR1622-1 D EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
10974230	KMDA7774-1 FR B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974270	KMDA7774-1 FR NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974260	KMDA7774-1 FR IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974250	KMDA7774-1 FR F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974240	KMDA7774-1 FR DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974210	KMDA7774-1 FR D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974310	KMDA7774-1 FL B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974370	KMDA7774-1 FL NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974360	KMDA7774-1 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974350	KMDA7774-1 FL F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974340	KMDA7774-1 FL E 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974330	KMDA7774-1 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974290	KMDA7774-1 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10974320	KMDA7774-1 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10939840	KM3034-1 RU EDST 230/50	Residual heat ind. 5-fold 3034	Lead	7439-92-1
10902450	HR1955-2 G USA EDST/CLST 120/240/60	Heater element Catalyst 208-240V	Lead	7439-92-1
10902470	HR1956-2 LP USA EDST/CLST 120/240/60	Heater element Catalyst 208-240V	Lead	7439-92-1
10902460	HR1956-2 G USA EDST/CLST 120/240/60	Heater element Catalyst 208-240V	Lead	7439-92-1
10941510	KM6565 FR RU 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10773310	HR1724 LP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10773310	HR1724 LP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10773310	HR1724 LP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10773300	HR1724 G USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10773300	HR1724 G USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
10773300	HR1724 G USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
10750470	DA6698D D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10750450	DA6698D D BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10750490	DA6698D D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10767370	DA4248VD D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10767330	DA4208VD D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10767240	DA4208D D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10684490	CS7612 FL IB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10684490	CS7612 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10557490	DO6860 D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10557490	DO6860 D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
10557490	DO6860 D BRWS 230/50	Supply cable DO	Lead	7439-92-1
10557480	DO6860 D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10557480	DO6860 D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
10557480	DO6860 D OBSW 230/50	Supply cable DO	Lead	7439-92-1
10557470	DO6860 D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10557470	DO6860 D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10557470	DO6860 D EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
10564630	KM6565 FR R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10564630	KM6565 FR R01 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10564610	KM6564 FR R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10564610	KM6564 FR R01 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10584750	HR1936 LP AUS 27,5 mbar EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
10584750	HR1936 LP AUS 27,5 mbar EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
10512600	CS7612 FL R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10512600	CS7612 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12894920	Power-/Control unit ELP 7794 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11985103	Power-/Control unit ELP 7755 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11985096	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
9543350	H6800BP B EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9519040	H6800BP D EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
7464443	Drive clean side kpl.	Sensor	Lead	7439-92-1
7464343	Drive unclean side kpl.	Sensor	Lead	7439-92-1
7307360	KM2050 USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
7222760	B995 D D 220-240/50-60 3,2-3,8kW	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
7051650	KM2011 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7129320	CS1112 P EDST 230/50	Heater plate 1,8-0,7KW 230V	Lead	7439-92-1
7129320	CS1112 P EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10585610	HR1936 G RU EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
10941480	KM6542 FL RU 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10941480	KM6542 FL RU 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10941470	KM6542 FR RU 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10941470	KM6542 FR RU 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10941460	KM6540 FR RU 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10941460	KM6540 FR RU 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10941430	KM6522 FR RU 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10941430	KM6522 FR RU 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10941400	KM6520 FL RU 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10941400	KM6520 FL RU 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10941380	KM6520 FR RU 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10941380	KM6520 FR RU 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10888680	KM6520 FR AUS 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
10888680	KM6520 FR AUS 230/50	Heater plate 1,5KW 230V	Lead	7439-92-1
10888680	KM6520 FR AUS 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10888680	KM6520 FR AUS 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10735660	KM2032G USA EDST	Sealing ring 7,65x1,78	Lead	7439-92-1
10873520	KM6542 FL IB 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10873520	KM6542 FL IB 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10862560	KM6542 FL R01 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10862560	KM6542 FL R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10873510	KM6540 FR IB 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10873510	KM6540 FR IB 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10564580	KM6540 FR R01 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10564580	KM6540 FR R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10873500	KM6520 FR IB 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10873500	KM6520 FR IB 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10564550	KM6520 FR R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10564550	KM6520 FR R01 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10882050	KM6564 FR D 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10882050	KM6564 FR D 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
9743100	HR1956 G AUS EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
9743090	HR1936 G AUS EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
9743090	HR1936 G AUS EDST/CLST 230/50	Heater element Bottom heat 208V	Lead	7439-92-1
10831600	H6800BPXC CN GRGR 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10831680	H6800BPXC CN OBSW 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10869030	DA4248VD PAC EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10787010	CS7612 FL AUS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10787010	CS7612 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10776470	CS7612 FL RU 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10776470	CS7612 FL RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10585620	HR1956 G RU EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
10585610	HR1936 G RU EDST/CLST 230/50	Heater element Hot air 208V	Lead	7439-92-1
12447840	H2455BP XE1/D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12447830	H2455B XE1/D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12447830	H2455B XE1/D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12447840	H2455BP XE1/D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12447910	H2455-55B XS2/CH OBSW 230/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12447910	H2455-55B XS2/CH OBSW 230/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12423920	G7380 SCVI GB ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12423790	G7210 SCi GB ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12423770	G7185 SCVi XXL GB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12423740	G7180 SCVi GB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12401530	H2457IP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401530	H2457IP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12447910	H2455-55B XS2/CH OBSW 230/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12447920	H2455-55BP XS2/CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12447920	H2455-55BP XS2/CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12447920	H2455-55BP XS2/CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12369120	DG7141 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12423930	G7600 SC GB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12423950	G7600 SC GB ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12423960	G7622 SC GB BW230 1,9 AutoDosSelection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11570184	Power-/Control unit ELP 7784 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11208546	Power-/Control unit ELP 7775 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
12423970	G7650 SCVi GB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12423980	G7655 SCVi XXL GB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12401400	H2457E D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401400	H2457E D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401320	H2455EP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401320	H2455EP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401350	H2455EP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401350	H2455EP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401430	H2457EP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401430	H2457EP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401440	H2457EP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401440	H2457EP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401360	H2455I D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401360	H2455I D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401380	H2455I D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401380	H2455I D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401370	H2455I D BRWS 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401370	H2455I D BRWS 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401590	H2456I D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401590	H2456I D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401500	H2457I D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401500	H2457I D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401510	H2457I D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401510	H2457I D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401520	H2457IP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401520	H2457IP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12424000	G7760 SCVi GB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12410610	H2455BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12410610	H2455BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12418820	H2455IP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12418820	H2455IP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12410630	H2457BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12410630	H2457BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12446860	H2455B D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12446860	H2455B D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12446870	H2455BP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12446870	H2455BP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12446850	H2455IP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12446850	H2455IP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12411070	H2455B NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12411070	H2455B NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12411080	H2455BP NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12411080	H2455BP NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12422630	H2455B AUS OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12422630	H2455B AUS OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12422640	H2457B AUS OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12422640	H2457B AUS OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12422650	H2457BP AUS OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12422650	H2457BP AUS OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12426110	G7130 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12408770	H2455B GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12405160	H2455B F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12405160	H2455B F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12405170	H2455BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12405170	H2455BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12405180	H2457BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12405180	H2457BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12405120	H2455B I OBSW/EDST-LOOK230/50<3KW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12405120	H2455B I OBSW/EDST-LOOK230/50<3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12405130	H2455BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12405130	H2455BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12402210	H2455B B OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12402210	H2455B B OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12402220	H2455BP B OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12402220	H2455BP B OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12449010	H2455E XK4/CDN OBSW 120/240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12449010	H2455E XK4/CDN OBSW 120/240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12449000	H2455E XK5/CDN OBSW 120/208/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12449000	H2455E XK5/CDN OBSW 120/208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12424010	G7980 SCVi GB OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424020	G7985 SCVi XXL GB OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12410600	H2455B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12410600	H2455B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12410620	H2457B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12410620	H2457B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12342510	DAH1950 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12342570	DAH2960 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12342590	DAH4870 XS1/CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342600	DAH4870 XS1/CH GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342610	DAH4870 XS1/CH CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342620	DAH4870 XS1/CH PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342630	DAH4970 XS1/CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342640	DAH4970 XS1/CH GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342650	DAH4970 XS1/CH CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342660	DAH4970 XS1/CH PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342670	DAH4880 XS1/CH OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342680	DAH4980 XS1/CH OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12343400	DAH1650 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12343420	DAH1850 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12343440	DAH1950 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12343460	DAH2660 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12343480	DAH2860 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12343500	DAH2960 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12343520	DAH4870 XN1/UA OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12343530	DAH4870 XN1/UA GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12343540	DAH4870 XN1/UA PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12343550	DAH4870 XN1/UA CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12343560	DAH4970 XN1/UA OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12343570	DAH4970 XN1/UA GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12428910	H2466B D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12428910	H2466B D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12428920	H2466BP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12428920	H2466BP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12428970	H2467B D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12428970	H2467B D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12429000	H2467BP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12429000	H2467BP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12429010	H2468B D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12429010	H2468B D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12429060	H2468BP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12429060	H2468BP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12342350	DAH2960 XG1/GB OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12342370	DAH4870 XG1/GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342380	DAH4870 XG1/GB GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342390	DAH4870 XG1/GB CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342400	DAH4870 XG1/GB PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342410	DAH4970 XG1/GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342420	DAH4970 XG1/GB GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342430	DAH4970 XG1/GB CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342440	DAH4970 XG1/GB PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342450	DAH4880 XG1/GB OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342460	DAH4980 XG1/GB OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342470	DAH1650 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12343580	DAH4970 XN1/UA PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12440420	G7785 SCVi XXL OE1 OS230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440430	G7790 SCVi OE1 OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440440	G7795 SCVi XXL OE1 OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440450	G7930 SCi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440460	G7980 SCVi OE1 OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440470	G7985 SCVi XXL OE1 OS/CS230 1,9 K2O AD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11208398	Power-/Control unit ELP 7774 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11568894	Power-/Control unit ELP 7771 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
12488720	G7020 SC D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12488730	G7020 SCU D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12488740	G7020 SCi D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12488750	G7060 Vi D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12488760	G7060 SCVi D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12488770	G7065 SCVi XXL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12423690	G7130 SC GB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12423700	G7130 SC GB ED230 1,9 AutoDos CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12401260	H2455E D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401260	H2455E D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401290	H2455E D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401290	H2455E D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401280	H2455E D BRWS 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401280	H2455E D BRWS 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401390	H2457E D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401390	H2457E D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12343590	DAH4970 XN1/UA CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12347830	H7440BPX SER OBSW/MATT 230/50	Heater element Top heat 230V	Lead	7439-92-1
12347850	H7464BPX SER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12347860	H7840BPX SER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12347840	H7440BMX SER OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12347880	H7860BPX SER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12347870	H7840BMX SER OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12440240	G7210 SC OE1 BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440250	G7210 SC OE1 ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440260	G7210 SCi OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440270	G7260 SCVi OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12305200	H7860BPX F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12440290	G7265 SCVi XXL OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440300	G7380 SCVi OE1 ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440310	G7385 SCVi XXL OE1 ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440320	G7600 SC OE1 BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440330	G7600 SC OE1 ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440340	G7600 SCi OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440350	G7605 SCi XXL OE1 ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440370	G7650 SCVi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440380	G7655 SCVi XXL OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440390	G7674 SCVi OE1 OS230 1,9 AutoDos Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440400	G7710 SCi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440410	G7783 SCVi OE1 OS230 1,9 k2o AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12408770	H2455B GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12435890	H2861-1B SER OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12435890	H2861-1B SER OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12435900	H2861-1B SER GRGR 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12435900	H2861-1B SER GRGR 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12435910	H2861-1B IB EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12435910	H2861-1B IB EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12435920	H2861-1BP SER OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12435920	H2861-1BP SER OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12435930	H2861-1BP SER GRGR 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12435930	H2861-1BP SER GRGR 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12435990	H2861-1BP IB EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12435990	H2861-1BP IB EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12472480	H7260B UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12472490	H7260BP UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12435150	DG8540L XE1/R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12327270	H7464BPX UA OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12327280	H7840BMX UA OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12327290	H7860BPX UA OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12434370	H2861-1B TR EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12434370	H2861-1B TR EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12434720	H2861-1BP TR EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12434720	H2861-1BP TR EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12434900	H2766-1BP GB OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12434900	H2766-1BP GB OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442690	H2761-1BP NL EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442690	H2761-1BP NL EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442720	H2861-1BP NL EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442720	H2861-1BP NL EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442810	H2766-1B EU1 OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442810	H2766-1B EU1 OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442830	H2861-1B EU1 OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442830	H2861-1B EU1 OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442870	H2861-1B EU1 GRGR 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442870	H2861-1B EU1 GRGR 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442820	H2766-1BP EU1 OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442820	H2766-1BP EU1 OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442880	H2861-1BP EU1 OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442880	H2861-1BP EU1 OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442890	H2861-1BP EU1 GRGR 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442890	H2861-1BP EU1 GRGR 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442930	H2861-1B B EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442930	H2861-1B B EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442940	H2861-1BP B EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442940	H2861-1BP B EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12435870	H2766-1B SER OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12435870	H2766-1B SER OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12435880	H2766-1BP SER OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12435880	H2766-1BP SER OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12434810	H2861-1B UA OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12426750	G7674 SCVi NER OS230 1,9 AutoDos Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12395170	H2456E CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12395170	H2456E CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12395170	H2456E CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12395160	H2456E CH BRWS 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12395160	H2456E CH BRWS 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12395160	H2456E CH BRWS 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12395200	H2456EP CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12395200	H2456EP CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12395200	H2456EP CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12395190	H2456EP CH BRWS 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12395190	H2456EP CH BRWS 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12395190	H2456EP CH BRWS 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12446300	H2456BP CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12446300	H2456BP CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12446300	H2456BP CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12426700	G7655 SCVi XXL NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426720	G7657 SCVi XXL NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12446290	H2456B CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12446290	H2456B CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12446290	H2456B CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12426780	G7679 SCVi XXL NER OS230 1,9 AutoD Excel	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426790	G7760 SCVi NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426800	G7765 SCVi XXL NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12434810	H2861-1B UA OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12434820	H2861-1B UA EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12434820	H2861-1B UA EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12434830	H2861-1BP UA OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12434830	H2861-1BP UA OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12434840	H2861-1BP UA EDST/CLST 125 Edition230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12434840	H2861-1BP UA EDST/CLST 125 Edition230/50	Heater element Top heat 230V	Lead	7439-92-1
12471510	PG8504 EXE AE-ADP 3 AC 220-230V 60HZ	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12484650	KM7466 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12481390	H2861B NER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12481390	H2861B NER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12494120	KM7466 FL UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12494110	KM7466 FR UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12497230	H7660BP CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12497230	H7660BP CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12497230	H7660BP CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12497240	H7660-55BP CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12497240	H7660-55BP CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12497240	H7660-55BP CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12497250	H7640BP CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12497250	H7640BP CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12497260	H7640BM CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12426670	G7650 SCVi NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426690	G7652 SCVi NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420980	G27985 SCVi XXL CH OS/CS230 1,9 K2O AD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420860	G27605 SCi XXL CH ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420870	G27605 SCi XXL CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420880	G27628 SCi XXL CH ED230 1,9 AD CLST Exce	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420890	G27628 SCi XXL CH BW230 1,9 AD Exce	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420910	G27655 SCVi XXL CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420920	G27678 SCVi XXL CH OS230 1,9 AD Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420930	G27715 SCi XXL CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12447850	H2455B XU4/USA OBSW 120/240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12447850	H2455B XU4/USA OBSW 120/240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12447860	H2455B XU2/USA OBSW 120/208/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12447860	H2455B XU2/USA OBSW 120/208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12447880	H2455E XU4/USA OBSW 120/240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12447870	H2455E XU2/USA OBSW 120/208/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12447870	H2455E XU2/USA OBSW 120/208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12447890	H2455i XU4/USA OBSW 120/240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12447890	H2455i XU4/USA OBSW 120/240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12447900	H2455i XU2/USA OBSW 120/208/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12447900	H2455i XU2/USA OBSW 120/208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12420940	G27788 SCVi XXL CH OS230 1,9 K2O AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420950	G27795 SCVi XXL CH OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420970	G27935 SCi XXL CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12480500	G5310 SCU I OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426440	G7260 SCVi NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426120	G7130 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426130	G7133 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426150	G7133 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12408780	H2455BP GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12408780	H2455BP GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12426170	G7138 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426180	G7138 SCU XXL NER ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426190	G7180 SCVi NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426200	G7183 SCVi NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426210	G7185 SCVi XXL NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426220	G7188 SCVi XXL NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12369130	DGM7341 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12426300	G7210 SCU NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426310	G7210 SCU NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426320	G7210 SCi NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426370	G7212 SCU NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426380	G7212 SCU NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426420	G7233 SCU NER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426430	G7233 SCU NER ED230 1,9 CLST Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426410	G7217 SCU XXL NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12488210	KM7466 FL BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12472470	H2841B D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12426390	G7217 SCU XXL NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420850	G17980 SCVi CH OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426450	G7262 SCVi NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12433330	H2761-1BP NER EDST/CLST 125Edition230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12433330	H2761-1BP NER EDST/CLST 125Edition230/50	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12433870	H2766-1BP NER OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12433870	H2766-1BP NER OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12433880	H2861-1BP NER OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12433880	H2861-1BP NER OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12433890	H2861-1BP NER GRGR 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12433890	H2861-1BP NER GRGR 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12433900	H2861-1BP NER EDST/CLST 125Edition230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12433900	H2861-1BP NER EDST/CLST 125Edition230/50	Heater element Top heat 230V	Lead	7439-92-1
12426570	G7600 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426580	G7600 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426610	G7602 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426620	G7602 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426590	G7600 SCi NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426600	G7600 SCi NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426640	G7605 SCU XXL NER ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426630	G7605 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426650	G7607 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426660	G7607 SCU XXL NER ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12442680	H2761-1B NL EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442680	H2761-1B NL EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12442710	H2861-1B NL EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12442710	H2861-1B NL EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12426460	G7265 SCVi XXL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426470	G7267 SCVi XXL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426480	G7293 SCVi NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426500	G7294 SCVi NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426510	G7298 SCVi XXL NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12405720	PDR908HP P ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12426520	G7299 SCVi XXL NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12432430	H2861-1B D EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12432430	H2861-1B D EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12432420	H2861-1B D OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12432420	H2861-1B D OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12432450	H2861-1BP D EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12432450	H2861-1BP D EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12432440	H2861-1BP D OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12432440	H2861-1BP D OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12431440	H2766-1B D OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12431440	H2766-1B D OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12432410	H2766-1BP D OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12432410	H2766-1BP D OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12434240	H2761-1BP F EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12434240	H2761-1BP F EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12405690	PDR508HP P ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12426530	G7380 SCVi NER ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426560	G7385 SCVi XXL NER ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12361630	G7609 SCi XXL ANL ED230 1,9 AD CLST AUS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12361610	G7189 SCVi XXL ANL ED230 1,9 AutoDos AUS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12361640	G7719 SCi XXL ANL OS230 1,9 AutoDos AUS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12382840	KM7576 FL ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12382840	KM7576 FL ANL 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
8239040	Regulator 230V 50.57021.052	Regulator 230V 50.57021.052	Lead	7439-92-1
12263690	PDR516TOP SL EL NBI IG-IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263700	PDR516ROP SL EL NBI IG-IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263530	PDR511ROP SL HP EX IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12263520	PDR511ROP SL HP EX IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12263510	PDR516TOP SL G EX IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263140	PDR516TOP SL G GB IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
8239040	Regulator 230V 50.57021.052	Regulator 230V 50.57021.052	Lead	7439-92-1
8239000	Regulator 230V 50.55021.117/+Z	Regulator 230V 50.55021.117/+Z	Lead	7439-92-1
8239000	Regulator 230V 50.55021.117/+Z	Regulator 230V 50.55021.117/+Z	Lead	7439-92-1
4771020	Heater plate 1,2KW 230V	Heater plate 1,2KW 230V	Lead	7439-92-1
8240680	Heater plate 1,8-0,7KW 230V	Heater plate 1,8-0,7KW 230V	Lead	7439-92-1
8240680	Heater plate 1,8-0,7KW 230V	Heater plate 1,8-0,7KW 230V	Lead	7439-92-1
12302210	CS1112 KW EDST 220/50 STORNO	Heater plate 1,2KW 230V	Lead	7439-92-1
12395570	H2767BP F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12395570	H2767BP F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12382860	KM7576 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12382860	KM7576 FL R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12289620	DGM7440 UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12295770	PDR511COP SL HP SEE IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12295780	PDR511COP SL HP SEE IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12262520	PDR516ROP SL EL GB IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262550	PDR516ROP SL EL GB IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262860	PDR516COP SL GB EL IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262880	PDR516COP SL EL GB IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262890	PDR516TOP SL EL GB IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262900	PDR516TOP SL EL GB IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262910	PDR516ROP SL G GB IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262920	PDR516ROP SL G GB IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262960	PDR516COP SL G GB IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263040	PDR516COP SL G GB IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263090	PDR516TOP SL G GB IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263180	PDR511ROP SL HP GB IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12263190	PDR511ROP SL HP GB IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12295730	PDR511COP SL HP GB IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12295740	PDR511COP SL HP GB IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12263440	PDR516ROP SL EL EX IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263450	PDR516ROP SL EL EX IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263460	PDR516TOP SL EL EX IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263470	PDR516TOP SL EL EX IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263480	PDR516ROP SL G EX IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263490	PDR516ROP SL G EX IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12263500	PDR516TOP SL G EX IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12289630	DGM7440 UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12382750	KM7466 FL ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12345890	PDR909 EL CP NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12374650	G7131 SCi D ED230 1,9 CLST AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12374660	G7137 SCi XXL D ED230 1,9 CLST AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
8534990	Burner tap 0,27	Jet 0,27MM	Lead	7439-92-1
8535000	Burner tap 0,32	Jet 0,32MM	Lead	7439-92-1
8119220	Jet 0,54MM	Jet 0,54MM	Lead	7439-92-1
8535020	Burner tap 0,54	Jet 0,54MM	Lead	7439-92-1
12302180	KM2032G KW EDST 220/50 STORNO	Sealing ring 7,65x1,78	Lead	7439-92-1
10920300	Burner tap 0,88/0,42 (Wok)	Burner tap 0,88/0,42 (Wok)	Lead	7439-92-1
8119160	Jet 0,39MM	Jet 0,39MM	Lead	7439-92-1
12302190	KM2357-1 KW FL.bdg. 220/50 STORNO	Sealing ring 7,65x1,78	Lead	7439-92-1
12302190	KM2357-1 KW FL.bdg. 220/50 STORNO	Jet 0,27MM	Lead	7439-92-1
12302190	KM2357-1 KW FL.bdg. 220/50 STORNO	Burner tap 0,52	Lead	7439-92-1
12302190	KM2357-1 KW FL.bdg. 220/50 STORNO	Jet 0,39MM	Lead	7439-92-1
12374880	G7771 SCVi D OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12374900	G7777 SCVi XXL D OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12374920	G7793 SCVi D OS230 1,9 K20 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12374930	G7797 SCVi XXL D OS230 1,9 K20 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12374680	G7191 SCVi D ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12374690	G7197 SCVi XXL D ED230 1,9 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12374700	G7731 SCi D OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12374870	G7737 SCi XXL D OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428750	DAD4841 XD1/D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12289640	DGM7440 UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289650	DGM7440 UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289660	DGM7840 UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289670	DGM7840 UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289700	DGM7840 UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289720	DGM7840 UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
8126190	Burner tap 0,52	Burner tap 0,52	Lead	7439-92-1
12302200	CS1012-2 G KW EDST 220/50 STORNO	Sealing ring 7,65x1,78	Lead	7439-92-1
12302200	CS1012-2 G KW EDST 220/50 STORNO	Jet 0,27MM	Lead	7439-92-1
12302200	CS1012-2 G KW EDST 220/50 STORNO	Jet 0,32MM	Lead	7439-92-1
12302200	CS1012-2 G KW EDST 220/50 STORNO	Burner tap 0,52	Lead	7439-92-1
12271740	PDR910 EL NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12289560	DG2840 UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289570	DG7240 UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289580	DG7440 UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289590	DG7440 UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289600	DG7440 UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289610	DG7440 UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12010050	PDR514ROP G AUS IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12010060	PDR522ROP G AUS IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12010080	PDR544ROP G AUS IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12010100	PDR944 G AUS IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12271750	PDR910 G NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12382740	KM7466 FR ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12097940	DGC7840 HCX Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097960	DGC7840 HCX Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097970	DGC7860 HC Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097980	DGC7860 HC Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12098000	DGC7860 HC Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12098020	DGC7860 HC Pro RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12098030	DGC7860 HCX Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12098060	DGC7860 HCX Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12098080	DGC7860 HCX Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12310230	DGC7840 HCX Pro GB OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12310260	DGC7845 HCX Pro GB OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12310270	DGC7860 HCX Pro GB OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12310280	DGC7865 HCX Pro GB OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326430	DGC7845 HCX Pro AUS OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12327440	DGC7440 HCX Pro UA OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12327500	DGC7460 HCX Pro UA OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12327510	DGC7840 HCX Pro UA OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12327520	DGC7860 HCX Pro UA OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12346520	DGC7840 HCX Pro CH OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12346540	DGC7860 HCX Pro CH OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12354380	H2466BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12354380	H2466BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12276850	KMDA7676 FL-A ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12276860	KMDA7676 FL-U ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10884759	Power-/Control unit ELP 7482	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12097600	DGC7440 HC Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097610	DGC7440 HC Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097620	DGC7440 HC Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097630	DGC7440 HC Pro RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097640	DGC7440 HCX Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097650	DGC7440 HCX Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097660	DGC7440 HCX Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097670	DGC7460 HC Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097700	DGC7460 HC Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097710	DGC7460 HC Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097730	DGC7460 HC Pro RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097780	DGC7460 HCX Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097790	DGC7460 HCX Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097800	DGC7460 HCX Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097810	DGC7640 HC Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097820	DGC7640 HC Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097830	DGC7640 HC Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097840	DGC7640 HC Pro RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097850	DGC7840 HC Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097860	DGC7840 HC Pro RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097870	DGC7840 HC Pro RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097900	DGC7840 HC Pro RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097920	DGC7840 HCX Pro RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12341330	PDR909 EL CP SOM SST B03Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260370	PDR516ROP SL G NWE IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260460	PDR516ROP SL G NWE IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260510	PDR516COP SL G NWE IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260550	PDR516COP SL G NWE IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260560	PDR516TOP SL G NWE IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260570	PDR516TOP SL G NWE IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260580	PDR511ROP SL HP NWE IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12260590	PDR511ROP SL HP NWE IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12295750	PDR511COP SL HP NWE IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12295760	PDR511COP SL HP NWE IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12261470	PDR516ROP SL EL SEE IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12261480	PDR516ROP SL EL SEE IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12261490	PDR516COP SL EL SEE IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12261820	PDR516COP SL EL SEE IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12261870	PDR516TOP SL EL SEE IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12261930	PDR516TOP SL EL SEE IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12261980	PDR516ROP SL G SEE IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262030	PDR516ROP SL G SEE IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262090	PDR516COP SL G SEE IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262140	PDR516COP SL G SEE IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262190	PDR516TOP SL G SEE IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262250	PDR516TOP SL G SEE IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12262310	PDR511ROP SL HP SEE IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12262330	PDR511ROP SL HP SEE IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12341280	PDR909 EL CP SOM SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12341310	PDR909 EL CP SOM SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259760	PDR516ROP SL EL DAC IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259770	PDR516ROP SL EL DAC IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259780	PDR516COP SL EL DAC IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259790	PDR516COP SL EL DAC IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259800	PDR516TOP SL EL DAC IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259810	PDR516TOP SL EL DAC IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259820	PDR516ROP SL G DAC IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259830	PDR516ROP SL G DAC IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259840	PDR516COP SL G DAC IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259850	PDR516COP SL G DAC IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259860	PDR516TOP SL G DAC IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259870	PDR516TOP SL G DAC IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12259880	PDR511ROP SL HP DAC IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12259890	PDR511ROP SL HP DAC IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12295710	PDR511COP SL HP DAC IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12295720	PDR511COP SL HP DAC IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12260090	PDR516ROP SL EL NWE IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260110	PDR516ROP SL EL NWE IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260130	PDR516COP SL EL NWE IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260190	PDR516COP SL EL NWE IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260240	PDR516TOP SL EL NWE IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12260310	PDR516TOP SL EL NWE IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12383040	KMDA7876 FL-U ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12424600	G7180 SCVi A ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424620	G7185 SCVi XXL A ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424630	G7210 SC A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424640	G7210 SC A ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424650	G7210 SCU A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424660	G7210 SCU A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424680	G7210 SCi A OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424690	G7210 SCi A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424720	G7210 SCi A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424740	G7215 SCi XXL A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424760	G7260 SCVi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12424780	G7265 SCVi XXL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424790	G7380 SCVi A ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424800	G7385 SCVi XXL A ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424820	G7600 SC A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424830	G7600 SC A ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424840	G7600 SCU A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424850	G7600 SCU A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424860	G7600 SCi A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424880	G7600 SCi A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424890	G7605 SCi XXL A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424900	G7650 SCVi A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424910	G7655 SCVi XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424930	G7710 SCi A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12419010	G7185 SCVi XXL IB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12381780	DG7141 C XC1/CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12419020	G7380 SCVi IB ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12381820	DGM7341 C XC1/CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12419030	G7600 SC IB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12419040	G7600 SC IB ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12419050	G7650 SCVi IB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12419060	G7655 SCVi XXL IB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12411090	KM7576-2 FL ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12411090	KM7576-2 FL ANL 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12419070	G7790 SCVi IB OS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12419080	G7980 SCVi IB OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12419090	G7985 SCVi XXL IB OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424440	G7130 SC A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424460	G7130 SC A ED230 1,9 CLST Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424480	G7130 SCU A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424500	G7130 SCU A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424530	G7130 SCi A BW230 1,9 Auto Dos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12298850	HR1422-3 I USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
12298850	HR1422-3 I USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
12298850	HR1422-3 I USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12424550	G7130 SCi A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424580	G7135 SCi XXL A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424590	G7135 SCi XXL A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424950	G7715 SCi XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440190	G7130 SC OE1 ED230 1,9 AutoD CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12342040	DAH4970 XD1/D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342080	DAH4970 XD1/D CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12440200	G7130 SCi OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12341870	DAH1850 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12341890	DAH1950 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12440210	G7135 SCi XXL OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12440220	G7180 SCVi OE1 ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12341980	DAH2860 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12342000	DAH2960 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12440230	G7185 SCVi XXL OE1 ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12342160	DAH2960EXTA XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12342020	DAH4870 XD1/D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342030	DAH4870 XD1/D GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342070	DAH4870 XD1/D PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342060	DAH4870 XD1/D CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342180	DAH4880 XD1/D OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342050	DAH4970 XD1/D GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342090	DAH4970 XD1/D PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12342190	DAH4980 XD1/D OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12428770	H2465B D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12428770	H2465B D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12428860	H2465BP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12428860	H2465BP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12424960	G7760 SCVi A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424970	G7765 SCVi XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424980	G7783 SCVi A OS230 1,9 k2o AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12424990	G7788 SCVi XXL A OS230 1,9 K2O AutoD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12425000	G7790 SCVi A OS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12425020	G7795 SCVi XXL A OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12425030	G7930 SCi A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12425040	G7935 SCi XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12425050	G7980 SCVi A OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12425060	G7985 SCVi XXL A OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12443170	G7190 SCVi A ED230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420630	G17600 SC CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420640	G17600 SCi CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420660	G17600 SCi CH ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420690	G17623 SCi CH ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420670	G17623 SCi CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420710	G17650 SCVi CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420720	G17673 SCVi CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420740	G17710 SCi CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420750	G17783 SCVi CH OS230 1,9 K2O AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12420840	G17790 SCVi CH OS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12341850	DAH1650 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12341910	DAH2660 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12440160	G7130 SC OE1 BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12326150	H2761-1BP XE1/D EDST/CLST 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326230	H2861-1BP XE1/D EDST/CLST 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326230	H2861-1BP XE1/D EDST/CLST 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326260	H2861-1BP XE1/D OBSW 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326260	H2861-1BP XE1/D OBSW 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326170	H2766-1BP XE1/D OBSW 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326170	H2766-1BP XE1/D OBSW 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326250	H2861-1BP XE1/D GRGR 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326250	H2861-1BP XE1/D GRGR 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
11844914	Power-/Control unit ELP 7442-A 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12446040	Power-/Control unit ELP 7442 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11570183	Power-/Control unit ELP 7784 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
12305060	H7440BPX D OBSW/MATT 230/50	Heater element Top heat 230V	Lead	7439-92-1
12305090	H7840BPX D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305080	H7464BPX D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305110	H7860BPX D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12420480	G5161 SCVI F ED230 1,9 DUOCLEAN	Drain pump 220-240V 50HZ	Lead	7439-92-1
12305070	H7440BMX D OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12305100	H7840BMX D OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12305140	H7440BPX F OBSW/MATT 230/50	Heater element Top heat 230V	Lead	7439-92-1
12305180	H7840BPX F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305170	H7464BPX F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305160	H7440BMX F OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12305190	H7840BMX F OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12383050	KMDA7876 FL-A ANL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12421750	H2467B AUS OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12421750	H2467B AUS OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12421760	H2467BP AUS OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12421760	H2467BP AUS OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12421710	H2756B AUS OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12421710	H2756B AUS OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12382800	KM7466 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12382790	KM7466 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12383060	KMDA7876 FL-U R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12383070	KMDA7876 FL-A R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12383080	KMDA7876 FL-U R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12383090	KMDA7876 FL-A R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12326140	H2761-1B XE1/D EDST/CLST 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326140	H2761-1B XE1/D EDST/CLST 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326180	H2861-1B XE1/D EDST/CLST 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326180	H2861-1B XE1/D EDST/CLST 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326210	H2861-1B XE1/D OBSW 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326210	H2861-1B XE1/D OBSW 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326160	H2766-1B XE1/D OBSW 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326160	H2766-1B XE1/D OBSW 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326190	H2861-1B XE1/D GRGR 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12326190	H2861-1B XE1/D GRGR 230/50 Air Fry	Heater element Top heat 230V	Lead	7439-92-1
12326150	H2761-1BP XE1/D EDST/CLST 230/50 Air Fry	Heater element Unterhitze 230-240V	Lead	7439-92-1
12310180	H7860BPX GB OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12428820	DAD4941 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12429400	DAD4841 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12429500	DAD4941 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12440700	DAD4841 GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12440710	DAD4841 C CN OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12438820	KMDA7676 FL-A R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12438830	KMDA7676 FL-U R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12440720	DAD4841 AUS OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12382880	KM7576 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12382880	KM7576 FL D 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12440730	DAD4941 AUS OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12392830	KM7746 FL USA 208/240/60 STORNO	Induction coil G5 Octa OL L250	Lead	7439-92-1
12438870	KMDA7676 FL-A R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12438890	KMDA7676 FL-U R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12383100	KMDA7876 FL-U D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10749580	DA4298W D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12456400	DA SOAF Virtual Test Device	SMD- Diode STTH1R04A	Lead	7439-92-1
12383110	KMDA7876 FL-A D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12418970	G7130 SC IB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12418980	G7130 SC IB ED230 1,9 AutoDos CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12418990	G7130 SCi IB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12438930	KMDA7676 FL-U D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12438920	KMDA7676 FL-A D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12419000	G7180 SCVI IB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12310190	H7840BMX GB OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12317160	H7440BPX NER OBSW/MATT 230/50	Heater element Top heat 230V	Lead	7439-92-1
12382810	KM7466 FR D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12317190	H7840BPX NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12382820	KM7466 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12317180	H7464BPX NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12317210	H7860BPX NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12317170	H7440BMX NER OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12317200	H7840BMX NER OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12326470	H7440BPX EU1 OBSW/MATT 230/50	Heater element Top heat 230V	Lead	7439-92-1
12326510	H7840BPX EU1 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326490	H7464BPX EU1 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326530	H7860BPX EU1 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326520	H7840BMX EU1 OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12326480	H7440BMX EU1 OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12326420	H7860BPX AUS OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326410	H7840BMX AUS OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12346450	H7840BPX CH OBSW/MATT 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12346500	H7860BPX CH OBSW/MATT 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12346500	H7860BPX CH OBSW/MATT 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12346470	H7840BMX CH OBSW/MATT 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12406440	H7565BP SEE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12392820	KM7746 FL AN3 208/240/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
12428800	DAD4841 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12426810	G7783 SCVI NER OS230 1,9 k2o AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
11108830	H7840BP F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108820	H7440BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108810	H7840BP F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108840	H7840BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108890	H7840BPX F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108910	H7840BPX F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108570	H7440BPX F GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108560	H7440BPX F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108550	H7440BPX F BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108490	H7264BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108480	H7264BP F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108470	H7264BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108920	H7840BPX F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129690	H2265-1B NER EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129690	H2265-1B NER EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11129710	H2267-1B NER EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129710	H2267-1B NER EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11129700	H2265-1BP NER EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129700	H2265-1BP NER EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11129720	H2267-1BP NER EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129720	H2267-1BP NER EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11129730	H2760B NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129730	H2760B NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129770	H2860B NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11182920	H2266-1E D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11182940	H2266-1EP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11182940	H2266-1EP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11182950	H2266-1I D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11182950	H2266-1I D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11182960	H2268-1E D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11182960	H2268-1E D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11182970	H2268-1EP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11182970	H2268-1EP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11182980	H2266-1B D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11182980	H2266-1B D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11183000	H2266-1BP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11183000	H2266-1BP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11183010	H2268-1B D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11183010	H2268-1B D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11183020	H2268-1BP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11183020	H2268-1BP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11108360	H7164BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108410	H7244BP F BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108420	H7244BP F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108430	H7244BP F GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108440	H7244BP F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108450	H7260BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108460	H7264BP F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129770	H2860B NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110280	H2850B B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110280	H2850B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110260	H2840B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110240	H2760BP B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110240	H2760BP B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110380	H2860BP B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110380	H2860BP B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110300	H2850BP B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110300	H2850BP B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110320	H2860B EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110320	H2860B EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110340	H2860B EU1 GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110340	H2860B EU1 GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110360	H2860BP EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110360	H2860BP EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110370	H2860BP EU1 GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110370	H2860BP EU1 GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11115760	H2265-1IP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11115760	H2265-1IP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11115770	H2267-1BP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11115770	H2267-1BP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11115780	H2850B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11115780	H2850B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11115790	H2850BP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129750	H2860B NER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129750	H2860B NER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129760	H2860B NER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129760	H2860B NER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129740	H2760BP NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129740	H2760BP NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129810	H2860BP NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129810	H2860BP NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129780	H2860BP NER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129780	H2860BP NER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129790	H2860BP NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129790	H2860BP NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129800	H2860BP NER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129800	H2860BP NER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11109800	H7161BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110190	H2265-1B B EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110190	H2265-1B B EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11110210	H2265-1BP B EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110210	H2265-1BP B EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11108760	H7640BP F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110230	H2760B B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110230	H2760B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110350	H2860B B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11110350	H2860B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104030	H7164B D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104210	H7264B D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104180	H7264B D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104190	H7264B D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104200	H7264B D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104130	H7244B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104100	H7244B D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104110	H7244B D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104120	H7244B D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104170	H7244BP D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104140	H7244BP D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104150	H7244BP D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104160	H7244BP D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11105650	H7460B D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104420	H7460B D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104430	H7460B D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105640	H7460B D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104310	H7440B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104280	H7440B D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104290	H7440B D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104300	H7440B D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104370	H7440BPX D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104360	H7440BPX D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104380	H7440BPX D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103860	H2267-1EP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103880	H2267-1IP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103880	H2267-1IP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103970	H2860B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103970	H2860B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103930	H2860B D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103930	H2860B D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103950	H2860B D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103950	H2860B D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103960	H2860B D GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103960	H2860B D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103900	H2760B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103900	H2760B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103920	H2840B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104010	H2860BP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11104010	H2860BP D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103980	H2860BP D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103980	H2860BP D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103990	H2860BP D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103990	H2860BP D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11104000	H2860BP D GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11104000	H2860BP D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11103910	H2760BP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103910	H2760BP D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11105920	H7840BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093490	H7260BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093500	H7264BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108040	H2265-1B F EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108040	H2265-1B F EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11108060	H2267-1B F EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108060	H2267-1B F EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11108050	H2265-1BP F EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108050	H2265-1BP F EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11108250	H2267-1BP F EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108250	H2267-1BP F EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11108280	H2850B F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108280	H2850B F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108270	H2840B F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108330	H2860BP F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108330	H2860BP F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108300	H2860BP F BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108300	H2860BP F BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108310	H2860BP F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108310	H2860BP F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108320	H2860BP F GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108320	H2860BP F GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108290	H2850BP F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108290	H2850BP F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11182920	H2266-1E D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11105890	H7840BP D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105900	H7840BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105910	H7840BP D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105980	H7840BPX D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105970	H7840BPX D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105990	H7840BPX D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11092980	H2265-1B GB EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11092980	H2265-1B GB EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11092990	H2265-1BP GB EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11092990	H2265-1BP GB EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11093000	H2267-1BP GB EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11093000	H2267-1BP GB EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11093330	H2860B GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11093330	H2860B GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11093010	H2760B GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11093010	H2760B GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11093310	H2850B GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11093310	H2850B GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11093350	H2860BP GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11093350	H2860BP GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11093020	H2760BP GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11093020	H2760BP GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11093420	H7164B GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093450	H7164BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11115790	H2850BP D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129400	H2860BP IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129320	H2860B SER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129320	H2860B SER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129330	H2860B SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129330	H2860B SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129370	H2860BP SER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129370	H2860BP SER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129380	H2860BP SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129380	H2860BP SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129390	H2860BP SER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129390	H2860BP SER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129510	H7164B IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129540	H7264B SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129520	H7164BP IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129560	H7264BP IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106520	DGM7440 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106530	DGM7440 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130460	H7440BPX NER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129340	H2860B SER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129340	H2860B SER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129550	H7264B IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130440	H7440BPX NER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11130450	H7440BPX NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11098690	H7264B TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10938030	DGM7645 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10936880	DGM7840 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10936890	DGM7640 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10936900	DGM7440 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150870	H2266-1B NER EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11150870	H2266-1B NER EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11150990	H7160BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150960	H2751BP NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11150960	H2751BP NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11150980	H2752BP NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11150980	H2752BP NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11151010	H7163BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129280	H2265-1B IB EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129280	H2265-1B IB EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11129300	H2267-1B IB EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129300	H2267-1B IB EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11129290	H2265-1BP IB EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11129290	H2265-1BP IB EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11129310	H2267-1BP IB EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129310	H2267-1BP IB EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11129420	H2840B IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129360	H2860B IB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11129360	H2860B IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11129400	H2860BP IB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11098710	H7460B TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937010	DGM7845 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937020	DGM7845 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10936960	DGM7840 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10938010	DGM7645 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121000	H7840BP SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121010	H7840BP SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121040	H7840BPX SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121050	H7840BPX SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121060	H7840BPX SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132830	DGM7340 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132840	DGM7440 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133040	DGM7440 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133050	DGM7440 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133060	DGM7640 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133070	DGM7640 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133080	DGM7640 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133120	DGM7840 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133130	DGM7840 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133140	DGM7840 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135470	DGM7440 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135480	DGM7440 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135490	DGM7440 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135500	DGM7440 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135510	DGM7640 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11098700	H7264BP TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11098640	H2265-1B TR EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11098640	H2265-1B TR EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11098650	H2265-1BP TR EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11098650	H2265-1BP TR EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11098660	H2860B TR EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11098660	H2860B TR EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11098670	H2860BP TR EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11098670	H2860BP TR EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11120540	H7264BP SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120550	H7264BP SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120560	H7264BP SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11136390	H7260B GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120570	H7440B SER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11120580	H7440B SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11120590	H7440B SER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11120640	H7460B SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120650	H7460B SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120660	H7460B SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120610	H7440BPX SER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11120620	H7440BPX SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11120630	H7440BPX SER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11120990	H7840BP SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430170	DGM7340 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099420	H2265-1BP NL EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11099420	H2265-1BP NL EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11099430	H2267-1BP NL EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11099430	H2267-1BP NL EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11099500	H7164B NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099630	H7264B NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099600	H7244B NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099580	H7244B EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099590	H7244B EU1 GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099610	H7260B NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099620	H7260BP NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099510	H7164BP NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099680	H7264BP NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099650	H7264BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099660	H7264BP EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099730	H7440B EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099740	H7440B EU1 GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099750	H7440B NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099830	H7440BPX EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099840	H7440BPX EU1 GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110720	H7840BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110460	H7244B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110490	H7244BP B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110410	H7164B B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11115800	H7260B D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108260	H2760BP F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108260	H2760BP F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11115810	H7260BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11099440	H2760B NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11099440	H2760B NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099460	H2860B NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11099460	H2860B NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099450	H2760BP NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11099450	H2760BP NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11099470	H2860BP NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11099470	H2860BP NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11187330	H7360B D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130070	H7164BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130080	H7260BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130120	H7264BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130090	H7264BP NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130100	H7264BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130110	H7264BP NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130290	H7840BPX NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130300	H7840BPX NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130310	H7840BPX NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099410	H2265-1B NL EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11099410	H2265-1B NL EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11110570	H7264B B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430210	DGM7440 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430190	DGM7440 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430200	DGM7440 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10677980	DGM7640 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10678010	DGM7440 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937190	DGM7440 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937200	DGM7440 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937210	DGM7440 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101530	H7840BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937220	DGM7440 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937230	DGM7340 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101540	H7840BP EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937100	DGM7640 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101550	H7840BP NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937120	DGM7640 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101590	H7840BPX EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937130	DGM7640 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101600	H7840BPX EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937180	DGM7640 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937040	DGM7845 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10936920	DGM7840 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10936930	DGM7840 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10938000	DGM7645 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10938020	DGM7645 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110500	H7260B B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110420	H7164BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110580	H7264BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110510	H7260BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110470	H7244BP EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110480	H7244BP EU1 GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110520	H7264B EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110550	H7264B EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110610	H7440B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11110650	H7460B B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430260	DGM7840 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430290	DGM7840 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430270	DGM7840 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430300	DGM7845 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430330	DGM7845 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430310	DGM7845 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10677950	DGM7840 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110630	H7460B EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430220	DGM7640 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110640	H7460B EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430250	DGM7640 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430230	DGM7640 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430240	DGM7640 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430180	DGM7440 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12428440	G7678 SCVi XXL F OS230 1,9 AutoD Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428430	G7673 SCVi F OS230 1,9 AutoDos Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12435810	H2766-1B I OBSW 125 Edition 230/50 <3kW	Heater element Top heat 230V	Lead	7439-92-1
12428450	G7760 SCVi F OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428470	G7765 SCVi XXL F OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428480	G7785 SCVi XXL F OS230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12435810	H2766-1B I OBSW 125 Edition 230/50 <3kW	Heater element Unterhitze 230-240V	Lead	7439-92-1
12428420	G7655 SCVi XXL F OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12435820	H2861-1B I EDST/CLST125Edition230/50<3kW	Heater element Top heat 230V	Lead	7439-92-1
12435820	H2861-1B I EDST/CLST125Edition230/50<3kW	Heater element Unterhitze 230-240V	Lead	7439-92-1
12428410	G7650 SCVi F OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12509590	KMDA7676 FL-A CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12428500	G7790 SCVi F OS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428510	G7795 SCVi XXL F OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428530	G7930 SCi F OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12428540	G7980 SCVi F OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428560	G7985 SCVi XXL F OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12509540	KMDA7676 FL-A NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12509550	KMDA7676 FL-U NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12427790	G7130 SC TR ED230 1,9 AutoDos CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12415530	H2455B TW OBSW/EDST-LOOK 220/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12427810	G7130 SCi TR ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12453490	H2455B NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12453490	H2455B NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12428150	G7130 SCi F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452980	G7788 SCVi XXL MER OS230 1,9 K2OAutoD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452990	G7790 SCVi MER OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12453000	G7795 SCVi XXL MER OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12453010	G7935 SCi XXL MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12453030	G7980 SCVi MER OS/CS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428160	G7180 SCVi F ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12453080	G7985 SCVi XXL MER OS/CS230 1,9 K2O AD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428170	G7185 SCVi XXL F ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428180	G7190 SCVi F ED230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428190	G7195 SCVi XXL F ED230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428200	G7210 SC F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428210	G7210 SC F ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428300	G7210 SCi F OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428310	G7210 SCi F ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428320	G7260 SCVi F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428330	G7265 SCVi XXL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428340	G7293 SCVi F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428350	G7298 SCVi XXL F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428360	G7600 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428370	G7600 SCU F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428380	G7600 SCi F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428390	G7623 SC F BW230 1,9 AutoDos Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428400	G7623 SC F ED230 1,9 AutoDos CLST Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12453600	H2455BP NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401540	H2456E D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401540	H2456E D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401560	H2458E D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401560	H2458E D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12401570	H2458EP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12401570	H2458EP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12451550	H2455E USA OBSW 120/208/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12451550	H2455E USA OBSW 120/208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12451560	H2455E USA OBSW 120/240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12451560	H2455E USA OBSW 120/240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12410140	H2457B GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12410140	H2457B GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12410150	H2457BP GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12410150	H2457BP GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12403040	H2455B KZ OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12403040	H2455B KZ OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12403060	H2455BP KZ OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12403060	H2455BP KZ OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12460060	DAS4631 UA OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12428020	G7600 SC TR ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428030	G7600 SCi TR ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428040	G7710 SCi TR OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428050	G7795 SCVi XXL TR OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12462750	G7210 SC ZA BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12453600	H2455BP NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12453610	H2456B NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12453610	H2456B NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12453620	H2456BP NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12453620	H2456BP NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12453630	H2457B NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12453630	H2457B NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12453640	H2457BP NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12453640	H2457BP NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12427980	G7180 SCVi TR ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12427990	G7185 SCVi XXL TR ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428010	G7260 SCVi TR ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12451600	H2455I USA OBSW 120/208/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12451600	H2455I USA OBSW 120/208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12451700	H2455E CDN OBSW 120/208/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12451700	H2455E CDN OBSW 120/208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12451710	H2455E CDN OBSW 120/240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12451710	H2455E CDN OBSW 120/240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12451610	H2455I USA OBSW 120/240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12451610	H2455I USA OBSW 120/240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12451620	H2455B USA OBSW 120/208/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12451620	H2455B USA OBSW 120/208/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12451630	H2455B USA OBSW 120/240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12451630	H2455B USA OBSW 120/240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12481310	H2465B F OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12481310	H2465B F OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12481320	H2465BP F OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12481320	H2465BP F OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12481330	H2467BP F OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12481330	H2467BP F OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12460010	H2455BP GB OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12460010	H2455BP GB OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12426870	G7132 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426890	G7132 SCU NER ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426900	G7181 SCVi NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452200	G7130 SC MER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452210	G7180 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452220	G7181 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452230	G7182 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452240	G7185 SCVi XXL MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452250	G7187 SCVi XXL MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452260	G7188 SCVi XXL MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472380	H2465B NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12472380	H2465B NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12472390	H2467B NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12472390	H2467B NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12472400	H2465BP NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12472400	H2465BP NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12426820	G7788 SCVi XXL NER OS230 1,9 K20AutoD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426840	G7790 SCVi NER OS230 1,9 K20 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12426850	G7795 SCVi XXL NER OS230 1,9 K20 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459980	DAS4631 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12459990	DAS4931 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12426860	G7985 SCVi XXL NER OS/CS230 1,9 K20 AD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12395250	H2456-55E CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12395250	H2456-55E CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12395250	H2456-55E CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12395240	H2456-55E CH BRWS 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12395240	H2456-55E CH BRWS 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12395240	H2456-55E CH BRWS 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12395270	H2456-55EP CH BRWS 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12395270	H2456-55EP CH BRWS 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12395270	H2456-55EP CH BRWS 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12395280	H2456-55EP CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12395280	H2456-55EP CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12395280	H2456-55EP CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12446310	H2456-55B CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12446310	H2456-55B CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12446310	H2456-55B CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12446320	H2456-55BP CH OBSW 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
12446320	H2456-55BP CH OBSW 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
12446320	H2456-55BP CH OBSW 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
12472420	H2466BP NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11985102	Power-/Control unit ELP 7755 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11612856	Power-/Control unit ELP 7757 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10921088	Power-/Control unit ELP 7792 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10921008	Power-/Control unit ELP 7794 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12452750	G7298 SCVi XXL MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452770	G7380 SCVi MER ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452790	G7385 SCVi XXL MER ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452830	G7600 SCi MER ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452840	G7623 SCi MER ED230 1,9 Ados CLST Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12484700	KM7466 FR NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12484720	KM7466 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12452870	G7650 SCVi MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452890	G7672 SCVi MER OS230 1,9 AutoDos Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452900	G7673 SCVi MER OS230 1,9 AutoDos Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452880	G7655 SCVi XXL MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452910	G7677 SCVi XXL MER OS230 1,9 AD Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452920	G7678 SCVi XXL MER OS230 1,9 Ados Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452940	G7715 SCi XXL MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452950	G7760 SCVi MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428120	G7130 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452960	G7765 SCVi XXL MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452970	G7785 SCVi XXL MER OS230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428130	G7130 SC F ED230 1,9 CLST Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428140	G7130 SCi F BW230 1,9 Auto Dos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472420	H2466BP NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12472430	H2467BP NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12472430	H2467BP NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12472440	H2469BP NER OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12472440	H2469BP NER OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12452350	G7210 SC MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452400	G7210 SCU MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452420	G7210 SCU MER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452440	G7210 SCi MER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452570	G7232 SC MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452590	G7232 SCU MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452600	G7232 SCi MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452610	G7233 SC MER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12452620	G7233 SCU MER ED230 1,9 CLST Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452630	G7233 SCI MER ED230 1,9 CLST Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452640	G7260 SCVi MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452710	G7292 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452720	G7293 SCVi MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452690	G7265 SCVi XXL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10920988	Power-/Control unit ELP 7751 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12452740	G7297 SCVi XXL MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12511890	Power-/Control unit ELP 7752 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12511990	Power-/Control unit ELP 7753 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11985092	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12428060	G7935 SCi XXL TR OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10552470	H7264B ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10552470	H7264B ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10552470	H7264B ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10684730	H2265B SA EDST/CLST 220/60 ACTIVE	Temperature regul. Sub-assembly	Lead	7439-92-1
10780610	H7260B ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780610	H7260B ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780610	H7260B ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780620	H7260BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780620	H7260BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780620	H7260BP ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10616380	H2265I CDN EDST/CLST 208/60	Temperature regul. Sub-assembly	Lead	7439-92-1
10616380	H2265I CDN EDST/CLST 208/60	Heater element Bottom heat	Lead	7439-92-1
10616390	H2265I CDN EDST/CLST 240/60	Temperature regul. Sub-assembly	Lead	7439-92-1
10616390	H2265I CDN EDST/CLST 240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
10430280	DGM7840 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430320	DGM7845 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780630	H7164BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780630	H7164BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780630	H7164BP ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780650	H7264BP ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780650	H7264BP ANL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780650	H7264BP ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780660	H7264BP ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780660	H7264BP ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
10400210	H7264BP ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10585650	H2265B D EDST/CLST 230/50 Active	Temperature regul. Sub-assembly	Lead	7439-92-1
10585650	H2265B D EDST/CLST 230/50 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10586690	H2265E D EDST/CLST 230/50 Active	Temperature regul. Sub-assembly	Lead	7439-92-1
10586690	H2265E D EDST/CLST 230/50 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10586080	H2267BP ROK EDST/CLST 220/60 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10585890	H2267B ROK EDST/CLST 220/60 Active	Temperature regul. Sub-assembly	Lead	7439-92-1
10585890	H2267B ROK EDST/CLST 220/60 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10599390	H2265B C CN EDST/CLST 220/50 Active	Temperature regul. Sub-assembly	Lead	7439-92-1
10471960	Regulator Zweikreis 208V	Regulator Zweikreis 208V	Lead	7439-92-1
10471960	Regulator Zweikreis 208V	Regulator Zweikreis 208V	Lead	7439-92-1
10471970	Regulator Einkreis 208V	Regulator Einkreis 208V	Lead	7439-92-1
10471970	Regulator Einkreis 208V	Regulator Einkreis 208V	Lead	7439-92-1
10499470	H2265E CDN EDST/CLST 208/60	Temperature regul. Sub-assembly	Lead	7439-92-1
10499470	H2265E CDN EDST/CLST 208/60	Heater element Bottom heat	Lead	7439-92-1
10499490	H2265B CDN EDST/CLST 208/60	Temperature regul. Sub-assembly	Lead	7439-92-1
10499490	H2265B CDN EDST/CLST 208/60	Heater element Bottom heat	Lead	7439-92-1
10499480	H2265E CDN EDST/CLST 240/60	Temperature regul. Sub-assembly	Lead	7439-92-1
10499480	H2265E CDN EDST/CLST 240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
10499500	H2265B CDN EDST/CLST 240/60	Temperature regul. Sub-assembly	Lead	7439-92-1
10499500	H2265B CDN EDST/CLST 240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
10562790	H2265B TW EDST/CLST 220/60 Active	Temperature regul. Sub-assembly	Lead	7439-92-1
10608750	H2265B J EDST/CLST 200/50 Active	Temperature regul. Sub-assembly	Lead	7439-92-1
10608750	H2265B J EDST/CLST 200/50 Active	Heater element Bottom heat	Lead	7439-92-1
10780660	H7264BP ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11119610	H2265-1B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103790	H2265-1B D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103790	H2265-1B D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103890	H2267-1B D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103890	H2267-1B D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103710	H2265-1E D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103710	H2265-1E D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103700	H2265-1E D BRWS 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103700	H2265-1E D BRWS 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103690	H2265-1E D HVBR 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103690	H2265-1E D HVBR 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103850	H2267-1E D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103850	H2267-1E D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103870	H2267-1I D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103870	H2267-1I D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103810	H2265-1BP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103810	H2265-1BP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103740	H2265-1EP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103740	H2265-1EP D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103730	H2265-1EP D BRWS 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103730	H2265-1EP D BRWS 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103720	H2265-1EP D HVBR 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103720	H2265-1EP D HVBR 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11103860	H2267-1EP D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780690	H7440B ANL BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780800	H7840BP ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780810	H7840BP ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780840	H7840BPX ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780700	H7440BPX ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
10900370	H2265-1B ANL EDST/CLST 230/50 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10900370	H2265-1B ANL EDST/CLST 230/50 Active	Heater element Top heat 230V	Lead	7439-92-1
10900510	H2265-1BP ANL EDST/CLST 230/50 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10900510	H2265-1BP ANL EDST/CLST 230/50 Active	Heater element Top heat 230V	Lead	7439-92-1
10900600	H2267-1BP ANL EDST/CLST 230/50 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10900600	H2267-1BP ANL EDST/CLST 230/50 Active	Heater element Top heat 230V	Lead	7439-92-1
10900540	H2265-1EP ANL EDST/CLST 230/50 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10900540	H2265-1EP ANL EDST/CLST 230/50 Active	Heater element Top heat 230V	Lead	7439-92-1
10901380	H2267-1IP ANL EDST/CLST 230/50 Active	Heater element Unterhitze 230-240V	Lead	7439-92-1
10901380	H2267-1IP ANL EDST/CLST 230/50 Active	Heater element Top heat 230V	Lead	7439-92-1
10901400	H2860BP ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10901400	H2860BP ANL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
10937060	DGM7845 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10936990	DGM7840 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11042890	H2265-1B ANO EDST/CLST 240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11042890	H2265-1B ANO EDST/CLST 240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11042860	H2265-1I ANO EDST/CLST 240/60 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11042860	H2265-1I ANO EDST/CLST 240/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11119610	H2265-1B I EDST/CLST 230/50 <3KW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12500250	H7240BM UA EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12508700	H2457BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12508700	H2457BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11103780	H2265-1I D EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11103780	H2265-1I D EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11226390	HR1934-3 G DF AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11226390	HR1934-3 G DF AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11226390	HR1934-3 G DF AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11226400	HR1934-3 LP DF AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11226400	HR1934-3 LP DF AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11226400	HR1934-3 LP DF AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11226410	HR1935-3 G DF GR AN3 EDST/CLST120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11226410	HR1935-3 G DF GR AN3 EDST/CLST120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11226410	HR1935-3 G DF GR AN3 EDST/CLST120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11226420	HR1936-3 G DF GD AN3 EDST/CLST120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11226420	HR1936-3 G DF GD AN3 EDST/CLST120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11226420	HR1936-3 G DF GD AN3 EDST/CLST120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11226560	HR1936-3 LP DF GD AN3EDST/CLST120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11226560	HR1936-3 LP DF GD AN3EDST/CLST120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11226560	HR1936-3 LP DF GD AN3EDST/CLST120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11307690	DGC7865 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307600	DGC7860 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308110	DGC7785 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308130	DGC7780 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12462770	G7380 SCVi ZA ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12428070	G7985 SCVi XXL TR OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459740	G7130 SCi UA ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12506080	DA9299W D BLBO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12462780	G7600 SC ZA BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12462790	G7600 SC ZA ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459750	G7180 SCVi UA ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459780	G7260 SCVi UA ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459790	G7650 SCVi UA OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459800	G7710 SCi UA OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459810	G7783 SCVi UA OS230 1,9 k2o AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459820	G7790 SCVi UA OS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12170380	H2465B UA OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12170380	H2465B UA OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12170390	H2465BP UA OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12170390	H2465BP UA OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12459830	G7980 SCVi UA OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12170400	H2861B UA OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12170400	H2861B UA OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12170410	H2861BP UA OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12170410	H2861BP UA OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12170420	H2861B UA EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12170420	H2861B UA EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12459840	G7985 SCVi XXL UA OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11308190	DGC7585 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11796810	DGC7860 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11634880	DGC7665 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11634890	DGC7465 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11721510	DGC7465 HCX Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723050	DGC7465 HC Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723060	DGC7465 HC Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723090	DGC7665 HC Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723110	DGC7665 HC Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723160	DGC7865 HCX Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723230	DGC7865 HC Pro ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11723240	DGC7865 HC Pro ANC GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723270	DGC7865 HC Pro ANC OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11796830	DGC7860 HC Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10461524	Power electron.unit ELFU 3100	SMD- Diode STTH1R04A	Lead	7439-92-1
10874290	H7890BP AN7 EDST/CLST 200/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10874300	H7890BP AN8 EDST/CLST 200/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11129530	H7264B SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11179310	HR1622-3 I AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11179310	HR1622-3 I AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11179310	HR1622-3 I AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11208103	Power-/Control unit ELP 7770 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
10400260	H7440B ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10400210	H7264BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10400210	H7264BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11308240	DGC7580 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307280	DGC7880X AN3 GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308120	DGC7885 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308150	DGC7880 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308160	DGC7880 AN3 OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308170	DGC7880 AN3 BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308180	DGC7880 AN3 GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308210	DGC7685 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308250	DGC7680 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307630	DGC7860 AN3 OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307640	DGC7860 AN3 BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307650	DGC7860 AN3 GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11634860	DGC7865 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11639030	DGC7865 HCX Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723040	DGC7465 HC Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723070	DGC7465 HCX Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723080	DGC7465 HCX Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723100	DGC7665 HC Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723120	DGC7865 HC Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723130	DGC7865 HC Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723140	DGC7865 HC Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723150	DGC7865 HCX Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723260	DGC7865 HC Pro ANC BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723320	DGC7860 HCX Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100700	DGC7845 HCX Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12852940	G7080 SCVi NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852680	G5836 SCU XXL NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12854910	PDR909WSC G CP GB IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12852690	G5836 SCU XXL NER ED230 1,9 Active Pl CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852950	G7083 SCVi NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11791540	HR1724-3 LP DF USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
12849470	G7040 SCU I ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849460	G7040 SC I ED230 1,9 AutoDos CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852740	G5842 SCU NER ED230 1,9 Active Plus CS S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852710	G5842 SCU NER BW230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852640	G5831 SCU NER ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852630	G5831 SCU NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11791540	HR1724-3 LP DF USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791540	HR1724-3 LP DF USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12852960	G7085 SCVi XXL NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852970	G7088 SCVi XXL NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849410	G5851 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849420	G5852 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849430	G5853 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12857500	PDR1909HP ANL NAM LW 2 AC 208/240V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
12849440	G5863 SCVi I ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852860	G7040 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852870	G7040 SCU NER ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852880	G7042 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852500	G5611 SCU NER ED230 1,9 Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852510	G5632 SCU NER BW230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852520	G5632 SCU NER ED230 1,9 Active CS S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852530	G5633 SCU NER BW230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852540	G5633 SCU NER ED230 1,9 Active CS E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852550	G5651 Vi NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852560	G5651 SCVi NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852570	G5656 SCVi XXL NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852580	G5662 SCVi NER ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852590	G5667 SCVi XXL NER ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852600	G5668 SCVi XXL NER ED230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12820830	DGC7440 HC Pro AUS PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12854940	PDR909WSC EL CP GB IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12852610	G5811 SCU NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852620	G5811 SCU NER ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849340	G5811 SCU I ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849330	G5811 SCU I OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849350	G5811 SCi I ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849360	G5833 SCU I ED230 1,9 Active Plus CS E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852650	G5832 SCU NER BW230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852670	G5832 SCU NER ED230 1,9 Active Plus CS S	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12849450	G7040 SC I BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852750	G5843 SCU NER BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852760	G5843 SCU NER ED230 1,9 Active Plus CS E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867930	G5632 SC MER ED230 1,9 Active CS Front S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867940	G5632 SCU MER ED230 1,9 Active CS S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867950	G5632 SCi MER ED230 1,9 Active CS S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867960	G5633 SC MER BW230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867970	G5633 SC MER ED230 1,9 Active CS Front E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12865880	PDR1509HP ANL MAR LW 1N AC 230V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
12885000	H7464BP D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12867980	G5651 Vi MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12874500	H7464BP GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12874490	H7440BM GB PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12821570	H7464BP EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12821580	H7440BM EU3 PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12821660	H7464BP NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12821670	H7440BM NER PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12867990	G5651 SCVi MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12868010	G5662 SCVi MER ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12868020	G5663 SCVi MER ED230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12868030	G5664 SCVi MER ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12868000	G5656 SCVi XXL MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12868040	G5667 SCVi XXL MER ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12868050	G5668 SCVi XXL MER ED230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12821470	H7460BP CH PEBE 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12821470	H7460BP CH PEBE 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12821470	H7460BP CH PEBE 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12852890	G7042 SCU NER ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849480	G7080 SCVi I ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12690140	BOM8330-60F XS3/CH EDLK 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12852900	G7043 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852910	G7043 SCU NER ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852920	G7048 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852770	G5851 SCVi NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852930	G7048 SCU XXL NER ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852780	G5856 SCVi XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852790	G5861 SCVi NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852800	G5862 SCVi NER ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852820	G5867 SCVi XXL NER ED230 1,9 Active Pl S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867840	G5611 MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852830	G5873 SCVi NER ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852850	G5896 SCVi XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867850	G5611 MER ED230 1,9 Active CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852840	G5878 SCVi XXL NER ED230 1,9 Active Pl E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867880	G5611 i MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867890	G5611 i MER ED230 1,9 Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867860	G5611 SC MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867870	G5611 SC MER ED230 1,9 Active CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867900	G5611 SCi MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867910	G5611 SCi MER ED230 1,9 CLST Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12867920	G5632 SC MER BW230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12820740	DGC7440 HC Pro CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12820750	DGC7460 HC Pro CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12867620	DG7440 D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12867630	DGC7440 HC Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12867640	DGC7460 HC Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12762640	OWD1232W D BL	Fitting OC Module	Lead	7439-92-1
12820320	DGC7440 HC Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12820360	DGC7460 HC Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12820370	DGC7440 HC Pro XS1/CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12820380	DGC7460 HC Pro XS1/CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12851130	G25656 Vi XXL CH ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12752720	PDR508HP P AUS LW 10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12752750	PDR908HP P AUS SST 10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12851150	G15811 i CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851160	G15811 i CH ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851140	G15811 i CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851210	G25817 i XXL CH ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851200	G25817 i XXL CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851180	G25817 i XXL CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851220	G15851 Vi CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851230	G25856 Vi XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851240	G25856 SCVi XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849170	G5611 i I ED230 1,9 Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849130	G5611 SC I BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845790	G5811 SC D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845800	G5811 SC D ED230 1,9 ActivePlus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845870	G5811 SCU D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845880	G5811 SCU D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845750	G5811 SCi D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845910	G5811 SCi D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12846050	G5811 SCi D OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845970	G5833 SC D BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12821370	H7460B XE1/D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12821390	H7440BM XE1/D PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12845980	G5833 SCU D ED230 1,9 Active Plus CS E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12821380	H7460BP XE1/D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12865900	H7464BP XE1/D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12845990	G5833 SCi D ED230 1,9 Active Plus CS E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845920	G5817 i XXL D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845930	G5817 SCi XXL D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12837340	G3725 SCi CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12837350	G3725 SCi CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12837360	G3725 SCi CH ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12837370	G3785 SCVi CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12820560	DG7440 XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12820730	DG7440 R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12820710	DGC7440 HC Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12820720	DGC7460 HC Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12849310	G5662 SCVi I ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849320	G5663 SCVi I ED230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849300	G5656 SCVi XXL I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12797720	PLW8604 EX3 SST PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12797780	PLW8604 EX3 SST ADP PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12800760	PLW8693 EX3 SST DS5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12800810	PLW8693 EX3 SST OIL DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12874470	DGC7440 HC Pro GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12874480	DGC7460 HC Pro GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12802250	DGC7440 HCX Pro AUS PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12802270	DGC7845 HCX Pro AUS PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12850720	PDR910WSC EL GB IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12799870	PLW8683CD EX3 LD DC5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12799920	PLW8683CD EX3 ADP LD DC5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12799960	PLW8683CD EX3 GD LD DC5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12850730	PDR910WSC G GB IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12800030	PLW8683CD EX3 OIL LD DC5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12857420	PDR1909HP ANL MAR LW 1N AC 230V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
12852480	G5611 SCU NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852450	G5611 U NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12798970	PLW8683 EX3 SST LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12799060	PLW8683 EX3 SST ADP LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12799130	PLW8683 EX3 SST OIL LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12799240	PLW8683 EX3 SST GD LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12849140	G5611 SC I ED230 1,9 Active CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849150	G5611 SCU I BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849160	G5611 SCU I ED230 1,9 CLST Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849180	G5611 SCi I ED230 1,9 Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12876790	DGC7440 HC Pro SER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12876800	DGC7460 HC Pro SER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12849210	G5633 SC I BW230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849220	G5633 SC I ED230 1,9 Active CS Front E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12872460	DGC7440 HC Pro NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12872470	DGC7460 HC Pro NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12849230	G5633 SCU I BW230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849240	G5633 SCU I ED230 1,9 Active CS E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12874350	DGC7440 HC Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12874360	DGC7460 HC Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12849250	G5651 Vi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12690021	Thermocouple Ceram surface burnr G32	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
12680901	Supply cable G32	Supply cable G32	Lead	7439-92-1
12821420	H7460B D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12821430	H7460BP D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12821440	H7440BM D PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12849260	G5651 SCVi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12849270	G5653 Vi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12800710	PLW8693 EX3 SST DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12849290	G5653 SCVi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12821480	H7440BM CH PEBE 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12852340	G7085 SCVi XXL F ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858840	G5611 TR BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858850	G5611 SC TR BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852350	G7090 SCVi F ED230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858860	G5611 SC TR ED230 1,9 Active CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858870	G5611 SCi TR ED230 1,9 CLST Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858890	G5651 Vi TR ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858900	G5651 SCVi TR ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858910	G7040 SC TR ED230 1,9 AutoDos CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858920	G7040 SCi TR ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858930	G7080 SCVi TR ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858940	G7085 SCVi XXL TR ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870250	G5611 SC OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870260	G5611 SCi OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870270	G5611 SCi OE1 ED230 1,9 Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870280	G5651 SCVi OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870290	G5662 SCVi OE1 ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870340	G5817 SCi XXL OE1 ED230 1,9 Active Pl CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870300	G5811 SC OE1 BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870310	G5811 SC OE1 ED230 1,9 ActPlus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12870320	G5811 SCi OE1 OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870330	G5811 SCi OE1 ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870350	G5851 SCVi OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870400	G5862 SCVi OE1 ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858350	G5851 SCVi IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858360	G5856 SCVi XXL IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858370	G7040 SC IB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858380	G7040 SC IB ED230 1,9 AutoDos CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858390	G7040 SCi IB ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852140	G5811 SC F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852150	G5811 SC F ED230 1,9 ActivePlus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852160	G5811 SCi F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852170	G5811 SCi F ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852210	G5833 SC F BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852180	G5812 SC F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852190	G5812 SC F ED230 1,9 ActivePlus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852200	G5812 SCi F OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852220	G5851 SCVi F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852260	G5863 SCVi F ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852250	G5856 SCVi XXL F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852270	G5868 SCVi XXL F ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858400	G7080 SCVi IB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852280	G7040 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858410	G7085 SCVi XXL IB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852300	G7040 SC F ED230 1,9 AutoDos CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852310	G7040 SCi F ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852320	G7042 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852330	G7080 SCVi F ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12938750	Module H7-3BM packed	Heater element Top heat 200-208V	Lead	7439-92-1
12938750	Module H7-3BM packed	Release element 220/240V 50/60HZ	Lead	7439-92-1
12906870	G7601 SCi OE1 ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12912220	G7651 SCVi A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12912230	G7658 SCVi XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906880	G7651 SCVi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906900	G7658 SCVi XXL OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906830	G7651 SCVi MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906840	G7658 SCVi XXL MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12925560	G5811 SCi IB ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906800	G7651 SCVi I OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906810	G7651 SCVi IB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906820	G7658 SCVi XXL IB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12911940	G17601 SCi CH ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906850	G7651 SCVi NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12906860	G7658 SCVi XXL NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12911950	G17601 SCi CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12911960	G27608 SCi XXL CH ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12885410	KM3011 XE1/R01 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12885410	KM3011 XE1/R01 230/50	Holder	Lead	7439-92-1
12885410	KM3011 XE1/R01 230/50	Burner tap 0,39	Lead	7439-92-1
12885410	KM3011 XE1/R01 230/50	Burner tap 0,42	Lead	7439-92-1
12911970	G27608 SCi XXL CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12911980	G17651 SCVi CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870370	G5856 SCVi XXL OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870410	G7040 SC OE1 ED230 1,9 AutoDos CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870420	G7040 SCi OE1 ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870470	G7045 SCi XXL OE1 ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12821510	H7464BP AUS PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12821530	H7440BM AUS PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12870490	G7080 SCVi OE1 ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870500	G7082 SCVi OE1 ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12870520	G7085 SCVi XXL OE1 ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12864160	TXR960WP NAM LW Eco&Steam	SMD- Diode STTH1R04A	Lead	7439-92-1
12912160	G7601 SCi D ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12912170	G7608 SCi XXL D ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12819070	TXB360WP NAM LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12819080	TXF360WP NAM LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12926070	G5666 SCVi XXL MER ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12926080	G5864 SCVi MER ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12926090	G5866 SCVi XXL MER ED230 1,9 Active Pl S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12914580	G5612 SCU NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12914590	G5612 SCU NER ED230 1,9 Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12912190	G7658 SCVi XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12912180	G7651 SCVi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12961510	Sub-assembly BM 48"-3	Heater element Top heat 200-208V	Lead	7439-92-1
12938730	Module H7-3BM	Heater element Top heat 200-208V	Lead	7439-92-1
12938730	Module H7-3BM	Release element 220/240V 50/60HZ	Lead	7439-92-1
12866030	KMDA7676-1 FL XE3/R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12868260	G5867 SCVi XXL MER ED230 1,9 Active Pl S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12866210	KMDA7676-1 FL XR1/OER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12868280	G7040 SC MER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12866240	KMDA7876-1 FL XE1/R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12866250	KMDA7876-1 FL XE3/R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12866290	KMDA7876-1 FL C XC1/CN 220/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12868300	G7080 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12668310	G7081 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668320	G7082 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668330	G7085 SCVi XXL MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668340	G7087 SCVi XXL MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668350	G7088 SCVi XXL MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664910	G5611 SC GB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664920	G5632 SC GB BW230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664930	G5651 Vi GB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664940	G5651 SCVi GB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664950	G5662 SCVi GB ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664960	G5811 SC GB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664970	G5811 SC GB ED230 1,9 Active Pl CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664980	G5832 SC GB BW230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664990	G5832 SC GB ED230 1,9 ActPlus CS Front S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12665000	G5851 SCVi GB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12665010	G5862 SCVi GB ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12821700	H7464BP SER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12821710	H7440BM SER PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12668060	G5811 MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668070	G5811 MER ED230 1,9 Active Plus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668080	G5811 SC MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668090	G5811 SC MER ED230 1,9 ActivePl CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668100	G5811 SCi MER OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668110	G5811 SCi MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668120	G5811 SCi MER ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668150	G5832 SC MER BW230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668160	G5832 SC MER ED230 1,9 ActPlu CS Front S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668170	G5832 SCU MER ED230 1,9 Active Plus CS S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668180	G5832 SCi MER ED230 1,9 Active Plus CS S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668190	G5833 SC MER BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668140	G5817 SCi XXL MER ED230 1,9 Active Pl CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668130	G5817 SCi XXL MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668200	G5851 Vi MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668210	G5851 SCVi MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668250	G5863 SCVi MER ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668240	G5862 SCVi MER ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668220	G5856 Vi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12668230	G5856 SCVi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12666020	KMDA7676-1 FL XE1/R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12668270	G5868 SCVi XXL MER ED230 1,9 Active Pl E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851990	G5611 SC F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852000	G5611 SCU F ED230 1,9 CLST Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852030	G5611 SCi F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852040	G5611 SCi F ED230 1,9 Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12896770	G5666 Vi XXL MER ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852050	G5612 SC F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852060	G5612 SC F ED230 1,9 Active CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852070	G5612 SCi F ED230 1,9 Active CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12896780	G5864 Vi MER ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12896790	G5866 Vi XXL MER ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852080	G5651 Vi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852090	G5651 SCVi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852100	G5652 SCVi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852120	G5661 SCVi F ED230 1,9 Active DUOCLEAN	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852130	G5663 SCVi F ED230 1,9 Active E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12852110	G5656 SCVi XXL F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858230	G5611 IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858240	G5611 SC IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858250	G5611 SC IB ED230 1,9 Active CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858260	G5611 SCi IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858300	G5651 Vi IB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858310	G5651 SCVi IB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858320	G5811 SC IB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12858340	G5811 SC IB ED230 1,9 Active Pl CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12795990	PLW8604 J LW ADP PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12865020	G7040 SC GB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12865030	G7040 SC GB ED230 1,9 AutoDos CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12800230	PWD8692 J U SST DS5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12800240	PWD8692 J U SST DS5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12798500	PWD8682 J U SST LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12798510	PWD8682 J U SST LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12865040	G7080 SCVi GB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12799800	PLW8683CD J ADP LD DS5 CM MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12865050	G7085 SCVi XXL GB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12799820	PLW8683CD J GD LD DS5 CM MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12798910	PLW8683 J SST ADP PD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12798920	PLW8683 J SST GD LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12836740	PWD8682 EXJ U SST LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12836750	PWD8682 EXJ U SST LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12836760	PWD8692 EXJ U SST DS5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12836770	PWD8692 EXJ U SST DS5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12836780	PLW8604 EXJ LW ADP PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12836790	PLW8683 EXJ SST ADP PD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12836810	PLW8683 EXJ SST GD LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12836820	PLW8683CD EXJ ADP LD DS5 CM MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12836830	PLW8683CD EXJ GD LD DS5 CM MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12851960	G5611 F BW230 1,9 ACTIVE	Drain pump 220-240V 50HZ	Lead	7439-92-1
12851970	G5611 F ED230 1,9 Active CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12843200	G7045 SCI XXL A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12750970	PDR908ROP EL FIN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12801700	DAH4980 GB PEBE 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12753120	PDR908ROP EL EXP SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12693040	DG8140-60L XS4/CH PEBE 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12693010	DG8140-60L XS4/CH OBSW 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12693030	DG8140-60L XS4/CH MASW 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12753090	PDR908ROP EL EXP LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752980	PDR908HP P EXP SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752940	PDR908HP P EXP LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752410	PDR908ROP EL B SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752400	PDR908ROP EL B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752390	PDR508ROP EL B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12648950	DG8140L XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12435020	DG8140L XE1/R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12435050	DG8140L XE1/R01 MASW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12693000	DG8130-60F XS4/CH EDLK 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12721150	DG8130-60F XS4/CH BLST 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12435010	DG8130F XE1/R01 EDLK 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12721140	DG8130F XE1/R01 BLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12752170	PDR508HP P TR SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752810	PDR508HP P EXP LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752880	PDR508HP P EXP SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12802160	H7440BMX AUS PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12802170	H7464BPX AUS PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12750690	PDR908ROP EL NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750720	PDR908ROP EL NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750540	PDR508ROP EL IB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750500	PDR508ROP EL IB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750860	PDR908HP P FIN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750200	PDR908HP P S SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12751850	PDR508HP P CN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750560	PDR908ROP EL IB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750770	PDR908HP P NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750750	PDR908HP P NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750150	PDR508ROP EL S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751740	PDR508ROP EL N LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752100	PDR508ROP EL I LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750950	PDR508ROP EL FIN LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12753040	PDR508ROP EL EXP LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12749360	PDR508ROP EL DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750060	PDR908HP P CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750080	PDR908HP P CH SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752010	PDR508ROP EL IRL LW 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
12750160	PDR908ROP EL S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751560	PDR508ROP EL F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751570	PDR508ROP EL F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752250	PDR908ROP EL TR SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12751750	PDR908ROP EL N LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12831410	PWD8692 NBI SST DC5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11753660	KM7464 FR BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11753670	KM7465 FL BNE 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11753710	KM7564 FL BNE 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11753740	KM7575 FL BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11753740	KM7575 FL BNE 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11753750	KM7575 FR BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11753750	KM7575 FR BNE 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11753780	KM7594 FL BNE 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11753810	KM7629 FX BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11753860	KM7684 FL BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11753860	KM7684 FL BNE 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11753880	KM7689 FL BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11753890	KM7699 FR BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11753950	KM7899 FL BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10564620	KM6564 FL R01 230/50	Heater plate 2,2-0,75kW 230V	Lead	7439-92-1
10564620	KM6564 FL R01 230/50	Heater plate 1,2kW 230V	Lead	7439-92-1
10564590	KM6542 FR R01 230/50	Heater plate 1,2kW 230V	Lead	7439-92-1
10564590	KM6542 FR R01 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10882000	KM6540 FR D 230/50	Heater plate 1,2kW 230V	Lead	7439-92-1
10882000	KM6540 FR D 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10882010	KM6542 FR D 230/50	Heater plate 1,2kW 230V	Lead	7439-92-1
10882010	KM6542 FR D 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10882040	KM6542 FL D 230/50	Heater plate 1,2kW 230V	Lead	7439-92-1
12802190	H7840BMX AUS PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12802200	H7860BPX AUS PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12751950	PDR508HP P IRL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752020	PDR508ROP EL IRL LW 400V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
12753060	PDR508ROP EL EXP SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752790	PDR508ROP EL AUS LW 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
12752080	PDR508ROP EL I SST	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12752120	PDR908ROP EL I SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12751580	PDR908ROP EL F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751620	PDR908ROP EL F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12748750	PDR307ROP EL ZER LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752210	PDR508ROP EL TR SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12749370	PDR908ROP EL DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751870	PDR508ROP EL CN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752220	PDR508ROP EL TR LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752800	PDR908ROP EL AUS SST 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
12752040	PDR908ROP EL IRL SST 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
12751880	PDR908ROP EL CN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12749410	PDR908ROP EL DK LW BL	SMD- Diode STTH1R04A	Lead	7439-92-1
12797620	PLW8604 NBI SST PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12797650	PLW8604 GB SST PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12797660	PLW8604 GB SST ADP PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12798440	PWD8682 NBI LW LD DC5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12798700	PLW8683 NBI SST LD DC10	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12752560	PDR508HP P GB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752650	PDR307HP P GB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750100	PDR300-08HP P CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750110	PDR500-08HP P CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750130	PDR900-08HP P CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750170	PDR508HP P S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750180	PDR908HP P S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750050	PDR508HP P CH SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750730	PDR508HP P NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12723110	DAD4970 XD1/D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723240	DAD6980 XD1/D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12750740	PDR508HP P NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12751900	PDR508HP P I LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751890	PDR508HP P I SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12751920	PDR908HP P I SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750850	PDR908HP P FIN LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752600	PDR908HP P GB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12722970	DAD4870 XD1/D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723050	DAD4370 XD1/D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12752620	PDR908HP P GB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12723180	DAD6880 XD1/D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12751710	PDR908HP P F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752270	PDR508HP P B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751830	PDR908HP P N LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12693080	DG8340-60L XS4/CH MASW 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12693060	DG8340-60L XS4/CH OBSW 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12693090	DG8340-60L XS4/CH PEBE 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12617630	DS8010 XE1/R01 MASW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12617640	DS8010 XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11635933	Power-/Control unit EPL 8630	SMD- Diode STTH1R04A	Lead	7439-92-1
12721080	DG8530F XE1/R01 BLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12693100	DG8530-60F XS4/CH EDLK 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12435140	DG8530F XE1/R01 EDLK 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12693130	DG8540-60L XS4/CH MASW 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12693110	DG8540-60L XS4/CH OBSW 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12693140	DG8540-60L XS4/CH PEBE 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12435170	DG8540L XE1/R01 MASW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12648970	DG8540L XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12721090	DG8530-60F XS4/CH BLST 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12792250	Fitting OC Module	Fitting OC Module	Lead	7439-92-1
12792250	Fitting OC Module	Fitting OC Module	Lead	7439-92-1
12562080	OWD1232W XQ1 BL	Fitting OC Module	Lead	7439-92-1
12773570	G5260 C SCVi CN ED220/50 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12763330	H7260BP GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12749770	PDR508HP P D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12749850	PDR908HP P D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12749810	PDR508HP P D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12749870	PDR908HP P D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12723030	DAD4870 C XC2/CN OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723150	DAD4970 C XC2/CN OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723090	DAD4370 C XC2/CN OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723220	DAD6880 C XC2/CN OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723280	DAD6980 C XC2/CN OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723040	DAD4870 XZ1/KZ OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723160	DAD4970 XZ1/KZ OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723100	DAD4370 XZ1/KZ OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723230	DAD6880 XZ1/KZ OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723290	DAD6980 XZ1/KZ OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12750420	PDR508HP P IB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750410	PDR508HP P IB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750830	PDR508HP P FIN LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752180	PDR508HP P TR LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750440	PDR908HP P IB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752190	PDR908HP P TR SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12749710	PDR508HP P DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12749720	PDR908HP P DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12749260	PDR508ROP EL D LW	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12749310	PDR508ROP EL D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12749320	PDR908ROP EL D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12749330	PDR908ROP EL D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12750620	PDR508ROP EL NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12750650	PDR508ROP EL NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12752350	PDR908HP P B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12752370	PDR908HP P B SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12751690	PDR508HP P F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751700	PDR508HP P F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12751730	PDR908HP P F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12751790	PDR508HP P N LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12751840	PDR908HP P N SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12723020	DAD4870 XS1/CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723140	DAD4970 XS1/CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723080	DAD4370 XS1/CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12749110	PDR307HP P ZER LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12723210	DAD6880 XS1/CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723270	DAD6980 XS1/CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12722990	DAD4870 XG1/GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723120	DAD4970 XG1/GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723060	DAD4370 XG1/GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723190	DAD6880 XG1/GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723250	DAD6980 XG1/GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723010	DAD4870 XA1/AUS OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723130	DAD4970 XA1/AUS OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723070	DAD4370 XA1/AUS OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723200	DAD6880 XA1/AUS OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12723260	DAD6980 XA1/AUS OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12750040	PDR508HP P CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
10882040	KM6542 FL D 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
12488230	KM7466 FR F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12488200	KM7466 FR BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12485350	KM7466 FR I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12484640	KM7466 FR DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12463620	KM7466 FL TR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527290	KM7576 FL TR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527290	KM7576 FL TR 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12527030	KM7576 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527030	KM7576 FL CH 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12527240	KM7576 FL I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527240	KM7576 FL I 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12526900	KM7576-2 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12526900	KM7576-2 FL IB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12527010	KM7576 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527010	KM7576 FL DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12526890	KM7576 FL BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12526890	KM7576 FL BNE 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12546810	KM7684-1 FL HK 220/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12546810	KM7684-1 FL HK 220/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12535250	HR1432-3 I USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
12535250	HR1432-3 I USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
12535250	HR1432-3 I USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12831400	PWD8682 NBI SST LD DC5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12800170	PWD8692 NBI LW DC5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11167460	KM7594 FL B 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11145160	KM7684 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11145160	KM7684 FL D 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11390350	KM7404 FX DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11325910	KMDA7633 FL TR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11506140	KM7629 FX D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11506330	KM7689 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11506360	KM7899 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11515560	KM7629 FX B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11515590	KM7689 FL B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11515600	KM7699 FR B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11515620	KM7899 FL B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11515520	KM7629 FX GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11515550	KM7699 FR GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11512530	KM7629 FX NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11512580	KM7699 FR NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11512290	KM7699 FR I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11512300	KM7899 FL I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11508070	KM7629 FX DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11508100	KM7689 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11508120	KM7899 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11598740	KM7464 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12198270	KM7594 FL DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12198280	KM7594 FR DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12853780	H2761B I EDST/CLST 230/50 <3KW	Heater element Unterhitze 230-240V	Lead	7439-92-1
12853780	H2761B I EDST/CLST 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
12845610	G5662 SCVI D ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845470	G5656 Vi XXL D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845460	G5656 SCVI XXL D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845620	G5667 SCVI XXL D ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12843210	G7080 SCVi A ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12843220	G7085 SCVi XXL A ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11985095	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12845630	G7040 SC D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845640	G7040 SC D ED230 1,9 AutoDos CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845660	G7040 SCU D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12843150	G7040 SC A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845670	G7040 SCU D ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845680	G7040 SCi D ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845710	G7045 SCi XXL D ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12843170	G7040 SCU A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845780	G5811 D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12843190	G7040 SCi A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12843180	G7040 SCi A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845850	G5811 U D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845860	G5811 U D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845890	G5811 i D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845900	G5811 i D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12800360	PLW8693 NBI SST DC10 CM	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12845720	G7080 SCVi D ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845730	G7085 SCVi XXL D ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845760	G5851 SCVi D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12752470	PDR307ROP EL GB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12845940	G5851 Vi D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12846010	G5863 SCVi D ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845770	G5856 SCVi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845960	G5856 Vi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12846020	G5868 SCVi XXL D ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12846030	G5611 D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845580	G5611 i D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12846040	G5611 i D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12752490	PDR508ROP EL GB LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
12752510	PDR508ROP EL GB LW 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
12752520	PDR908ROP EL GB LW 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
12845480	G5611 SC D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12752530	PDR908ROP EL GB LW 400V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
12845550	G5611 SCU D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845570	G5611 SCU D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845440	G5611 SCi D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845590	G5611 SCi D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845600	G5651 Vi D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12845450	G5651 SCVi D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11153140	KM7464 FR CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11153230	KM7575 FR CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11153230	KM7575 FR CH 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11153290	KM7575 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11153290	KM7575 FL CH 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11153330	KM7684 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11153330	KM7684 FL CH 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11128630	KM7404 FX D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144020	KM7464 FR GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144030	KM7464 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144050	KM7564 FL GB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144060	KM7575 FR GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144060	KM7575 FR GB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144070	KM7684 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144070	KM7684 FL GB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144710	KM7464 FR DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144720	KM7464 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144730	KM7465 FR DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144740	KM7465 FL DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144770	KM7564 FR DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144780	KM7564 FL DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144790	KM7575 FR DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144790	KM7575 FR DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144800	KM7575 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
10882070	KM6565 FR D 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10882070	KM6565 FR D 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10882060	KM6564 FL D 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10882060	KM6564 FL D 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10889800	KM6542 FR DFS 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10889800	KM6542 FR DFS 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10890170	KM6540 FR I 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10890170	KM6540 FR I 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10890180	KM6542 FR I 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10890180	KM6542 FR I 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10890190	KM6542 FL I 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10890190	KM6542 FL I 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10948650	KM6540 FR B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948650	KM6540 FR B 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10948660	KM6542 FR B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948660	KM6542 FR B 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10948670	KM6542 FL B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948670	KM6542 FL B 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10948680	KM6565 FR B 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10948680	KM6565 FR B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948710	KM6540 FR NL 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948710	KM6540 FR NL 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10974380	KMDA7774-1 FL TR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11153050	KM7404 FX CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11126680	KM7684 FL F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11033060	KM6542 FR TR 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11033060	KM6542 FR TR 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
11033120	KM6564 FR TR 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11033120	KM6564 FR TR 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11033130	KM6565 FR TR 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11033130	KM6565 FR TR 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11205380	KM7464 FR NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11205390	KM7465 FL NL 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11205440	KM7564 FL NL 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11205490	KM7575 FR NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11205490	KM7575 FR NL 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11205510	KM7575 FL NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11205510	KM7575 FL NL 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11205520	KM7594 FL NL 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11205530	KM7684 FL NL 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11205530	KM7684 FL NL 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11167280	KM7464 FR B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11167370	KM7564 FL B 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11167470	KM7684 FL B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11167470	KM7684 FL B 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11167490	KM7465 FL B 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11167450	KM7575 FL B 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11167450	KM7575 FL B 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144800	KM7575 FL DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11144820	KM7684 FL DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11144820	KM7684 FL DFS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11153890	KM7404 FX I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11153900	KM7464 FR I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11153910	KM7464 FL I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11153920	KM7465 FL I 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11154100	KM7564 FL I 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11154120	KM7575 FL I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11154120	KM7575 FL I 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11154130	KM7594 FL I 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11154150	KM7684 FL I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11154150	KM7684 FL I 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11120710	KM7464 FL TR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11126480	KM7404 FX F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11126520	KM7464 FR F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11126530	KM7465 FR F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11126540	KM7465 FL F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11126580	KM7564 FR F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11126590	KM7564 FL F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11126630	KM7575 FR F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11126630	KM7575 FR F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11126670	KM7594 FL F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11126680	KM7684 FL F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12602440	OG 1232L XA1 BL	Electronic unit EW G01120	Lead	7439-92-1
12602440	OG 1232L XA1 BL	Socket food probe GP	Lead	7439-92-1
12602440	OG 1232L XA1 BL	Distributor kpl	Lead	7439-92-1
13052580	PDR914 HP P ANL IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12904890	KMDA7876-1 FL BNI 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12904880	KMDA7676-1 FL BNI 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12602440	OG 1232L XA1 BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
12602440	OG 1232L XA1 BL	Ignitiontransformer	Lead	7439-92-1
10948720	KM6542 FR NL 230/50	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
10948720	KM6542 FR NL 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12929320	PDR516ROP SL EL NAM IG-IG F04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
13074360	Power-/Control unit EPL 8810-U	SMD- Diode STTH1R04A	Lead	7439-92-1
11128620	KM7174 FR D 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11126350	KM7164 FR F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12970570	KMDA7676-1 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12970580	KMDA7876-1 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12970630	KMDA7676-1 FL F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12970640	KMDA7876-1 FL F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12970780	KMDA7676-1 FL TR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12970680	KMDA7676-1 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12970690	KMDA7876-1 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
13052590	PDR918 HP P ANL IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
13064270	PDR508ROP EL UA LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12934020	LAB5010 J SST LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10933900	CS1012-2 D EDST 230/50	Burner tap 0,52	Lead	7439-92-1
11402800	CS7101-1 FL B 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402810	CS7102-1 FL B 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402780	CS7101-1 FL NER 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402790	CS7102-1 FL NER 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402740	CS7101-1 FL NL 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11402750	CS7102-1 FL NL 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402720	CS7101-1 FL GB 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402730	CS7102-1 FL GB 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402850	CS7101-1 FL F 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402860	CS7102-1 FL F 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12291690	KM2356-1 UA EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12291690	KM2356-1 UA EDST 230/50	Jet 0,42MM	Lead	7439-92-1
12291690	KM2356-1 UA EDST 230/50	Burner tap 0,52	Lead	7439-92-1
12291690	KM2356-1 UA EDST 230/50	Jet 0,54MM	Lead	7439-92-1
12291690	KM2356-1 UA EDST 230/50	Jet 0,39MM	Lead	7439-92-1
12933610	DS5010 NAM U SST LD DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933710	DS5010 NAM U SST GD LD DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933830	DS5011 NAM U SST DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933940	DS5020 NAM U GD LD DS5 CM MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
6792730	KM3465LP USA EDST	Sealing ring 7,65x1,78	Lead	7439-92-1
12601150	OGC1332L XS1 BL	Ignitiontransformer	Lead	7439-92-1
12601150	OGC1332L XS1 BL	Adapter Gas connection	Lead	7439-92-1
12601150	OGC1332L XS1 BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
13028610	DAD4370 OER OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
13028620	DAD6980 OER OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
13081330	PDR908HP P NL LW REF	SMD- Diode STTH1R04A	Lead	7439-92-1
12933640	DS5010 EX3 U SST LD DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933740	DS5010 EX3 U SST GD LD DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933860	DS5011 EX3 U SST DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933970	DS5020 EX3 U GD LD DS5 CM MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933590	DS5010 J U SST LD DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
6449390	KM520 R01 EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6449390	KM520 R01 EDST 230/50	Heater plate 2,3KW 230V	Lead	7439-92-1
6449390	KM520 R01 EDST 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
6442860	KM520 D EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6442860	KM520 D EDST 230/50	Heater plate 2,3KW 230V	Lead	7439-92-1
6442860	KM520 D EDST 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
6449410	KM523 R01 EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6449410	KM523 R01 EDST 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
6449410	KM523 R01 EDST 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
6442870	KM523 D EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
6442870	KM523 D EDST 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
6442870	KM523 D EDST 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889790	KM6520 FR DFS 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889790	KM6520 FR DFS 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10890150	KM6520 FR I 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10890150	KM6520 FR I 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12934120	LAB5010 J SST GD LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934210	LAB5011 J SST DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934300	LAB5020 J LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12952380	LAB5010 EXJ SST LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12952360	LAB5010 EXJ SST GD LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12952390	LAB5011 EXJ SST DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12952400	LAB5020 EXJ LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934030	LAB5010 NAM SST LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934130	LAB5010 NAM SST GD LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934220	LAB5011 NAM SST DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934310	LAB5020 NAM LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
13052140	Air mixer OC	Air mixer OC	Lead	7439-92-1
13052140	Air mixer OC	Air mixer OC	Lead	7439-92-1
13052150	Cartridge OC	Cartridge OC	Lead	7439-92-1
13052150	Cartridge OC	Cartridge OC	Lead	7439-92-1
13069620	Rotary knob	Rotary knob	Lead	7439-92-1
13069620	Rotary knob	Rotary knob	Lead	7439-92-1
13052740	OG1232N D BL	Ignitiontransformer	Lead	7439-92-1
13052740	OG1232N D BL	Adapter Gas connection	Lead	7439-92-1
13052740	OG1232N D BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
13052740	OG1232N D BL	Supply cable G32	Lead	7439-92-1
13052740	OG1232N D BL	Socket food probe GP	Lead	7439-92-1
13052740	OG1232N D BL	Electronic unit EW G01120	Lead	7439-92-1
13029510	DAD6980 AUS OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10939260	KM2356-1 B EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10940240	KM2357-1 R01 FL.bdg. 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940240	KM2357-1 R01 FL.bdg. 230/50	Jet 0,42MM	Lead	7439-92-1
10940240	KM2357-1 R01 FL.bdg. 230/50	Burner tap 0,52	Lead	7439-92-1
10940240	KM2357-1 R01 FL.bdg. 230/50	Jet 0,54MM	Lead	7439-92-1
10940240	KM2357-1 R01 FL.bdg. 230/50	Jet 0,39MM	Lead	7439-92-1
10939680	KM2357-1 I FL.bdg. 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10939680	KM2357-1 I FL.bdg. 230/50	Jet 0,42MM	Lead	7439-92-1
10939680	KM2357-1 I FL.bdg. 230/50	Burner tap 0,52	Lead	7439-92-1
10939680	KM2357-1 I FL.bdg. 230/50	Jet 0,54MM	Lead	7439-92-1
10939680	KM2357-1 I FL.bdg. 230/50	Jet 0,39MM	Lead	7439-92-1
10933880	KM2356-1 D EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10933880	KM2356-1 D EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10933880	KM2356-1 D EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10933880	KM2356-1 D EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10933880	KM2356-1 D EDST 230/50	Jet 0,39MM	Lead	7439-92-1
7111120	KM2032 B EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7111090	KM2034 D EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
7111100	KM2052 D EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7051710	KM2012 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7051730	KM2014 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7051770	KM2032 I EDST 230/50	Jet 0,27MM	Lead	7439-92-1
7051770	KM2032 I EDST 230/50	Jet 0,32MM	Lead	7439-92-1
7051770	KM2032 I EDST 230/50	Jet 0,54MM	Lead	7439-92-1
12981430	PDR1909HP ANL LW -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981440	PDR1909HP ANL SST -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981420	PDR1509EL ANL SST -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981460	PDR1909EL ANL SST -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981450	PDR1909EL ANL LW -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981410	PDR1509EL ANL LW -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
13019990	PDR1509HPB ANL LW -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
13020040	PDR1909HPB ANL SST -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981530	PDR1300-09HP ANL LW -CH-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981560	PDR1500-09HP ANL LW -CH-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981580	PDR1900-09HP ANL LW -CH-	SMD- Diode STTH1R04A	Lead	7439-92-1
11402760	CS7101-1 FL D 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402770	CS7102-1 FL D 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402830	CS7101-1 FL I 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
11402840	CS7102-1 FL I 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10939210	KM2356-1 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10939210	KM2356-1 I EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10939210	KM2356-1 I EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10939210	KM2356-1 I EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10939210	KM2356-1 I EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10939260	KM2356-1 B EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10939260	KM2356-1 B EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10939260	KM2356-1 B EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10939260	KM2356-1 B EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10938530	CS1011-1 B EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10938540	CS1011-1 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10933960	CS1012-2 F EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10933960	CS1012-2 F EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10933960	CS1012-2 F EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10938770	CS1012-2 B EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10938770	CS1012-2 B EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10938770	CS1012-2 B EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10938810	CS1012-2 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10938810	CS1012-2 I EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10938810	CS1012-2 I EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10933940	KM2356-1 F EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10933940	KM2356-1 F EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10933940	KM2356-1 F EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10933940	KM2356-1 F EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10933940	KM2356-1 F EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10939240	KM2356-1 TR EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10939240	KM2356-1 TR EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10939240	KM2356-1 TR EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10939240	KM2356-1 TR EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10939240	KM2356-1 TR EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10933890	CS1011-1 D EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10933900	CS1012-2 D EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10933900	CS1012-2 D EDST 230/50	Jet 0,42MM	Lead	7439-92-1
7051790	KM2034 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7051830	KM2052 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7111160	KM2012 F EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7111170	KM2032 F EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7126980	KM2014 GR EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7165400	KM2032 TR EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7165410	KM2052 TR EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9265890	KM2354 D EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9265890	KM2354 D EDST 230/50	Jet 0,39MM	Lead	7439-92-1
9305210	KM2354 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9305210	KM2354 I EDST 230/50	Jet 0,39MM	Lead	7439-92-1
9348570	KM2355 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9348570	KM2355 I EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10940380	CS1011-1 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940120	KM2356-1 NL EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940120	KM2356-1 NL EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10940120	KM2356-1 NL EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10940120	KM2356-1 NL EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10940120	KM2356-1 NL EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10940180	KM2357-1 GB Fl.bdg. 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940180	KM2357-1 GB Fl.bdg. 230/50	Jet 0,42MM	Lead	7439-92-1
10940180	KM2357-1 GB Fl.bdg. 230/50	Burner tap 0,52	Lead	7439-92-1
10940180	KM2357-1 GB Fl.bdg. 230/50	Jet 0,54MM	Lead	7439-92-1
10940180	KM2357-1 GB Fl.bdg. 230/50	Jet 0,39MM	Lead	7439-92-1
10890160	KM6520 FL I 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
13093430	G7713 C SCi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093450	G7763 C SCVi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093470	G7782 C SCVi CN OS220/50 1,9 K2O ADos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
13094390	G7241 SCi D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
13094420	G7248 SCi XXL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
13093520	G7993 C SCVi CN OS/CS220/50 1,9K2O AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093500	G7933 C SCi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13094430	G7281 SCVi D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093560	G5740 C SCiSL CN ED220/50 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
13094460	G7288 SCVi XXL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093580	G5740 C SCU SL CN BW220/50	Drain pump 220-240V 50HZ	Lead	7439-92-1
13095160	G7281 SCVi F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13095170	G7288 SCVi XXL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12776090	OG1332L D BL	Ignitiontransformer	Lead	7439-92-1
12776090	OG1332L D BL	Adapter Gas connection	Lead	7439-92-1
12776090	OG1332L D BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
12776190	OG1332L CH BL	Ignitiontransformer	Lead	7439-92-1
12776190	OG1332L CH BL	Adapter Gas connection	Lead	7439-92-1
12776190	OG1332L CH BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
13097720	G7241 SCi OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
13097730	G7281 SCVi OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13095180	G7281 SCVi MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13095190	G7288 SCVi XXL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13097700	G7281 SCVi NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12998970	OG1232L AUS BL	Ignitiontransformer	Lead	7439-92-1
12998970	OG1232L AUS BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
12998970	OG1232L AUS BL	Distributor kpl	Lead	7439-92-1
12998970	OG1232L AUS BL	Socket food probe GP	Lead	7439-92-1
12998970	OG1232L AUS BL	Electronic unit EW G01120	Lead	7439-92-1
11402650	KM520 AUS EDST 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11402650	KM520 AUS EDST 230/50	Heater plate 2,3KW 230V	Lead	7439-92-1
11402650	KM520 AUS EDST 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
13119500	H7260B D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
13003780	OWD1232W AUS BL	Fitting AUS	Lead	7439-92-1
13093180	G5611 C SCU CN BW220/50 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
13119510	H7260BP D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
13093190	G5811 C SCi CN ED220/50 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093200	G5851 C SCVi CN ED220/50 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093240	G7064 C SCVi CN ED220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093250	G7603 C SC CN BW220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093270	G7603 C SCi CN ED220/50 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093280	G7603 C SCU CN BW220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093210	G7013 C SCU CN BW220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093220	G7014 C SCi CN ED220/50 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093230	G7014 C SCU CN ED220/50 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11816620	HR1956-3 LP DF GD BR EDST/CLST127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
13093320	G7664 C SCVi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13093400	G7711 C SCi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13025880	KM3015 XE1/R01 EDST 230/50	Burner tap 0,42	Lead	7439-92-1
13025880	KM3015 XE1/R01 EDST 230/50	Burner tap 0,42	Lead	7439-92-1
12997290	OG1332L NER BL	Ignitiontransformer	Lead	7439-92-1
12997290	OG1332L NER BL	Adapter Gas connection	Lead	7439-92-1
12997290	OG1332L NER BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
13025890	KM3015 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
13025890	KM3015 R01 EDST 230/50	Holder	Lead	7439-92-1
13025890	KM3015 R01 EDST 230/50	Burner tap 0,39	Lead	7439-92-1
13025890	KM3015 R01 EDST 230/50	Burner tap 0,42	Lead	7439-92-1
13025890	KM3015 R01 EDST 230/50	Burner tap 0,42	Lead	7439-92-1
12503241	LED lamp Cornered HV DAH BLACK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12503241	LED lamp Cornered HV DAH BLACK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
11990680	KD7714E Active EU1	KD7714E Active EU1	Lead	7439-92-1
11990680	KD7714E Active EU1	KD7714E Active EU1	Lead	7439-92-1
12967590	KM3055 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12967590	KM3055 R01 EDST 230/50	Holder	Lead	7439-92-1
12967600	KM3056 R01 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12967600	KM3056 R01 230/50	Holder	Lead	7439-92-1
13115330	DS8010 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
13115340	DS8010 GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
13101480	OWD1232W EU1 BL	Fitting OC Module	Lead	7439-92-1
13117490	DS8010 SEE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
13117500	DS8010 SEE PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
13176190	PFD101 AUS ED/CS 230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
13097710	G7288 SCVi XXL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13094520	G7241 SCi A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
13094530	G7248 SCi XXL A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
13094580	G7281 SCVi I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11779650	PW6321 EL ZER 3N 380-415/50-60 MF	Control electr.unit EW 235-A	Lead	7439-92-1
11813780	PW6241 EL ZER 3N 380-415/50-60 FT	Control electr.unit EW 235-A	Lead	7439-92-1
11813740	PW6241 EL ZER 3 440/60	Control electr.unit EW 235-A	Lead	7439-92-1
11814070	PW6321 EL ZER 3N 380-415/50-60 MF WI	Control electr.unit EW 235-A	Lead	7439-92-1
11814080	PW6321 EL ZER 3N 380-415/50-60 FT	Control electr.unit EW 235-A	Lead	7439-92-1
11814020	PW6321 EL ZER 3 440/60	Control electr.unit EW 235-A	Lead	7439-92-1
11813980	PW6321 EL ZER 3 220-240/50-60 TRF	Control electr.unit EW 235-A	Lead	7439-92-1
11813680	PW6241 EL ZER 3 220-240/50-60 TRF	Control electr.unit EW 235-A	Lead	7439-92-1
11813810	PW6241 EL ZER 3 220-240/50-60 MF	Control electr.unit EW 235-A	Lead	7439-92-1
13071210	DAS4920 XY1/IN EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
13071220	DA4228W XY1/IN EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
13094590	G7288 SCVi XXL I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13094550	G7281 SCVi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
13094570	G7288 SCVi XXL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
13059470	DS8010 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
13059500	DS8010 R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
13136140	G7798 SCVi XXL NER OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13025880	KM3015 XE1/R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
13025880	KM3015 XE1/R01 EDST 230/50	Holder	Lead	7439-92-1
13025880	KM3015 XE1/R01 EDST 230/50	Burner tap 0,39	Lead	7439-92-1
12060460	KM6521 FR B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060460	KM6521 FR B 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
12060460	KM6521 FR B 230/50	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
12060480	KM6523 FL B 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12060480	KM6523 FL B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060480	KM6523 FL B 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
12060480	KM6523 FL B 230/50	Heater plate 2,6-1,5KW 230V	Lead	7439-92-1
12060490	KM6521 FR F 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12060490	KM6521 FR F 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060490	KM6521 FR F 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
12060490	KM6521 FR F 230/50	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
12060530	KM6522 FR F 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12060530	KM6522 FR F 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060540	KM6521 FR I 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12060540	KM6521 FR I 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060540	KM6521 FR I 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
12060540	KM6521 FR I 230/50	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
12060560	KM6522 FR I 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12060560	KM6522 FR I 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060570	KM6523 FL I 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12060570	KM6523 FL I 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060570	KM6523 FL I 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
12060570	KM6523 FL I 230/50	Heater plate 2,6-1,5kW 230V	Lead	7439-92-1
12076470	KM6522 FR TR 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10890160	KM6520 FL I 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10873530	KM6527 FR E 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
10873530	KM6527 FR E 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
10889620	KM6520 FR GB 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889620	KM6520 FR GB 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10889570	KM6520 FR F 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889570	KM6520 FR F 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10889580	KM6520 FL F 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889580	KM6520 FL F 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10889590	KM6527 FR F 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
10889590	KM6527 FR F 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
10889540	KM6520 FR N 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889540	KM6520 FR N 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948620	KM6520 FR B 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10948620	KM6520 FR B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948630	KM6520 FL B 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10948630	KM6520 FL B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948640	KM6522 FR B 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10948640	KM6522 FR B 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10948700	KM6520 FR NL 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10948700	KM6520 FR NL 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11033040	KM6520 FR TR 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11033040	KM6520 FR TR 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12060460	KM6521 FR B 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12934050	LAB5010 EX3 SST LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934150	LAB5010 EX3 SST GD LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934240	LAB5011 EX3 SST DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12934330	LAB5020 EX3 LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10939860	KM3034-1 R01 EDST 230/50	Residual heat ind. 5-fold 3034	Lead	7439-92-1
10940130	KM2356-1 RU EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940130	KM2356-1 RU EDST 230/50	Jet 0,42MM	Lead	7439-92-1
10940130	KM2356-1 RU EDST 230/50	Burner tap 0,52	Lead	7439-92-1
10940130	KM2356-1 RU EDST 230/50	Jet 0,54MM	Lead	7439-92-1
10940130	KM2356-1 RU EDST 230/50	Jet 0,39MM	Lead	7439-92-1
10940190	KM2357-1 AUS FL.BDG. 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10940190	KM2357-1 AUS FL.BDG. 230/50	Burner tap 0,52	Lead	7439-92-1
10939820	KM3034-1 AUS EDST 230/50	Residual heat ind. 5-fold 3034	Lead	7439-92-1
10939890	KM3054-1 AUS EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
10939890	KM3054-1 AUS EDST 230/50	Control panel Display Timer 3054-1	Lead	7439-92-1
10939800	KM3034-1 GB EDST 230/50	Residual heat ind. 5-fold 3034	Lead	7439-92-1
10939870	KM3054-1 GB EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
10939770	KM3034-1 NL EDST 230/50	Residual heat ind. 5-fold 3034	Lead	7439-92-1
10939880	KM3054-1 NL EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
11121030	KM3054-1 RU EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
11370670	KM3054-1 SGP EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
11370670	KM3054-1 SGP EDST 230/50	Control panel Display Timer 3054-1	Lead	7439-92-1
12291710	KM3034-1 UA EDST 230/50	Residual heat ind. 5-fold 3034	Lead	7439-92-1
12291750	KM3054-1 UA EDST 230/50	Residual heat ind. 5-fold 3054	Lead	7439-92-1
12076470	KM6522 FR TR 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12933700	DS5010 J U SST GD LD DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933820	DS5011 J U SST DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933930	DS5020 J U GD LD DS5 CM MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933560	DS5010 EXJ U SST LD DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12933690	DS5010 EXJ U SST GD LD DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933800	DS5011 EXJ U SST DS5 MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12933920	DS5020 EXJ U GD LD DS5 CM MON LAN	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
13096710	G7014 C SCi ANL ED220/50 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
13096720	G7713 C SCi ANL OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13096730	G7933 C SCi ANL OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
13111110	G5740 C SCi SL ANL ED220/50 CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
13096700	G7013 C SCU ANL BW220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12638970	ETD PTG 2-Scope JAPAN (50Hz)	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
13061470	Fitting AUS	Fitting AUS	Lead	7439-92-1
13061470	Fitting AUS	Fitting AUS	Lead	7439-92-1
13003770	OWD1232W XA3 BL	Fitting AUS	Lead	7439-92-1
12997280	OG1232L NER BL	Ignitiontransformer	Lead	7439-92-1
12997280	OG1232L NER BL	Adapter Gas connection	Lead	7439-92-1
12997280	OG1232L NER BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
12997280	OG1232L NER BL	Distributor kpl	Lead	7439-92-1
12997280	OG1232L NER BL	Socket food probe GP	Lead	7439-92-1
12997280	OG1232L NER BL	Electronic unit EW G01120	Lead	7439-92-1
11635934	Power-/Control unit EPL 8630	SMD- Diode STTH1R04A	Lead	7439-92-1
12981400	PDR1509HP ANL SST -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12934720	DAD6880 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12934700	DAD4370 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12934710	DAD4970 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12934730	DAD6980 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12963330	DAD4370 GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12963340	DAD6880 GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12965970	G5990 SCVi SL UA ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965950	G5590 SCVi SL UA ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965940	G7981 SCVi UA OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965930	G7792 SCVi UA OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965920	G7781 SCVi UA OS230 1,9 k2o AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12048070	KM6523 FL D 230/50	Heater plate 2,6-1,5KW 230V	Lead	7439-92-1
12963350	DAD6980 GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12963280	DAD4370 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12963290	DAD4870 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12963300	DAD4970 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12963310	DAD6880 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12963320	DAD6980 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12963360	DAD4370 C CN OBSW 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12848800	HM16-83 CH 220-240/50-60 2,7-3,3KW	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
12600930	OGD1332L XD1 BL	Ignitiontransformer	Lead	7439-92-1
12600930	OGD1332L XD1 BL	Adapter Gas connection	Lead	7439-92-1
12600930	OGD1332L XD1 BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
11978000	B4847 USA	Electronic unit	Lead	7439-92-1
10564570	KM6522 FR R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10862550	KM6520 FL R01 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10862550	KM6520 FL R01 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10881980	KM6520 FR D 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10881980	KM6520 FR D 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10881990	KM6522 FR D 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10881990	KM6522 FR D 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10882030	KM6520 FL D 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10882030	KM6520 FL D 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10889470	KM6520 FR R02 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889470	KM6520 FR R02 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10889490	KM6522 FR R02 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889490	KM6522 FR R02 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10889500	KM6527 FR R02 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
10889500	KM6527 FR R02 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
10889480	KM6520 FL R02 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
10889480	KM6520 FL R02 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11327640	KM6521 FR R02 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11327640	KM6521 FR R02 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
11327640	KM6521 FR R02 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
11327640	KM6521 FR R02 230/50	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
12048070	KM6523 FL D 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12048070	KM6523 FL D 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12048070	KM6523 FL D 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
10481370	PW413 EL NER WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481390	PW413 EL NER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481360	PW413 EL NER WEK Mopstar 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481320	PW413SES EL NER MF 3N380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481310	PW413SES OH NER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481350	PW413 EL OER WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10481380	PW413 EL NER WEK MF Sluice 3NAC380-415	Control electr.unit EW 235-A	Lead	7439-92-1
10481510	PW814 EL ZER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481550	PW814 EL ZER MF VI 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481430	PW814 EL NER WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10481530	PW814 EL NER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481440	PW814 EL OER WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10481540	PW814 EL OER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481470	PW814 EL ZER WEK 3 AC 400V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10481480	PW814 EL ZER WEK 3 AC 440-480V 60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10481570	PW814 EL ZER WEK ST 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10481730	PW418 EL ZER FT WEK Mopstar 3NAC380-415	Control electr.unit EW 235-A	Lead	7439-92-1
10481710	PW418SES EL ZER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481580	PW418 EL NER WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10481630	PW418 EL NER WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481620	PW418 EL NER WEK Mopstar 3N AC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481720	PW418SES EL NER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481700	PW418SES OH NER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481610	PW418 EL OER WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
12975430	BO8155F XE1/D EDLK 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12975430	BO8155F XE1/D EDLK 230/50	Heater element Top heat 230V	Lead	7439-92-1
10296340	PW814 EL ZER WEK 3 AC 220-240V 50/60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10269670	PW811 EL ZER WEK ST 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269560	PW811 EL ZER FT MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10296520	PW814 Ddir ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10297230	PW818 EL ZER WEK WI 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10297450	PW818 ELred ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269250	PW811 EL ZER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269640	PW811 EL ZER WEK 3AC220-240 50/60	Control electr.unit EW 235-A	Lead	7439-92-1
10481770	PW818 EL ZER WEK 3AC220-240 50/60	Control electr.unit EW 235-A	Lead	7439-92-1
10481410	PW413 EL NER MF Mopstar 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269460	PW811 EL ZER WEK FT 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269580	PW811 EL NER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269590	PW811 EL NER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269600	PW811 EL OER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269620	PW811 EL OER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269700	PW811 EL ZER WEK 3AC400/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269800	PW811 EL ZER WEK 3AC440/480/60	Control electr.unit EW 235-A	Lead	7439-92-1
10269850	PW413 EL ZER WEK Mopstar 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269860	PW413 EL ZER MF Mopstar 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10269870	PW413 EL ZER FT MF Mopstar 3N380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481290	PW413SES OH ZER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481340	PW413 EL NER WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
12900570	KM3056 XE1/R01 230/50	Holder	Lead	7439-92-1
12906910	G7601 SCI TR ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12904830	KMDA7876-1 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12800830	PWA8672 NAM U SST LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12920040	G7792 SCVi IB OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12904820	KMDA7676-1 FL D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12894720	Power-/Control unit ELP 7751 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12821560	H7460B EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12511893	Power-/Control unit ELP 7752 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12511993	Power-/Control unit ELP 7753 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11985097	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12894910	Power-/Control unit ELP 7792 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12894921	Power-/Control unit ELP 7794 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12934690	DAD4870 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11985105	Power-/Control unit ELP 7755 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11612859	Power-/Control unit ELP 7757 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12446041	Power-/Control unit ELP 7442 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11844916	Power-/Control unit ELP 7442-A 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12594722	Power-/Control unit ELP 7482	SMD- Diode STTH1R04A	Lead	7439-92-1
12384022	Power-/Control unit ELP 7202 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12842540	DGC7440 XU5/USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12842530	DGC7470 XU5/USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12842500	DGC7870X XU5/USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12842520	DGC7880X XU5/USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12911990	G27658 SCVi XXL CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12885420	KM3015 XE3/R02 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12885420	KM3015 XE3/R02 EDST 230/50	Holder	Lead	7439-92-1
12797800	PLW8604 NAM U SST PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12885430	KM3035 XE1/R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12885430	KM3035 XE1/R01 EDST 230/50	Holder	Lead	7439-92-1
12885440	KM3055 XE1/R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12885440	KM3055 XE1/R01 EDST 230/50	Holder	Lead	7439-92-1
12798520	PWD8682 NAM U SST LD DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12904720	KMDA7676-1 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12904730	KMDA7876-1 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12799290	PLW8683 NAM U SST LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12799340	PLW8683 NAM U SST GD LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12822190	PLW8683 NAM U SST PD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12799310	PLW8683 NAM U SST OIL LD DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12800050	PLW8683CD NAM U LD DS5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12800070	PLW8683CD NAM U OIL LD DS5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12912200	G7601 SCi A ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12800060	PLW8683CD NAM U GD LD DS5 CM MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12912210	G7608 SCi XXL A ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12800250	PWD8692 NAM U SST DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12800840	PLW8693 NAM U SST DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12800850	PLW8693 NAM U SST OIL DS5	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12900570	KM3056 XE1/R01 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12775720	OG1232L D BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
12775720	OG1232L D BL	Distributor kpl	Lead	7439-92-1
12775720	OG1232L D BL	Socket food probe GP	Lead	7439-92-1
12775720	OG1232L D BL	Electronic unit EW G01120	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12945650	PWD8682 C NBI SST DST DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12526160	DA9299W TR BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12792974	Electronic unit EW G01120	Electronic unit EW G01120	Lead	7439-92-1
12965810	G5611 SC UA BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12775750	OG1232L CH BL	Ignitiontransformer	Lead	7439-92-1
12775750	OG1232L CH BL	Adapter Gas connection	Lead	7439-92-1
12775750	OG1232L CH BL	Thermocouple Ceram surface burnr G32	Lead	7439-92-1
12775750	OG1232L CH BL	Distributor kpl	Lead	7439-92-1
12775750	OG1232L CH BL	Socket food probe GP	Lead	7439-92-1
12775750	OG1232L CH BL	Electronic unit EW G01120	Lead	7439-92-1
12965840	G5611 SC UA ED230 1,9 Active CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12969730	KMDA7676-1 FL R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12969740	KMDA7876-1 FL R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12965850	G5651 SCVi UA ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965860	G5851 SCVi UA ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965880	G7040 SCi UA ED230 1,9 AutoDos CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965890	G7080 SCVi UA ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965900	G7261 SCVi UA ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12965910	G7651 SCVi UA OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10564570	KM6522 FR R01 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12555210	DAH1650 TR OBSW 230/50 TL	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12555220	DAH1950 TR OBSW 230/50 TL	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12555240	DAH4970 TR OBSW 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12555250	DAH4970 TR CONO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12555260	DAH4970 TR PABO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12555270	DAH4980 TR OBSW/MATT 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12688432	Socket food probe GP	Socket food probe GP	Lead	7439-92-1
12553640	DAH4980 IB OBSW/MATT 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12568680	DAH4980 F OBSW/MATT 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12559600	DAH4980 NER OBSW/MATT 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12578020	DAH4980 BNE OBSW/MATT 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12842730	H7263BP USA OBSW 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
12842730	H7263BP USA OBSW 120/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12842740	H7240BM USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11968190	H7270BM USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
12842590	H7870BMX USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
12945660	PWD8682 C NBI LW DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12945670	PWD8682 C NBI LW DST DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12945640	PWD8682 C NBI SST DS5 MON	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12535260	HR1632-3 I USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
12535260	HR1632-3 I USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
12535260	HR1632-3 I USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12775720	OG1232L D BL	Ignitiontransformer	Lead	7439-92-1
12775720	OG1232L D BL	Adapter Gas connection	Lead	7439-92-1
10481640	PW418 EL NER WEK MF Sluice 3NAC380-415	Control electr.unit EW 235-A	Lead	7439-92-1
10085870	PW818 EL ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085590	PW413 EL ZER WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085880	PW818 EL ZER WEK WI MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10084990	PW811 EL ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085570	PW811 Ddir ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085560	PW811 Elred ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085600	PW413 EL ZER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085610	PW413 EL ZER FT WEK Mopstar3N380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085630	PW413SES EL ZER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085640	PW814 EL ZER WEK 3N AC380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10085670	PW814 EL ZER WEK WI 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085680	PW814 EL ZER WEK MF WI 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085690	PW814 EL ZER WEK FT 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085700	PW814 Elred ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10029670	PW418 EL ZER WEK Mopstar 3N AC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085890	PW818 EL ZER MF WI 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085910	PW818 EL ZER WEK FT 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085940	PW818 EL ZER WEK 3AC440/480/60	Control electr.unit EW 235-A	Lead	7439-92-1
10085950	PW818 Ddir ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10262770	KM2010 FLG EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10262770	KM2010 FLG EDST 230/50	Jet 0,27MM	Lead	7439-92-1
10262770	KM2010 FLG EDST 230/50	Jet 0,32MM	Lead	7439-92-1
10296760	PW418SES OH ZER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
7111050	KM2010 RU EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12291700	KM3010 UA EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12291700	KM3010 UA EDST 230/50	Holder	Lead	7439-92-1
12291700	KM3010 UA EDST 230/50	Burner tap 0,39	Lead	7439-92-1
12291700	KM3010 UA EDST 230/50	Burner tap 0,42	Lead	7439-92-1
7053560	KM2014 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7077460	KM6002 D EDST/LPT 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
7077460	KM6002 D EDST/LPT 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
7077460	KM6002 D EDST/LPT 230/50	Heater plate 1,8KW 230V	Lead	7439-92-1
7113300	KM2010 GB EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7111200	KM2012 AUS EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7116850	KM2010 NL EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7116860	KM2014 NL EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9326290	KM2014 SA EDST 220/60	Sealing ring 7,65x1,78	Lead	7439-92-1
9326290	KM2014 SA EDST 220/60	Jet 0,27MM	Lead	7439-92-1
9326290	KM2014 SA EDST 220/60	Jet 0,32MM	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
9966680	PW811 EL ZER WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
9973460	PW413 EL ZER WEK 3N AC380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
9974140	PW418 EL ZER WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10025590	PW818 Dind ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
9974190	PW818 EL ZER WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
9973990	PW814 EL ZER WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10025550	PW814 Dind ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085580	PW811 Dind ZER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10085710	PW418 EL ZER WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
11978020	B4312 A	Electronic unit	Lead	7439-92-1
11978030	B4847 A	Electronic unit	Lead	7439-92-1
11978080	B4847 NER	Electronic unit	Lead	7439-92-1
11978090	B4312 NER	Electronic unit	Lead	7439-92-1
11978150	B4847 NL	Electronic unit	Lead	7439-92-1
11978100	B4847 OER	Electronic unit	Lead	7439-92-1
11978110	B4312 OER	Electronic unit	Lead	7439-92-1
11978070	B4312 SER	Electronic unit	Lead	7439-92-1
12087650	B4826 OER	Electronic unit	Lead	7439-92-1
12087830	B4826 NL	Electronic unit	Lead	7439-92-1
7111110	KM2010 B EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7111080	KM2010 D EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7165380	KM2010 TR EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10615540	KM2010 F EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7051640	KM2010 I EDST 230/50	Jet 0,27MM	Lead	7439-92-1
7051640	KM2010 I EDST 230/50	Jet 0,32MM	Lead	7439-92-1
11978040	B4312 B	Electronic unit	Lead	7439-92-1
11978050	B4847 B	Electronic unit	Lead	7439-92-1
11978120	B4312 F	Electronic unit	Lead	7439-92-1
11978130	B4826 F	Electronic unit	Lead	7439-92-1
11978140	B4847 F	Electronic unit	Lead	7439-92-1
11978060	B4847 SER	Electronic unit	Lead	7439-92-1
12981380	PDR1309HP ANL LW -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12981390	PDR1509HP ANL LW -EU-	SMD- Diode STTH1R04A	Lead	7439-92-1
12291670	KM2010 UA EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12968860	KMDA7876-1 FL C CN 220/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12969800	KMDA7676-1 FL ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
12969810	KMDA7876-1 FL ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
13000860	PDR909 EL CP SOM SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12975520	BO8155-55PF XS2/CH EDLK 400/50	Heater element Hot air 400V	Lead	7439-92-1
12975520	BO8155-55PF XS2/CH EDLK 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12975520	BO8155-55PF XS2/CH EDLK 400/50	Heater element Top heat 400V	Lead	7439-92-1
12874890	BO8145L XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12940270	DGC7440 USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11987060	DGC7470 USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12940250	DGC7870X USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12940260	DGC7880X USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12975650	BO8190L XA1/AUS OBSW 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
11041460	KM6520 FR SA 220/60	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11041460	KM6520 FR SA 220/60	Heater plate 1,2KW 230V	Lead	7439-92-1
12048130	KM6521 FR RU 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12048130	KM6521 FR RU 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12048130	KM6521 FR RU 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
12048130	KM6521 FR RU 230/50	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
12291770	KM6520 FR UA 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12291770	KM6520 FR UA 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12291780	KM6520 FL UA 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12291780	KM6520 FL UA 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
10698970	PW814 EL GB MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10698980	PW814 Ddir GB WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10698990	PW814 Dind GB WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10699000	PW818 EL GB WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10699010	PW818 EL GB MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10699020	PW818 Ddir GB WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10699030	PW818 Dind GB WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10674950	PW413LAV OH ED 3NAC380-415 50/60	Control electr.unit EW 235-A	Lead	7439-92-1
10696370	PW413 EL S WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10748450	PW811 EL SOM WEK MF 3NAC 380-415/50/60	Control electr.unit EW 235-A	Lead	7439-92-1
10748550	PW811 EL SOM WEK MF 3AC 220-240/60	Control electr.unit EW 235-A	Lead	7439-92-1
10748460	PW811 EL SOM WEK MF 3AC 400/50	Control electr.unit EW 235-A	Lead	7439-92-1
10748570	PW814 EL SOM WEK MF 3NAC 380-415//50/60	Control electr.unit EW 235-A	Lead	7439-92-1
10748580	PW814 EL SOM WEK MF 3AC 220-240/60	Control electr.unit EW 235-A	Lead	7439-92-1
10748600	PW814 EL SOM WEK MF 3AC 400/50	Control electr.unit EW 235-A	Lead	7439-92-1
10748620	PW818 EL SOM WEK MF 3NAC 380-415/50/60	Control electr.unit EW 235-A	Lead	7439-92-1
10748630	PW818 EL SOM WEK MF 3AC 220-240/60	Control electr.unit EW 235-A	Lead	7439-92-1
10748640	PW818 EL SOM WEK MF 3AC 400/50	Control electr.unit EW 235-A	Lead	7439-92-1
10761310	PW811 EL B WEK MF 3AC 220-240V 50/60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10761330	PW814 EL B WEK MF 3AC 220-240V 50/60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10761340	PW818 EL B WEK MF 3AC 220-240V 50/60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10737000	PW418 EL B WEK 3 AC 220-240V 50/60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10759750	PW413 EL GB WEK Mopstar 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10736990	PW413 EL B WEK 3 AC 220-240V 50/60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10481800	PW818 EL ZER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481830	PW818 EL ZER FT MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481750	PW818 EL NER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10481810	PW818 EL NER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481760	PW818 EL OER WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481820	PW818 EL OER MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481780	PW818 EL ZER WEK 3AC400/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481840	PW818 EL ZER WEK ST 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10497170	PW814 EL ZER FT MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10481960	PW413 EL NAM WEK 3 AC 200-240V 60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10481970	PW413 OH NAM WEK 3AC200-208/220-240	Control electr.unit EW 235-A	Lead	7439-92-1
10481990	PW418 OH NAM WEK 3AC200-208/220-240	Control electr.unit EW 235-A	Lead	7439-92-1
10481980	PW418 EL NAM WEK 3 AC 200-240V 60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10482000	PW811 EL NAM WEK MF 3AC200-208/220-240	Control electr.unit EW 235-A	Lead	7439-92-1
10482010	PW814 EL NAM WEK MF 3AC200-208/220-240	Control electr.unit EW 235-A	Lead	7439-92-1
10482020	PW814 Dind NAM WEK MF 3AC200-208/220-240	Control electr.unit EW 235-A	Lead	7439-92-1
10482030	PW818 EL NAM WEK MF 3AC200-208/220-240	Control electr.unit EW 235-A	Lead	7439-92-1
10482040	PW818 Dind NAM WEK MF 3AC200-208/220-240	Control electr.unit EW 235-A	Lead	7439-92-1
10698900	PW413 EL GB WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10698910	PW418 EL GB WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
10698930	PW811 EL GB WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10698940	PW811 Ddir GB WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10698950	PW811 Dind GB WEK 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10698960	PW814 EL GB WEK 3N AC 380-415V 50Hz	Control electr.unit EW 235-A	Lead	7439-92-1
7132770	KM2052 FLG EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7132770	KM2052 FLG EDST 230/50	Jet 0,27MM	Lead	7439-92-1
7132770	KM2052 FLG EDST 230/50	Jet 0,32MM	Lead	7439-92-1
7111220	KM2054 AUS EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7116880	KM2054 NL EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7307350	KM2030 USA EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
7138120	KM2050 MEX EDST 120/60	Sealing ring 7,65x1,78	Lead	7439-92-1
7138120	KM2050 MEX EDST 120/60	Jet 0,27MM	Lead	7439-92-1
7138120	KM2050 MEX EDST 120/60	Jet 0,32MM	Lead	7439-92-1
7361830	KM2052 SGP EDST 230/50	Jet 0,27MM	Lead	7439-92-1
7361830	KM2052 SGP EDST 230/50	Jet 0,32MM	Lead	7439-92-1
7761050	KM3010 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7761050	KM3010 R01 EDST 230/50	Holder	Lead	7439-92-1
7761050	KM3010 R01 EDST 230/50	Burner tap 0,39	Lead	7439-92-1
7761050	KM3010 R01 EDST 230/50	Burner tap 0,42	Lead	7439-92-1
9101240	KM3010 NL EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
9101240	KM3010 NL EDST 230/50	Holder	Lead	7439-92-1
9101240	KM3010 NL EDST 230/50	Burner tap 0,39	Lead	7439-92-1
9101240	KM3010 NL EDST 230/50	Burner tap 0,42	Lead	7439-92-1
9062070	KM2052 SA EDST 220/60	Sealing ring 7,65x1,78	Lead	7439-92-1
9062070	KM2052 SA EDST 220/60	Jet 0,27MM	Lead	7439-92-1
9062070	KM2052 SA EDST 220/60	Jet 0,32MM	Lead	7439-92-1
7111070	KM2034 RU EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12291680	KM2034 UA EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
10828050	PW418 EL GB WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10828070	PW814 EL GB WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10828090	PW818 EL GB WEK MF 3NAC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10828140	PW418 EL GB WEK Mopstar 3N AC380-415/50	Control electr.unit EW 235-A	Lead	7439-92-1
10853700	PW413 EL ZER MF Mopstar 3AC220-240 50/60	Control electr.unit EW 235-A	Lead	7439-92-1
10853710	PW413 EL ZER FT MF Mopst 3/220-240 50/60	Control electr.unit EW 235-A	Lead	7439-92-1
11095390	PW818 EL SOM WEK MF 3 AC 440V 60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11095370	PW814 EL SOM WEK MF 3 AC 440V 60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11095360	PW811 EL SOM WEK MF 3 AC 440V 60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
11374400	PW413SES EL ROK MF 3NAC380-415/60	Control electr.unit EW 235-A	Lead	7439-92-1
11374390	PW413 EL ROK WEK MF 3NAC380-415/60	Control electr.unit EW 235-A	Lead	7439-92-1
12975540	BO8155PF XJ3/J EDLK 200/50/60	Heater element Top heat 200V	Lead	7439-92-1
12975540	BO8155PF XJ3/J EDLK 200/50/60	Heater element Bottom heat	Lead	7439-92-1
12970740	KMDA7676-1 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12970750	KMDA7676-1 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12968770	KMDA7676-1 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12968780	KMDA7676-1 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12968810	KMDA7676-1 FL OER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
7054070	KM2032 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7054100	KM2052 R01 EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7051780	KM2033 I EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7113320	KM2032 GB EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7113340	KM2054 GB EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
7132760	KM2032 FLG EDST 230/50	Sealing ring 7,65x1,78	Lead	7439-92-1
12693050	DG8330-60F XS4/CH EDLK 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12470540	G7197 SCVi XXL IB ED230 1,9 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470530	G7191 SCVi IB ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470520	G7131 SCi IB ED230 1,9 CLST AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470560	G7793 SCVi IB OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472560	G7131 SCi OE1 ED230 1,9 CLST AutoD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472570	G7137 SCi XXL OE1 ED230 1,9 CLST AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469720	G7797 SCVi XXL NER OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469710	G7793 SCVi NER OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469700	G7777 SCVi XXL NER OS230 1,9 ADos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469690	G7771 SCVi NER OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469680	G7197 SCVi XXL NER ED230 1,9 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469670	G7191 SCVi NER ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472580	G7191 SCVi OE1 ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472590	G7197 SCVi XXL OE1 ED230 1,9 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12472600	G7731 SCi OE1 OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472610	G7793 SCVi OE1 OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472620	G7797 SCVi XXL OE1 OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469660	G7191 SCVi GB ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469840	G7131 SCi TR ED230 1,9 CLST AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469850	G7191 SCVi TR ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469860	G7197 SCVi XXL TR ED230 1,9 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12534150	DAH4980 D OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12533860	DAH1650 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12533880	DAH1850 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12520660	DA9299W C CN BLBO 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12469590	G7197 SCVi XXL A ED230 1,9 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12535050	DAS4620 CH MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12541030	DAS4520 CH MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12470490	G7191 SCVi I ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470500	G7771 SCVi I OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470510	G7793 SCVi I OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469600	G7731 SCi A OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469610	G7737 SCi XXL A OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469620	G7771 SCVi A OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469630	G7777 SCVi XXL A OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469640	G7793 SCVi A OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469650	G7797 SCVi XXL A OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12405670	PDR307HP P ANL SST -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12470040	G7191 SCVi F ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470050	G7197 SCVi XXL F ED230 1,9 AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470070	G7771 SCVi F OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470080	G7777 SCVi XXL F OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470110	G7793 SCVi F OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12470140	G7797 SCVi XXL F OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472510	G7771 SCVi MER OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472530	G7777 SCVi XXL MER OS230 1,9 ADos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472540	G7793 SCVi MER OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472550	G7797 SCVi XXL MER OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12545640	DAH2960 GB OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12545670	DAH4970 GB CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12545680	DAH4970 GB PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12545650	DAH4980 GB OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12531610	G7130 SC AUS ED230 1,9 AutoD CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531620	G7130 SCU AUS ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531640	G7130 SCi AUS ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12472810	G7771 SCVi OE1 OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531650	G7180 SCVi AUS ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531660	G7185 SCVi XXL AUS ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531670	G7604 SCU AUS ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531690	G7609 SCi XXL AUS ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531680	G7609 SCU XXL AUS ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531700	G7659 SCVi XXL AUS OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531710	G7719 SCi XXL AUS OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531720	G7799 SCVi XXL AUS OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12507550	KMDA7676 FL-U ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
12507530	KMDA7676 FL-A ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
12531730	G7939 SCi XXL AUS OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12524580	KMDA7676 FL-U UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12524590	KMDA7676 FL-A UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12526910	KM7576-2 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12526910	KM7576-2 FL NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12591560	DAH1650 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12533900	DAH1950 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12533920	DAH2660 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12533940	DAH2860 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12533960	DAH2960 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12533990	DAH2960EXTA D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12469870	G7731 SCi TR OS230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12534020	DAH4870 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12534040	DAH4870 D GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12534070	DAH4970 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12534090	DAH4970 D CONO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12534120	DAH4970 D GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12534130	DAH4970 D PABO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12555650	DAH1852 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12469880	G7797 SCVi XXL TR OS230 1,9 K2O AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12534180	DAH1650 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12534190	DAH1950 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12472630	G7131 SCi UA ED230 1,9 CLST AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12534200	DAH2960 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12472640	G7191 SCVi UA ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12480510	G7191 SCVi RU ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12531740	G7989 SCVi XXL AUS OS/CS230 1,9 K2O AD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12534210	DAH4970 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12534220	DAH4970 CH GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12534230	DAH4980 CH OBSW/MATT 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12452160	H2861-1BP RU OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12459870	G7673 SCVi RU OS230 1,9 AutoDos Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12226293	Power-/Control unit EPL 8832	SMD- Diode STTH1R04A	Lead	7439-92-1
12226312	Power-/Control unit EPL 8835-NA	SMD- Diode STTH1R04A	Lead	7439-92-1
12524620	KMDA7676 FL-U F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12524630	KMDA7676 FL-A F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12010070	PDR528ROP G AUS IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12010090	PDR928 G AUS IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12459880	G7760 SCVi RU OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12380720	DAC2247 XU1/USA EDST 120/60 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12527220	KM7576-2 FL F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527220	KM7576-2 FL F 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12459890	G7980 SCVi RU OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459900	G7985 SCVi XXL RU OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12524610	H2455BP F OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12524610	H2455BP F OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12523710	H2465B EU1 OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12523710	H2465B EU1 OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12523720	H2465BP EU1 OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12523720	H2465BP EU1 OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12523730	H2455B EU1 OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12523730	H2455B EU1 OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12523750	H2455BP EU1 OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12523750	H2455BP EU1 OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12505350	KMDA7676 FL-A BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12505400	KMDA7676 FL-U BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12512800	KMDA7676 FL-U TR 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11791600	HR1935-3 G DF GR USA EDST/CLST120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11791600	HR1935-3 G DF GR USA EDST/CLST120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791600	HR1935-3 G DF GR USA EDST/CLST120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12500270	DGC7640 BR OBSW 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12512540	KMDA7676 FL-A DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12512550	KMDA7676 FL-U DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12508690	H2456B I OBSW/EDST-LOOK230/50<3KW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12508690	H2456B I OBSW/EDST-LOOK230/50<3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12462800	G7650 SCVi ZA OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12170430	H2861BP UA EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12170430	H2861BP UA EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12459850	G7180 SCVi RU ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12462810	G7985 SCVi XXL ZA OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12459860	G7293 SCVi RU ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445300	G7130 SC I BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445310	G7130 SC I ED230 1,9 AutoDos CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12452150	H2861-1B RU EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12452150	H2861-1B RU EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12452140	H2861-1B RU OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12452140	H2861-1B RU OBSW 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12452160	H2861-1BP RU OBSW 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12445460	G7650 SCVi I OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445470	G7655 SCVi XXL I OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445480	G7980 SCVi I OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445490	G7985 SCVi XXL I OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12497120	DGM7640 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12496790	DGC7640 HC Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12496780	DGC7660 HC Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12496800	DGC7640-55 HC PRO CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12526070	DA9299W F BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12526100	DA9299W IB BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12526500	DA9299W NER BLBO 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12405660	PDR307HP P ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12405700	PDR508HP P ANL SST -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12405730	PDR908HP P ANL SST -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12527320	KM7576-2 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527320	KM7576-2 FL AUS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12521000	DA9299W CH BLBO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12527280	KM7576 FL UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527280	KM7576 FL UA 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12527300	KM7576-2 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12527300	KM7576-2 FL GB 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12469560	G7131 SCiA ED230 1,9 CLST AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469570	G7137 SCiA ED230 1,9 CLST AD 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12469580	G7191 SCVi A ED230 1,9 AutoDos 125J	Drain pump 220-240V 50HZ	Lead	7439-92-1
12488250	KM7466 FL RU 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12397570	H7870BMX USA OBSW/MATT 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
12445320	G7180 SCVi I ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445330	G7185 SCVi XXL I ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445340	G7210 SC I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445350	G7210 SC I ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12466830	G7760 SCVi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445360	G7210 SCU I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445370	G7210 SCU I ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12466840	G7765 SCVi XXL OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445380	G7210 SCi I ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12466850	G7788 SCVi XXL OE1 OS230 1,9 K2oAutoD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445390	G7260 SCVi I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445410	G7293 SCVi I ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12445400	G7265 SCVi XXL I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12506040	DAS4620 D MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12445430	G7600 SC I ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445440	G7600 SCU I ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12445450	G7600 SCi I ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12506050	DAS4920 D MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12405740	PDR507HP P Special ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12397540	H7880BPX USA OBSW/MATT 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
12397540	H7880BPX USA OBSW/MATT 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12397540	H7880BPX USA OBSW/MATT 120/240/60	Heater element Top heat	Lead	7439-92-1
12591570	DAH1950 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12649100	G5410 SCi D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649260	G5410 SCi D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649140	G5410 D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649180	G5410 U D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649200	G5410 U D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12600510	DGC7440 HCX Pro XS1/CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12600520	DGC7460 HCX Pro XS1/CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12600530	DGC7840 HCX Pro XS1/CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12649240	G5410 i D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12600540	DGC7860 HCX Pro XS1/CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12649250	G5410 i D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649160	G5410 SC D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649170	G5410 SC D ED230 1,9 ActivePlus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649220	G5410 SCU D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12639080	H2469B D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12639080	H2469B D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12639090	H2469BP D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12639090	H2469BP D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12649230	G5410 SCU D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649330	G5433 SC D BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649340	G5433 SCU D ED230 1,9 Active Plus CS E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649360	G5433 SCi D ED230 1,9 Active Plus CS E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649380	G5463 SCVi D ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649270	G5415 i XXL D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12515070	KMDA7876 FL-U CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12515890	KMDA7876 FL-A DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12515910	KMDA7876 FL-U DFS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12514840	KMDA7876 FL-U I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12514930	KMDA7876 FL-U IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12515270	KMDA7876 FL-A ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
12515280	KMDA7876 FL-U ROK 220/60	Induction coil G5 Octa OL L100	Lead	7439-92-1
12518560	KMDA7876 FL-U C CN 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12549310	DGC7440 HCX Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12549320	DGC7445 HCX Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12549330	DGC7460 HCX Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12549340	DGC7465 HCX Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12549350	DGC7840 HCX Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12549360	DGC7845 HCX Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12549370	DGC7860 HCX Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12549380	DGC7865 HCX Pro XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12226292	Power-/Control unit EPL 8832	SMD- Diode STTH1R04A	Lead	7439-92-1
12491780	KMDA7876 FL-U C ANC 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12491790	KMDA7876 FL-A C ANC 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12604440	H2459E D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12604440	H2459E D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12604450	H2459I D OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12604450	H2459I D OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12620220	G5451 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653270	G5410 A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653280	G5410 SC A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653290	G5410 SCU A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653300	G5410 SCU A ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12624320	H7440BPX SER PEBE 230/50	Heater element Top heat 230V	Lead	7439-92-1
12653310	G5410 i A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12624330	H7440BMX SER PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12624340	H7464BPX SER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12624350	H7840BPX SER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12624360	H7840BMX SER PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12624370	H7860BPX SER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619270	H7440BPX NER PEBE 230/50	Heater element Top heat 230V	Lead	7439-92-1
12619390	H7464BPX NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619400	H7840BPX NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619440	H7860BPX NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619380	H7440BMX NER PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12619410	H7840BMX NER PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12653320	G5410 i A ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653330	G5410 SCi A OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653340	G5410 SCi A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653350	G5410 SCi A ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653370	G5415 SCi XXL A ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653380	G5450 Vi A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653390	G5450 SCVi A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649280	G5415 SCi XXL D ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12649390	G5468 SCVi XXL D ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12594780	DGC7440 HCX Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12613810	DGC7445 HCX Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12613820	DGC7460 HCX Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12613840	DGC7465 HCX Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12613870	DGC7840 HCX Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12613880	DGC7845 HCX Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12613890	DGC7860 HCX Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12613900	DGC7865 HCX Pro D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12640840	H7440BMX GB PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12640850	H7464BPX GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12640860	H7840BMX GB PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12640870	H7860BPX GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12599000	H7440BPX CH PEBE 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12599000	H7440BPX CH PEBE 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12599020	H7464BPX CH PEBE 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12599020	H7464BPX CH PEBE 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12599020	H7464BPX CH PEBE 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12599030	H7840BPX CH PEBE 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12599050	H7860BPX CH PEBE 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12599050	H7860BPX CH PEBE 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12599010	H7440BMX CH PEBE 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12599040	H7840BMX CH PEBE 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12405750	PDR300-08HP P ANL LW -CH-	SMD- Diode STTH1R04A	Lead	7439-92-1
12512270	G7180 C SCVi CN ED220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12524780	H2761-1B HK EDST/CLST 125 Edition 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12524780	H2761-1B HK EDST/CLST 125 Edition 230/50	Heater element Top heat 230V	Lead	7439-92-1
12529780	DAD4841 KZ OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12405760	PDR500-08HP P ANL LW -CH-	SMD- Diode STTH1R04A	Lead	7439-92-1
12515930	G7184 C SCVi CN ED220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12405770	PDR900-08HP P ANL LW -CH-	SMD- Diode STTH1R04A	Lead	7439-92-1
12544510	G7654 C SCVi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12565890	DAC2247 USA EDST 120/60 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12491120	DAS4631 RU OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12491130	DAS4931 RU OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12544470	G7604 C SC CN BW220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12544480	G7604 C SCU CN BW220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12544490	G7604 C SCi CN ED220/50 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12544520	G7714 C SCi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12544560	G7764 C SCVi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12544570	G7784 C SCVi CN OS220/50 1,9 K2O ADos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12544580	G7934 C SCi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12544600	G7994 C SCVi CN OS/CS220/50 1,9K2O AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12598320	G7132 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12548900	H7440BPX D PEBE 230/50	Heater element Top heat 230V	Lead	7439-92-1
12548950	H7464BPX D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12548970	H7840BPX D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12591580	DAH2960 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12555950	DAC2940 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12555940	DAC2940 D WSMA 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12555930	DAC2240 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12555920	DAC2240 D WSMA 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12556010	DAC4940 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12555990	DAC4940 D WSMA 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12556000	DAC4940 D MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12555980	DAC4240 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12555960	DAC4240 D WSMA 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12555970	DAC4240 D MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12549640	DAC4943EXTA D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12549760	DAC2940 GB EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12549770	DAC4940 GB WSMA 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12549610	DAC2940 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12549620	DAC4240 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12549630	DAC4940 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11985093	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12559980	DAC2940 TR EDST 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12559990	DAC4240 TR EDST 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12560000	DAC4940 TR MASW 230/50 TL	SMD- Diode STTH1R04A	Lead	7439-92-1
12512080	G7130 C SC CN BW220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12512240	G7130 C SCi CN ED220/50 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12601011	Power electron,unit EL 4006-B-A	SMD- Diode STTH1R04A	Lead	7439-92-1
12591480	DGC7860 HCX Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12591490	DGC7865 HCX Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12601770	PF401 U DAC LW WB 125 Edition	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12601760	PF401 U DAC SST WB 125 Edition	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12146580	H2465B RU OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12146580	H2465B RU OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12146550	H2465BP RU OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12146550	H2465BP RU OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12146590	H2761B RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12146590	H2761B RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12146600	H2761BP RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12146600	H2761BP RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12146750	H2861B RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12146750	H2861B RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12146760	H2861BP RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12146760	H2861BP RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12146620	H2861B RU OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12146620	H2861B RU OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12146720	H2861BP RU OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12146720	H2861BP RU OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12515670	KMDA7876 FL-A NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12515690	KMDA7876 FL-U NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12528280	KMDA7876 FL-U F 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12515060	KMDA7876 FL-A CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12548990	H7860BPX D PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12548910	H7440BMX D PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12548980	H7840BMX D PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12584230	H2455B I OBSW 230/50<3KW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12584230	H2455B I OBSW 230/50<3KW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12584300	H2457BP I OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12584300	H2457BP I OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12583230	PDR508EL CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12583350	PDR508EL CH SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12467321	Power electron.unit EL 4006-A-A	SMD- Diode STTH1R04A	Lead	7439-92-1
12385560	BOM8340L XE1/D OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12513340	KMDA7876 FL-A BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12513350	KMDA7876 FL-U BNE 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12515460	KMDA7876 FL-A GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12515480	KMDA7876 FL-U GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12002210	CS7612 FL J 200/50-60	Induction coil G5 Octa OL L100	Lead	7439-92-1
12002210	CS7612 FL J 200/50-60	Induction coil G5 Octa OL L250	Lead	7439-92-1
11612857	Power-/Control unit ELP 7757 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12591420	DGC7440 HCX Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12591430	DGC7445 HCX Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12591440	DGC7460 HCX Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12591450	DGC7465 HCX Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12591460	DGC7840 HCX Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12591470	DGC7845 HCX Pro R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12507670	KMDA7676 FL-U I 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12118430	DGC7460 HC Pro SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118420	DGC7440 HC Pro SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120870	DGC7865 HCX Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118440	DGC7640 HC Pro SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118470	DGC7660 HC Pro SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118490	DGC7840 HC Pro SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108090	DGC7445 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108250	DGC7465 HCX Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108700	DGC7865 HCX Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108690	DGC7865 HCX Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108680	DGC7865 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108670	DGC7865 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118500	DGC7860 HC Pro SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090780	DGC7340 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090800	DGC7440 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090810	DGC7440 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090820	DGC7440 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090830	DGC7440 HCX Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090840	DGC7440 HCX Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090880	DGC7440 HCX Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090890	DGC7460 HC Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090900	DGC7460 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090910	DGC7460 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090920	DGC7460 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108370	DGC7645 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108390	DGC7660 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108410	DGC7660 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108420	DGC7660 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108450	DGC7665 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108460	DGC7665 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108470	DGC7665 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108480	DGC7840 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108510	DGC7840 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108520	DGC7840 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108530	DGC7840 HCX Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108540	DGC7840 HCX Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108550	DGC7845 HC Pro BNE BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108560	DGC7845 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108570	DGC7845 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108580	DGC7845 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108590	DGC7845 HCX Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108600	DGC7845 HCX Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108610	DGC7860 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108620	DGC7860 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108630	DGC7860 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108640	DGC7860 HCX Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108650	DGC7860 HCX Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108660	DGC7865 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12091440	DGC7840 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091470	DGC7840 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091480	DGC7840 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091670	DGC7840 HCX Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091680	DGC7840 HCX Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091690	DGC7840 HCX Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091700	DGC7845 HC Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091710	DGC7845 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091730	DGC7845 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091740	DGC7845 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091750	DGC7845 HCX Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091760	DGC7845 HCX Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091770	DGC7845 HCX Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091800	DGC7860 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091810	DGC7860 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091820	DGC7860 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091860	DGC7860 HCX Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091870	DGC7860 HCX Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091880	DGC7865 HC Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091910	DGC7865 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091920	DGC7865 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091950	DGC7865 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091960	DGC7865 HCX Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091970	DGC7865 HCX Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090950	DGC7460 HCX Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090960	DGC7460 HCX Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090980	DGC7540 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090990	DGC7640 HC Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091000	DGC7640 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11507800	KM7689 FL NER 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11791530	HR1724-3 G DF USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11791530	HR1724-3 G DF USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791530	HR1724-3 G DF USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12091020	DGC7640 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091030	DGC7640 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091040	DGC7645 HC Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091060	DGC7645 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091070	DGC7645 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091080	DGC7645 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091150	DGC7660 HC Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091180	DGC7660 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091230	DGC7660 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091260	DGC7660 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091290	DGC7665 HC Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091320	DGC7665 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091350	DGC7665 HC Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091420	DGC7665 HC Pro NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091430	DGC7840 HC Pro NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100570	DGC7665 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100580	DGC7665 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120180	DGC7440 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120210	DGC7440 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120290	DGC7440 HCX Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120330	DGC7440 HCX Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120340	DGC7460 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120350	DGC7460 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120360	DGC7460 HCX Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120370	DGC7460 HCX Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120400	DGC7640 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120430	DGC7640 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120440	DGC7645 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120460	DGC7645 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120480	DGC7645 HC Pro IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120500	DGC7660 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120510	DGC7660 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120520	DGC7840 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120530	DGC7840 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120550	DGC7840 HCX Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120560	DGC7840 HCX Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120570	DGC7845 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120580	DGC7845 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120590	DGC7845 HC Pro IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100710	DGC7845 HCX Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100730	DGC7845 HCX Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100750	DGC7860 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100760	DGC7860 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100770	DGC7860 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100890	DGC7860 HCX Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100900	DGC7860 HCX Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100910	DGC7865 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100920	DGC7865 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100930	DGC7865 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100940	DGC7865 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100960	DGC7865 HCX Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12100970	DGC7865 HCX Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100980	DGC7865 HCX Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100410	DGC7645 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100420	DGC7645 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100460	DGC7645 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100490	DGC7645 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100510	DGC7660 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100520	DGC7660 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100530	DGC7660 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100540	DGC7660 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100550	DGC7665 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100560	DGC7665 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108020	DGC7440 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108030	DGC7440 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108040	DGC7440 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108050	DGC7440 HCX Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108060	DGC7440 HCX Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108070	DGC7445 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108100	DGC7445 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108120	DGC7445 HCX Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108130	DGC7445 HCX Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108150	DGC7460 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108160	DGC7460 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108180	DGC7460 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108190	DGC7460 HCX Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108200	DGC7460 HCX Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108210	DGC7465 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108220	DGC7465 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108230	DGC7465 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108240	DGC7465 HCX Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108260	DGC7541 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108270	DGC7640 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108320	DGC7640 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108330	DGC7640 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108350	DGC7645 HC Pro BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108360	DGC7645 HC Pro BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120600	DGC7860 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120630	DGC7860 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120650	DGC7860 HCX Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120660	DGC7860 HCX Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120680	DGC7865 HC Pro IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120690	DGC7865 HC Pro IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12120700	DGC7865 HC Pro IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101300	DGC7460 HC Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101310	DGC7460 HC Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101320	DGC7460 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101330	DGC7460 HCX Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101340	DGC7460 HCX Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101370	DGC7660 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101540	DGC7860 HC Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101670	DGC7860 HC Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101680	DGC7860 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101690	DGC7860 HCX Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101700	DGC7860 HCX Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101710	DGC7865 HC Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101720	DGC7865 HC Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101740	DGC7865 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101750	DGC7865 HCX Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101760	DGC7865 HCX Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12108000	DGC7340 HC Pro BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12091990	DGC7865 HCX Pro NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081620	DGC7860 HC Pro CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081640	DGC7860 HCX Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081630	DGC7860 HCX Pro CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081650	DGC7860 HCX Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081660	DGC7865 HC Pro CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081670	DGC7865 HC Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081680	DGC7865 HC Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081690	DGC7865 HC Pro CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11612854	Power-/Control unit ELP 7757 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
12254870	PDR516ROP SL G ANL IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254950	PDR516ROP SL G ANL IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254970	PDR516COP SL G ANL IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254980	PDR516COP SL G ANL IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12255000	PDR516TOP SL G ANL IG-GS E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12160280	H7260B NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12160290	H7260B NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12160300	H7260BP NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12160310	H7260BP NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12198290	KM7594 FR NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12187650	KM7899-2 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12198300	KM7594 FL NER 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12187600	KM7575-2 FL AUS 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12187600	KM7575-2 FL AUS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12187590	KM7594-2 FL AUS 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12095130	DGC7845 HCX Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095140	DGC7845 HCX Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095270	DGC7860 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095280	DGC7860 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095290	DGC7860 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095500	DGC7860 HCX Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095530	DGC7860 HCX Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095540	DGC7865 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095560	DGC7865 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095580	DGC7865 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095590	DGC7865 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095600	DGC7865 HCX Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095610	DGC7865 HCX Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095620	DGC7865 HCX Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081260	DGC7460 HC Pro CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081270	DGC7460 HC Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081280	DGC7460 HC Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081290	DGC7460 HC Pro CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081300	DGC7460 HCX Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081420	DGC7660 HC Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081430	DGC7660 HC Pro CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081590	DGC7860 HC Pro CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081600	DGC7860 HC Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081610	DGC7860 HC Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12092200	PW6241 EH NAM IG 2AC 240V 60Hz R	Control electr.unit EW 235-A	Lead	7439-92-1
12092330	PW6321 EH NAM IG 2AC 240V 60Hz R	Control electr.unit EW 235-A	Lead	7439-92-1
12308740	DA6698W UA OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12308750	DA6698W UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12308770	DA6698D UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12226245	Power-/Control unit EPL 8830	SMD- Diode STTH1R04A	Lead	7439-92-1
11816610	HR1936-3 LP DF GD BR EDST/CLST127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11816610	HR1936-3 LP DF GD BR EDST/CLST127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11816610	HR1936-3 LP DF GD BR EDST/CLST127/220/60	Heater element Hot air 208V	Lead	7439-92-1
12423580	DGC7870X USA OBSW/MATT 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12423590	DGC7880X USA OBSW/MATT 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12485580	KM7466 FL IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12485570	KM7466 FR IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12457460	KM7576-2 FL R02 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12457460	KM7576-2 FL R02 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12427690	DG8340L XE1/R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12467322	Power electron.unit EL 4006-A-A	SMD- Diode STTH1R04A	Lead	7439-92-1
12290180	DGS7500 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12488190	KM7466 FL GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12226246	Power-/Control unit EPL 8830	SMD- Diode STTH1R04A	Lead	7439-92-1
12509600	KMDA7676 FL-U CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12509220	KMDA7676 FL-A GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12509230	KMDA7676 FL-U GB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12509180	KMDA7676 FL-U IB 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12295000	H2455EP XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295000	H2455EP XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12295010	H2457EP XE1/D OBSW/EDST-LOOK 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295010	H2457EP XE1/D OBSW/EDST-LOOK 230/50	Heater element Top heat 230V	Lead	7439-92-1
12295110	H2457EP XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295110	H2457EP XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12295070	H2457EP XE1/D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295070	H2457EP XE1/D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12295280	H2455EP XS2/CH OBSW/EDST-LOOK 400/50	Heater element Hot air 400V	Lead	7439-92-1
12295280	H2455EP XS2/CH OBSW/EDST-LOOK 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12295280	H2455EP XS2/CH OBSW/EDST-LOOK 400/50	Heater element Top heat 400V	Lead	7439-92-1
12291800	KM6565 FR UA 230/50	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
12291800	KM6565 FR UA 230/50	Heater plate 1,2KW 230V	Lead	7439-92-1
12109250	DGC7460 HC Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109260	DGC7460 HC Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109270	DGC7460 HC Pro C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109410	DGC7460 HCX Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109420	DGC7460 HCX Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109480	DGC7660 HC Pro C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109590	DGC7860 HC Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109600	DGC7860 HC Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109610	DGC7860 HC Pro C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109630	DGC7860 HCX Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12092190	PW6241 EH NAM SST MF 2AC 240V 60Hz R	Control electr.unit EW 235-A	Lead	7439-92-1
12116450	DGC7460 HC Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116480	DGC7460 HC Pro I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116540	DGC7460 HC Pro I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116590	DGC7460 HCX Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116630	DGC7460 HCX Pro I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116770	DGC7660 HC Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116860	DGC7840 HC Pro I BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116920	DGC7840 HC Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116980	DGC7840 HC Pro I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12117030	DGC7840 HCX Pro I BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12117110	DGC7840 HCX Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12117190	DGC7840 HCX Pro I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12117550	DGC7860 HC Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12117580	DGC7860 HC Pro I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12117600	DGC7860 HC Pro I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12117630	DGC7860 HCX Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12117640	DGC7860 HCX Pro I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093620	DGC7340 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093660	DGC7440 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093680	DGC7440 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093700	DGC7440 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093750	DGC7440 HCX Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093770	DGC7440 HCX Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093790	DGC7440 HCX Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118570	DGC7340 HC Pro TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118580	DGC7440 HC Pro TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118590	DGC7440 HC Pro TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118600	DGC7440 HCX Pro TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118610	DGC7440 HCX Pro TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118620	DGC7460 HC Pro TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118630	DGC7460 HC Pro TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118640	DGC7460 HCX Pro TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118650	DGC7460 HCX Pro TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118660	DGC7840 HC Pro TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118670	DGC7840 HC Pro TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118680	DGC7840 HCX Pro TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118690	DGC7840 HCX Pro TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118700	DGC7860 HC Pro TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118710	DGC7860 HC Pro TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118720	DGC7860 HCX Pro TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12118730	DGC7860 HCX Pro TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116020	DGC7440 HC Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116050	DGC7440 HC Pro I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116100	DGC7440 HC Pro I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116130	DGC7440 HCX Pro I BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116360	DGC7440 HCX Pro I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116400	DGC7440 HCX Pro I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12116420	DGC7460 HC Pro I BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094580	DGC7645 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094630	DGC7645 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094650	DGC7645 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094680	DGC7645 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094710	DGC7660 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094730	DGC7660 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094760	DGC7660 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094790	DGC7660 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094840	DGC7665 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094860	DGC7665 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094870	DGC7665 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094890	DGC7665 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095010	DGC7840 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095020	DGC7840 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095030	DGC7840 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095040	DGC7840 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095050	DGC7840 HCX Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095060	DGC7840 HCX Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095070	DGC7840 HCX Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095080	DGC7845 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095090	DGC7845 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095100	DGC7845 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095110	DGC7845 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12095120	DGC7845 HCX Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094040	DGC7445 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094070	DGC7445 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094100	DGC7445 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094120	DGC7445 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094130	DGC7445 HCX Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094140	DGC7445 HCX Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094150	DGC7445 HCX Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094160	DGC7460 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094170	DGC7460 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094190	DGC7460 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094230	DGC7460 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094300	DGC7460 HCX Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094310	DGC7460 HCX Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094320	DGC7465 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094330	DGC7465 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094340	DGC7465 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094430	DGC7465 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094460	DGC7465 HCX Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094470	DGC7465 HCX Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094490	DGC7465 HCX Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094520	DGC7640 HC Pro F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094530	DGC7640 HC Pro F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12094540	DGC7640 HC Pro F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12094560	DGC7640 HC Pro F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170750	DGC7665 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170740	DGC7665 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170760	DGC7665 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106480	DGM7340 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107760	DGM7440 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106510	DGM7440 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170670	DGC7645 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170650	DGC7645 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170690	DGC7645 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11171010	DGC7865X NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11171020	DGC7865X NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170980	DGC7865 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106590	DGM7640 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106600	DGM7640 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106610	DGM7640 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106620	DGM7640 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106630	DGM7840 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106640	DGM7840 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106650	DGM7840 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106660	DGM7840 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106670	DGM7845 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106680	DGM7845 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106690	DGM7845 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106700	DGM7845 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170510	DGC7460X NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170540	DGC7840X NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170530	DGC7840X NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170560	DGC7845X NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170550	DGC7845X NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170620	DGC7640 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170570	DGC7640 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170590	DGC7640 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170730	DGC7660 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170710	DGC7660 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170720	DGC7660 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170800	DGC7840 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170770	DGC7840 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170790	DGC7840 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170830	DGC7845 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170810	DGC7845 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170820	DGC7845 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170910	DGC7860 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170850	DGC7860 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170860	DGC7860 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170950	DGC7860X NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170930	DGC7860X NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11171000	DGC7865 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170960	DGC7865 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11137890	DG7440 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134220	DG7240 I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134240	DG7240 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134260	DG7440 I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134270	DG7440 I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134280	DG7440 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099710	DG7140 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099760	DG7240 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099780	DG7240 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099800	DG7240 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100450	DG7240 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100460	DG7440 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100470	DG7440 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100480	DG7440 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100490	DG7440 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146240	DG7240 SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169910	DG7140 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169920	DG7240 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169930	DG7240 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169940	DG7240 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169950	DG7440 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169960	DG7440 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169970	DG7440 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101080	DGC7440 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106320	DG7140 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106360	DG7240 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106380	DG7240 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106400	DG7440 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106440	DG7440 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094410	DG7140 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094420	DG7240 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094430	DG7440 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168410	DG7140 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168440	DG7240 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168430	DG7240 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11168420	DG7240 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168450	DG7440 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168470	DG7440 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168460	DG7440 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11145420	DG7440 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11145430	DG7440 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11145440	DG7440 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11115340	DG7240 TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11115370	DG7240 TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11137870	DG7240 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11137880	DG7440 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11137910	DG7440 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11137900	DG7440 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146900	DGC7640 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146880	DGC7640 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146890	DGC7640 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146950	DGC7645 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146920	DGC7645 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146940	DGC7645 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146980	DGC7840 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146960	DGC7840 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146970	DGC7840 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149100	DGC7845 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149090	DGC7845 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149070	DGC7845 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149160	DGC7860 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149130	DGC7860 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149110	DGC7860 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149190	DGC7860X IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149200	DGC7860X IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149210	DGC7865 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149220	DGC7865 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149240	DGC7865 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159240	DGC7840X TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169360	DGC7440 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169330	DGC7440 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169350	DGC7440 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139030	DGC7860 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139040	DGC7860 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139050	DGC7860X NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139060	DGC7860X NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139070	DGC7860X NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139090	DGC7865 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139100	DGC7865 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139110	DGC7865 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139140	DGC7865X NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139150	DGC7865X NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139160	DGC7865X NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11154330	DGC7440 SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11154340	DGC7460 SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11154360	DGC7660 SER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146680	DGC7440 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146700	DGC7440 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146710	DGC7440X IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146760	DGC7440X IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146790	DGC7460 IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146800	DGC7460 IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146810	DGC7460X IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146820	DGC7460X IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146830	DGC7840X IB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146870	DGC7840X IB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169690	DGC7860 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169700	DGC7860 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169730	DGC7860X B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169720	DGC7860X B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169780	DGC7865 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169740	DGC7865 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169750	DGC7865 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169800	DGC7865X B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169790	DGC7865X B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169540	DGC7645 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169520	DGC7645 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169530	DGC7645 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169620	DGC7665 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169580	DGC7665 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169600	DGC7665 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170450	DGC7440 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170430	DGC7440 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170440	DGC7440 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170470	DGC7440X NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170460	DGC7440X NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170490	DGC7460 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170480	DGC7460 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170500	DGC7460 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11170520	DGC7460X NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169380	DGC7440X B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169390	DGC7440X B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169430	DGC7460 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169400	DGC7460 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169410	DGC7460 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169450	DGC7460X B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169440	DGC7460X B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169470	DGC7840X B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169460	DGC7840X B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169490	DGC7845X B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169480	DGC7845X B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169810	DGC7640 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169500	DGC7640 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169510	DGC7640 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169570	DGC7660 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169550	DGC7660 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169560	DGC7660 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169650	DGC7840 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169630	DGC7840 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169640	DGC7840 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169680	DGC7845 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169660	DGC7845 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169670	DGC7845 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11169710	DGC7860 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101060	DGC7440 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134600	DGM7840 I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134610	DGM7840 I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134620	DGM7840 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116570	DGM7440 TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116580	DGM7440 TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116590	DGM7440 TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094440	DGM7340 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094460	DGM7440 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094470	DGM7440 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094480	DGM7440 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094450	DGM7440 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094490	DGM7640 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103440	DGM7840 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103450	DGM7840 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094500	DGM7840 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103430	DGM7840 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094530	DGM7845 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094550	DGM7845 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094570	DGM7845 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094510	DGM7845 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11256590	DG7240 B BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11256630	DGM7440 B BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11256640	DGM7845 B BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11256610	DGC7440 B BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138180	DGM7840 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138160	DGM7840 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100780	DGM7340 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100800	DGM7440 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100810	DGM7440 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100820	DGM7440 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100790	DGM7440 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100840	DGM7640 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100850	DGM7640 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100830	DGM7640 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100920	DGM7840 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100930	DGM7840 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100940	DGM7840 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100910	DGM7840 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100960	DGM7845 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100970	DGM7845 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100980	DGM7845 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100950	DGM7845 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100880	DGM7645 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100890	DGM7645 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11100870	DGM7645 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134520	DGM7440 I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134530	DGM7440 I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134540	DGM7440 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12704430	DGC7250 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12744430	DAH4980 D PEBE 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12435190	DG8540-55L XS4/CH OBSW 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
12689560	BO8165L XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12689560	BO8165L XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12689570	BO8165PL XE1/D PEBE 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12689570	BO8165PL XE1/D PEBE 230/50	Heater element Top heat 230V	Lead	7439-92-1
12689550	BO8155PF XE1/D BLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12689550	BO8155PF XE1/D BLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12782950	DAH4980 XD1/D PEBE 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12782190	DAH4980 CH PEBE 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12786270	DAH2960 XO1/ROK OBSW 220/60 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12786260	DAH4980 XO1/ROK OBSW/MATT 220/60 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12690110	BOM8330F XE1/D BLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11086240	HR1956-1 G GB EDST/CLST 230/50	Heater element Catalyst 208-240V	Lead	7439-92-1
11791630	HR1936-3 LP DF GD USAEDST/CLST120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11791630	HR1936-3 LP DF GD USAEDST/CLST120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791630	HR1936-3 LP DF GD USAEDST/CLST120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12707970	PDR908EL DK LW BL	SMD- Diode STTH1R04A	Lead	7439-92-1
12720900	DG8330F XE1/R01 BLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12435060	DG8330F XE1/R01 EDLK 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12435130	DG8340L XE1/R01 MASW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12648960	DG8340L XE1/R01 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12721060	DG8330-60F XS4/CH BLST 230/50/10A	SMD- Diode STTH1R04A	Lead	7439-92-1
11256620	DGC7845 B BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11284810	DG7240 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11284830	DG7240 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11327760	DGC7340 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11324890	DG7440 B BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11312620	DGC7541 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11455670	DGC7541 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099900	DGC7440 HC Pro D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099910	DGC7440 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12100180	DGC7460 HC Pro D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12656300	H2861B GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12656300	H2861B GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12617600	DS8010 XE1/R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11681365	Power-/Control unit EPL 8760	SMD- Diode STTH1R04A	Lead	7439-92-1
12647440	H7440BPX EU3 PEBE 230/50	Heater element Top heat 230V	Lead	7439-92-1
12647460	H7464BPX EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12647470	H7840BPX EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12647490	H7860BPX EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12647450	H7440BMX EU3 PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12647480	H7840BMX EU3 PEBE 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12704490	H2861BP GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12704490	H2861BP GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12704430	DGC7250 GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12704430	DGC7250 GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11101280	DGC7845 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101290	DGC7845 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101310	DGC7845X F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101320	DGC7845X F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101330	DGC7845X F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102980	DGC7860 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102960	DGC7860 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102970	DGC7860 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102950	DGC7860 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103010	DGC7860X F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103000	DGC7860X F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102990	DGC7860X F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103050	DGC7865 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103030	DGC7865 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103040	DGC7865 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103020	DGC7865 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103080	DGC7865X F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103070	DGC7865X F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103060	DGC7865X F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101160	DGC7645 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101170	DGC7645 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101180	DGC7645 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102940	DGC7665 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102920	DGC7665 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101070	DGC7440 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101050	DGC7440 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101110	DGC7440X F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101100	DGC7440X F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101090	DGC7440X F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102750	DGC7460 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102740	DGC7460 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102760	DGC7460 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102770	DGC7460 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101260	DGC7840X F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101250	DGC7840X F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101240	DGC7840X F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101120	DGC7640 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101130	DGC7640 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101140	DGC7640 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101230	DGC7840 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101200	DGC7840 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101210	DGC7840 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101220	DGC7840 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102810	DGC7660 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102820	DGC7660 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102830	DGC7660 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11101300	DGC7845 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101270	DGC7845 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168670	DGM7645 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170130	DGM7340 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170140	DGM7440 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170150	DGM7440 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170160	DGM7440 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170180	DGM7640 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170190	DGM7640 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170200	DGM7640 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170260	DGM7840 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170280	DGM7840 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170290	DGM7840 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170300	DGM7845 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170320	DGM7845 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170330	DGM7845 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170210	DGM7645 NL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170220	DGM7645 NL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11170240	DGM7645 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11137980	DGM7340 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138000	DGM7440 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138030	DGM7440 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138050	DGM7440 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11137990	DGM7440 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138080	DGM7640 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138040	DGM7640 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102930	DGC7665 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102910	DGC7665 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102800	DGC7460X F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102790	DGC7460X F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102780	DGC7460X F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11193770	DGC7340 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11193740	DGC7540 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11193730	DGC7540 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11193750	DGC7340 NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168580	DGM7340 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168590	DGM7440 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168600	DGM7440 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168610	DGM7440 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168620	DGM7640 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168630	DGM7640 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168640	DGM7640 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168680	DGM7840 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168690	DGM7840 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168700	DGM7840 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168710	DGM7845 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168720	DGM7845 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168740	DGM7845 B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168650	DGM7645 B OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11168660	DGM7645 B GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139020	DGC7860 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12615750	CS7612-1 FL XH1/HK 220/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12652690	G5412 SC F ED230 1,9 ActivePlus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652680	G5412 SC F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12615750	CS7612-1 FL XH1/HK 220/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12652700	G5412 SCi F OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12648130	KM7564-1 FL HK 220/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12652670	G5410 SCi F ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652660	G5410 SCi F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652650	G5410 SC F ED230 1,9 ActivePlus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652640	G5410 SC F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664890	G5455 SCVi XXL IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664880	G5450 SCVi IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652710	G5433 SC F BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652720	G5433 SC F ED230 1,9 CS FRONT Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652730	G5450 SCVi F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652740	G5455 SCVi XXL F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652750	G5463 SCVi F ED230 1,9 EXCELLENCE	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652760	G5468 SCVi XXL F ED230 1,9 EXCELLENCE	Drain pump 220-240V 50HZ	Lead	7439-92-1
12569630	G7130 SC AE ED230 1,9 AutoDos CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12569640	G7180 SCVi AE ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12569650	G7600 SC AE ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12569660	G7650 SCVi AE OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12569680	G7985 SCVi XXL AE OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12561870	PDR508ROP EL ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12650270	DGC7860 HCX Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12650320	DGC7865 HCX Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12660120	G5450 Vi MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660130	G5450 SCVi MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660140	G5455 Vi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660150	G5455 SCVi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660160	G5462 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660180	G5463 SCVi MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660190	G5467 SCVi XXL MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12660200	G5468 SCVi XXL MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12623220	DAH4980 ROK OBSW/MATT 220/60 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12659890	G5432 SCi TR ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659900	G5467 SCVi XXL TR ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659010	G5410 SC OE1 BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659020	G5410 SC OE1 ED230 1,9 ActivePL CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659030	G5410 SCi OE1 OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659040	G5410 SCi OE1 ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659050	G5415 SCi XXL OE1 ED230 1,9 ActivePL CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659060	G5450 SCVi OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659070	G5455 SCVi XXL OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659080	G5462 SCVi OE1 ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664850	G5410 SC IB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664860	G5410 SC IB ED230 1,9 ActivePL CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12664870	G5410 SCi IB ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12691580	H2467BP IB OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12623210	DAH2960 ROK OBSW 220/60 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12679130	DAH1650 KZ OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12679140	DAH1950 KZ OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	Lead	7439-92-1
12679150	DAH4970 KZ OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11791590	HR1934-3 LP DF USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11791590	HR1934-3 LP DF USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791590	HR1934-3 LP DF USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11708590	DG7140 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11709120	DG7240 BNE BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708620	DG7240 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708610	DG7240 BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708600	DG7240 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11709130	DG7440 BNE BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708650	DG7440 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708640	DG7440 BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708630	DG7440 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708670	DGM7340 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708680	DGM7440 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708690	DGM7440 BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708710	DGM7440 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11709140	DGM7440 BNE BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708720	DGM7640 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708740	DGM7640 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12561880	PDR508ROP EL ANL SST -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12561890	PDR908ROP EL ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12685560	PLW8683CD U NAM SST DS5 MON CM 3AC208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12685590	PLW8693 U NAM SST DS5 3AC208V/60HZ	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12561900	PDR908ROP EL ANL SST -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12680010	CS7612-1 FL HK 220/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12680010	CS7612-1 FL HK 220/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12636230	G7653 C SCVi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12636240	G7712 C SCi CN OS220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12561860	PDR307ROP EL ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
12583300	G7604 C SC SG BW230/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12583170	G7130 C SC SG BW230/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12583240	G7264 C SCVi SG ED230/50 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12583370	G7604 C SCi SG ED230/50 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12583430	G7654 C SCVi SG OS230/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12583480	G7984 C SCVi SG OS/CS230/50 1,9k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12595822	Power-/Control unit EPL 8810-U	SMD- Diode STTH1R04A	Lead	7439-92-1
12691520	H2465B IB OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12691520	H2465B IB OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12691570	H2467B IB OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12691570	H2467B IB OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12691560	H2465BP IB OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12691560	H2465BP IB OBSW 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12691580	H2467BP IB OBSW 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12658560	G5432 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658600	G5435 SCU XXL NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658620	G5435 SCU XXL NER ED230 1,9 Active Pl CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658640	G5442 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11635932	Power-/Control unit EPL 8630	SMD- Diode STTH1R04A	Lead	7439-92-1
12658690	G5442 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652770	G15410 i CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658710	G5443 SCU NER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652780	G15410 i CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658730	G5443 SCU NER ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652790	G15410 i CH ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658750	G5450 SCVi NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658760	G5455 SCVi XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652800	G25415 i XXL CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658770	G5460 SCVi NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658780	G5462 SCVi NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652810	G25415 i XXL CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652820	G25415 i XXL CH ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652830	G15450 Vi CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658790	G5467 SCVi XXL NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12652840	G25455 Vi XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12652850	G25455 SCVi XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658800	G5473 SCVi NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658810	G5478 SCVi XXL NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12653400	G5455 SCVi XXL A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649420	G5410 SC I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649430	G5410 SC I ED230 1,9 ActivePlus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649440	G5410 SC I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649450	G5410 SC I ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649460	G5410 SCU I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649470	G5410 SCU I ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649490	G5432 SCU I ED230 1,9 CS SELECTION	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649500	G5433 SCU I BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649510	G5433 SCU I ED230 1,9 CS EXCELLENCE	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649520	G5450 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649530	G5453 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649540	G5455 SCVi XXL I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649550	G5462 SCVi I ED230 1,9 SELECTION	Drain pump 220-240V 50HZ	Lead	7439-92-1
12598910	DGC7440 HCX Pro CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12649560	G5463 SCVi I ED230 1,9 EXCELLENCE	Drain pump 220-240V 50HZ	Lead	7439-92-1
12649570	G5410 SCU I OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12650850	G5433 SC I ED230 1,9 Excellence CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658490	G5410 SCU NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658500	G5410 SCU NER ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658510	G5431 SCU NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12645190	G7672 SCVi GB OS230 1,9 AutoDos Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658520	G5431 SCU NER ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12658540	G5432 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12624530	DGC7460 HCX Pro I PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12656380	G5432 SC GB BW230 1,9 SELECTION	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659980	G5410 SC MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12656390	G5432 SC GB ED230 1,9 CS FRONT SELECTION	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659990	G5410 SC MER ED230 1,9 ActivePL CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660000	G5410 SC I MER OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660010	G5410 SC I MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12656400	G5450 SCVi GB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660020	G5410 SC I MER ED230 1,9 Active Plus CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12656410	G5462 SCVi GB ED230 1,9 SELECTION	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660040	G5415 SCi XXL MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12628260	KM7564-1 FL XH1/HK 220/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12660050	G5415 SCi XXL MER ED230 1,9 ActivePL CS	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660070	G5432 SC MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660080	G5432 SC MER ED230 1,9 CS Front Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660090	G5432 SCU MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660100	G5432 SCi MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12660110	G5433 SC MER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12650150	DGC7440 HCX Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12650170	DGC7445 HCX Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12650190	DGC7460 HCX Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12650210	DGC7465 HCX Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12650240	DGC7840 HCX Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12650250	DGC7845 HCX Pro EU3 PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12598920	DGC7460 HCX Pro CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12598930	DGC7840 HCX Pro CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12598940	DGC7860 HCX Pro CH PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12641090	DGC7440 HCX Pro GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12641100	DGC7460 HCX Pro GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12641110	DGC7840 HCX Pro GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12641130	DGC7845 HCX Pro GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12641140	DGC7860 HCX Pro GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12641150	DGC7865 HCX Pro GB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12658820	G5495 SCVi XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12656350	G5410 SC GB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12656360	G5410 SC GB ED230 1,9 ActivePL CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12659960	G5410 MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12619730	DGC7440 HCX Pro NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619740	DGC7460 HCX Pro NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619750	DGC7840 HCX Pro NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619760	DGC7845 HCX Pro NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619770	DGC7860 HCX Pro NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12619780	DGC7865 HCX Pro NER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12659970	G5410 MER ED230 1,9 Act Plus CS Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12624650	DGC7840 HCX Pro SER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12624670	DGC7860 HCX Pro SER PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12624590	DGC7865 HCX Pro IB PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12624500	DGC7440 HCX Pro I PEBE 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708750	DGM7645 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134630	DGC7440 I BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134640	DGC7440 I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134650	DGC7440 I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134660	DGC7440 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134670	DGC7440X I BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134680	DGC7440X I OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134690	DGC7440X I GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134700	DGC7460 I BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11134710	DGC7460 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134730	DGC7460 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134740	DGC7460 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134750	DGC7460X BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134760	DGC7460X OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134770	DGC7460X GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134780	DGC7840X BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134790	DGC7840X OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134800	DGC7840X GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134840	DGC7640 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134810	DGC7640 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134820	DGC7640 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134830	DGC7640 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134850	DGC7660 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134860	DGC7660 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134870	DGC7660 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094810	DGC7860 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103800	DGC7860X GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103820	DGC7860X GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103840	DGC7860X GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094820	DGC7865 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094830	DGC7865 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094840	DGC7865 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094850	DGC7865 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094860	DGC7865X GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094870	DGC7865X GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094890	DGC7865X GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116160	DGC7440 TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116170	DGC7440 TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116240	DGC7440X TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116290	DGC7460 TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116300	DGC7460 TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116370	DGC7460X TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116400	DGC7840 TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116380	DGC7840 TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116390	DGC7840 TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116430	DGC7860 TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116410	DGC7860 TR OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116420	DGC7860 TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11116440	DGC7860X TR GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138770	DGC7460X NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138780	DGC7840X NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138790	DGC7840X NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138800	DGC7840X NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138810	DGC7845X NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138820	DGC7845X NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138830	DGC7845X NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138870	DGC7640 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138840	DGC7640 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138850	DGC7640 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138860	DGC7640 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138910	DGC7660 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138880	DGC7660 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138890	DGC7660 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138900	DGC7660 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138920	DGC7840 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138930	DGC7840 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138940	DGC7840 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138950	DGC7840 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138960	DGC7845 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138970	DGC7845 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138980	DGC7845 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138990	DGC7845 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11139010	DGC7860 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134900	DGC7840 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134910	DGC7840 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134920	DGC7840 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134930	DGC7840 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134940	DGC7860 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134950	DGC7860 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134960	DGC7860 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134970	DGC7860 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134980	DGC7860X BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134990	DGC7860X OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135000	DGC7860X GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138440	DGC7440 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138450	DGC7440 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138460	DGC7440 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138470	DGC7440 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138480	DGC7440X NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138490	DGC7440X NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138500	DGC7440X NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138510	DGC7460 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138680	DGC7460 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11138710	DGC7460 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138740	DGC7460 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138750	DGC7460X NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11138760	DGC7460X NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107330	DGC7865 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107130	DGC7840 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107140	DGC7840 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107150	DGC7840 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107170	DGC7840 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107000	DGC7440X D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107010	DGC7440X D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107020	DGC7440X D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107070	DGC7460X D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107080	DGC7460X D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107090	DGC7460X D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107100	DGC7840X D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107110	DGC7840X D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107120	DGC7840X D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102490	DGC7845X D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102510	DGC7845X D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102520	DGC7845X D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107270	DGC7860X D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107280	DGC7860X D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107290	DGC7860X D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102560	DGC7865X D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102590	DGC7865X D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102600	DGC7865X D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106750	DGC7640 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708770	DGM7645 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708920	DGM7840 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708930	DGM7840 BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708940	DGM7840 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11708950	DGM7845 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11709100	DGM7845 BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11709110	DGM7845 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11734240	DGM7845 BNE BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11709370	DGC7640 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106490	DGC7440 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106980	DGC7440 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107030	DGC7460 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107050	DGC7460 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107180	DGC7845 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107190	DGC7845 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107200	DGC7845 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107210	DGC7845 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107230	DGC7860 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107240	DGC7860 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107250	DGC7860 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107260	DGC7860 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107300	DGC7865 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107310	DGC7865 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107320	DGC7865 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103500	DGC7460 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094660	DGC7460 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103510	DGC7460X GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103520	DGC7460X GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103530	DGC7460X GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103550	DGC7840X GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103560	DGC7840X GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103580	DGC7840X GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094670	DGC7845X GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094680	DGC7845X GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094690	DGC7845X GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094720	DGC7640 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094740	DGC7660 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103600	DGC7840 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103610	DGC7840 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103620	DGC7840 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094760	DGC7840 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094770	DGC7845 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094780	DGC7845 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094790	DGC7845 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094800	DGC7845 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103750	DGC7860 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103760	DGC7860 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103770	DGC7860 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106770	DGC7640 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106780	DGC7640 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106790	DGC7640 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106840	DGC7660 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106850	DGC7660 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106860	DGC7660 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106880	DGC7660 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106800	DGC7645 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11106810	DGC7645 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106820	DGC7645 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106830	DGC7645 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106890	DGC7665 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106900	DGC7665 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106910	DGC7665 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106920	DGC7665 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094580	DGC7440 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094590	DGC7440 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094600	DGC7440 GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094610	DGC7440 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094620	DGC7440X GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094640	DGC7440X GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11094650	DGC7440X GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103480	DGC7460 GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11103490	DGC7460 GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11492640	G5640 SC SL IB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492630	G5481 SCVi SL IB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11394240	KM7699 FR R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11506340	KM7699 FR D 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11394250	KM7629 FX R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11495780	G5840 SCi SL A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492620	G5430 SC SL IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495770	G5840 SCi SL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492610	G5265 SCVi XXL IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492580	G5260 SCVi IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492560	G5260 Vi IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11512090	KM7629 FX CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11395800	KM7689 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11512130	KM7689 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11395820	KM7899 FL R01 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11512180	KM7899 FL CH 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
11495800	G5890 SCVi SL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495760	G5690 SCVi SL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492740	G5000 F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492750	G5000 F ED230 1,9 Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492760	G5000 SC F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492770	G5000 SC F ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495750	G5640 SCi SL A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492310	G5000 SC IB ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11496670	G5481 SCVi SL A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492290	G5000 IB ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495380	G5050 Vi A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492380	G5000 SCi IB ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495390	G5050 SCVi A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495400	G5055 Vi XXL A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492320	G5000 SCi IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495410	G5055 SCVi XXL A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497040	G5210 SC A ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495660	G5430 SC SL A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495670	G5430 SCU SL A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495680	G5430 SCU SL A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495690	G5430 SCi SL A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492460	G5210 IB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495700	G5430 SCi SL A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492490	G5210 SC IB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495720	G5640 SC SL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492510	G5210 SC IB ED230 1,9 FrontActive Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495730	G5640 SCU SL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492540	G5210 SCi IB ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495740	G5640 SCi SL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492780	G5000 SCU F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11527720	DGC7450 ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11527720	DGC7450 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11493190	G5430 SC SL F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493200	G5430 SCi SL F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493210	G5481 SCVi SL F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493230	G5640 SC SL F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493260	G5690 SCVi SL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493280	G5890 SCVi SL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11527710	DGC7250 ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11527710	DGC7250 ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11527710	DGC7250 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11480020	G15210 i CH HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480030	G15210 i CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480040	G15210 i CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480110	G15210 i CH ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480130	G25215 i XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480120	G25215 i XXL CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480140	G15481 SCVi SL CH ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480150	G15640 SCi SL CH BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480160	G15640 SCi SL CH ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480170	G15690 SCVi SL CH ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480180	G15890 SCVi SL CH ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11527720	DGC7450 ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11492790	G5000 SCU F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492800	G5000 i F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492810	G5000 i F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492820	G5000 SCi F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492830	G5000 SCi F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492840	G5050 Vi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493020	G5050 SCVi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493040	G5210 F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493050	G5210 SC F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493060	G5210 SC F ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493070	G5210 SCU F ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493090	G5210 i F OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493110	G5210 i F ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493130	G5210 SCi F OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493140	G5210 SCi F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493150	G5210 SCi F ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493160	G5260 Vi F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493170	G5260 SCVi F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493180	G5265 SCVi XXL F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11612855	Power-/Control unit ELP 7757 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11816980	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11816980	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11492300	G5000 SC IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453900	G5000 SCU D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321230	G7599 SCVi XXL AUS OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453910	G5000 SCU D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453890	G5000 U D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453880	G5000 U D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453870	G5000 SC D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321250	G7919 SCi XXL AUS OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453850	G5000 D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454010	G5210 D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454720	G5215 i XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454120	G5210 SCi D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321260	G7969 SCVi XXL AUS OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454040	G5210 SCU D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454050	G5210 SCU D ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454030	G5210 U D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454710	G5210 U D ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454130	G5210 SCi D ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454100	G5210 SCi D HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454080	G5210 i D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454090	G5210 i D ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454060	G5210 i D HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11186550	G7965 SCVi XXL TR OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453930	G5000 i D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453920	G5000 i D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453940	G5000 SCi D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454150	G5260 SCVi D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454160	G5265 SCVi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321080	G7154 SCVi AUS ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454140	G5260 Vi D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454740	G5265 Vi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453990	G5055 SCVi XXL D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453960	G5050 Vi D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453980	G5055 Vi XXL D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321090	G7314 SCU AUS ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454370	G5640 SCi SL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454750	G5640 SCU SL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454400	G5840 SCi SL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454820	G5840 SCU SL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321110	G7319 SCU XXL AUS ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454810	G5840 SC SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321130	G7319 SCi XXL AUS ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454220	G5430 SCU SL D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454200	G5430 SCU SL D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454180	G5430 SC SL D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321190	G7369 SCVi XXL AUS OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11467630	PDR908EL MAR RU LW 3 AC 400-480V 50/60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11495360	G5000 SCi A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495370	G5000 SCi A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495420	G5210 A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495430	G5210 SC A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495470	G5210 U A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495480	G5210 SCU A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495500	G5210 SCU A ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495510	G5210 i A HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495530	G5210 i A OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495550	G5210 i A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495570	G5210 i A ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495580	G5210 SCi A HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495590	G5210 SCi A OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495600	G5210 SCi A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11495610	G5210 SCi A ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495620	G5260 Vi A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495630	G5260 SCVi A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495650	G5265 SCVi XXL A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492400	G5050 Vi IB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492430	G5050 SCVi IB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497030	G5210 SC D ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11492280	G5000 IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495350	G5000 i A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11467550	PDR908HP MAR RU SST 2 AC 208/240V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11452600	PFD101 ANL BW3N400 7,7kw	Drain pump 220-240V 50HZ	Lead	7439-92-1
11452610	PFD102 i ANL ED3N400 7,7 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11452620	PFD103 SCi XXL ANL ED3N400 7,7 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11452630	PFD104 SCVi XXL ANL ED3N400 7,7	Drain pump 220-240V 50HZ	Lead	7439-92-1
11472020	PFD101 ANL BW230/50 2,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11470850	PDR307EL ZER LW CC	SMD- Diode STTH1R04A	Lead	7439-92-1
11470810	PDR307HP ZER LW CC	SMD- Diode STTH1R04A	Lead	7439-92-1
11454070	G5210 i D OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454110	G5210 SCi D OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11452680	PFD103 SCi XXL ANL ED230 2,3 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11452670	PFD101 i ANL ED230 2,3 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11489770	PDR908EL IRL SST 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11489870	PDR908EL IRL SST 400V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11497020	G5000 SC A ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495260	G5000 A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495270	G5000 SC A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495290	G5000 U A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495300	G5000 U A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495320	G5000 SCU A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495330	G5000 SCU A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495340	G5000 i A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11537490	G7050 Vi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11537500	G7050 SCVi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11537520	G7055 SCVi XXL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11427860	G7100 C SCi CN ED220/50 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574720	PDR914 EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11578190	PDR914 HP CP ANL SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11427900	G7150 C SCVi CN ED220/50	Drain pump 220-240V 50HZ	Lead	7439-92-1
11427910	G7310 C SC CN BW220/50 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11427930	G7310 C SCU CN ED220/50 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11427960	G7310 C SCi CN ED220/50 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11427970	G7312 C SCi CN ED220/50 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11427990	G7360 C SCVi CN OS/CS220/50 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11428020	G7362 C SCVi CN OS/CS220/50 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11428040	G7510 C SCi CN OS220/50 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11428070	G7590 C SCVi CN OS/CS220/50 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574820	PDR922 EL ANL SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11428080	G7910 C SCi CN OS220/50 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11428090	G7960 C SCVi CN OS/CS220/50 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574750	PDR918 G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11574850	PDR922 G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11574870	PDR928 EL ANL SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11568830	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11537470	G7000 SCi A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493910	G5210 SC MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493920	G5210 SC MER ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493950	G5210 SCi MER OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493970	G5210 SCi MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493980	G5210 SCi MER ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11578140	PDR914 HP CP ANL IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11494000	G5260 Vi MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494010	G5260 SCVi MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494030	G5265 SCVi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11578840	PDR918 HP CP ANL IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11579030	PDR922 HP CP ANL IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11494110	G5640 SC SL MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494140	G5640 SCi SL MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494150	G5640 SCi SL MER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11844913	Power-/Control unit ELP 7442-A 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11307660	DGC7845 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11494170	G5690 SCVi SL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11537420	G7000 SC A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11537430	G7000 SCU A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11537440	G7000 SCU A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11537450	G7000 i A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11537460	G7000 SCi A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11568830	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11579060	PDR944 EL ANL SST B14Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11497170	G5690 SCVi SL UA ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497180	G5890 SCVi SL UA ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479730	G5210 SC OE1 BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479750	G5210 SC OE1 ED230 1,9 FrontActive Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11584250	PDR522ROP SI ANL IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11574790	PDR522ROP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11494620	G5000 SC RU BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494630	G5000 SC RU ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494640	G5000 SCi RU ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11584010	PDR528ROP G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11586240	PDR928 G ANL SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11579050	PDR544ROP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11494660	G5050 SCVi RU ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494670	G5210 SC RU BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494680	G5210 SCi RU ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494690	G5260 SCVi RU ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11584230	PDR522ROP EL ANL IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11494700	G5265 SCVi XXL RU ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11307250	DGC7775 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11494710	G5430 SC SL RU BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574890	PDR944 G ANL IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11497160	G5481 SCVi SL UA ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554860	H2465B ANL EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11554860	H2465B ANL EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11554880	H2465BP ANL EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11554880	H2465BP ANL EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11568800	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11568800	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11554890	H2840-1B ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11497060	G5000 SC UA BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479640	G5000 SC OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497070	G5000 SC UA ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479650	G5000 i OE1 ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497090	G5000 SCi UA ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479660	G5000 SCi OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479670	G5000 SCi OE1 ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497110	G5050 SCVi UA ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497120	G5210 SCi UA ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479690	G5050 Vi OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497130	G5260 SCVi UA ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479700	G5050 SCVi OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479720	G5055 SCVi XXL OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497140	G5265 Vi XXL UA ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11497150	G5430 SC SL UA BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493890	G5210 MER ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493290	G5000 SC i BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494350	G5000 U NER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494360	G5000 SCU NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494370	G5000 SCU NER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495090	G5000 SC i ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494380	G5000 i NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493300	G5000 U i ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493310	G5000 SCU i BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493320	G5000 SCU i ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493330	G5000 i i ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493340	G5000 SCi i ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11532870	Raising motor Set BL1	Raising motor Set BL1	Lead	7439-92-1
11532870	Raising motor Set BL1	Raising motor Set BL1	Lead	7439-92-1
11534980	Operating module Lifting mechanism 2	Operating module Lifting mechanism 2	Lead	7439-92-1
11534980	Operating module Lifting mechanism 2	Operating module Lifting mechanism 2	Lead	7439-92-1
11493350	G5050 Vi i ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494390	G5050 Vi NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493360	G5050 SCVi i ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494400	G5050 SCVi NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494420	G5055 SCVi XXL NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493370	G5055 SCVi XXL i ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493380	G5210 i BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495960	G5690 SCVi SL GB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480190	G15050 Vi CH ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480200	G25055 Vi XXL CH ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480220	G15260 Vi CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11480230	G25265 Vi XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11520860	G5210 U D HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11520880	G5210 SCU D HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11527450	H7840BMX TW GRGR 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11495820	G5000 SC GB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495840	G5000 SC GB ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495850	G5000 SCi GB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495860	G5000 SCi GB ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495870	G5050 SCVi GB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495880	G5055 SCVi XXL GB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495890	G5210 SC GB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495910	G5210 SC GB ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495930	G5260 SCVi GB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495940	G5265 SCVi XXL GB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070500	G7100 SCi A OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495950	G5640 SC SL GB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494340	G5000 U NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11534970	Operating module Lifting mechanism 1	Operating module Lifting mechanism 1	Lead	7439-92-1
11534970	Operating module Lifting mechanism 1	Operating module Lifting mechanism 1	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11493390	G5210 SC I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493530	G5640 SCi SL I ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494600	G5690 SCVi SL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493540	G5690 SCVi SL I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493750	G5000 MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493760	G5000 MER ED230 1,9 Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493770	G5000 SC MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493780	G5000 SC MER ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493790	G5000 i MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493810	G5000 i MER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493820	G5000 SCi MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493830	G5000 SCi MER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11477250	G5000 TR BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11477260	G5000 SC TR BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11477270	G5000 SC TR ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11477280	G5000 i TR ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11477290	G5000 SCi TR ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11477300	G5050 Vi TR ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11477310	G5050 SCVi TR ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493840	G5050 Vi MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493850	G5050 SCVi MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493870	G5055 SCVi XXL MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493880	G5210 MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493520	G5640 SC SL I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494450	G5210 U NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494460	G5210 SCU NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494480	G5210 SCU NER ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493400	G5210 SC I ED230 1,9 FrontActive Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494490	G5215 SCU XXL NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494510	G5215 SCU XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493410	G5210 SCU I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493420	G5210 SCU I ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494520	G5260 SCVi NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494530	G5265 SCVi XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493450	G5210 SCi I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493460	G5210 SCi I ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494540	G5430 SCU SL NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494550	G5430 SCU SL NER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493470	G5260 Vi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493480	G5260 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494570	G5481 SCVi SL NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11495100	G5265 SCVi XXL I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493500	G5430 SCU SL I BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494580	G5640 SCU SL NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11493510	G5481 SCVi SL I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494590	G5640 SCU SL NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11281820	H6680BP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11281780	H6580BP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11281820	H6680BP BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11281820	H6680BP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11281830	H6680BP BR OBSW 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11281780	H6580BP BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11281780	H6580BP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11146290	H2890B ROK EDST/CLST 220/60	Temperature regul. Sub-assembly	Lead	7439-92-1
11292890	H2890B TW EDST/CLST 220/60	Temperature regul. Sub-assembly	Lead	7439-92-1
11150260	H7890BP C CN EDST/CLST 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11143870	DO7860 C CN GRGR 220/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11281830	H6680BP BR OBSW 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11281830	H6680BP BR OBSW 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11281880	H6100BM BR EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11281880	H6100BM BR EDST/CLST 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281900	H6200BM BR EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11281900	H6200BM BR EDST/CLST 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281910	H6200BM BR OBSW 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11281910	H6200BM BR OBSW 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281890	H6700BM BR EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11281890	H6700BM BR EDST/CLST 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281920	H6800BM BR EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11143870	DO7860 C CN GRGR 220/50	Heater element Top heat 230V	Lead	7439-92-1
11150230	H7860BP C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150210	H7860BP C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150220	H7860BP C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150240	H7860BPX C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150250	H7860BPX C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149850	H7240BM C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11149860	H7240BM C CN GRGR 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11149930	H7440BM C CN EDST/CLST 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11149910	H7440BM C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11149920	H7440BM C CN GRGR 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11149940	H7440BMX C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11149950	H7440BMX C CN GRGR 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11150120	H7640BM C CN EDST/CLST 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11150080	H7640BM C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11150110	H7640BM C CN GRGR 220/50	Heater element Top heat 220-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11150180	H7840BM C CN EDST/CLST 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11150160	H7840BM C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11150170	H7840BM C CN GRGR 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11150190	H7840BMX C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11150200	H7840BMX C CN GRGR 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11143860	DO7860 C CN OBSW 220/50	Heater element Top heat 230V	Lead	7439-92-1
11143860	DO7860 C CN OBSW 220/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11281920	H6800BM BR EDST/CLST 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281790	H6780-2BP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11281790	H6780-2BP BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11281790	H6780-2BP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11281840	H6880-2BP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11281840	H6880-2BP BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11281840	H6880-2BP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11281850	H6880-2BP BR OBSW 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11281850	H6880-2BP BR OBSW 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11281850	H6880-2BP BR OBSW 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11164950	G5430 SCi SL ANL BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11164970	G5481 SCVi SL ANL ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11164920	G5440 SCi SL ANL BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11164960	G5490 SCVi SL ANL ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11164980	G5640 SCi SL ANL BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11164990	G5690 SCVi SL ANL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11165020	G5840 SCi SL ANL BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11165030	G5890 SCVi SL ANL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11165140	G5000 i ANL BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
10824730	PDR507HP ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10826460	PDR307HP ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10826630	PDR507HP ANL QSR LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10826730	PDR507EL ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
11226670	HR1955-3 G DF GR AN3 EDST/CLST120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281930	H6800BM BR OBSW 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11281930	H6800BM BR OBSW 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281940	H6770BM BR EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11281940	H6770BM BR EDST/CLST 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281950	H6870BM BR EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11281950	H6870BM BR EDST/CLST 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11281960	H6870BM BR OBSW 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11281960	H6870BM BR OBSW 127/220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11179250	HR1421-3 E AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11179250	HR1421-3 E AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11179250	HR1421-3 E AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11300980	PDR507EL MAR LW 3 AC 400-480V 50/60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
7765112	Heater element Top heat 208V	Heater element Top heat 208V	Lead	7439-92-1
7765112	Heater element Top heat 208V	Heater element Top heat 208V	Lead	7439-92-1
11316730	Module H7-3BM	Heater element Top heat 200-208V	Lead	7439-92-1
11226690	HR1956-3 G DF GD AN3 EDST/CLST120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11226690	HR1956-3 G DF GD AN3 EDST/CLST120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11226590	HR1954-3 G DF AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11226590	HR1954-3 G DF AN3 EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11226700	HR1956-3 LP DF GD AN3EDST/CLST120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11226700	HR1956-3 LP DF GD AN3EDST/CLST120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11226670	HR1955-3 G DF GR AN3 EDST/CLST120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11150140	H7660BP C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
7511121	Temperature regul. 45 - 185 °C +/- 7	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
7227540	Trough 3,00KW 230V	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
5333220	HM16-83 CH 3N 380-415/50-60 2,7-3,3kW	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
9342750	PT8257 WP DK CA3 KD-Version	Control electr.unit EW 430	Lead	7439-92-1
9342760	PT8257 WP DK CA5 KD-Version	Control electr.unit EW 430	Lead	7439-92-1
9342770	PT8257 WP DK iBR KD-Version	Control electr.unit EW 430	Lead	7439-92-1
9342780	PT8257 WP DK IK5 KD-Version	Control electr.unit EW 430	Lead	7439-92-1
10114170	PG8504 N AE-AD 3 AC 230	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10409340	PG8582CD USA i-Gerät VWV-AD-CM	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10250010	PG8504 USA AE-AD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10254290	PG8504 CDN AE-AD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10254300	PG8504 CDN AE-ADP	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10442010	PG8583CD EXE i-Gerät ADP	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10276730	PG8504 EXE AE-AD 3 AC 220-230V 60Hz	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10489710	PG8504 B AE-AD 6,7 kW	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10828190	PW418LAV OH ED 3NAC380-415 50/60	Control electr.unit EW 235-A	Lead	7439-92-1
11367020	H7670BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11411120	PDR928 Si ANL IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11411130	PDR544ROP G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11411140	PDR544ROP HW ANL IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11367040	H7870BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11141390	H7870BM AN3 GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
7511121	Temperature regul. 45 - 185 °C +/- 7	Temperature regul. 45 - 185 °C +/- 7	Lead	7439-92-1
11281770	H6180BP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11281800	H6280BP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11281800	H6280BP BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11281800	H6280BP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11281810	H6280BP BR OBSW 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11281810	H6280BP BR OBSW 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11281810	H6280BP BR OBSW 127/220/60	Heater element Hot air 208V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11141340	H7240BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11300970	PDR507HP MAR LW 1N AC 230V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11367000	H7170BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11411050	PDR514ROP G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11411060	PDR518ROP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11411070	PDR918 HW ANL IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11411080	PDR522ROP G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11365520	G7510 SCi D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11365540	G7515 SCi XXL D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11365530	G7510 SCU D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11411090	PDR522ROP HW ANL IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11411110	PDR528ROP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11141370	H7270BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11367010	H7270BM AN3 BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11141380	H7570BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11141400	H7870BMX AN3 GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11149880	H7264B C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149890	H7264B C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149990	H7460B C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149960	H7460B C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11149980	H7460B C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11146310	H7240BM ROK EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11146330	H7440BM ROK EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11146350	H7840BM ROK EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11146360	H7840BMX ROK GRGR 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11288210	H7860BP J GRGR 200/50	Heater element Bottom heat	Lead	7439-92-1
11288210	H7860BP J GRGR 200/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11288230	H7860BP J GRGR 200/60	Heater element Bottom heat	Lead	7439-92-1
11288230	H7860BP J GRGR 200/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11149870	H7240BM C CN EDST/CLST 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11149900	H7264B C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150050	H7464BP C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150010	H7464BP C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150020	H7464BP C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150060	H7464BPX C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150070	H7464BPX C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150150	H7660BP C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11150130	H7660BP C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10986130	DO7860 C CN EDST/CLST 220/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11292920	H7464BP TW EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11292930	H7860BP TW EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11292940	H7860BPX TW GRGR 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11292900	H7240BM TW EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11146340	H7464BP ROK EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11146370	H7860BP ROK EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11146380	H7860BPX ROK GRGR 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11136620	H7460BP J EDST/CLST 200/50	Heater element Bottom heat	Lead	7439-92-1
11136620	H7460BP J EDST/CLST 200/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11136630	H7460BP J EDST/CLST 200/60	Heater element Bottom heat	Lead	7439-92-1
11136630	H7460BP J EDST/CLST 200/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11136660	H7860BP J EDST/CLST 200/50	Heater element Bottom heat	Lead	7439-92-1
11136660	H7860BP J EDST/CLST 200/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11136670	H7860BP J EDST/CLST 200/60	Heater element Bottom heat	Lead	7439-92-1
11136670	H7860BP J EDST/CLST 200/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11136580	H7440BM J EDST/CLST 200/50	Heater element Top heat 200-208V	Lead	7439-92-1
11136590	H7440BM J EDST/CLST 200/60	Heater element Top heat 200-208V	Lead	7439-92-1
11136640	H7840BM J EDST/CLST 200/50	Heater element Top heat 200-208V	Lead	7439-92-1
11136650	H7840BM J EDST/CLST 200/60	Heater element Top heat 200-208V	Lead	7439-92-1
11288180	H7840BM J GRGR 200/50	Heater element Top heat 200-208V	Lead	7439-92-1
11288190	H7840BM J GRGR 200/60	Heater element Top heat 200-208V	Lead	7439-92-1
10986130	DO7860 C CN EDST/CLST 220/50	Heater element Top heat 230V	Lead	7439-92-1
11165320	G5265 SCVi XXL ANL ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11141410	H2880BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11141410	H2880BP AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11141410	H2880BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11374670	H7280BP AN3 BRWS 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11374670	H7280BP AN3 BRWS 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11374670	H7280BP AN3 BRWS 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
7840242	Heater element Bottom heat 230-240V	Heater element Unterhitze 230-240V	Lead	7439-92-1
7840242	Heater element Bottom heat 230-240V	Heater element Unterhitze 230-240V	Lead	7439-92-1
10979251	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
10979251	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11405920	H2850B IB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11405920	H2850B IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11450300	PG8583 W1 AE-WW-ADP-LD 3AC 220V60HZ	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11450330	PG8583CD W1 AE WW AD CM OIL 3AC220V60HZ	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11141440	H7585BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11141440	H7585BP AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11141440	H7585BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11374370	H7685BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11374370	H7685BP AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11374370	H7685BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11141450	H7885BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11165300	G5215 SCi XXL ANL BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11103370	PDR908HP N LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11103380	PDR908HP N SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11103390	PDR908EL N LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11114850	PDR507EL TR LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11137030	PDR507HP RU LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11137040	PDR507HP RU SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11137080	PDR507EL RU LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11137100	PDR507EL RU SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11137130	PDR908HP RU SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11137150	PDR908EL RU SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11170380	PDR507HP ZER LW Special	SMD- Diode STTH1R04A	Lead	7439-92-1
11180890	PDR507HP S LW Special	SMD- Diode STTH1R04A	Lead	7439-92-1
11178690	PDR507HP DK LW Special	SMD- Diode STTH1R04A	Lead	7439-92-1
11168560	PDR507HP IRL LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11168570	PDR507EL IRL LW 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11168730	PDR507EL IRL LW 400V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11165310	G5000 SCi ANL BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11165240	G5050 SCVi ANL ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11165290	G5210 SCi ANL BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11165310	G5260 SCVi ANL ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11165190	G5005 SCi XXL ANL BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11165270	G5055 SCVi XXL ANL ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11141450	H7885BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11454700	G5000 SC D ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11444760	PDR507HP IB LW Special	SMD- Diode STTH1R04A	Lead	7439-92-1
11453970	G5050 SCVi D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11133910	DO7860 CH EDST/CLST 400/N/50	Release element 10.0332.14	Lead	7439-92-1
11133870	DO7860 CH BRWS 400/N/50	Release element 10.0332.14	Lead	7439-92-1
11133890	DO7860 CH OBSW 400/N/50	Release element 10.0332.14	Lead	7439-92-1
11133900	DO7860 CH GRGR 400/N/50	Release element 10.0332.14	Lead	7439-92-1
11454020	G5210 SC D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454270	G5430 SCi SL D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454240	G5430 SCi SL D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454730	G5215 SCi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454330	G5640 SC SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454350	G5640 SCU SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454290	G5481 SCVi SL D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11320990	G7104 AUS BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321020	G7104 SC AUS ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321030	G7104 SCU AUS ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11321050	G7104 SCi AUS ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454360	G5640 SCi SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454380	G5690 SCVi SL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454390	G5840 SCi SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11454410	G5890 SCVi SL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11394920	PDR507EL AUS LW 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11374380	H7885BP AN3 GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11374380	H7885BP AN3 GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11455600	H7165BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11455610	H7365BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11455620	H7565BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11486690	PDR918 EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11159310	DG7440 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159330	DG7440 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159340	DG7440 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159290	DG7240 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159300	DG7240 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159320	DG7240 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159280	DG2840 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11488260	PDR928 G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11321200	G7519 SCi XXL AUS OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11451270	G7312 SCi F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11293800	G7150 SCVi AE ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11293840	G7310 SC AE ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11293850	G7360 SCVi AE OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11293860	G7965 SCVi XXL AE OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11453950	G5000 SCi D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11394750	PDR507HP AUS LW 10A	SMD- Diode STTH1R04A	Lead	7439-92-1
11073300	PDR507EL S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11087110	PDR908EL IB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11050530	PDR507HP D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11050700	PDR908HP D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11050710	PDR908HP D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11073330	PDR908EL S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11073350	PDR908HP S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11050510	PDR507EL D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11086980	PDR507EL IB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11086990	PDR507EL IB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11077940	PDR500-08HP CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11083080	PDR900-08HP CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11073320	PDR507HP S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11073740	PDR507HP DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11089160	PDR908HP DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11087510	PDR908EL NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11087520	PDR908EL NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11088890	PDR507EL FIN LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11088990	PDR908EL FIN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11087470	PDR507EL NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11087480	PDR507EL NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11117280	PDR908EL B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11088930	PDR908HP FIN LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11089170	PDR908EL DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
10838890	PDR307EL ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10886360	PDR507HP ANL SST -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10886370	PDR507EL ANL SST -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10885090	PDR908HP ANL MAR LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10885190	PDR908EL ANL MAR LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10885240	PDR908EL ANL MAR LW 230V -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10885480	PDR908EL ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10885490	PDR908HP ANL LW -D-	SMD- Diode STTH1R04A	Lead	7439-92-1
10905370	PDR908EL ANL MAR LW -D- 2AC 208/240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10905390	PDR908EL ANL MAR SST -D- 2AC 208/240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10905670	PDR908HP ANL MAR LW -D- 2AC 208/240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10905680	PDR908HP ANL MAR SST -D- 2AC 208/240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10921570	PDR908EL ANL LW -USA-	SMD- Diode STTH1R04A	Lead	7439-92-1
10921580	PDR908EL ANL SST -USA-	SMD- Diode STTH1R04A	Lead	7439-92-1
10922360	PDR908HP ANL LW -USA- 2AC 208/240V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
10922370	PDR908HP ANL SST -USA- 2AC 208/240V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
10975560	PDR508HP ANL LW -CH-	SMD- Diode STTH1R04A	Lead	7439-92-1
11050520	PDR507HP D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11050690	PDR908EL D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11050500	PDR507EL D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11050680	PDR908EL D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11073730	PDR507EL DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11086950	PDR507HP IB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11117110	PDR507HP B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11117230	PDR507EL B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11117250	PDR908HP B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11117260	PDR908HP B SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11117290	PDR908EL B SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11103340	PDR507HP N LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11108030	PDR908HP GB SST 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11105550	PDR908EL GB LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11105560	PDR908EL GB SST 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11105580	PDR908EL GB LW 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11103830	PDR507HP GB LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11114810	PDR507HP TR LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11114820	PDR507HP TR SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11114880	PDR908HP TR LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11114890	PDR908HP TR SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11114900	PDR908EL TR LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11114910	PDR908EL TR SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11088940	PDR908HP FIN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11104460	PDR908HP GB LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11105590	PDR908EL GB LW 400V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11114860	PDR507EL TR SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11103360	PDR507EL N LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11107720	PDR908EL I SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11086960	PDR507HP IB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11087030	PDR908HP IB SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11087450	PDR507HP NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11087460	PDR507HP NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11094210	PDR507HP F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11094230	PDR507HP F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11087490	PDR908HP NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11088850	PDR507HP FIN LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11094280	PDR908HP F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11094330	PDR908EL F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11087500	PDR908HP NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11094250	PDR507EL F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11094260	PDR507EL F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11094290	PDR908HP F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11094340	PDR908EL F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11103940	PDR507EL GB LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11104040	PDR507EL GB LW 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11107690	PDR507HP I SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11116710	PDR507HP I LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11107700	PDR507EL I SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11116760	PDR507EL I LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11107710	PDR908HP I SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11574900	PDR944 HW ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11723010	DGC7845 HC Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723000	DGC7845 HC Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723020	DGC7845 HCX Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723030	DGC7845 HCX Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11718610	PDR928 G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11722240	DGC7645 HC Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11722210	DGC7445 HCX Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11722200	DGC7445 HCX Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11722190	DGC7445 HC Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11722180	DGC7445 HC Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11722170	DGC7445 HC Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11718260	PDR928 SI EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795800	PDR928 G EU SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718350	PDR544ROP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718450	PDR544ROP G EU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718370	PDR544ROP HW EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718380	PDR944 EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718460	PDR944 G EU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718390	PDR944 SI EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718400	PDR944 HW EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717750	PDR514TOP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795500	PDR514TOP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11634920	DGC7645 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11718060	PDR918 HW EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795590	PDR918 G EU SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11717880	PDR522TOP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795610	PDR522ROP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717960	PDR522ROP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718200	PDR522ROP SI EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718210	PDR522ROP HW EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718300	PDR522ROP EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718320	PDR922 EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795620	PDR922 EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718590	PDR922 G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718440	PDR922 HP EU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718340	PDR528ROP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718600	PDR528ROP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718330	PDR928 EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795790	PDR928 EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11721500	DGC7445 HCX Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11722220	DGC7645 HC Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11722230	DGC7645 HC Pro ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11722990	DGC7845 HC Pro ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723220	DGC7445 HCX Pro ANC OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723310	DGC7840 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11717990	PDR518ROP EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11780950	G7110 SC OE1 ED230 1,9CS Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780960	G7110 SCi OE1 BW230 1,9 Auto Dos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780970	G7110 SCi OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780980	G7115 SCi XXL OE1 BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780990	G7115 SCi XXL OE1 ED230 1,9CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11717920	PDR518COP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11795550	PDR518COP G EU SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11781210	G7160 SCVi NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781220	G7165 SCVi XXL NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781280	G7163 SCVi NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781290	G7168 SCVi XXL NER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781000	G7160 SCVi OE1 ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781020	G7165 SCVi XXL OE1 ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11718050	PDR518ROP SI EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718040	PDR518ROP HW EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795560	PDR918 EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718000	PDR918 EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11723200	DGC7445 HCX Pro ANC GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723210	DGC7445 HCX Pro ANC BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11795890	PDR918 HP EU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11780850	G7110 SC IB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780860	G7110 SC IB ED230 1,9 CS Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780940	G7110 SC OE1 BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11717980	PDR914 EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717890	PDR522ROP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717770	PDR514TOP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11717800	PDR514COP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11780630	G7110 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780640	G7110 SC F ED230 1,9 CLST Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780650	G7110 SCi F BW230 1,9 Auto Dos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780660	G7110 SCi F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11795510	PDR514COP G EU SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11795930	PDR514ROP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795530	PDR914 G EU SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11795540	PDR518TOP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718030	PDR518TOP HW EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717910	PDR518TOP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11780670	G7160 SCVi F ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780680	G7165 SCVi XXL F ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781180	G7110 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781190	G7110 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781230	G7113 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781240	G7113 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781260	G7118 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781270	G7118 SCU XXL NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11639020	DGC7845 HCX Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11605140	PFD102 i EP2 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605150	PFD103 SCi XXL EP2 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605160	PFD104 SCVi XXL EP2 OS3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605170	PFD101 EP3 ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605180	PFD101 i EP3 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605200	PFD101 U EP3 ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605210	PFD102 i EP3 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605220	PFD103 SCi XXL EP3 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605240	PFD104 SCVi XXL EP3 OS3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605270	PFD101 EP4 ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605320	PFD101 i EP4 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605330	PFD101 U EP4 ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605340	PFD102 i EP4 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605350	PFD103 SCi XXL EP4 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605360	PFD104 SCVi XXL EP4 OS3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11712930	G5000 SC OE1 ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11726140	G5000 SCU OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11726150	G5000 SCU OE1 ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11712940	G5430 SCU SL OE1 ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605530	PFD101 RKU ED/BW3N400 7,3kw	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605540	PFD104 SCVi XXL RKU OS3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11690710	G5000 C SC SG BW230/50 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605130	PFD101 U EP2 ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11677110	PDR508EL S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11737040	H2860-1BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11737040	H2860-1BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11568820	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
11568820	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
11730523	Power electron unit EL 7712	SMD- Diode STTH1R04A	Lead	7439-92-1
11737060	H2860-1-55B AN1 BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
11737060	H2860-1-55B AN1 BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11737060	H2860-1-55B AN1 BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
11737070	H2860-1-55BP AN1 EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
11737070	H2860-1-55BP AN1 EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11737070	H2860-1-55BP AN1 EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11208205	Power-/Control unit ELP 7784 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11569590	H7240BM AN3 BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11569650	H7840BM AN3 OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11569660	H7840BM AN3 BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11569640	H7770BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11569690	H7870BM AN3 OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11569700	H7870BM AN3 BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11764420	PDR518COP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11605090	PFD101 EP2 ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605110	PFD101 i EP2 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
7464342	Drive unclean side kpl.	Sensor	Lead	7439-92-1
11736330	PDR908HP EXP LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11736340	PDR908HP EXP SST	SMD- Diode STTH1R04A	Lead	7439-92-1
8391671	Threaded bushing	Rundmessing D 15,0 MS 58-hartgezogen	Lead	7439-92-1
8283161	Holder	Holder	Lead	7439-92-1
8392990	Adapter	Sechskantmessing SW 14 MS 58-hartgezogen	Lead	7439-92-1
11634900	DGC7845 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11717780	PDR514COP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717820	PDR514ROP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717810	PDR514ROP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11717830	PDR914 EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795520	PDR914 EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717900	PDR914 G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718010	PDR914 HP EU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11795370	PDR914 HP EU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11717840	PDR518TOP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717850	PDR518COP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717860	PDR518ROP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717930	PDR518ROP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11634930	DGC7445 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11717870	PDR918 EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717940	PDR918 G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718020	PDR918 HP EU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11744250	G7115 SCi XXL D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
7464442	Drive clean side kpl.	Sensor	Lead	7439-92-1
11690720	G5050 C SCVi SG ED230/50 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11726160	G5210 SCU OE1 BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11726170	G5210 SCU OE1 ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11690740	G5210 C SCi SG ED230/50 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11179220	HR1421-3 E ANZ EDST/CLST 120/208/60	Heater element Bottom heat 208V	Lead	7439-92-1
11179220	HR1421-3 E ANZ EDST/CLST 120/208/60	Heater element Top heat 208V	Lead	7439-92-1
11179220	HR1421-3 E ANZ EDST/CLST 120/208/60	Heater element Hot air 208V	Lead	7439-92-1
11560290	DGC7440 TW EDST/CLST 220/50-60	SMD- Diode STTH1R04A	Lead	7439-92-1
11560300	DGC7460 TW EDST/CLST 220/50-60	SMD- Diode STTH1R04A	Lead	7439-92-1
11560310	DGC7840X TW GRGR 220/50-60	SMD- Diode STTH1R04A	Lead	7439-92-1
11736270	PDR507EL EXP LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11736280	PDR507EL EXP SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11736290	PDR507HP EXP LW	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11560240	DG7240 TW EDST/CLST 220/50-60	SMD- Diode STTH1R04A	Lead	7439-92-1
11736300	PDR507HP EXP SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11744200	G7110 SCi D BW230 1,9 Auto Dos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11744180	G7110 SCi D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11744270	G7110 SCU D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11736310	PDR908EL EXP LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11744300	G7110 SC D ED230 1,9 CLST Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11736320	PDR908EL EXP SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11722710	PDR922 EL SOM SST B14Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11722720	PDR922 EL SOM SST B11Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11895310	PDR922 EL SOM SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11722730	PDR928 EL SOM SST B14Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11722750	PDR928 EL SOM SST B11Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11895330	PDR928 EL SOM SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11722780	PDR944 EL SOM SST B11Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11895350	PDR944 EL SOM SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923230	PDR944 SI RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923220	PDR944 EL RU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923200	PDR944 EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923190	PDR544ROP SI RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923180	PDR544ROP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923170	PDR928 SI RU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923150	PDR928 EL RU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923140	PDR928 EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923130	PDR528ROP SI RU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923110	PDR528ROP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923060	PDR922 HP RU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11923050	PDR922 HP RU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11923040	PDR922 SI RU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11923030	PDR922 EL RU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11854120	G7165 SCVi XXL I ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11901270	PDR922 EL EU SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11901280	PDR928 EL EU SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11901290	PDR944 EL EU SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11808110	PFD101 EP4 ED/BW230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
11808120	PFD101 U EP4 ED/BW230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
11808130	PFD101 i EP4 ED230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
11808140	PFD104 SCVi XXL EP4 OS230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
10471910	Regulator 400V Zweikreis	Regulator 400V Zweikreis	Lead	7439-92-1
10471910	Regulator 400V Zweikreis	Regulator 400V Zweikreis	Lead	7439-92-1
10471920	Regulator 400V Einkreis	Regulator 400V Einkreis	Lead	7439-92-1
10471920	Regulator 400V Einkreis	Regulator 400V Einkreis	Lead	7439-92-1
11895080	PDR914 EL SOM SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11895270	PDR918 EL SOM SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11722690	PDR918 EL SOM SST B14Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11722700	PDR918 EL SOM SST B11Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11854070	G7110 SC I BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11854080	G7110 SC I ED230 1,9 CLST Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11874980	H2455-55BP AN1 EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
11874980	H2455-55BP AN1 EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11874980	H2455-55BP AN1 EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11854100	G7160 SCVi I ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11854110	G7161 SCVi I ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11923020	PDR922 EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11924260	PDR510ROP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11924400	PDR910 EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11924420	PDR910 EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11924460	PDR910 G EU SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11924470	PDR910 EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11791670	HR1954-3 G DF USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11791670	HR1954-3 G DF USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11791680	HR1954-3 LP DF USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11791680	HR1954-3 LP DF USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11791690	HR1955-3 G DF GR USA EDST/CLST120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11791690	HR1955-3 G DF GR USA EDST/CLST120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11791700	HR1956-3 G DF GD USA EDST/CLST120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11791700	HR1956-3 G DF GD USA EDST/CLST120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11793350	HR1421-3 E USA EDST/CLST 120/208/60	Heater element Bottom heat 208V	Lead	7439-92-1
11793350	HR1421-3 E USA EDST/CLST 120/208/60	Heater element Top heat 208V	Lead	7439-92-1
11793350	HR1421-3 E USA EDST/CLST 120/208/60	Heater element Hot air 208V	Lead	7439-92-1
11793360	HR1421-3 E USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11793360	HR1421-3 E USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11793360	HR1421-3 E USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11924480	PDR910 G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11924510	PDR910 EL EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11924490	PDR510ROP EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11924250	PDR510COP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922740	PDR522ROP SI RU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922730	PDR522ROP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922720	PDR522TOP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922690	PDR918 SI RU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922680	PDR918 HP RU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11922670	PDR918 HP RU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11922640	PDR918 EL RU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11922610	PDR918 EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922600	PDR518ROP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922580	PDR518TOP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922550	PDR914 HP RU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11922470	PDR914 HP RU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11922350	PDR914 EL RU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922340	PDR914 EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11921350	PDR514ROP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11921340	PDR514TOP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11791520	HR1622-3 I USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11791520	HR1622-3 I USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791520	HR1622-3 I USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11791550	HR1924-3 G DF USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11791550	HR1924-3 G DF USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11791550	HR1924-3 G DF USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11808100	PFD104 SCVi XXL GB OS230 6,3 32A	Drain pump 220-240V 50HZ	Lead	7439-92-1
11718240	PDR528ROP SI EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795780	PDR528ROP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718250	PDR528ROP HW EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718310	PDR928 EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718270	PDR928 HW EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795820	PDR928 HW EU SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795810	PDR928 SI EU SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718360	PDR544ROP SI EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795830	PDR544ROP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718290	PDR944 EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795860	PDR944 SI EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795840	PDR944 EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795850	PDR944 G EU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11795870	PDR944 HW EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11780510	G7110 SC A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780520	G7110 SC A ED230 1,9 CLST Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780530	G7110 SCU A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780550	G7110 SCU A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780560	G7110 SCi A BW230 1,9 Auto Dos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780570	G7110 SCi A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11722760	PDR944 EL SOM SST B14Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11843380	PDR514ROP EL SOM IG B11Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795880	PDR922 HP EU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11796840	DGC7840 HCX Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11734420	DGC7440-55 HC PRO ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11780880	G7110 SCi IB BW230 1,9 Auto Dos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11734460	DGC7660-55 HC PRO ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11780890	G7110 SCi IB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780910	G7160 SCVi IB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780920	G7165 SCVi XXL IB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11795570	PDR918 HW EU SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718070	PDR918 SI EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11746550	H7270BM AB2 EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11746530	H7870BM AB2 EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11795580	PDR918 SI EU SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795600	PDR522TOP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11717950	PDR522TOP G EU IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11718280	PDR922 EL EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11746490	H7870BM AB2 OBSW 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11746540	H7870BM AB2 GRGR 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11718230	PDR922 HW EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795700	PDR922 SI EU SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11795670	PDR922 G EU SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11795770	PDR922 HW EU SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11718220	PDR922 SI EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11780580	G7115 SCi XXL A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11788070	G7110 SC GB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11788080	G7110 SC GB ED230 1,9 CS Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11788090	G7160 SCVi GB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11788100	G7165 SCVi XXL GB ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10907480	Control panel Display Timer 3054-1	Control panel Display Timer 3054-1	Lead	7439-92-1
10907480	Control panel Display Timer 3054-1	Control panel Display Timer 3054-1	Lead	7439-92-1
8287160	Residual heat ind. 5-fold 3054	Residual heat ind. 5-fold 3054	Lead	7439-92-1
11766750	KM3054-1 G USA EDST 120/60	Residual heat ind. 5-fold 3054	Lead	7439-92-1
11779710	G7160 SCVi UA ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781040	G7160 SCVi RU ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11722670	PDR914 EL SOM SST B14Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11722680	PDR914 EL SOM SST B11Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11901220	PDR914 EL EU SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11901210	PDR518ROP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11901250	PDR918 EL EU SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11807700	PFD101 i AUS ED230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11807780	PFD103 SCi XXL AUS ED230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11807790	PFD104 SCVi XXL AUS OS230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11807820	PFD101 GB ED/BW230 6,3 32A	Drain pump 220-240V 50HZ	Lead	7439-92-1
11808020	PFD101 i GB ED230 6,3 32A	Drain pump 220-240V 50HZ	Lead	7439-92-1
11808040	PFD102 i GB ED230 6,3 32A	Drain pump 220-240V 50HZ	Lead	7439-92-1
11808080	PFD103 SCi XXL GB ED230 6,3 32A	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11773070	G3885 SCVi CH ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780590	G7115 SCi XXL A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780600	G7160 SCVi A ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780610	G7165 SCVi XXL A ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11698030	DO7840 ANL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11781060	G7110 SC TR ED230 1,9 CLST Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781070	G7110 SCi TR ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781080	G7165 SCVi XXL TR ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781110	G7110 SC MER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781120	G7160 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781130	G7165 SCVi XXL MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781140	G7161 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781150	G7162 SCVi MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11781160	G7166 SCVi XXL MER ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11791060	H7145BM EU1 OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11772970	G3625 SCi CH BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11773010	G3625 SCi CH ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11772980	G3625 SCi CH OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11773000	G3625 SCi CH HB230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11773030	G3825 SCi CH BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11773050	G3825 SCi CH ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11773040	G3825 SCi CH OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11773060	G3685 SCVi CH ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11619730	TWD360WP USA LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11619650	TXD160WP USA LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11619850	TXI680WP USA LW Eco&Steam	SMD- Diode STTH1R04A	Lead	7439-92-1
11433380	G7100 C SCi SG ED230/50 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11619970	TWI680WP USA LW Eco&Steam	SMD- Diode STTH1R04A	Lead	7439-92-1
11432490	G7100 C SC SG BW230/50	Drain pump 220-240V 50HZ	Lead	7439-92-1
11619590	TWD160WP USA LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11587220	G5430 SCi SL ANL BW230 1,9 Australien	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586200	G5053 SCVi ANL ED230 1,9 AUS Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586190	G5000 i ANL ED230 1,9 CLST AUS Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11581490	G5265 Vi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11620030	TXR860WP USA LW Eco&Steam	SMD- Diode STTH1R04A	Lead	7439-92-1
11432540	G7310 C SC SG BW230/50 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11432550	G7310 C SCi SG ED230/50 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11432560	G7360 C SCVi SG OS/CS230/50 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11432580	G7960 C SCVi SG OS/CS230/50 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11433390	G7150 C SCVi SG ED230/50	Drain pump 220-240V 50HZ	Lead	7439-92-1
11620440	PDR507HP FIN LW Special	SMD- Diode STTH1R04A	Lead	7439-92-1
11667040	PDR510ROP EL ANL IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11667050	PDR910 EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11667070	PDR910 EL ANL IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11667190	PDR910 G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11581430	G5890 SCVi SL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573990	G5262 SCVi NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574000	G5267 SCVi XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574610	G7372 SCVi I OS/CS230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574620	G7373 SCVi I OS/CS230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554420	G5022 SC F BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554440	G5023 SC F BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554460	G5023 SC F ED230 1,9 CS FrontExcellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554560	G5022 F BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554220	G5002 SC F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554230	G5002 SC F ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554260	G5052 SCVi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554280	G5212 SC F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554240	G5002 SCi F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554300	G5212 SC F ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554310	G5212 SCi F OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554350	G5262 SCVi F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554500	G5222 SC F BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554510	G5223 SC F BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554520	G5223 SC F ED230 1,9 Front Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554530	G5272 SCVi F ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554540	G5273 SCVi F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554550	G5278 SCVi XXL F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11667680	PDR910 EL ANL SST B03Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11519330	H7680BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
10763101	Heater element Top heat	Heater element Top heat	Lead	7439-92-1
10763101	Heater element Top heat	Heater element Top heat	Lead	7439-92-1
11519420	H7780BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11519420	H7780BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11519420	H7780BP AN3 EDST/CLST 120/240/60	Heater element Top heat	Lead	7439-92-1
11519370	H7880BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11519370	H7880BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11519370	H7880BP AN3 EDST/CLST 120/240/60	Heater element Top heat	Lead	7439-92-1
11519390	H7880BP AN3 OBSW 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11519390	H7880BP AN3 OBSW 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11519390	H7880BP AN3 OBSW 120/240/60	Heater element Top heat	Lead	7439-92-1
11519400	H7880BP AN3 BRWS 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11519400	H7880BP AN3 BRWS 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11519400	H7880BP AN3 BRWS 120/240/60	Heater element Top heat	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11519380	H7880BP AN3 GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11519380	H7880BP AN3 GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11519380	H7880BP AN3 GRGR 120/240/60	Heater element Top heat	Lead	7439-92-1
11519410	H7880BPX AN3 GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11519410	H7880BPX AN3 GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11519410	H7880BPX AN3 GRGR 120/240/60	Heater element Top heat	Lead	7439-92-1
11569790	H7880BP2 AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11519330	H7680BP AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11667930	PDR510COP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11526440	G5000 SC AE ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11526480	G5050 SCVi AE ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11433780	G7100 SC ZA BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11433800	G7310 SC ZA ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11433810	G7360 SCVi ZA OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11433820	G7965 SCVi XXL ZA OS/CS2301,9 k2oAutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11528600	G5000 SC ZA BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11528610	G5000 SC ZA ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11374340	H2780BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11374340	H2780BP AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11374340	H2780BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11569770	H7180BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11569770	H7180BP AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11569770	H7180BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11569780	H7280BP AN3 GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11569780	H7280BP AN3 GRGR 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11569780	H7280BP AN3 GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11519350	H7580BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11519350	H7580BP AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11519350	H7580BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11519330	H7680BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11574600	G5273 SCVi I ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11307870	DGC7770 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308040	DGC7570 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11574710	PDR514COP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11308070	DGC7370 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307270	DGC7870X AN3 GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307850	DGC7875 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307920	DGC7870 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307930	DGC7870 AN3 OBSV 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308020	DGC7870 AN3 BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308030	DGC7870 AN3 GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308060	DGC7670 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308080	DGC7470 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308090	DGC7470 AN3 BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11308100	DGC7470 AN3 GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307440	DGC7840 AN3 OBSV 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307530	DGC7840 AN3 BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307560	DGC7840 AN3 GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307580	DGC7440 AN3 BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11307590	DGC7440 AN3 GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11550950	G5430 SC SL GB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11550960	G5481 SCVi SL GB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11550980	G5022 SC GB BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11307570	DGC7440 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11494720	G5481 SCVi SL RU ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11494730	G5690 SCVi SL RU ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11496100	G5890 SCVi SL RU ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11578100	PDR514ROP EL ANL IG B11Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11527380	G25215 i XXL CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479760	G5210 SCi OE1 OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479770	G5210 SCi OE1 BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479790	G5210 SCi OE1 ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479800	G5215 SCi XXL OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574740	PDR518ROP G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11479820	G5260 SCVi OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479830	G5265 SCVi XXL OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11568570	G25215 i XXL CH HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479840	G5430 SC SL OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11307200	DGC7840 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11479860	G5430 SCi SL OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479870	G5430 SCi SL OE1 ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479880	G5481 SCVi SL OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479890	G5640 SCi SL OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479900	G5690 SCVi SL OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11479910	G5840 SCi SL OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11307680	DGC7640 AN3 EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11550990	G5022 SC GB ED230 1,9 CS FrontSelection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574540	G5073 SCVi I ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573250	G5073 SCVi NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573290	G5078 SCVi XXL NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574550	G5222 SCU I ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574560	G5223 SC I ED230 1,9 CS Front Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573350	G5232 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574570	G5223 SCU I BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11574580	G5223 SCU I ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573400	G5232 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573440	G5233 SCU NER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573450	G5233 SCU NER ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11575550	G5242 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11575560	G5242 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573460	G5272 SCVi NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573470	G5283 SCVi NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573480	G5288 SCVi XXL NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573940	G5212 U NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573950	G5212 SCU NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573960	G5212 SCU NER ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573970	G5217 SCU XXL NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573980	G5217 SCU XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574590	G5272 SCVi I ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573210	G5072 SCVi NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551050	G5023 SC GB BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551060	G5023 SC GB ED230 1,9 CS FrontExcellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551080	G5072 SCVi GB ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574640	PDR514ROP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11551090	G5077 SCVi XXL GB ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551200	G5222 SC GB BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551230	G5222 SC GB ED230 1,9 Front Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551240	G5223 SC GB BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551250	G5223 SC GB ED230 1,9 Front Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551260	G5272 SCVi GB ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11551270	G5277 SCVi XXL GB ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574460	G5022 SC I ED230 1,9 CS Front Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574470	G5022 SCU I BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574480	G5023 SC I BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574490	G5023 SC I ED230 1,9 CS FrontExcellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574510	G5023 SCU I BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574520	G5023 SCU I ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11572910	G5022 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573040	G5022 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573110	G5023 SCU NER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11573160	G5023 SCU NER ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11574530	G5072 SCVi I ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604320	G7373 SCVi TR OS/CS230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604330	G7377 SCVi XXL TR OS/CS230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
10471890	Regulator 230V Zweikreis	Regulator 230V Zweikreis	Lead	7439-92-1
10471890	Regulator 230V Zweikreis	Regulator 230V Zweikreis	Lead	7439-92-1
10471900	Regulator 230V Einkreis	Regulator 230V Einkreis	Lead	7439-92-1
10471900	Regulator 230V Einkreis	Regulator 230V Einkreis	Lead	7439-92-1
11687410	H2455E ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11687410	H2455E ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11687430	H2455IP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11687430	H2455IP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11687440	H2457IP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11687440	H2457IP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11605600	PFD101i GB ED230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11717450	Operating module VSxH-single	Operating module VSxH-single	Lead	7439-92-1
11717450	Operating module VSxH-single	Operating module VSxH-single	Lead	7439-92-1
11587480	G5000 AUS BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587500	G5000 SC AUS BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587510	G5000 SC AUS ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587490	G5000 AUS ED230 1,9 Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587520	G5000 SCU AUS BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605630	PFD101 U GB ED/BW230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587530	G5000 SCU AUS ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604310	G7372 SCVi TR OS/CS230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11555800	G3885 SCVi ANL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11377283	Power electron.unit EL 4005-B	SMD- Diode STTH1R04A	Lead	7439-92-1
11604960	PFD103 SCi XXL D ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604750	PFD102i D ED3N400 7,3kw	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604670	PFD101 D ED/BW3N400 7,3kw	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604970	PFD104 SCVi XXL D OS3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605050	PFD103 SCi XXL EP1 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11659740	G5215 SCi XXL MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11659750	G5215 SCi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11667030	G5430 SCi SL F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11655890	G5055 SCVi XXL F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11662340	G5078 SCVi XXL F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604680	PFD101i D ED3N400 7,3kw	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604690	PFD101 U D ED/BW3N400 7,3kw	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605060	PFD104 SCVi XXL EP1 OS3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605800	PFD101i AUS ED230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605810	PFD103 SCi XXL AUS ED230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
11667290	TXD160WP CDN LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11605560	PFD101 GB ED/BW230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604170	G7322 SC TR BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604280	G7323 SC TR ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11715200	PDR944 SI ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11587540	G5000i AUS ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11731010	PDR518TOP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11730990	PDR522TOP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11509610	G7160 SCVi D ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11509630	G7165 SCVi XXL D ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587600	G5210 U AUS ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587610	G5210 SCU AUS ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587620	G5210 i AUS ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587630	G5210 SCi AUS ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11693360	PDR307HP GB LW CC	SMD- Diode STTH1R04A	Lead	7439-92-1
11693550	PDR307EL GB LW CC	SMD- Diode STTH1R04A	Lead	7439-92-1
11587640	G5263 SCVi AUS ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587650	G5430 SCi SL AUS BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587660	G5481 SCVi SL AUS ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11695890	H7240BM ROK OBSW 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11690600	G5000 C SCi CN ED220/50 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11690620	G5050 C SCVi CN ED220/50 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11690630	G5210 C SC CN BW220/50 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11690640	G5210 C SCU CN BW220/50 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11208154	Power-/Control unit ELP 7773 120V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11690660	G5430 C SC SL CN BW220/50 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11690670	G5430 C SCU SL CN BW220/50 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11690690	G5640 C SCi SL CN ED220/50 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11509600	G7115 SCi XXL D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587550	G5000 SCi AUS ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605660	PFD102 i GB ED230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605690	PFD103 SCi XXL GB ED230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605720	PFD104 SCVi XXL GB OS230 2,1	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605790	PFD101 AUS ED/BW230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605820	PFD104 SCVi XXL AUS OS230 3,2	Drain pump 220-240V 50HZ	Lead	7439-92-1
11667300	TXI680WP CDN LW Eco&Steam	SMD- Diode STTH1R04A	Lead	7439-92-1
11667310	TXR860WP CDN LW Eco&Steam	SMD- Diode STTH1R04A	Lead	7439-92-1
11605000	PFD101 EP1 ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605020	PFD101 i EP1 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605030	PFD101 U EP1 ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11605040	PFD102 i EP1 ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587560	G5053 SCVi AUS ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587570	G5210 AUS BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587580	G5210 AUS ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587590	G5210 SC AUS ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11509570	G7110 SC D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10564540	KM6527 FR R01 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
10564540	KM6527 FR R01 230/50	Heater plate 1,8kW 230V	Lead	7439-92-1
11705880	KM6527 FR IB 230/50	Heater plate 1,5kW 230V	Lead	7439-92-1
11705880	KM6527 FR IB 230/50	Heater plate 1,8kW 230V	Lead	7439-92-1
11509590	G7110 SCU D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11555790	G3825 SCi ANL ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586920	G5072 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586930	G5073 SCVi MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586940	G5077 SCVi XXL MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586960	G5078 SCVi XXL MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586500	G5274 SCVi MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587050	G5272 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587070	G5273 SCVi MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587100	G5277 SCVi XXL MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587110	G5278 SCVi XXL MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586970	G5222 SC MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586990	G5222 SC MER ED230 1,9 Front Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587010	G5222 SCU MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587030	G5222 SCi MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11587040	G5223 SC MER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11635610	G5222 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11635630	G5222 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11603940	G5022 SC TR BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11603990	G5022 SC TR ED230 1,9 CS FrontSelection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604000	G5022 SCi TR ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604010	G5072 SCVi TR ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604070	G5077 SCVi XXL TR ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604090	G5227 SCi XXL TR ED230 2,1 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586480	G5074 SCVi MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11569790	H7880BP2 AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11569790	H7880BP2 AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11528620	G5050 SCVi ZA ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11603680	G5210 SCU I OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11598160	DG7240 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11554470	G5072 SCVi F ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554750	G5072 Vi F ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11554490	G5073 SCVi F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586360	G5022 MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586370	G5022 U MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586380	G5022 U MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586410	G5022 i MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586420	G5022 i MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586660	G5022 SC MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586820	G5022 SC MER ED230 1,9CS Front Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11586840	G5022 SCU MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586850	G5022 SCU MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586870	G5022 SCi MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586880	G5022 SCi MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586900	G5023 SC MER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586910	G5023 SC MER ED230 1,9CS FrontExcellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11586460	G5072 Vi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604120	G5277 SCVi XXL TR ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629010	G5273 SCVi D ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629060	G5278 SCVi XXL D ED230 1,9 ActivePlus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629080	G7123 SC D BW230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629120	G7123 SC D ED230 1,9 CLST Front E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629130	G7123 SCU D BW230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629140	G7123 SCU D ED230 1,9 CLST E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11634000	G5053 Vi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11634010	G5053 SCVi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629180	G7323 SC D BW230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11634020	G5263 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629210	G7323 SC D ED230 1,9 CS AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629230	G7323 SCU D BW230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629240	G7323 SCU D ED230 1,9 CS AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629150	G7173 SCVi D ED230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629170	G7178 SCVi XXL D ED230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11555740	G3625 SCi ANL BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11450270	PG8592TS J AE-WW-AD 200V50HZ	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11450280	PG8592TS EXJ AE-WW-AD 200V60HZ	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11555750	G3625 SCi ANL ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11643620	PDR300-08HP CH LW CC	SMD- Diode STTH1R04A	Lead	7439-92-1
11555760	G3685 SCVi ANL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11555770	G3825 SCi ANL BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11628800	G5223 SCU D ED230 1,9 CS Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604340	G5215 SCi XXL TR ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604350	G5022 SC OE1 BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604360	G5022 SCU OE1 ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604370	G5022 SCi OE1 ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604380	G5023 SC OE1 BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604390	G5023 SCU OE1 ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604400	G5072 SCVi OE1 ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604410	G5073 SCVi OE1 ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604450	G5222 SC OE1 ED230 1,9 Front Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604560	G5222 SC OE1 BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604570	G5222 SCi OE1 ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604500	G5223 SC OE1 ED230 1,9 Front Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604510	G7373 SCVi OE1 OS/CS230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604580	G5272 SCVi OE1 ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11604590	G7172 SCVi OE1 ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629290	G7373 SCVi D OS/CS230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11629300	G7378 SCVi XXL D OS/CS230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11628680	G5072 SCVi D ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
11628700	G5077 SCVi XXL D ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
11628710	G5223 SC D BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11628750	G5223 SC D ED230 1,9Front ActivePlus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11628760	G5223 SCU D BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092190	G7100 SCU I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092180	G7100 SC I ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092200	G7100 SCU I ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092210	G7100 SCi I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092220	G7100 SCi I ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092170	G7100 SC I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11108000	DO7860 GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108000	DO7860 GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11109650	G27105 iXXL CH HB230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090430	G27105 iXXL CH BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109660	G27105 iXXL CH OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092160	G7100 I ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109280	G7100 SC B BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109410	G7100 SC B ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109420	G7100 SCi B BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109450	G7100 SCi B ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109470	G7105 SCi XXL B ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109460	G7105 SCi XXL B BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070480	G7100 i A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070510	G7100 SCi A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070520	G7100 SCi A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070450	G7100 SCU A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090440	G27105 iXXL CH ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
10917090	DGC7640 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10917130	DGC7840 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10917160	DGC7840X CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10917180	DGC7845 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10917100	DGC7640-55 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10917200	DGC7440-55 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10992750	G7100 SCi D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992760	G7100 SCi D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10992770	G7100 SCi D OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992740	G7100 i D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992790	G7105 SCi XXL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992800	G7100 U D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992820	G7100 SCU D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992810	G7100 SCU D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992830	G7100 SCU D HB230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992840	G7100 D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992850	G7100 SC D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992860	G7100 SC D ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090420	G17100 i CH ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090410	G17100 i CH BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109630	G17100 i CH HB230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109640	G17100 i CH OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070460	G7100 SCU A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11135690	DGC7460 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135710	DGC7460 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135730	DGC7460 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135770	DGC7840X AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135780	DGC7840X AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135790	DGC7840X AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135800	DGC7845X AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135810	DGC7845X AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135820	DGC7845X AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135830	DGC7840 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135840	DGC7840 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135850	DGC7840 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135860	DGC7840 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135870	DGC7845 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135880	DGC7845 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135890	DGC7845 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135900	DGC7845 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135910	DGC7860 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135920	DGC7860 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135930	DGC7860 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135940	DGC7860 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135950	DGC7865 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135650	DGC7440X AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11070400	G7100 SC A ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070390	G7100 SC A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070370	G7100 A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070380	G7100 A ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110110	G7100 SC NL BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110120	G7100 SCU NL ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110140	G7100 SCi NL ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091800	G7100 SC IB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091840	G7100 SC IB ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091850	G7100 SCU IB ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091870	G7100 SCi IB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091900	G7100 SCi IB ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11106970	DGC7440 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106990	DGC7440 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107040	DGC7460 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107060	DGC7460 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135460	DGC7440 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135600	DGC7440 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135610	DGC7440 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135620	DGC7440 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135630	DGC7440X AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135640	DGC7440X AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10917030	DGC7440 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673280	DGC7640-55 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673290	DGC7660-55 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905190	DGC7460 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905240	DGC7460 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905250	DGC7460 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905260	DGC7460 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905300	DGC7660 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905310	DGC7660 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905320	DGC7660 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905330	DGC7660 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905380	DGC7860 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905400	DGC7860 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905410	DGC7860 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905420	DGC7860 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905460	DGC7865 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905470	DGC7865 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905480	DGC7865 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905490	DGC7865 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905270	DGC7460X R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905280	DGC7460X R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905290	DGC7460X R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905430	DGC7860X R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673270	DGC7865X ANC OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10430020	DGC7860 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430030	DGC7860 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430050	DGC7860X ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430060	DGC7860X ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430110	DGC7865 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430090	DGC7865 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430100	DGC7865 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430120	DGC7865X ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430130	DGC7865X ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673110	DGC7440 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673120	DGC7440X ANC OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673170	DGC7640 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673200	DGC7840 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673210	DGC7840X ANC OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673220	DGC7845 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673230	DGC7845X ANC OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673140	DGC7460 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673150	DGC7460X ANC OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673190	DGC7660 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673240	DGC7860 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673250	DGC7860X ANC OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10673260	DGC7865 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905440	DGC7860X R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916870	DGC7840X R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916880	DGC7840X R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916890	DGC7840X R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916960	DGC7845X R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916990	DGC7845X R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10917000	DGC7845X R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937350	DGC7645 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937400	DGC7645 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937410	DGC7645 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937420	DGC7645 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937430	DGC7665 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937440	DGC7665 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937450	DGC7665 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10937470	DGC7665 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905750	DGC7460 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905770	DGC7660 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905790	DGC7860 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905800	DGC7860X CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905810	DGC7865 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905780	DGC7660-55 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10907900	DGC7460-55 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10907920	DGC7460-55 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916780	DGC7440X R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905450	DGC7860X R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905500	DGC7865X R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905510	DGC7865X R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10905530	DGC7865X R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10909970	DGC7440 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10913620	DGC7440 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10913630	DGC7440 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10913640	DGC7440 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916790	DGC7640 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916800	DGC7640 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916810	DGC7640 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916820	DGC7640 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916830	DGC7840 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916840	DGC7840 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916850	DGC7840 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916860	DGC7840 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916900	DGC7845 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916910	DGC7845 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916920	DGC7845 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916940	DGC7845 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10913660	DGC7440X R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10916770	DGC7440X R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102250	DGC7860 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102260	DGC7860 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102240	DGC7860 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102300	DGC7865 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102310	DGC7865 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102290	DGC7865 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102280	DGC7860X CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102270	DGC7860X CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102360	DGC7640-55 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102370	DGC7460-55 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11090930	G7100 SC F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11117430	H7840BMX CH BRWS 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11117440	H7840BMX CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11090950	G7100 SCI F OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090960	G7100 SCI F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090970	G7100 SCI F ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11985091	Power-/Control unit ELP 7754 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
7840091	Heater element Hot air 400V	Heater element Hot air 400V	Lead	7439-92-1
7840091	Heater element Hot air 400V	Heater element Hot air 400V	Lead	7439-92-1
11111180	H7840BP CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11090980	G7150 SCVi F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11111150	H7840BP CH BRWS 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11102210	DGC7845 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11152270	DGC7840X C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11148100	DGC7840X C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160030	DGC7860 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160020	DGC7860 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160010	DGC7860 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160060	DGC7860X C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11160050	DGC7860X C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102040	DGC7440 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102050	DGC7440 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102030	DGC7440 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102070	DGC7460 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102080	DGC7460 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102060	DGC7460 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102140	DGC7840X CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102130	DGC7840X CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102150	DGC7640 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102160	DGC7660 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102180	DGC7840 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102190	DGC7840 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102170	DGC7840 CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102220	DGC7845 CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11102230	DGC7845 CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11091000	G7155 SCVi XXL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091020	G7310 SC F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091080	G7312 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091030	G7310 SCU F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091040	G7310 SCi F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091050	G7310 SCi F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091100	G7360 SCVi F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091120	G7365 SCVi XXL F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
8137570	Heater plate 1,5kW 230V	Heater plate 1,5kW 230V	Lead	7439-92-1
8137570	Heater plate 1,5kW 230V	Heater plate 1,5kW 230V	Lead	7439-92-1
8220720	Heater plate 2,2-0,75KW 230V	Heater plate 2,2-0,75KW 230V	Lead	7439-92-1
11124060	H7140BM RU EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124070	H7240BM RU EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124100	H7440BM RU EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124080	H7440BM RU OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124090	H7440BM RU GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124120	H7440BMX RU GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124110	H7440BMX RU OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124300	H7640BM RU EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124270	H7640BM RU OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124290	H7640BM RU GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124330	H7840BM RU EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124310	H7840BM RU OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11091010	G7310 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11111160	H7840BP CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111170	H7840BP CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11090990	G7152 SCVi F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
7840262	Heater element Bottom heat 400V	Heater element Bottom heat 400V	Lead	7439-92-1
7840262	Heater element Bottom heat 400V	Heater element Bottom heat 400V	Lead	7439-92-1
11117490	H7860BP CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117490	H7860BP CH EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11117460	H7860BP CH BRWS 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117460	H7860BP CH BRWS 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11117470	H7860BP CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117470	H7860BP CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11117480	H7860BP CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117480	H7860BP CH GRGR 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11117420	H7840BPX CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117400	H7840BPX CH BRWS 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117410	H7840BPX CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117520	H7860BPX CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117520	H7860BPX CH GRGR 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11117500	H7860BPX CH BRWS 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117500	H7860BPX CH BRWS 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11117510	H7860BPX CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11117510	H7860BPX CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11159970	DGC7840 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133920	DO7860 NER BRWS 230/50	Supply cable DO	Lead	7439-92-1
11133920	DO7860 NER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11133920	DO7860 NER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11133930	DO7860 NER OBSW 230/50	Supply cable DO	Lead	7439-92-1
11133930	DO7860 NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11133930	DO7860 NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11092480	G7107 SCU XXL NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092470	G7107 SCU XXL NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11109710	G7100 SC OE1 BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109720	G7100 SCi OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11180330	DGC7540 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11180340	DGC7340 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11091260	G7100 SC GB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091380	G7100 SC GB ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11133690	DGC7440 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133340	DGC7440 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133360	DGC7440 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133380	DGC7440 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133800	DGC7440X RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133400	DGC7440X RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133410	DGC7440X RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11152160	DGC7460 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133950	DO7860 NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11135960	DGC7865 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135980	DGC7865 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11136000	DGC7865 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11092390	G7100 SCU NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11135750	DGC7460 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11092400	G7100 SCU NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092410	G7100 SCi NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092420	G7102 SCU NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092430	G7102 SCU NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092440	G7103 SCU NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092450	G7103 SCU NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11111650	DO7860 NL EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11111650	DO7860 NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11111650	DO7860 NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11111630	DO7860 NL OBSW 230/50	Supply cable DO	Lead	7439-92-1
11111630	DO7860 NL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11111630	DO7860 NL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11111640	DO7860 NL GRGR 230/50	Supply cable DO	Lead	7439-92-1
11111640	DO7860 NL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11111640	DO7860 NL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11133950	DO7860 NER EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11133950	DO7860 NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11133420	DGC7460 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133770	DGC7860X RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11091500	G7100 SCi GB ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091520	G7102 SC GB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091540	G7102 SC GB ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11133510	DGC7440X C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133520	DGC7440X C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159660	DGC7440 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159650	DGC7440 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159640	DGC7440 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159840	DGC7460 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159820	DGC7460 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159750	DGC7460 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133820	DGC7460X C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133810	DGC7460X C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159880	DGC7640 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159870	DGC7640 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159860	DGC7640 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159960	DGC7660 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159930	DGC7660 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159900	DGC7660 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159990	DGC7840 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11159980	DGC7840 C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133760	DGC7860X RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133430	DGC7460 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133440	DGC7460 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11148080	DGC7840X RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133480	DGC7840X RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133500	DGC7840X RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11152170	DGC7460X RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133450	DGC7460X RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133470	DGC7460X RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133780	DGC7840 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133650	DGC7840 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133660	DGC7840 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11091390	G7100 SCi GB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11133670	DGC7840 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133790	DGC7640 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133530	DGC7640 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133540	DGC7640 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133560	DGC7640 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11152190	DGC7860 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133720	DGC7860 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133730	DGC7860 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133750	DGC7860 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11152230	DGC7860X RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093730	H7840BMX GB BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11093760	H7840BMX GB GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093750	H7840BMX GB OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10407285	Power-/Control unit ELP 7695 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11108350	H7140BM F EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093700	H7840BM GB GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093690	H7840BM GB OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093680	H7840BM GB BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093720	H7840BM GB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093660	H7640BM GB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10921007	Power-/Control unit ELP 7794 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11108400	H7240BM F EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108370	H7240BM F BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108380	H7240BM F OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108390	H7240BM F GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108540	H7440BM F EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108510	H7440BM F BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108520	H7440BM F OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108530	H7440BM F GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108600	H7440BMX F GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108580	H7440BMX F BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108590	H7440BMX F OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093570	H7440BMX GB OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10966750	DG7440-55 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11985101	Power-/Control unit ELP 7755 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
6986500	Release element 220/240V 50/60HZ	Release element 220/240V 50/60HZ	Lead	7439-92-1
6986500	Release element 220/240V 50/60HZ	Release element 220/240V 50/60HZ	Lead	7439-92-1
10874920	H7890BP AN6 EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
6873531	Drive top	Drive top	Lead	7439-92-1
6873531	Drive top	Drive top	Lead	7439-92-1
9115231	Heater element Hot air 220-240V	Heater element Hot air 220-240V	Lead	7439-92-1
9115231	Heater element Hot air 220-240V	Heater element Hot air 220-240V	Lead	7439-92-1
9412090	Heater element Top heat 220-240V	Heater element Top heat 220-240V	Lead	7439-92-1
9412090	Heater element Top heat 220-240V	Heater element Top heat 220-240V	Lead	7439-92-1
10921087	Power-/Control unit ELP 7792 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
4311530	Release element 220/240V 50/60HZ	Release element 220/240V 50/60HZ	Lead	7439-92-1
4311530	Release element 220/240V 50/60HZ	Release element 220/240V 50/60HZ	Lead	7439-92-1
11093410	H7140BM GB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093470	H7240BM GB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093550	H7440BM GB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093520	H7440BM GB BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093530	H7440BM GB OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093540	H7440BM GB GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093580	H7440BMX GB GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11093560	H7440BMX GB BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108750	H7640BM F EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11106370	DG7240 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106390	DG7240 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106420	DG7440 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106430	DG7440 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099520	H7240BM EU1 OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099530	H7240BM EU1 GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099770	H7440BM EU1 OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099790	H7440BM EU1 GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099850	H7440BMX EU1 OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099860	H7440BMX EU1 GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11101580	H7840BM NL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099920	H7640BM EU1 OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11101480	H7640BM EU1 GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11101560	H7840BM EU1 OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11101570	H7840BM EU1 GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11101610	H7840BMX EU1 OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11101620	H7840BMX EU1 GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129820	H7140BM NER EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129860	H7240BM NER EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129830	H7240BM NER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129840	H7240BM NER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129850	H7240BM NER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11106290	DG2840 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108720	H7640BM F BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108730	H7640BM F OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108740	H7640BM F GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108880	H7840BM F EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108850	H7840BM F BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108860	H7840BM F OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108950	H7840BMX F GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108870	H7840BM F GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108930	H7840BMX F BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11108940	H7840BMX F OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11110700	H7640BM B EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11110400	H7140BM B EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11110440	H7240BM B EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11110620	H7440BM B EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11110730	H7840BM B EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11112910	DG2840 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11112920	DG2840 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11112930	DG2840 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101490	H7640BM NL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099490	H7140BM NL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099540	H7240BM NL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11099820	H7440BM NL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10966740	DG7440 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10088720	PG8591 B AW-WW-AD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10088730	PG8591 B AE-WW-AD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10087380	PG8583 B AW-WW-AD-LD 3 AC 230	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10087390	PG8583 B AE-WW-AD-LD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10087410	PG8593 B AE-WW-AD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10183020	PG8592 J AE-WW-AD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10183030	PG8592 EXJ AE-WW-AD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10144470	PG8581 J AE-AD-LD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10144640	PG8581 EXJ AE-AD-LD 60Hz	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10144680	PG8591 J AE-WW-AD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10144730	PG8591 EXJ AE-WW-AD 60Hz	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10399270	PG8582CD J i-Gerät WW-AD-CM	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10226930	PG8582CD J AE-WW-AD-CM-w/lid	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10226940	PG8582CD EXJ AE-WW-AD-CM-w/lid	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10144770	PG8582 J AE-WW-AD-LD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10144810	PG8582 EXJ AE-WW-AD-LD 60Hz	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10144880	PG8583 EXJ AE-WW-ADP-PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10250020	PG8583 USA AE-WW-AD-PD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10250030	PG8593 USA AE-WW-AD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10249980	PG8581 USA AE-WW-AD-LD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10419630	PG8583CD CDN i-Gerät	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10262720	PG8583CD CDN AE-WW-AD-CM-w/lid	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10114200	PG8593 N AE-WW-AD-CM 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
5634684	Drain pump BE28B3-186 230V/50HZ	Drain pump BE28B3-186 230V/50HZ	Lead	7439-92-1
9513790	ETD4 Olympus Basic PAA	Drain pump BE28B3-186 230V/50HZ	Lead	7439-92-1
9513800	ETD4 Olympus Plus PAA	Drain pump BE28B3-186 230V/50HZ	Lead	7439-92-1
7831841	Heater element Bottom heat 208V	Heater element Bottom heat 208V	Lead	7439-92-1
7831841	Heater element Bottom heat 208V	Heater element Bottom heat 208V	Lead	7439-92-1
7758673	Heater element Top heat 208V	Heater element Top heat 208V	Lead	7439-92-1
7758673	Heater element Top heat 208V	Heater element Top heat 208V	Lead	7439-92-1
7840051	Heater element Hot air 208V	Heater element Hot air 208V	Lead	7439-92-1
7840051	Heater element Hot air 208V	Heater element Hot air 208V	Lead	7439-92-1
9810110	HR1421 USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
9810110	HR1421 USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
9810110	HR1421 USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
9810120	HR1421 USA EDST/CLST 120/208/60	Heater element Bottom heat 208V	Lead	7439-92-1
9810120	HR1421 USA EDST/CLST 120/208/60	Heater element Top heat 208V	Lead	7439-92-1
9810120	HR1421 USA EDST/CLST 120/208/60	Heater element Hot air 208V	Lead	7439-92-1
10088710	PG8581 B AW-WW-LD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10088340	PG8581 N AW-WW-LD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10088860	PG8592 N AE-WW-AD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10088320	PG8581 N AW-WW-PD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10088350	PG8591 N AW-WW-AD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10088850	PG8562 N AE-WW 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10114180	PG8583 N AE-WW-AD-PD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10254310	PG8583 CDN AE-WW-AD-LD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10424590	DG7240 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424600	DG7240 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424610	DG7240 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424620	DG7240 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424640	DG7440 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424650	DG7440 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424660	DG7440 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10680140	DG7440 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10680150	DG7240 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10748990	DG7440-55 ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966610	DG2740 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966620	DG2840 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966630	DG7140 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966640	DG7240 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966650	DG7240 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966660	DG7240 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966670	DG7240 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966680	DG7440 R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966700	DG7440 R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966710	DG7440 R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966720	DG7440 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10966730	DG7240 CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424570	DG7140 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10254320	PG8583 CDN AE-WW-ADP-LD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10254330	PG8583 CDN AE-WW-AD-LD-OIL	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10254340	PG8593 CDN AE-WW-AD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10276820	PG8582 EXE AE-WW-AD-LD 3 AC 220-230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10276840	PG8592 EXE AE-WW-AD-CM 3 AC 220-230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10441980	PG8582CD EXE i-Gerät WW-AD-CM	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10276860	PG8582CD EXE AE-WW-AD-CM 3 AC 220-230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10442040	PG8583CD EXE i-Gerät OEL	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10276910	PG8583CD EXE AE-WW-AD-CM-OIL 60Hz	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10276770	PG8583 EXE AE-WW-ADP-LD 3 AC 220-230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10276800	PG8593 EXE AE-WW-AD-CM 3 AC 220-230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10254360	PG8581 CDN AE-WW-AD-LD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10254430	PG8591 CDN AE-WW-AD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
8122370	Induction coil G5 Octa OL L100	Induction coil G5 Octa OL L100	Lead	7439-92-1
8122370	Induction coil G5 Octa OL L100	Induction coil G5 Octa OL L100	Lead	7439-92-1
8122390	Induction coil G5 Octa OL L250	Induction coil G5 Octa OL L250	Lead	7439-92-1
8122390	Induction coil G5 Octa OL L250	Induction coil G5 Octa OL L250	Lead	7439-92-1
10714830	PG8583 USA AE-WW-AD-LD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12384020	Power-/Control unit ELP 7202 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10424630	DG7440 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424440	DG2740 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424470	DG2840 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107990	DO7860 GB BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107990	DO7860 GB BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108010	DO7860 GB GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11108010	DO7860 GB GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11136380	DO7860 B EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11136380	DO7860 B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11136380	DO7860 B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11136350	DO7860 B BRWS 230/50	Supply cable DO	Lead	7439-92-1
11136350	DO7860 B BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11136350	DO7860 B BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11136360	DO7860 B OBSW 230/50	Supply cable DO	Lead	7439-92-1
11136360	DO7860 B OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11136360	DO7860 B OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11136370	DO7860 B GRGR 230/50	Supply cable DO	Lead	7439-92-1
11136370	DO7860 B GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11136370	DO7860 B GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11111090	H7640BM CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111220	H7840BM CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111190	H7840BM CH BRWS 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111200	H7840BM CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111210	H7840BM CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11117450	H7840BMX CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11108020	DO7860 GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11107960	DO7860 A OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107960	DO7860 A OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11107970	DO7860 A GRGR 230/50	Supply cable DO	Lead	7439-92-1
11107970	DO7860 A GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107970	DO7860 A GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11142121	Drain pump 220-240V 50HZ	Drain pump 220-240V 50HZ	Lead	7439-92-1
11142121	Drain pump 220-240V 50HZ	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090940	G7100 SCU F ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11107740	G7100 SC F ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11107930	DO7860 D EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11107930	DO7860 D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107930	DO7860 D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11107900	DO7860 D BRWS 230/50	Supply cable DO	Lead	7439-92-1
11107900	DO7860 D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107900	DO7860 D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11107910	DO7860 D OBSW 230/50	Supply cable DO	Lead	7439-92-1
11107910	DO7860 D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107910	DO7860 D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11107920	DO7860 D GRGR 230/50	Supply cable DO	Lead	7439-92-1
11107920	DO7860 D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107920	DO7860 D GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11108020	DO7860 GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10114190	PG8583 N AE-WW-ADP-PD 3 AC230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10429740	DGC7640 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429700	DGC7640 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429720	DGC7640 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429850	DGC7840 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429830	DGC7840 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429840	DGC7840 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429860	DGC7840X ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429870	DGC7840X ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429940	DGC7845 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429910	DGC7845 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429930	DGC7845 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429960	DGC7845X ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429970	DGC7845X ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424530	DGC7460 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424510	DGC7460 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10424520	DGC7460 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10462080	DGC7460X ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10462100	DGC7460X ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429810	DGC7660 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429790	DGC7660 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429800	DGC7660 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430040	DGC7860 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10462070	DGC7440X ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10144850	PG8583 J AE-WW-ADP-PD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10722090	Drain valve SBS DGC	Drain valve SBS DGC	Lead	7439-92-1
10722090	Drain valve SBS DGC	Drain valve SBS DGC	Lead	7439-92-1
10884949	Power-/Control unit ELP 7442 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
10429780	DGC7660 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430080	DGC7865 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430150	DGC7865X ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430000	DGC7860 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429820	DGC7840 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429990	DGC7845X ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429680	DGC7640 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429520	DGC7440 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10462060	DGC7440X ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429880	DGC7840X ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429900	DGC7845 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10430070	DGC7860X ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10461130	DGC7460 ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10462090	DGC7460X ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429640	DGC7440 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429550	DGC7440 ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10429580	DGC7440 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10462040	DGC7440X ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11107960	DO7860 A OBSW 230/50	Supply cable DO	Lead	7439-92-1
11129480	H7640BM SER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129490	H7640BM SER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11098680	H7240BM TR EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11098730	H7840BM TR EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11132810	DG2740 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132820	DG2840 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132860	DG2840 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132870	DG2840 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132850	DG7240 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132880	DG7440 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132890	DG7440 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11132910	DG7440 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135330	DG2740 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135390	DG2840 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135350	DG2840 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135380	DG2840 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135340	DG2840 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135410	DG7440 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135420	DG7440 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135430	DG7440 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11135400	DG7440 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11119390	H7240BM I EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129470	H7840BM IB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129910	H7440BM NER EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129880	H7440BM NER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129890	H7440BM NER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129900	H7440BM NER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129940	H7440BMX NER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129920	H7440BMX NER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129930	H7440BMX NER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129980	H7640BM NER EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129950	H7640BM NER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129960	H7640BM NER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129970	H7640BM NER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11130020	H7840BM NER EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129990	H7840BM NER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11130000	H7840BM NER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11130010	H7840BM NER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11130050	H7840BMX NER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11130030	H7840BMX NER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11130040	H7840BMX NER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11101690	H7340BM NL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11182510	H7340BM B EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129440	H7240BM IB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11129460	H7640BM IB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119480	H7440BM I EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11110990	H7240BM CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11110960	H7240BM CH BRWS 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11110970	H7240BM CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11110980	H7240BM CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
7512511	Temperature regul. Sub-assembly	Temperature regul. Sub-assembly	Lead	7439-92-1
7512511	Temperature regul. Sub-assembly	Temperature regul. Sub-assembly	Lead	7439-92-1
10400200	H2890B ANL EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
10874880	H2890B AN6 EDST/CLST 220/60	Temperature regul. Sub-assembly	Lead	7439-92-1
9670673	Heater element Oberhitze 230V	Heater element Top heat 230V	Lead	7439-92-1
9670673	Heater element Oberhitze 230V	Heater element Top heat 230V	Lead	7439-92-1
9666872	Heater element Unterhitze 230-240V	Heater element Unterhitze 230-240V	Lead	7439-92-1
9666872	Heater element Unterhitze 230-240V	Heater element Unterhitze 230-240V	Lead	7439-92-1
9909633	Supply cable DO	Supply cable DO	Lead	7439-92-1
9909633	Supply cable DO	Supply cable DO	Lead	7439-92-1
10418350	Release element 10.0332.14	Release element 10.0332.14	Lead	7439-92-1
10418350	Release element 10.0332.14	Release element 10.0332.14	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11107980	DO7860 A EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11107980	DO7860 A EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107980	DO7860 A EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11107950	DO7860 A BRWS 230/50	Supply cable DO	Lead	7439-92-1
11107950	DO7860 A BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11107950	DO7860 A BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11111100	H7640BM CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11119570	H7840BM I EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119330	H7240BM SER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119360	H7240BM SER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119380	H7240BM SER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119400	H7440BM SER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119430	H7440BM SER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119460	H7440BM SER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119500	H7440BMX SER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119510	H7440BMX SER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119520	H7440BMX SER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119540	H7840BM SER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119550	H7840BM SER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119560	H7840BM SER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119580	H7840BMX SER BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119590	H7840BMX SER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11119600	H7840BMX SER GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11133640	DG2840 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11133620	DG7440 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
9183391	Heater element Hot air 400V	Heater element Hot air 400V	Lead	7439-92-1
9183391	Heater element Hot air 400V	Heater element Hot air 400V	Lead	7439-92-1
9415600	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
9415600	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
11124320	H7840BM RU GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11092740	G7965 SCVi XXL NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092730	G7915 SCi XXL NER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110840	G7560 SCVi NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110870	G7565 SCVi XXL NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109970	G7360 SCVi OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092720	G7595 SCVi XXL NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092710	G7590 SCVi NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109960	G7315 SCi XXL OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109950	G7310 SCi OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109940	G7310 SC OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109930	G7310 SC OE1 BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109980	G7365 SCVi XXL OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109990	G7510 SCi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110000	G7590 SCVi OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110010	G7595 SCVi XXL OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110020	G7910 SCi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110030	G7960 SCVi OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110040	G7965 SCVi XXL OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091560	G7150 SCVi GB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091620	G7155 SCVi XXL GB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091600	G7152 SCVi GB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091650	G7310 SC GB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092690	G7367 SCVi XXL NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110220	G7157 SCVi XXL NL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092370	G7960 SCVi SER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092380	G7965 SCVi XXL SER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109730	G7150 SCVi OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109750	G7155 SCVi XXL OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092500	G7150 SCVi NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092510	G7152 SCVi NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092520	G7155 SCVi XXL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092530	G7157 SCVi XXL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092560	G7310 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092570	G7310 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092580	G7310 SCi NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092590	G7310 SCi NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092600	G7312 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092610	G7312 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092630	G7315 SCU XXL NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092620	G7315 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092640	G7317 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092650	G7317 SCU XXL NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092660	G7360 SCVi NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092680	G7365 SCVi XXL NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092670	G7362 SCVi NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091670	G7310 SC GB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
9682460	H6800BM SA EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9637840	H6800BM ROK EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
9637840	H6800BM ROK EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9637810	H6200BM ROK EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
9637810	H6200BM ROK EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9769620	H6100BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9769620	H6100BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9769630	H6200BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
9769630	H6200BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9769640	H6700BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9769640	H6700BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9769650	H6800BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9769650	H6800BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9660040	H6800BM USA BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9660040	H6800BM USA BRWS 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9624720	H6400BM C CN EDST/CLST 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
9624720	H6400BM C CN EDST/CLST 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9624770	H6800BM C CN EDST/CLST 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
9624770	H6800BM C CN EDST/CLST 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9624700	H6400BM C CN BRWS 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
9624700	H6400BM C CN BRWS 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9624750	H6800BM C CN BRWS 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
9682460	H6800BM SA EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11091680	G7310 SCI GB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091700	G7315 SCI XXL GB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091690	G7312 SC GB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091720	G7360 SCVi GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091740	G7365 SCVi XXL GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091730	G7362 SCVi GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091750	G7560 SCVi GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091770	G7590 SCVi GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091780	G7960 SCVi GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091790	G7965 SCVi XXL GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11095350	G7910 SCI GB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11186510	G7510 SCI TR OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11186520	G7595 SCVi XXL TR OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11284070	H7240BM HK BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11284080	H7240BM HK GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11284090	H7264B HK BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11284100	H7264B HK GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11186540	G7915 SCI XXL TR OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
9518000	H6400BM D BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
9518000	H6400BM D BRWS 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9563500	H6200BM GB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
9563500	H6200BM GB EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11110200	G7155 SCVi XXL NL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071170	G7910 SCI A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071180	G7915 SCI XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071190	G7960 SCVi A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071200	G7965 SCVi XXL A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092340	G7560 SCVi SER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090450	G17150 Vi CH ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090460	G27155 Vi XXL CH ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090470	G17310 SC CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090480	G17310 SCI CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090490	G17310 SCI CH ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090540	G27315 SCI XXL CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090550	G27315 SCI XXL CH ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090510	G17312 SCI CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090520	G17312 SCI CH ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090560	G27317 SCI XXL CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090570	G27317 SCI XXL CH ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090660	G17590 SCVi CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090680	G27595 SCVi XXL CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090580	G17360 SCVi CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090610	G27365 SCVi XXL CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090590	G17362 SCVi CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090620	G27367 SCVi XXL CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070740	G7155 SCVi XXL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992710	G7150 SCVi D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992720	G7155 SCVi XXL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992690	G7150 Vi D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992700	G7155 Vi XXL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070780	G7310 SC A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070790	G7310 SC A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070970	G7360 SCVi A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070800	G7310 SCU A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070810	G7310 SCU A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070820	G7310 SCI A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071040	G7365 SCVi XXL A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070830	G7310 SCI A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070910	G7315 SCI XXL A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070920	G7315 SCI XXL A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071120	G7560 SCVi A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071100	G7510 SCI A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071130	G7565 SCVi XXL A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071140	G7590 SCVi A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071110	G7515 SCI XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11071150	G7595 SCVi XXL A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070700	G7150 Vi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070710	G7150 SCVi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090640	G17510 SCI CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11090730	G27965 SCVi XXL CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109570	G7360 SCVi B OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109590	G7367 SCVi XXL B OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109580	G7362 SCVi B OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110250	G7310 SCi NL ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091930	G7310 SC IB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091940	G7310 SC IB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110270	G7360 SCVi NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091950	G7360 SCVi IB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110290	G7362 SCVi NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110310	G7365 SCVi XXL NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091960	G7590 SCVi IB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091970	G7910 SCi IB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091980	G7960 SCVi IB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091990	G7965 SCVi XXL IB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110150	G7150 Vi NL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091910	G7150 SCVi IB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11091920	G7155 SCVi XXL IB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110160	G7150 SCVi NL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110170	G7152 SCVi NL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110180	G7153 SCVi NL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092360	G7910 SCi SER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090710	G17960 SCVi CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090630	G27515 SCi XXL CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092270	G7310 SC I ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092280	G7310 SCU I BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092290	G7310 SCU I ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092300	G7310 SCi I ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092310	G7360 SCVi I OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092330	G7365 SCVi XXL I OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092320	G7362 SCVi I OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092230	G7150 Vi I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092240	G7150 SCVi I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092260	G7155 SCVi XXL I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092250	G7152 SCVi I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11092350	G7590 SCVi SER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109480	G7150 Vi B ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109490	G7150 SCVi B ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109500	G7155 SCVi XXL B ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109520	G7310 SC B BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109530	G7310 SCi B BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109540	G7310 SCi B ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109550	G7315 SCi XXL B BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11109560	G7315 SCi XXL B ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11090700	G27915 SCi XXL CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11323670	Sealing ring 7,65x1,78	Sealing ring 7,65x1,78	Lead	7439-92-1
8534100	Distributor CS 1028 iso	Rundmessing D 17,0 MS 58-hartgezogen	Lead	7439-92-1
8537580	Distributor CS 1028 npt	Rundmessing D 17,0 MS 58-hartgezogen	Lead	7439-92-1
8119120	Jet 0,27MM	Jet 0,27MM	Lead	7439-92-1
8119140	Jet 0,32MM	Jet 0,32MM	Lead	7439-92-1
3091450	Jet 0,42MM	Jet 0,42MM	Lead	7439-92-1
11281360	DO7860 CH EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11281360	DO7860 CH EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11281360	DO7860 CH EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11281380	DO7860 CH GRGR 230/50	Supply cable DO	Lead	7439-92-1
11281380	DO7860 CH GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11281380	DO7860 CH GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11281400	DO7860 CH OBSW 230/50	Supply cable DO	Lead	7439-92-1
11281400	DO7860 CH OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11281400	DO7860 CH OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11281420	DO7860 CH BRWS 230/50	Supply cable DO	Lead	7439-92-1
11281420	DO7860 CH BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11281420	DO7860 CH BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11254770	PDR507EL UA LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11254780	PDR507EL UA SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11254790	PDR507HP UA LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11254800	PDR507HP UA SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11310940	DGC7541 R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105820	H7640BM D GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11105840	H7640BM D EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11105930	H7840BM D BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11105940	H7840BM D OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11105950	H7840BM D GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11105960	H7840BM D EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11106010	H7840BMX D BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11106020	H7840BMX D OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11106030	H7840BMX D GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104020	H7140BM D EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104060	H7240BM D EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104070	H7240BM D BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104080	H7240BM D OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104090	H7240BM D GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104330	H7440BM D OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104320	H7440BM D BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11104340	H7440BM D GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104350	H7440BM D EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104390	H7440BMX D BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104400	H7440BMX D OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11104410	H7440BMX D GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11271910	G7100 SCU B ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11254810	PDR908EL UA SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11158760	G7150 SCVi RU ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11166590	G7150 SCVi UA ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11208153	Power-/Control unit ELP 7773 120V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11158770	G7360 SCVi RU OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11166600	G7360 SCVi UA OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11166620	G7560 SCVi UA OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11158780	G7560 SCVi RU OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11166650	G7590 SCVi UA OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11166680	G7960 SCVi UA OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11166700	G7965 SCVi XXL UA OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11158790	G7590 SCVi RU OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11158800	G7960 SCVi RU OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11158810	G7965 SCVi XXL RU OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11166740	G7310 SCi RU BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11147230	DG7240 J EDST/CLST 200/50/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11166770	G7910 SCi RU OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11148030	DG7240 ROK EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11402030	PDR914 EL ANL SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11402060	PDR914 G ANL IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11402110	PDR918 G ANL SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11281770	H6180BP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11281770	H6180BP BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11391760	PDR928 EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11254820	PDR908HP UA SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11267580	PDR507HP UA LW Special	SMD- Diode STTH1R04A	Lead	7439-92-1
11187990	G7114 ANL BW230 1,9 AUS	Drain pump 220-240V 50HZ	Lead	7439-92-1
11187980	G7114 SC ANL ED230 1,9 CLST AUS	Drain pump 220-240V 50HZ	Lead	7439-92-1
4559020	Sensor	Sensor	Lead	7439-92-1
7814540	PG8527 F EL AP BO PRT 316L 380V60HZ	Sensor	Lead	7439-92-1
10399830	PG8583CD J i-Gerät ADP	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10226950	PG8583CD J AE-WW-ADP-CM-w/lid	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10226960	PG8583CD EXJ AE-WW-ADP-CM-w/lid	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10410040	PG8583CD USA i-Gerät	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10262730	PG8583CD USA AE-WW-AD-CM-w/lid	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10410420	PG8583CD USA i-Gerät OEL	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
10262740	PG8583CD USA AE-WW-AD-CM-OIL-w/lid	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
6482409	Control electr.unit EW 430	Control electr.unit EW 430	Lead	7439-92-1
6482409	Control electr.unit EW 430	Control electr.unit EW 430	Lead	7439-92-1
7964880	PT8257 WP NER 3N AC 380-415V 50Hz BSS	Control electr.unit EW 430	Lead	7439-92-1
11227930	PT8257 WP DK CA3 KD-Version 2018	Control electr.unit EW 430	Lead	7439-92-1
11227960	PT8257 WP DK iBR KD-Version 2018	Control electr.unit EW 430	Lead	7439-92-1
10327800	Control electr.unit EW 235-A	Control electr.unit EW 235-A	Lead	7439-92-1
10327800	Control electr.unit EW 235-A	Control electr.unit EW 235-A	Lead	7439-92-1
11391700	PDR922 EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11391780	PDR944 EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11105810	H7640BM D OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
9770670	H6500BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9770690	H6600BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9770690	H6600BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9863010	H6600BM USA BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9863010	H6600BM USA BRWS 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9862990	H6600BM USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9862990	H6600BM USA OBSW 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9862950	H6200BM USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9862950	H6200BM USA OBSW 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9863020	H6800BM USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9863020	H6800BM USA OBSW 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10301280	H6401BM GB EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10301280	H6401BM GB EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10400230	H7440BMX ANL OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10486330	H6670BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
10486330	H6670BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10486200	H6570BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
10486200	H6570BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10486340	H6870BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
10486340	H6870BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10486350	H6870BM USA BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
10486350	H6870BM USA BRWS 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9770670	H6500BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9624750	H6800BM C CN BRWS 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9782490	H6200BM TW EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
9782490	H6200BM TW EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9799590	PG8056 FIN AW o.K.	Circulation pump S35 PP (00-53)	Lead	7439-92-1
9183362	Heater element Hot air 200V	Heater element Hot air 200V	Lead	7439-92-1
9183362	Heater element Hot air 200V	Heater element Hot air 200V	Lead	7439-92-1
9646220	H6400BM J EDST/CLST 200/50	Heater element Top heat 200-208V	Lead	7439-92-1
9646220	H6400BM J EDST/CLST 200/50	Release element 220/240V 50/60HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
9769720	H6400BM J EDST/CLST 200/60	Heater element Top heat 200-208V	Lead	7439-92-1
9769720	H6400BM J EDST/CLST 200/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9646210	H6800BM J EDST/CLST 200/50	Heater element Top heat 200-208V	Lead	7439-92-1
9646210	H6800BM J EDST/CLST 200/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
9769710	H6800BM J EDST/CLST 200/60	Heater element Top heat 200-208V	Lead	7439-92-1
9769710	H6800BM J EDST/CLST 200/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9878840	H6400BM ROK EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
9878840	H6400BM ROK EDST/CLST 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9878830	H6400BM ROK OBSW 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
9878830	H6400BM ROK OBSW 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9878820	H6400BM ROK BRWS 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
9878820	H6400BM ROK BRWS 220/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
9862980	H6200BM USA BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
9862980	H6200BM USA BRWS 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10486360	H6870BM USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
10831750	H6401BMX C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
10831750	H6401BMX C CN OBSW 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10831640	H6401BMX C CN GRGR 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
10831640	H6401BMX C CN GRGR 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10933020	H7440BMX ANL GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10875940	H7240BM AN6 EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
10875940	H7240BM AN6 EDST/CLST 220/60	Drive top	Lead	7439-92-1
10875960	H7440BM AN6 EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
10875960	H7440BM AN6 EDST/CLST 220/60	Drive top	Lead	7439-92-1
10875970	H7840BM AN6 EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
10875970	H7840BM AN6 EDST/CLST 220/60	Drive top	Lead	7439-92-1
10875980	H7840BMX AN6 EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
10875980	H7840BMX AN6 EDST/CLST 220/60	Drive top	Lead	7439-92-1
10874310	H7440BM AN7 EDST/CLST 200/50	Heater element Top heat 200-208V	Lead	7439-92-1
10874310	H7440BM AN7 EDST/CLST 200/50	Drive top	Lead	7439-92-1
10874320	H7440BM AN8 EDST/CLST 200/60	Heater element Top heat 200-208V	Lead	7439-92-1
10874320	H7440BM AN8 EDST/CLST 200/60	Drive top	Lead	7439-92-1
10874330	H7840BM AN7 EDST/CLST 200/50	Heater element Top heat 200-208V	Lead	7439-92-1
10874330	H7840BM AN7 EDST/CLST 200/50	Drive top	Lead	7439-92-1
10874340	H7840BM AN8 EDST/CLST 200/60	Heater element Top heat 200-208V	Lead	7439-92-1
10874340	H7840BM AN8 EDST/CLST 200/60	Drive top	Lead	7439-92-1
11105800	H7640BM D BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10831610	H6800BMX C CN GRGR 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10486360	H6870BM USA OBSW 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10486320	H6770BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
10486320	H6770BM USA EDST/CLST 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10762270	H6500BM NL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10762270	H6500BM NL EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10754770	H6870BM USA GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
10754770	H6870BM USA GRGR 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10754800	H6800BM USA GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
10754800	H6800BM USA GRGR 120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
10552480	H7640BM ANL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10552510	H7240BM ANL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10781200	H7140BM ANL EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10781230	H7840BM ANL GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10781240	H7840BM ANL OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10781290	H7840BMX ANL BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10781270	H7840BMX ANL GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10830500	H6800-1BM D EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10830510	H6800-1BM D BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10830600	H6800-1BM EU1 OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10831690	H6800BMX C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
10831690	H6800BMX C CN OBSW 220/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
10831610	H6800BMX C CN GRGR 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
11120230	H7264BP I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120180	H7164BP I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120240	H7364BP I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120910	H7464BP I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120980	H7660BP I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120600	H7440B I EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11120500	H7244B I GRGR 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
11120260	H7244B I OBSW 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
11120250	H7244B I BRWS 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
11120200	H7244B I EDST/CLST 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
10979281	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11121100	H7860BP I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121020	H7840BP I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134070	DO7860 I EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11134070	DO7860 I EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11134070	DO7860 I EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11134040	DO7860 I BRWS 230/50	Supply cable DO	Lead	7439-92-1
11134040	DO7860 I BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11134040	DO7860 I BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11134050	DO7860 I OBSW 230/50	Supply cable DO	Lead	7439-92-1
11134050	DO7860 I OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11134050	DO7860 I OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10979281	Heater element Top heat 230V	Heater element Top heat 230V	Lead	7439-92-1
11128450	H7464BP AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11128460	H7464BP AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128480	H7464BPX AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128490	H7464BPX AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128500	H7464BPX AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128540	H7660BP AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128510	H7660BP AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128520	H7660BP AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128530	H7660BP AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128580	H7860BP AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128550	H7860BP AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128560	H7860BP AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128570	H7860BP AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128590	H7860BPX AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128600	H7860BPX AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128610	H7860BPX AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120160	H7164B I EDST/CLST 230/50 <3KW	SMD- Diode STTH1R04A	Lead	7439-92-1
11120220	H7264B I EDST/CLST 230/50 <3KW	SMD- Diode STTH1R04A	Lead	7439-92-1
11120510	H7264B I BRWS 230/50 <3KW	SMD- Diode STTH1R04A	Lead	7439-92-1
11120520	H7264B I OBSW 230/50 <3KW	SMD- Diode STTH1R04A	Lead	7439-92-1
11120530	H7264B I GRGR 230/50 <3KW	SMD- Diode STTH1R04A	Lead	7439-92-1
11120760	H7460B I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134060	DO7860 I GRGR 230/50	Supply cable DO	Lead	7439-92-1
11167180	H7464BP UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11164390	H7464BPX UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11164400	H7464BPX UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11167190	H7464BPX UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11214340	G7590 SCVi F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214350	G7595 SCVi XXL F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11164430	H7860BP UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11164410	H7860BP UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11164420	H7860BP UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11167200	H7860BP UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11164470	H7840BM UA OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11164440	H7860BPX UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11164480	H7840BM UA GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11164500	H7840BMX UA OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11164510	H7840BMX UA GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11164450	H7860BPX UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11167210	H7860BPX UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11568893	Power-/Control unit ELP 7771 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11141420	H7280BP AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11141420	H7280BP AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11141420	H7280BP AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11214360	G7910 SCi F OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11164360	H7464BP UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11134060	DO7860 I GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11134060	DO7860 I GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11203170	PDR908EL CN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11270290	PDR507HP D LW ISS T	SMD- Diode STTH1R04A	Lead	7439-92-1
11270450	PDR908HP D LW ISS T	SMD- Diode STTH1R04A	Lead	7439-92-1
11737813	Power-/Control unit EPL 8810-U	SMD- Diode STTH1R04A	Lead	7439-92-1
11070410	G7100 F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070590	G7102 SCi F ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11070980	G7362 SCVi F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214280	G7510 SCi F OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214300	G7560 SCVi F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214320	G7565 SCVi XXL F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11164320	H7264B UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11164340	H7264BP UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11258060	H7244B EU1 BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11258090	H7264B EU1 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11258080	H7244BP EU1 BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11164380	H7464BP UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11258100	H7264BP EU1 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11258050	H7240BM EU1 BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11164350	H7464BP UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11164490	H7840BM UA EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128440	H7464BP AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
9415610	Heater element Top heat 200-208V	Heater element Top heat 200-208V	Lead	7439-92-1
11208204	Power-/Control unit ELP 7784 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11141350	H7640BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11613960	Power electron.unit EL 4005	SMD- Diode STTH1R04A	Lead	7439-92-1
11204480	PDR908HP NAM LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11204490	PDR908HP NAM SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11204500	PDR908EL NAM LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11128320	H7840BM AUS EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128140	H7140BM AUS EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128190	H7240BM AUS EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128160	H7240BM AUS BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128170	H7240BM AUS OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11670010	Power electron.unit ELFU 3100	SMD- Diode STTH1R04A	Lead	7439-92-1
11128180	H7240BM AUS GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128230	H7440BM AUS EDST/CLST 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128200	H7440BM AUS BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11128210	H7440BM AUS OBSW 230/50 DE	Heater element Top heat 220-240V	Lead	7439-92-1
11128220	H7440BM AUS GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11204510	PDR908EL NAM SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11128280	H7440BMX AUS GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128250	H7440BMX AUS BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128270	H7440BMX AUS OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
9415610	Heater element Top heat 200-208V	Heater element Top heat 200-208V	Lead	7439-92-1
10921029	Power-/Control unit ELP 7752 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11124350	H7840BMX RU GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11124340	H7840BMX RU OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11141160	H7440BM RU BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11141170	H7440BMX RU BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11141180	H7640BM RU BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11141190	H7840BM RU BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11141200	H7840BMX RU BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10979261	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
10979261	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
11119010	H7460-55BP CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11119010	H7460-55BP CH EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11119010	H7460-55BP CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
10921049	Power-/Control unit ELP 7753 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11119020	H7660-55BP CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11119020	H7660-55BP CH EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11119020	H7660-55BP CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11231660	PG8504 Series 120 AD 3 AC 230V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11119040	H7660-55BP CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11119040	H7660-55BP CH GRGR 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11119040	H7660-55BP CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11117530	H7890BP CH EDST/CLST 3N AC 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11128290	H7840BM AUS BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11125100	H7860BP RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11125080	H7860BP RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11125090	H7860BP RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11125120	H7860BPX RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11125110	H7860BPX RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11141210	H7460B RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11141220	H7464BP RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11141230	H7464BPX RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11141240	H7660BP RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11141250	H7860BP RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11141260	H7860BPX RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11267730	PDR507HP N LW Special	SMD- Diode STTH1R04A	Lead	7439-92-1
11214490	G7590 SCVi B OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214520	G7595 SCVi XXL B OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214540	G7915 SCi XXL B OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214570	G7965 SCVi XXL B OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10853730	PG8055 RKU AE m.K.	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11214390	G7510 SCi B OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214410	G7515 SCi XXL B OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214440	G7560 SCVi B OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214470	G7565 SCVi XXL B OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11128470	H7464BP AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11125060	H7660BP RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11128300	H7840BM AUS OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128310	H7840BM AUS GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128350	H7840BMX AUS GRGR 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11141360	H7840BM AN3 EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11128330	H7840BMX AUS BRWS 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11128340	H7840BMX AUS OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
10920987	Power-/Control unit ELP 7751 200-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11124390	H7164B RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124430	H7264B RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124400	H7164BP RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124440	H7264BP RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124510	H7460B RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124490	H7460B RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124500	H7460B RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124450	H7364BP RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124750	H7464BP RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124730	H7464BP RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124740	H7464BP RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124770	H7464BPX RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11124760	H7464BPX RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11125070	H7660BP RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11125050	H7660BP RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11233730	DO7860 F GRGR 230/50	Supply cable DO	Lead	7439-92-1
11233730	DO7860 F GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11233730	DO7860 F GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11214120	DO7860 RU EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11214120	DO7860 RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11214120	DO7860 RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11214130	DO7860 RU BRWS 230/50	Supply cable DO	Lead	7439-92-1
11214130	DO7860 RU BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11214130	DO7860 RU BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11214110	DO7860 RU OBSW 230/50	Supply cable DO	Lead	7439-92-1
11214110	DO7860 RU OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11214110	DO7860 RU OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11214150	DO7860 RU GRGR 230/50	Supply cable DO	Lead	7439-92-1
11214150	DO7860 RU GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11214150	DO7860 RU GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11251050	PDR908EL MAR SST 3N AC 400V 50/60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11188000	G7919 SCI XXL ANL OS230 1,9 AUS	Drain pump 220-240V 50HZ	Lead	7439-92-1
11137670	DO7860 AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11137670	DO7860 AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11137640	DO7860 AUS BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11137640	DO7860 AUS BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11137650	DO7860 AUS OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11233720	DO7860 F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11109030	H7890BP F EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11101680	H7890BP NL EDST/CLST 3N AC230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11129410	H7890BP IB EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11130430	H7890BP NER EDST/CLST 3N AC 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11110750	H7890BP B EDST/CLST 3N AC 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11130060	H7890BP N EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11119240	H7890BP I EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11124040	H7890BP RU EDST/CLST 3N AC 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11250960	PDR908EL MAR LW 3 AC 400-480V 50/60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11250970	PDR908EL MAR SST 3 AC 400-480V 50/60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11251040	PDR908EL MAR LW 3N AC 400V 50/60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11127820	H2890B AUS EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
11127830	H7890BP AUS EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11164460	H7890BP UA EDST/CLST 3N AC 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11233740	DO7860 F EDST/CLST 230/50	Supply cable DO	Lead	7439-92-1
11233740	DO7860 F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11233740	DO7860 F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11233710	DO7860 F BRWS 230/50	Supply cable DO	Lead	7439-92-1
11233710	DO7860 F BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11233710	DO7860 F BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11233720	DO7860 F OBSW 230/50	Supply cable DO	Lead	7439-92-1
11233720	DO7860 F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11137650	DO7860 AUS OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11148340	DGC7840X ROK GRGR 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11148360	DGC7840 ROK EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11286710	DGC7840 J GRGR 200/50/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11186490	G7365 SCVi XXL TR OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992390	G7510 SCi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992400	G7515 SCi XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992340	G7560 SCVi D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992350	G7565 SCVi XXL D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992360	G7590 SCVi D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992370	G7595 SCVi XXL D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992420	G7365 SCVi XXL D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992560	G7310 SCi D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992640	G7960 SCVi D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992580	G7315 SCi XXL D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992660	G7965 SCVi XXL D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992590	G7315 SCi XXL D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992630	G7310 SC D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992670	G7910 SCi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992680	G7915 SCi XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992620	G7310 SC D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992600	G7310 SCU D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10992610	G7310 SCU D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11148310	DGC7440 ROK EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11137660	DO7860 AUS GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11137660	DO7860 AUS GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11312580	DA2668 UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11250990	PDR908EL MAR LW 3 AC 230V 50/60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11251000	PDR908EL MAR SST 3 AC 230V 50/60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11203050	PDR507EL CN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11147250	DGC7440 J EDST/CLST 200/50/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11147260	DGC7840 J EDST/CLST 200/50/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11377284	Power electron.unit EL 4005-B	SMD- Diode STTH1R04A	Lead	7439-92-1
11348630	PDR510ROP EL ANL IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11348650	PDR910 EL ANL SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11263860	PDR507HP RU LW Special	SMD- Diode STTH1R04A	Lead	7439-92-1
11267250	PDR507HP CN SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11306290	H7365BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11306300	H7565BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11186440	G7100 SC TR BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11186450	G7100 SCi TR ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11186460	G7150 SCVi TR ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11181500	PG8056 U AE m.K. MAR	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11186470	G7310 SC TR ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11186480	G7310 SCi TR ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11348660	PDR910 G ANL SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11099480	H2890B NL EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
8285650	Heater plate 3,2-1,5kW 230V	Heater plate 3,2-1,5kW 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
8285620	Heater plate 2,9-1,20kW 230V	Heater plate 2,9-1,20kW 230V	Lead	7439-92-1
8245200	Heater plate 3,2-2,05-1,05kW 230V	Heater plate 3,2-2,05-1,05kW 230V	Lead	7439-92-1
8245200	Heater plate 3,2-2,05-1,05kW 230V	Heater plate 3,2-2,05-1,05kW 230V	Lead	7439-92-1
10337058	Power-/Control unit EPL 8810	SMD- Diode STTH1R04A	Lead	7439-92-1
10751290	DA2628 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10744670	DA6488W D GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10744690	DA6498W D GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10751350	DA2628 D BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10744680	DA6488W D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10744720	DA6498W D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10751440	DA2668 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10751460	DA2698 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10751480	DA2698 D BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10751500	DA2808 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10751520	DA2808 D BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10800870	DA6498W CH GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10800860	DA6498W CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10805790	DA6498W GB GRGR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10805780	DA6498W GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10837570	DA6498W RU OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10851360	DA2628 GB BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
8285650	Heater plate 3,2-1,5kW 230V	Heater plate 3,2-1,5kW 230V	Lead	7439-92-1
11214370	G7960 SCVi F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11214380	G7965 SCVi XXL F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
7617310	Heater element Catalyst 208-240V	Heater element Catalyst 208-240V	Lead	7439-92-1
7617310	Heater element Catalyst 208-240V	Heater element Catalyst 208-240V	Lead	7439-92-1
11141470	H7885BPX AN3 GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11141470	H7885BPX AN3 GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11208397	Power-/Control unit ELP 7774 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11500113	Power-/Control unit ELP 7777 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11141460	H7780BP2 AN3 EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11141460	H7780BP2 AN3 EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11141460	H7780BP2 AN3 EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11110330	G7560 SCVi NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110450	G7565 SCVi XXL NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
9513770	ETD4 Olympus Basic GA	Drain pump BE28B3-186 230V/50HZ	Lead	7439-92-1
9513780	ETD4 Olympus Plus GA	Drain pump BE28B3-186 230V/50HZ	Lead	7439-92-1
8224200	Heater plate 1,8kW 230V	Heater plate 1,8kW 230V	Lead	7439-92-1
8224200	Heater plate 1,8kW 230V	Heater plate 1,8kW 230V	Lead	7439-92-1
8239870	Heater plate 1,2kW 230V	Heater plate 1,2kW 230V	Lead	7439-92-1
8224280	Heater plate 2,4-1,5kW 230V	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
8224280	Heater plate 2,4-1,5kW 230V	Heater plate 2,4-1,5kW 230V	Lead	7439-92-1
8219760	Heater plate 2,6-1,5kW 230V	Heater plate 2,6-1,5kW 230V	Lead	7439-92-1
8219760	Heater plate 2,6-1,5kW 230V	Heater plate 2,6-1,5kW 230V	Lead	7439-92-1
10851370	DA2628 GB EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11110590	G7965 SCVi XXL NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11198960	PDR908EL AUS SST 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11129090	H7460B GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129070	H7460B GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129080	H7460B GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129050	H2890B HK EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
11198830	PDR908HP AUS SST 10A	SMD- Diode STTH1R04A	Lead	7439-92-1
11106120	H7890BP D EDST/CLST 3N AC 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11098760	H7890BP TR EDST/CLST 3N AC 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11093840	H7890BP GB EDST/CLST 230/50	Release element 220/240V 50/60HZ	Lead	7439-92-1
11251140	PDR908EL MAR SST 2 AC 208/240V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11251180	PDR908HP MAR LW 1N AC 230V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11251190	PDR908HP MAR SST 1N AC 230V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11251200	PDR908HP MAR LW 1N AC 230V 50Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11251210	PDR908HP MAR SST 1N AC 230V 50Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11251250	PDR908HP MAR SST 2 AC 208/240V 60Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11208545	Power-/Control unit ELP 7775 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11570182	Power-/Control unit ELP 7784 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11316880	Sub-assembly BM 48"-3	Heater element Top heat 200-208V	Lead	7439-92-1
11093380	H2890B GB EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
11110390	H2890B B EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
11119230	H2890B I EDST/CLST 230/50	Temperature regul. Sub-assembly	Lead	7439-92-1
11110560	G7960 SCVi NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10851380	DA2668 GB EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10851390	DA2698 GB BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10851400	DA2698 GB EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10842600	DA2668 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10842610	DA2698 CH BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10842620	DA2698 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10863220	DA2628 RU EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10863230	DA2668 RU EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10863240	DA2698 RU EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10851410	DA2808 GB BRWS 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10842630	DA2808 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10868960	DA2628 PAC EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10868970	DA2668 PAC EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10868980	DA2698 PAC EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10869000	DA2808 PAC EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10866520	DA2808 C CN EDST 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10866530	DA2808 C CN BRWS 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10897330	DA6498W PAC OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
10967130	DA2698 C CN EDST 220/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11226990	DA2698 UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11110530	G7590 SCVi NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11110540	G7595 SCVi XXL NL OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11724630	DGC7845 HCX Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724620	DGC7845 HCX Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724640	DGC7845 HCX Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820720	DGC7840 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820760	DGC7840 HCX Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12190830	G5790 SCVi SL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12220010	G7405 SCi XXL ANL ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065400	PF405 DAC LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065410	PF405 DAC LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11724610	DGC7845 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820940	DGC7860 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820450	DGC7340 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820460	DGC7440 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820480	DGC7440 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820490	DGC7440 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820500	DGC7440 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820530	DGC7440 HCX Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820540	DGC7440 HCX Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820570	DGC7440 HCX Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820590	DGC7540 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820600	DGC7541 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724470	DGC7845 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724460	DGC7845 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724450	DGC7845 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723740	DGC7645 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723730	DGC7645 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723720	DGC7645 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12190840	G5990 SCVi SL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12220040	G7480 SCVi ANL ED230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12220060	G7605 SCi XXL ANL ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12220070	G7650 SCVi ANL OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12220080	G7715 SCi XXL ANL OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12220090	G7783 SCVi ANL OS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169130	H2465B J OBSW/EDST-LOOK 200/50 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12169130	H2465B J OBSW/EDST-LOOK 200/50 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12169500	H2465B J OBSW/EDST-LOOK 200/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12169500	H2465B J OBSW/EDST-LOOK 200/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12220100	G7935 SCi XXL ANL OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12066660	PF400 EXP LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065570	PF400 NWE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11723710	DGC7645 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723700	DGC7445 HCX Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723690	DGC7445 HCX Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820610	DGC7640 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097530	DGC7250 RU GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12097530	DGC7250 RU GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12097520	DGC7250 RU OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097520	DGC7250 RU OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12097520	DGC7250 RU OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12097540	DGC7250 RU EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097540	DGC7250 RU EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12097540	DGC7250 RU EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12086520	DGC7250 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12086520	DGC7250 AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12086520	DGC7250 AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11820980	DGC7860 HCX Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820970	DGC7860 HCX Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820960	DGC7860 HCX Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820930	DGC7860 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820910	DGC7860 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820900	DGC7860 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820890	DGC7660 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820880	DGC7660 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820870	DGC7660 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820860	DGC7660 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820850	DGC7460 HCX Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820840	DGC7460 HCX Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820830	DGC7460 HCX Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820820	DGC7460 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12065360	PF405 DAC SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11820810	DGC7460 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820800	DGC7460 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820790	DGC7460 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12139510	H2880BP CDN EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12065370	PF405 DAC SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12139510	H2880BP CDN EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
12139510	H2880BP CDN EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11820740	DGC7840 HCX Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11820730	DGC7840 HCX Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820710	DGC7840 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820690	DGC7840 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820670	DGC7840 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12219930	G7180 SCVi ANL ED230 1,9 AutoDos BI	Drain pump 220-240V 50HZ	Lead	7439-92-1
12219950	G7180 SCVi ANL ED230 1,9 AutoDos UN	Drain pump 220-240V 50HZ	Lead	7439-92-1
11820650	DGC7640 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820630	DGC7640 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11820620	DGC7640 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12066280	PFD400 SEE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12107800	DGC7351 BNE OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12107800	DGC7351 BNE OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11825530	DGC7350 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11825530	DGC7350 BNE EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11825530	DGC7350 BNE EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11825620	DGC7450 BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11825620	DGC7450 BNE GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11825620	DGC7450 BNE GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11825610	DGC7450 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11825610	DGC7450 BNE OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11825610	DGC7450 BNE OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11825630	DGC7450 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11825630	DGC7450 BNE EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11825630	DGC7450 BNE EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12096850	DGC7351 SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12096850	DGC7351 SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12096850	DGC7351 SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11821050	DGC7450 SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12066340	PFD401 SEE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11821050	DGC7450 SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11821050	DGC7450 SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11790250	DGC7450-55 CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11790250	DGC7450-55 CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11790250	DGC7450-55 CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12066680	PFD401 EXP SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065590	PFD401 NWE SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11790260	DGC7450-55 CH EDST/CLST 400/N//50	Heater element Top heat 400V	Lead	7439-92-1
12066300	PFD401 SEE SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066710	PFD401 U EXP LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11790260	DGC7450-55 CH EDST/CLST 400/N//50	Heater element Bottom heat 400V	Lead	7439-92-1
12065660	PFD401 U NWE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066360	PFD401 U SEE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11790260	DGC7450-55 CH EDST/CLST 400/N//50	Heater element Hot air 400V	Lead	7439-92-1
12066690	PFD401 U EXP SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065610	PFD401 U NWE SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11790190	DGC7450 CH BRWS 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11790190	DGC7450 CH BRWS 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11790190	DGC7450 CH BRWS 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11790220	DGC7450 CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11790220	DGC7450 CH GRGR 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11790220	DGC7450 CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11790210	DGC7450 CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11790210	DGC7450 CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12107800	DGC7351 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12066640	PFD400 EXP SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11723680	DGC7445 HCX Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12065550	PFD400 NWE SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066260	PFD400 SEE SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11723670	DGC7445 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12066670	PFD400 U EXP LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065580	PFD400 U NWE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11723660	DGC7445 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723650	DGC7445 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11723640	DGC7445 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12066290	PFD400 U SEE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066650	PFD400 U EXP SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065560	PFD400 U NWE SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066270	PFD400 U SEE SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12173520	PDR918 HP APDR902 EU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12173530	PDR918 HP APDR902 EU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12173590	PDR918 HP APDR902 EX SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12173580	PDR918 HP APDR902 EX IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12173550	PDR918 HP APDR902 RU SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12173540	PDR918 HP APDR902 RU IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12096840	DGC7151 SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12096840	DGC7151 SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12096840	DGC7151 SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12113850	DGC7250 SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12113850	DGC7250 SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12113850	DGC7250 SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12066700	PFD401 EXP LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12107760	DGC7151 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12065640	PFD401 NWE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12107760	DGC7151 BNE OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12107760	DGC7151 BNE OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12107750	DGC7150 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12107750	DGC7150 BNE EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12107750	DGC7150 BNE EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12107780	DGC7250 BNE GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12107780	DGC7250 BNE GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12107780	DGC7250 BNE GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12107770	DGC7250 BNE OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12107770	DGC7250 BNE OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12107770	DGC7250 BNE OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12107790	DGC7250 BNE EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12107790	DGC7250 BNE EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12107790	DGC7250 BNE EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12097530	DGC7250 RU GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12142720	G5740 SC SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142760	G5940 SC SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142770	G5940 SCU SL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142780	G5940 SCi SL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11819090	DGC7450 AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11819090	DGC7450 AUS BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11819090	DGC7450 AUS BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11819140	DGC7450 AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11819140	DGC7450 AUS GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11819140	DGC7450 AUS GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11819120	DGC7450 AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11819120	DGC7450 AUS OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11819120	DGC7450 AUS OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11819160	DGC7450 AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11819160	DGC7450 AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11819160	DGC7450 AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12101530	DGC7845 HCX Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101520	DGC7845 HCX Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101510	DGC7845 HCX Pro GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101500	DGC7845 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101490	DGC7845 HC Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101480	DGC7845 HC Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101470	DGC7845 HC Pro GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101460	DGC7840 HCX Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101450	DGC7840 HCX Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101440	DGC7840 HCX Pro GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101410	DGC7840 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101400	DGC7840 HC Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101390	DGC7840 HC Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101380	DGC7840 HC Pro GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101360	DGC7640 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101290	DGC7440 HCX Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101280	DGC7440 HCX Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101260	DGC7440 HCX Pro GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101250	DGC7440 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101240	DGC7440 HC Pro GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101230	DGC7440 HC Pro GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101220	DGC7440 HC Pro GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12107630	G7285 SCVi XXL D ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12208220	PDR910 EL SOM SSt B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12107620	G7280 SCVi D ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189270	H2465B AN8 OBSW/EDST-LOOK 200/60 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12189270	H2465B AN8 OBSW/EDST-LOOK 200/60 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12142730	G5740 SCU SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087320	DGC7440 HCX Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087240	DGC7440 HCX Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087200	DGC7440 HC Pro AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087190	DGC7440 HC Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12086870	DGC7440 HC Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12142480	G5332 SCi D ED230 1,9 CS Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12086840	DGC7440 HC Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087620	DGC7840 HCX Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12142440	G5332 SCi D BW230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142420	G5332 SCU D ED230 1,9 CS Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142410	G5332 SCU D BW230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149320	G15790 SCVi SL CH ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142400	G5332 SC D ED230 1,9 CS Front ActPlus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142370	G5332 SC D BW230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142220	G5310 SCU D ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142210	G5310 SCU D HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142200	G5310 SCU D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012270	PDR522ROP SI NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12142160	G5310 SC D ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142150	G5310 SC D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142240	G5310 i D ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149330	G15990 SCVi SL CH ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142230	G5310 i D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142190	G5310 U D ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142180	G5310 U D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142140	G5310 D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12142250	G5310 SCi D HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142260	G5310 SCi D ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142340	G5315 SCi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142330	G5315 i XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12112260	DGC7340 HC Pro GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12012210	PDR918 Si NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12142710	G5540 SCi SL D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012200	PDR918 Si NAM SST D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12012110	PDR914 EL NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12092010	DGC7541 HC Pro NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12142700	G5540 SCU SL D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142660	G5540 SCU SL D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142640	G5540 SC SL D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153580	H7244B SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12153510	H7244B IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12142750	G5740 SCi SL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142740	G5740 SCU SL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189260	H2465B AN7 OBSW/EDST-LOOK 200/50 ACTIVE	Heater element Bottom heat	Lead	7439-92-1
12189040	H2465B ANL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11724030	H2455B AN3 EDST/CLST 120/240/60	Heater element Top heat 230V	Lead	7439-92-1
11724030	H2455B AN3 EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
12173510	H7240BM GB OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11821060	DGC7450 SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11821060	DGC7450 SER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11821060	DGC7450 SER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11724890	DGC7865 HCX Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724860	DGC7865 HCX Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724850	DGC7865 HCX Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724830	DGC7865 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724820	DGC7865 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724800	DGC7865 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724790	DGC7865 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724780	DGC7665 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724750	DGC7665 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724720	DGC7665 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724710	DGC7665 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724700	DGC7465 HCX Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724690	DGC7465 HCX Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724680	DGC7465 HCX Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724670	DGC7465 HC Pro R01 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724660	DGC7465 HC Pro R01 BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724650	DGC7465 HC Pro R01 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11724440	DGC7465 HC Pro R01 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103180	DGC7250 UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103180	DGC7250 UA BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12103180	DGC7250 UA BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12103200	DGC7250 UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103200	DGC7250 UA GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12103200	DGC7250 UA GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12103190	DGC7250 UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103190	DGC7250 UA OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12103190	DGC7250 UA OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12103210	DGC7250 UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103210	DGC7250 UA EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12103210	DGC7250 UA EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12113870	DGC7250 SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12113870	DGC7250 SER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12113870	DGC7250 SER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12097510	DGC7250 RU BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12097510	DGC7250 RU BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12097510	DGC7250 RU BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12189040	H2465B ANL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12189260	H2465B AN7 OBSW/EDST-LOOK 200/50 ACTIVE	Heater element Top heat 200V	Lead	7439-92-1
12189240	H2841B C ANC EDST/CLST 220/50	Heater element Top heat 230V	Lead	7439-92-1
12189250	H2851B C ANC EDST/CLST 220/50	Heater element Top heat 230V	Lead	7439-92-1
12189230	H2766BP C ANC OBSW 220/50	Heater element Top heat 230V	Lead	7439-92-1
12189220	H2861BP AN6 EDST/CLST 220/60	Heater element Top heat 230V	Lead	7439-92-1
12142630	G5368 SCVi XXL D ED230 1,9 ActivePlus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12109580	G7688 SCVi XXL K20 D OS/CS230 1,9 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12109570	G7683 SCVi D OS/CS230 1,9 k2o AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12107600	G7685 SCVi XXL D OS/CS230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142620	G5363 SCVi D ED230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142550	G5367 SCVi XXL D ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12107580	G7680 SCVi D OS/CS230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142540	G5362 SCVi D ED230 1,9 Active Plus S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142360	G5355 Vi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142350	G5350 Vi D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12141960	G5110 SCU D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142070	G5167 SCVi XXL D ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1
12141950	G5110 SCU D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12099720	DGC7640 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099670	DGC7440 HC Pro D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099680	DGC7440 HC Pro D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12142060	G5162 SCVi D ED230 1,9 Active S	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12141940	G5110 U D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142030	G5150 Vi D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12141930	G5110 U D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12141920	G5110 SC D ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12141890	G5110 SC D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12141880	G5110 D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142010	G5110 i D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12141990	G5110 i D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12142020	G5110 SCi D ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189180	H2761BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12189180	H2761BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12189150	H2761B ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12189150	H2761B ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12189130	H2861BP ANL BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12189130	H2861BP ANL BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12189090	H2861B ANL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12189090	H2861B ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12189080	H2861B ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12189080	H2861B ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12189060	H2861B ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12189060	H2861B ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11790210	DGC7450 CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12012400	PDR944 EL NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12030710	DAS8930 UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12012420	PDR944 SI NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12085800	H7860BP BR EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
12085810	H7240BM BR EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
12030700	DAS8630 UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12030690	DAS4940 UA GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12030680	DAS4920 UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12030670	DAS4640 UA GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12030660	DAS4630 UA OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12087000	G5540 SCi SL D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087010	G5590 SCVi SL D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11941420	DGC7440 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087020	G5740 SCi SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11941430	DGC7440 HCX Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11941470	DGC7640 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11941450	DGC7540 HC Pro ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11942220	DGC7840 HC Pro ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087030	G5940 SCi SL D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087060	G5990 SCVi SL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087390	G5790 SCVi SL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12030650	DAS4620 UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12012380	PDR928 EL NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12012320	PDR928 SI NAM SST D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12012290	PDR922 SI NAM SST D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12012280	PDR922 EL NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12012140	PDR918 EL NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
11788390	DGC7870 BR OBSW 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11788410	DGC7870 BR GRGR 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11788400	DGC7870 BR EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11994920	PG8504 EXP EXE AD 3AC 220-230V 60HZ	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11734390	DGC7840 HC Pro ANC EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12027500	G7473 SCVi A OS230 1,9 AutoDos Excellenc	Drain pump 220-240V 50HZ	Lead	7439-92-1
12034690	G7423 SCi MER ED230 1,9 CLST AutoD Excel	Drain pump 220-240V 50HZ	Lead	7439-92-1
12035190	G7200 SCU MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12220110	G7980 SCVi ANL OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12168800	H2861BP ROK EDST/CLST 220/60	Heater element Top heat 230V	Lead	7439-92-1
12168780	H2467BP ROK OBSW/EDST-LOOK 220/60 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12168790	H2841B ROK EDST/CLST 220/60	Heater element Top heat 230V	Lead	7439-92-1
11945020	PDR508EL GB LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
12145960	H2861B CH EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
12145960	H2861B CH EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12145960	H2861B CH EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
12081180	PDR508HP IB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11818960	DGC7350 F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11818960	DGC7350 F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11819030	DGC7450 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11819030	DGC7450 F GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11819030	DGC7450 F GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11819020	DGC7450 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11819020	DGC7450 F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11819020	DGC7450 F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11819010	DGC7450 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11819010	DGC7450 F BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11819010	DGC7450 F BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11819040	DGC7450 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11819040	DGC7450 F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11819040	DGC7450 F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12065680	PF402 NWE SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12087210	G5350 SCVi D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11785140	DGC7450 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11785140	DGC7450 D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11785140	DGC7450 D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11785120	DGC7350 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11785120	DGC7350 D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11785120	DGC7350 D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11785170	DGC7450 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11785170	DGC7450 D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11785170	DGC7450 D GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11785160	DGC7450 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11785160	DGC7450 D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11785160	DGC7450 D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11785200	DGC7450 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11785200	DGC7450 D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11785200	DGC7450 D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12087170	G5315 SCI XXL D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087180	G5315 i XXL D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087160	G5310 SCI D BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065800	PFD405 NWE LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065810	PFD405 NWE LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065790	PFD405 NWE SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12095420	PDR508EL TR LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12095380	PDR508HP TR LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12082020	PDR508HP i LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12066330	PFD401 U SEE SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12081970	PDR508EL i LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12081240	PDR508EL IB LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12145920	H2861B CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
12007280	G7423 SCI OE1 ED230 1,9 CLST AutoD Excel	Drain pump 220-240V 50HZ	Lead	7439-92-1
12007270	G7423 SC OE1 BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12007260	G7278 SCVi XXL OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11863100	DAS8930 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11863080	DAS8630 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12145970	H2861BP CH EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
11863040	DAS4940 CH GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11862960	DAS4640 CH GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11863030	DAS4930 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11862940	DAS4630 CH OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11862920	DAS4620 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12007250	G7223 SCI OE1 ED230 1,9 CLST Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12007240	G7223 SC OE1 ED230 1,9 CS Front Excellen	Drain pump 220-240V 50HZ	Lead	7439-92-1
12007230	G7065 SCVi XXL OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12007220	G7025 SCI XXL OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12007210	G7020 SCI OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11994410	PDR909 EL CP GB SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994400	PDR909 EL CP GB IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994390	PDR909 EL CP GB SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994380	PDR909 EL CP GB IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11568892	Power-/Control unit ELP 7771 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11921970	G7020 SC A ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12145970	H2861BP CH EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12145970	H2861BP CH EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
12145940	H2861BP CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
12145940	H2861BP CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12145940	H2861BP CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
12007200	G7423 SCi A ED230 1,9 CLST AutoD Excellen	Drain pump 220-240V 50HZ	Lead	7439-92-1
12007190	G7423 SC A ED230 1,9 AutoD CLST Excellen	Drain pump 220-240V 50HZ	Lead	7439-92-1
12007170	G7423 SC A BW230 1,9 AutoDos Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12145930	H2861BP CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
12145930	H2861BP CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12145930	H2861BP CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
12007160	G7273 SCVi A ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12146080	H2861-55B CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
12146080	H2861-55B CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12146080	H2861-55B CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
12146120	H2861-55B CH EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
12007110	G7223 SC A BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12146120	H2861-55B CH EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11862900	DAS4520 CH EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11926360	G3625 SCHE ZER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12146120	H2861-55B CH EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
12007290	G7478 SCVi XXL OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12145920	H2861B CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12145920	H2861B CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
12145910	H2861B CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
12145910	H2861B CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12145910	H2861B CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
12009920	PDR922 HP AUS IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12009910	PDR914 HP AUS IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11867900	PFD100 GB ED/BW230 2,3 13A	Drain pump 220-240V 50HZ	Lead	7439-92-1
11994550	PDR909 EL CP EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994530	PDR909 EL CP EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994540	PDR909 EL CP EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994670	PDR909 EL CP RU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994660	PDR909 EL CP RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11877160	H2455i AC1 EDST/CLST 120/240/60	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11877160	H2455I AC1 EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11874740	H2455E AN0 EDST/CLST 240/60	Heater element Top heat 230V	Lead	7439-92-1
11874690	H2455E AN4 EDST/CLST 208/60	Heater element Top heat 200V	Lead	7439-92-1
11902170	Regulator Einkreis PTT 208V	Regulator Einkreis PTT 208V	Lead	7439-92-1
11902170	Regulator Einkreis PTT 208V	Regulator Einkreis PTT 208V	Lead	7439-92-1
11902490	Regulator Zweikreis PTT 208V	Regulator Zweikreis PTT 208V	Lead	7439-92-1
11902490	Regulator Zweikreis PTT 208V	Regulator Zweikreis PTT 208V	Lead	7439-92-1
11568810	Heater element Top heat 200V	Heater element Top heat 200V	Lead	7439-92-1
11568810	Heater element Top heat 200V	Heater element Top heat 200V	Lead	7439-92-1
11878240	DAS4940 GB GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11878230	DAS4640 GB GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11878210	DAS4630 GB OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11962890	PFD100 EP4 ED/BW230 2,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11962880	PFD100 EP3 ED/BW230 2,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11962870	PFD100 EP2 ED/BW230 2,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11867860	PFD100 EP1 ED/BW230 2,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11962860	PFD100 D ED/BW230 2,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
12010000	PDR544ROP EL AUS IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12009990	PDR528ROP EL AUS IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12009980	PDR522ROP EL AUS IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12009970	PDR514ROP EL AUS IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11987680	G5430 SC SL A ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012840	G27165 SCVi XXL CH ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11878690	DAS8930 RU EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11878680	DAS8630 RU EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11878670	DAS4940 RU GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11878660	DAS4640 RU GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11878650	DAS4930 RU OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11878640	DAS4630 RU OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11818960	DGC7350 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093280	DGC7250 F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093280	DGC7250 F GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12093280	DGC7250 F GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12093270	DGC7250 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093270	DGC7250 F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12093270	DGC7250 F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12093290	DGC7250 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093290	DGC7250 F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12093290	DGC7250 F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12101200	DGC7250 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101200	DGC7250 GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12101200	DGC7250 GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12114080	DGC7250 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12114080	DGC7250 IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12114080	DGC7250 IB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11824360	DGC7450 IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11824360	DGC7450 IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11824360	DGC7450 IB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12090570	DGC7151 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090570	DGC7151 NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12090570	DGC7151 NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12090540	DGC7150 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090540	DGC7150 NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12090540	DGC7150 NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12090580	DGC7250 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090580	DGC7250 NER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12090580	DGC7250 NER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12090610	DGC7250 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090610	DGC7250 NER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12090610	DGC7250 NER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12090600	DGC7250 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090600	DGC7250 NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12090600	DGC7250 NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12090620	DGC7250 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12090620	DGC7250 NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12090620	DGC7250 NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12065620	PFD401 U NWE SST WOB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12090630	DGC7351 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12065670	PFD401 U NWE LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12090630	DGC7351 NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12090630	DGC7351 NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11814300	DGC7350 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11814300	DGC7350 NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12093240	DGC7250 F BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12066320	PFD401 U SEE SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11790240	DGC7450 CH EDST/CLST 400/N//50	Heater element Top heat 400V	Lead	7439-92-1
11790240	DGC7450 CH EDST/CLST 400/N//50	Heater element Bottom heat 400V	Lead	7439-92-1
11790240	DGC7450 CH EDST/CLST 400/N//50	Heater element Hot air 400V	Lead	7439-92-1
12082110	DGC7250-55 CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12082110	DGC7250-55 CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12082110	DGC7250-55 CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12082140	DGC7250-55 CH EDST/CLST 400/N//50	Heater element Top heat 400V	Lead	7439-92-1
12082140	DGC7250-55 CH EDST/CLST 400/N//50	Heater element Bottom heat 400V	Lead	7439-92-1
12082140	DGC7250-55 CH EDST/CLST 400/N//50	Heater element Hot air 400V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12080380	DGC7250 CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12080380	DGC7250 CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12080380	DGC7250 CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12080640	DGC7250 CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
12080640	DGC7250 CH EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
12080640	DGC7250 CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12074240	KM7755 FL USA 208/240/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
12074230	KM7745 FL USA 208/240/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
12113600	H7365B EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12113580	H7165B EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101830	H7365B SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101840	H7365BP SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101820	H7165BP SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101810	H7165B SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12102270	H7365B D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12102240	H7145BM D OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12102280	H7365BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12102260	H7165BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12102250	H7165B D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12101870	H7145BM F OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12101880	H7365BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12110210	G5355 SCVi XXL D ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12093310	DGC7351 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093310	DGC7351 F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12093310	DGC7351 F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12093230	DGC7151 F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093230	DGC7151 F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12093230	DGC7151 F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12093210	DGC7150 F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093210	DGC7150 F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12093210	DGC7150 F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12093240	DGC7250 F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12093240	DGC7250 F BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11814300	DGC7350 NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12099530	DGC7250 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099530	DGC7250 D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12099530	DGC7250 D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12084640	G7660 SCVi OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12084630	G7273 SCVi OE1 ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12084620	G7060 SCVi OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12105860	H7145BM GB OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12084610	G7200 SCi OE1 OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12084600	G7200 SCi OE1 BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12097500	H7145BM NER OBSW 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
12091210	G5210 C SCU CN ED220/50 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12123390	PDR908HP CH SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12123380	PDR908HP CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12123370	PDR508HP CH SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12123350	PDR508HP CH LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12084590	G7223 SC OE1 BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12084580	G7222 SC OE1 BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12066310	PFD401 SEE SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065710	PFD402 U NWE LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065700	PFD402 NWE LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065690	PFD402 U NWE SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11825490	DGC7350 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11825490	DGC7350 GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11825490	DGC7350 GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12087110	G5155 SCVi XXL D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087130	G5155 Vi XXL D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087090	G5150 SCVi D ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087080	G5110 SCi D BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11821030	DGC7350 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11821030	DGC7350 I EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11821030	DGC7350 I EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11821040	DGC7450 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11821040	DGC7450 I EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11821040	DGC7450 I EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11821000	DGC7350 TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11821000	DGC7350 TR EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11821000	DGC7350 TR EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11821020	DGC7450 TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11821020	DGC7450 TR EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11821020	DGC7450 TR EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11825500	DGC7450 GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11825500	DGC7450 GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11825500	DGC7450 GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12099460	DGC7250 D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11814310	DGC7450 NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11814310	DGC7450 NER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11814310	DGC7450 NER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11814330	DGC7450 NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11814330	DGC7450 NER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11814330	DGC7450 NER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11814320	DGC7450 NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11814320	DGC7450 NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11814320	DGC7450 NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11814340	DGC7450 NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11814340	DGC7450 NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11814340	DGC7450 NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12096830	DGC7150 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12096830	DGC7150 I EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12096830	DGC7150 I EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12113840	DGC7250 I EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12113840	DGC7250 I EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12113840	DGC7250 I EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12114500	DGC7150 TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12114500	DGC7150 TR EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12114500	DGC7150 TR EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12103650	DGC7151 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103650	DGC7151 D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12103650	DGC7151 D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12103660	DGC7351 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12066370	PFD401 U SEE LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12103660	DGC7351 D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12065650	PFD401 NWE LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12103660	DGC7351 D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12099400	DGC7150 D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099400	DGC7150 D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12099400	DGC7150 D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12099440	DGC7250 D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099440	DGC7250 D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12099440	DGC7250 D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12099500	DGC7250 D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12099500	DGC7250 D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12099500	DGC7250 D GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12099460	DGC7250 D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12066350	PFD401 SEE LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065630	PFD401 U NWE SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065600	PFD401 NWE SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12099460	DGC7250 D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12087340	DGC7440 HCX Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12159820	H2766B EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159930	H2861BP EU1 GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159820	H2766B EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159830	H2766BP EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159830	H2766BP EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159930	H2861BP EU1 GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159910	H2861BP EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159910	H2861BP EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159890	H2861B EU1 GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159890	H2861B EU1 GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12173960	G5350 SCVi OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173980	G5355 SCVi XXL OE1 ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173990	G5362 SCVi OE1 ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174000	G5540 SC SL OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174010	G5540 SCi SL OE1 ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12150030	H2465B NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150030	H2465B NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12150040	H2465BP NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150040	H2465BP NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12150270	H2467B NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150270	H2467B NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12159880	H2861B EU1 OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159880	H2861B EU1 OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159970	H2756B B OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159970	H2756B B OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159800	H2761B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159800	H2761B B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159840	H2841B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159860	H2851BP B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159860	H2851BP B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159850	H2851B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159850	H2851B B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159900	H2861BP B BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159900	H2861BP B BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159950	H2861BP B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159950	H2861BP B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159870	H2861B B BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159870	H2861B B BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159940	H2861B B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159940	H2861B B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159790	H2465BP B OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12159790	H2465BP B OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159770	H2465B B OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12150290	H2467BP NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12184650	H2861B I EDST/CLST 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
12184650	H2861B I EDST/CLST 230/50 <3KW	Heater element Unterhitze 230-240V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12184660	H2861BP I EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12184660	H2861BP I EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12184580	H2467B I OBSW/EDST-LOOK 230/50<3KWACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12184580	H2467B I OBSW/EDST-LOOK 230/50<3KWACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12184540	H2466B I OBSW/EDST-LOOK 230/50<3KWACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12190600	G5310 SC MER ED230 1,9 CLST Front ActPlu	Drain pump 220-240V 50HZ	Lead	7439-92-1
12184540	H2466B I OBSW/EDST-LOOK 230/50<3KWACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12184530	H2465B I OBSW/EDST-LOOK 230/50<3KWACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12184530	H2465B I OBSW/EDST-LOOK 230/50<3KWACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12184600	H2468BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12184600	H2468BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12184590	H2467BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12184590	H2467BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12184570	H2465BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12184570	H2465BP I OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174050	G5940 SCi SL OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174040	G5790 SCVi SL OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174030	G5740 SCi SL OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174020	G5590 SCVi SL OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12150440	H2863BP NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150440	H2863BP NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150320	H2766BP NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150320	H2766BP NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150300	H2761BP NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150300	H2761BP NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150350	H2861BP NER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150350	H2861BP NER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150450	H2861BP NER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150450	H2861BP NER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150390	H2861BP NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150390	H2861BP NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150330	H2861B NER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150330	H2861B NER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150470	H2861BP NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150470	H2861BP NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150460	H2861B NER EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12150460	H2861B NER EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12190610	G5310 SCi MER OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12150200	H2466BP NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12150200	H2466BP NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12150290	H2467BP NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12159770	H2465B B OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145630	H2861BP F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145630	H2861BP F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145510	H2467BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12145510	H2467BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145500	H2465BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12145500	H2465BP F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145470	H2465B F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12145470	H2465B F OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12173950	G5315 SCi XXL OE1 ED230 1,9 CLST Act Plu	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173940	G5310 SCU OE1 ED230 1,9 CLST Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173930	G5310 SCi OE1 OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173920	G5310 SCi OE1 ED230 1,9 CLST Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173910	G5310 SCi OE1 BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173900	G5310 SC OE1 ED230 1,9 CLST Front Act Pl	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173890	G5310 SC OE1 BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173880	G5162 SCVi OE1 ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173870	G5155 SCVi XXL OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173860	G5150 Vi OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173850	G5150 SCVi OE1 ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173840	G5132 SC OE1 BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173830	G5110 SCi OE1 ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173820	G5110 SCi OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173810	G5110 SC OE1 ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12173790	G5110 SC OE1 BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12258570	PDR910 G GB LW E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12258560	PDR910 G GB IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12258550	PDR910 EL GB LW A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258540	PDR910 EL GB LW E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258530	PDR910 EL GB SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258520	PDR910 EL GB IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258510	PDR910 G GB SST E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12258500	PDR910 EL GB SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258490	PDR910 EL GB IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258470	PDR910 EL GB IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258460	PDR910 EL GB SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258330	PDR510ROP EL GB IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258320	PDR510ROP EL GB IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258050	PDR510ROP EL GB IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258030	PDR510COP EL GB IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12258000	PDR510TOP EL GB SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12257950	PDR510TOP EL GB IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12197020	G7688 SCVi XXL OE1 OSCS230 1,9 K20 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12197010	G7683 SCVi OE1 OS/CS230 1,9 K20 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12145610	H2861BP F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12154640	H2841B IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12154940	H2861BP IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12154940	H2861BP IB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12154650	H2861B IB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12154650	H2861B IB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12154340	H2467BP IB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12154340	H2467BP IB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12154330	H2467B IB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12154330	H2467B IB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12154320	H2465BP IB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12154320	H2465BP IB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12154310	H2465B IB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12154310	H2465B IB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155150	H2761BP NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155150	H2761BP NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155140	H2761B NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155140	H2761B NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155170	H2861BP NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155170	H2861BP NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155160	H2861B NL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155160	H2861B NL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155130	H2467BP NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12155130	H2467BP NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155120	H2465BP NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12155120	H2465BP NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155110	H2465B NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12155110	H2465B NL OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145550	H2766BP F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145550	H2766BP F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145540	H2766B F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145540	H2766B F OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145560	H2841B F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145570	H2851B F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145570	H2851B F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145580	H2851BP F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145580	H2851BP F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145530	H2761BP F EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145530	H2761BP F EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145600	H2861BP F BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145600	H2861BP F BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145620	H2861BP F GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12145620	H2861BP F GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12145610	H2861BP F OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12184630	H2766B I OBSW 230/50 <3KW	Heater element Unterhitze 230-240V	Lead	7439-92-1
11221990	WH USA teon AW AD LD	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12190490	G5150 SCVi MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190500	G5155 SCVi XXL MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169730	G5312 SCi F OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190510	G5162 Vi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189650	G5110 SC MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169720	G5312 SC F ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190520	G5162 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189670	G5110 SC MER ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065070	PF401 U DAC SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12190530	G5163 SCVi MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189680	G5110 i MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169710	G5312 SC F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189690	G5110 i MER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189710	G5110 SCi MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169700	G5310 SCi F ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190540	G5164 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189720	G5110 SCi MER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169680	G5310 SCi F OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190550	G5167 SCVi XXL MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190560	G5168 SCVi XXL MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169690	G5310 SCi F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189750	G5132 MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189780	G5132 U MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169670	G5310 i F ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189840	G5132 U MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189760	G5132 SC MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169660	G5310 SCU F ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190570	G5310 MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189770	G5132 SC MER ED230 1,9 CS Front Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169650	G5310 SC F ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189850	G5132 SCU MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189860	G5132 SCU MER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169640	G5310 SC F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190580	G5310 MER ED230 1,9 CLST Front Act Pl	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189870	G5132 i MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169630	G5310 F BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189880	G5132 i MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12189910	G5132 SCi MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169530	G5133 SC F ED230 1,9 CLST Front Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189920	G5132 SCi MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190590	G5310 SC MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169520	G5133 SC F BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189640	G5110 MER ED230 1,9 Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11208396	Power-/Control unit ELP 7774 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
12169930	G5990 SCVi SL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169920	G5790 SCVi SL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160400	G5110 TR BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065160	PF402 DAC SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065200	PF402 DAC LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12160410	G5110 SC TR BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160420	G5110 SC TR ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169910	G5740 SC SL F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160430	G5110 i TR ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160440	G5110 SCi TR ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169900	G5590 SCVi SL F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065210	PF402 DAC LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12169890	G5540 SCi SL F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169880	G5540 SCi SL F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169870	G5540 SC SL F ED230 1,9 CLST Front Act	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160450	G5132 SC TR BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160460	G5132 SC TR ED230 1,9 CS Front Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169860	G5540 SC SL F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160470	G5132 SCi TR ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160520	G5150 Vi TR ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169850	G5368 SCVi XXL F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169820	G5355 SCVi XXL F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160530	G5150 SCVi TR ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160540	G5332 SCi TR ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169840	G5363 SCVi F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12160550	G5367 SCVi XXL TR ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12189630	G5110 MER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169830	G5362 SCVi F ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169810	G5352 SCVi F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065120	PF401 DAC LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12169800	G5350 SCVi F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065140	PF401 U DAC LW WOB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065130	PF401 U DAC LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12169790	G5350 Vi F ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065080	PF401 U DAC SST WOB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065110	PF401 DAC LW WOB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065100	PF401 DAC LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12169780	G5333 SC F ED230 1,9 CLST Front Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169770	G5333 SC F BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169760	G5332 SC F ED230 1,9 Front Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169750	G5332 SC F BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190480	G5150 Vi MER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190460	G5133 SC MER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12254890	PDR511ROP SL HP ANL IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12254880	PDR511ROP SL HP ANL IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12254990	PDR516TOP SL G ANL IG-IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254940	PDR516TOP SL EL ANL IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12065000	PF400 DAC SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12254930	PDR516TOP SL EL ANL IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254920	PDR516COP SL EL ANL IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254910	PDR516COP SL EL ANL IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254900	PDR516ROP SL EL ANL IG-GS A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254860	PDR516TOP SL EL ANL IG-IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12254840	PDR516ROP SL EL ANL IG-IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12065020	PF400 DAC LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12205160	G7685 SCVi XXL F OS/CS230 1,9 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12205150	G7280 SCVi F ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12205930	G7688 SCVi XXL MER OSCS230 1,9 K20 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012460	PDR944 G NAM IG B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12205920	G7685 SCVi XXL MER OS/CS230 1,9 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012450	PDR944 G NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12012370	PDR528ROP G NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12012360	PDR528ROP G NAM SST D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12012260	PDR522ROP G NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12205910	G7285 SCVi XXL MER ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012250	PDR522ROP G NAM SST D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12205900	G7280 SCVi MER ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012240	PDR918 G NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12012230	PDR918 G NAM SST D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12012130	PDR914 G NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12012120	PDR914 G NAM SST D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12205390	G7688 SCVi XXL A OS/CS230 1,9 K20 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12205380	G7683 SCVi A OS/CS230 1,9 K20 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12205370	G7285 SCVi XXL A ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12205360	G7280 SCVi A ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12217020	G27688 SCVi XXL CH OSCS230 1,9 K20 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12216980	G17683 SCVi CH OS/CS230 1,9 K20 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12205020	G7688 SCVi XXL NER OSCS230 1,9 K2O AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12205010	G7683 SCVi NER OS/CS230 1,9 K2O AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12188250	G7280 SCVi GB ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12205000	G7285 SCVi XXL NER ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12204990	G7280 SCVi NER ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12196980	G7280 SCVi IB ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
11750880	PFD104 SCVi XXL MAR OS3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
12184640	H2841B I EDST/CLST 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
12184630	H2766B I OBSW 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
12065090	PFD401 U DAC SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12190470	G5133 SC MER ED230 1,9 CS Front Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169470	G5132 SC F BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169480	G5132 SC F ED230 1,9 CS Front Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169450	G5112 SCi F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169440	G5112 SC F ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169430	G5112 SC F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169420	G5110 SCi F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169410	G5110 SCi F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169400	G5110i F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169390	G5110i F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169380	G5110 SCU F ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12228660	H2851BP D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12228660	H2851BP D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12228650	H2851B D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12228650	H2851B D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12169370	G5110 SCU F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169350	G5110 SC F ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065150	PFD401 U DAC LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12151220	H2465BP TR OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12151220	H2465BP TR OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12151210	H2465B TR OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12151210	H2465B TR OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12151250	H2861BP TR EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12151250	H2861BP TR EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12169330	G5110 SC F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12151230	H2861B TR EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12151230	H2861B TR EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12169320	G5110 F ED230 1,9 Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169290	G5110 F BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065060	PFD401 DAC SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065050	PFD401 DAC SST WOB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065030	PFD400 U DAC LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065010	PFD400 U DAC SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12169620	G5168 SCVi XXL F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169610	G5163 SCVi F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169600	G5162 SCVi F ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169590	G5155 SCVi XXL F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169580	G5155 Vi XXL F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169570	G5152 SCVi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12169550	G5150 SCVi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065040	PFD401 DAC SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12169540	G5150 Vi F ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065390	PFD405 U DAC SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12197000	G7285 SCVi XXL OE1 ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174370	H2465B AUS OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12174370	H2465B AUS OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174380	H2465BP AUS OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174380	H2465BP AUS OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12174400	H2467BP AUS OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12081520	DGC7840 HCX Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081510	DGC7840 HCX Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12144670	H2766BP D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144670	H2766BP D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144660	H2766B D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12174400	H2467BP AUS OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12219920	G7135 SCi XXL ANL BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190800	G5740 SC SL MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190790	G5368 SCVi XXL MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12219990	G7260 SCVi ANL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174390	H2467B AUS OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174390	H2467B AUS OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12174510	H2861B AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174510	H2861B AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12190780	G5367 SCVi XXL MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190770	G5364 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12144660	H2766B D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12143910	H2766BP GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12143910	H2766BP GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12143840	H2761BP GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12143840	H2761BP GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12081500	DGC7840 HCX Pro CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12143960	H2861BP GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12143960	H2861BP GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12143940	H2851B GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12143940	H2851B GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12143890	H2766B GB OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12143890	H2766B GB OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12143830	H2761B GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12143830	H2761B GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12081480	DGC7840 HC Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081470	DGC7840 HC Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081460	DGC7840 HC Pro CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12143950	H2861B GB EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12143950	H2861B GB EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12081490	DGC7840 HC Pro CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12143650	H2467BP GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12143650	H2467BP GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12190760	G5363 SCVi MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012340	PDR528ROP EL NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12147820	G5540 SCU SL A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149290	G15590 SCVi SL CH ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012310	PDR922 HW NAM SST D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12147810	G5540 SCU SL A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012300	PDR922 SI NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12147790	G5540 SC SL A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12082210	DGC7640-55 HC PRO CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12082240	DGC7640-55 HC PRO CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12082200	DGC7440-55 HC PRO CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081580	DGC7845 HC Pro CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081570	DGC7845 HC Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081540	DGC7845 HC Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081530	DGC7845 HC Pro CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12174430	H2851BP AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12174430	H2851BP AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174470	H2861BP AUS BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12174470	H2861BP AUS BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174500	H2861BP AUS GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12174500	H2861BP AUS GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174490	H2861BP AUS OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12174490	H2861BP AUS OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174530	H2861BP AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12174530	H2861BP AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174410	H2851B AUS EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12065180	PF402 U DAC SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065220	PF402 U DAC LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12174410	H2851B AUS EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12065230	PF402 U DAC LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12219870	G7035 SCi XXL ANL BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174440	H2861B AUS BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12219890	G7070 SCVi ANL ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190710	G5350 Vi MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12174440	H2861B AUS BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174460	H2861B AUS GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12174460	H2861B AUS GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12174450	H2861B AUS OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12174450	H2861B AUS OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12190720	G5350 SCVi MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190730	G5355 Vi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12219970	G7215 SCi XXL ANL ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190740	G5355 SCVi XXL MER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190750	G5362 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12143640	H2465BP GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12144300	H2468B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144270	H2467BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12144270	H2467BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144230	H2467B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12144230	H2467B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144220	H2466BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12144220	H2466BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144210	H2466B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12144210	H2466B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12142580	G5333 SCU D BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12144190	H2465BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12144190	H2465BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144170	H2465B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12144170	H2465B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12142570	G5333 SC D ED230 1,9 CS Front ActPlusE	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149310	G15740 SCi SL CH ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149300	G15740 SCi SL CH BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087940	DGC7865 HC Pro AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087930	DGC7865 HC Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087920	DGC7865 HC Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087910	DGC7865 HC Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087900	DGC7860 HC Pro AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087890	DGC7860 HC Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087870	DGC7860 HC Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087860	DGC7860 HC Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087850	DGC7845 HCX Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12087840	DGC7845 HCX Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087820	DGC7845 HCX Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087800	DGC7845 HC Pro AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087740	DGC7845 HC Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087700	DGC7845 HC Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087690	DGC7845 HC Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12142560	G5333 SC D BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12087670	DGC7840 HCX Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087590	DGC7840 HCX Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087560	DGC7840 HC Pro AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087550	DGC7840 HC Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087530	DGC7840 HC Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087510	DGC7840 HC Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087450	DGC7460 HC Pro AUS BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087480	DGC7460 HC Pro AUS EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087470	DGC7460 HC Pro AUS GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12087460	DGC7460 HC Pro AUS OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12144300	H2468B D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12143640	H2465BP GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12081400	DGC7640 HC Pro CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081390	DGC7640 HC Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12142610	G5333 SCi D ED230 1,9 CS Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12081250	DGC7440 HCX Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081030	DGC7440 HC Pro CH EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12081010	DGC7440 HC Pro CH GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12080980	DGC7440 HC Pro CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12080960	DGC7440 HC Pro CH BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12142600	G5333 SCi D BW230 1,9 Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12144460	H2851BP D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144460	H2851BP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144360	H2761BP D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144360	H2761BP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144540	H2861BP D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144540	H2861BP D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144590	H2861BP D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144590	H2861BP D GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144550	H2861BP D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144550	H2861BP D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144610	H2861BP D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12190810	G5740 SCiSL MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12144610	H2861BP D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12143630	H2465B GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12190820	G5740 SCiSL MER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12143630	H2465B GB OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12142590	G5333 SCU D ED230 1,9 CS Active Plus E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12144430	H2841B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144450	H2851B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12065380	PF405 U DAC SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12144450	H2851B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144350	H2761B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144350	H2761B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12219900	G7130 SC ANL BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12144480	H2861B D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144480	H2861B D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144510	H2861B D GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144510	H2861B D GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144600	H2861B D EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12065420	PF405 U DAC LW WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12144600	H2861B D EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12144340	H2468BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
12144340	H2468BP D OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12147840	G5540 SCiSL A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159030	G5362 SCVi NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12155010	H2766B SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155010	H2766B SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155060	H2861BP SER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155060	H2861BP SER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155080	H2861BP SER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155080	H2861BP SER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155070	H2861BP SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155070	H2861BP SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155030	H2861B SER BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155030	H2861B SER BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155050	H2861B SER GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155050	H2861B SER GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12155040	H2861B SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155040	H2861B SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159020	G5395 SCVi XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159010	G5360 SCVi NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179920	G5110 SCi IB ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179910	G5110 SCi IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179900	G5110 SC IB ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159000	G5355 SCVi XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158980	G5350 SCVi NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12179890	G5110 SC IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179880	G5110 IB ED230 1,9 Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179870	G5110 IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159080	G5540 SCU SL NER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159070	G5540 SCU SL NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153220	G5132 SC GB BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190640	G5315 SCI XXL MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153210	G5110 SC GB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159110	G5740 SCU SL NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159100	G5740 SCU SL NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153250	G5162 SCVi GB ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153240	G5150 SCVi GB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153230	G5150 Vi GB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159120	G5790 SCVi SL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159090	G5590 SCVi SL NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153360	G5332 SC GB ED230 1,9 Front Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153290	G5332 SC GB BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153270	G5310 SC SC GB ED230 1,9 Front Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153260	G5310 SC GB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147770	G5355 SCVi XXL A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147740	G5350 SCVi A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159040	G5367 SCVi XXL NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12196990	G7280 SCVi OE1 ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12180030	G5590 SCVi SL IB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12180020	G5540 SC SL IB BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12180010	G5355 SCVi XXL IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12180000	G5350 SCVi IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179990	G5350 Vi IB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179980	G5310 SCi IB ED230 1,9 CLST Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179970	G5310 SC IB ED230 1,9 CLST Front Act Pl	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179950	G5310 IB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179960	G5310 SC IB BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158840	G5168 SCVi XXL NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158830	G5167 SCVi XXL NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158810	G5155 SCVi XXL NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179940	G5150 SCVi IB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158820	G5162 SCVi NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158800	G5150 SCVi NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12179930	G5150 Vi IB ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190620	G5310 SCi MER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190630	G5310 SCi MER ED230 1,9 CLST Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158790	G5150 Vi NER ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158780	G5133 SCU NER ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158760	G5133 SCU NER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158750	G5132 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158740	G5132 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12155820	G5110 SCU NER ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12155810	G5110 SCU NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12155800	G5110 U NER BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158900	G5335 SCU XXL NER ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158890	G5335 SCU XXL NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158960	G5343 SCU NER ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158950	G5343 SCU NER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158940	G5342 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158930	G5342 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158920	G5332 SCU NER ED230 1,9 CS Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158910	G5332 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158880	G5330 SCU NER ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158870	G5330 SCU NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158860	G5310 SCU NER ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12158850	G5310 SCU NER BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12155020	H2766BP SER OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12155020	H2766BP SER OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12159060	G5378 SCVi XXL NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159050	G5373 SCVi NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147730	G5350 Vi A ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190660	G5332 SC MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012440	PDR944 HW NAM SST B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12147150	G5110 SCi A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147130	G5110 i A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147120	G5110 i A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012430	PDR944 Si NAM IG B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12012410	PDR944 EL NAM SST B14YY	SMD- Diode STTH1R04A	Lead	7439-92-1
12149150	G25155 Vi XXL CH ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147100	G5110 SCU A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147090	G5110 SCU A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147080	G5110 U A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147070	G5110 U A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147060	G5110 SC A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147020	G5110 A BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190670	G5332 SC MER ED230 1,9 CS Front Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149250	G25315 i XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190680	G5332 SCU MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149240	G25315 i XXL CH HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12190690	G5332 SCi MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12148120	G5990 SCVi SL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065430	PF405 U DAC LW DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12148110	G5940 SCi SL A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149220	G25315 i XXL CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149210	G25315 i XXL CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149190	G15310 i CH ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149180	G15310 i CH HB230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12148090	G5790 SCVi SL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12148100	G5940 SCi SL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149170	G15310 i CH BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149160	G15310 i CH OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12148070	G5740 SCi SL A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12148040	G5740 SCU SL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12065170	PF402 DAC SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12065190	PF402 U DAC SST DOS WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12148030	G5740 SC SL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190700	G5333 SC MER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147920	G5590 SCVi SL A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149280	G25355 SCVi XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149270	G25355 Vi XXL CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12149260	G15350 Vi CH ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012330	PDR928 Si NAM IG D04YD	SMD- Diode STTH1R04A	Lead	7439-92-1
12147880	G5540 SCi SL A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12012350	PDR528ROP EL NAM IG B04YX	SMD- Diode STTH1R04A	Lead	7439-92-1
12147170	G5110 SCi A ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153400	G5362 SCVi GB ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147700	G5310 SCi A ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147680	G5310 SCi A OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147690	G5310 SCi A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153390	G5350 SCVi GB ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147670	G5310 i A ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147480	G5310 i A OS230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147650	G5310 i A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147460	G5310 SCU A ED230 1,9 CS Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153420	G5790 SCVi SL GB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147430	G5310 SCU A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147400	G5310 U A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12144500	H2861B D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12144500	H2861B D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12147380	G5310 SC A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147360	G5310 A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12153410	G5740 SC SL GB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147720	G5315 SCi XXL A ED230 1,9 CS Active Pl	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147710	G5315 SCi XXL A BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12148060	H2841B C CN EDST/CLST 220/50	Heater element Top heat 230V	Lead	7439-92-1
12148020	H2766BP C CN OBSW 220/50	Heater element Top heat 230V	Lead	7439-92-1
12148010	H2766B C CN OBSW 220/50	Heater element Top heat 230V	Lead	7439-92-1
12148080	H2851B C CN EDST/CLST 220/50	Heater element Top heat 230V	Lead	7439-92-1
12109040	DGC7351 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109040	DGC7351 C CN OBSW 220/50	Heater element Top heat 230V	Lead	7439-92-1
12109040	DGC7351 C CN OBSW 220/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12109020	DGC7151 C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109020	DGC7151 C CN OBSW 220/50	Heater element Top heat 230V	Lead	7439-92-1
12109020	DGC7151 C CN OBSW 220/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12109030	DGC7250 C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109030	DGC7250 C CN EDST/CLST 220/50	Heater element Top heat 230V	Lead	7439-92-1
12109030	DGC7250 C CN EDST/CLST 220/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12103990	H7365B C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103940	H7145BM C CN OBSW 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
12104000	H7365BP C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103960	H7165BP C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12103950	H7165B C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12160620	H7264BP C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12147340	G5155 SCVi XXL A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147310	G5155 Vi XXL A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147260	G5150 SCVi A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12147220	G5150 Vi A ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12190650	G5315 SCi XXL MER ED230 1,9 CLST Act Plu	Drain pump 220-240V 50HZ	Lead	7439-92-1
11862300	DAS8630 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12338050	G7210 SCi D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338030	G7210 SCi D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338040	G7210 SCi D OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12328490	G7360 SCVi KW OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338020	G7210 SCU D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12148050	G5740 SCi SL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338070	G7233 SC D BW230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338080	G7233 SC D ED230 1,9 CLST Front E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338090	G7233 SCU D BW230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338110	G7233 SCU D ED230 1,9 CLST E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338010	G7210 SCU D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338000	G7210 SC D ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
12328480	G7100 SCi KW ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337990	G7210 SC D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12328460	G5000 SC KW ED230 1,9 CLST Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338130	G7238 SCI XXL D ED230 1,9 CLST E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338060	G7215 SCI XXL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337970	G7195 SCVi XXL D ED230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337950	G7185 SCVi XXL D ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337960	G7190 SCVi D ED230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338120	G7233 SCI D ED230 1,9 CLST E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910270	G7415 SCI XXL D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910260	G7410 SCI D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910250	G7410 SCi D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910240	G7410 SCU D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910230	G7410 SCU D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910220	G7410 SC D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910180	G7410 SC D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338140	G7260 SCVi D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338160	G7293 SCVi D ED230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910170	G7278 SCVi XXL D ED230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910160	G7273 SCVi D ED230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910150	G7255 SCVi XXL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910140	G7250 SCVi D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910130	G7228 SCI XXL D ED230 1,9 CLST E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910120	G7223 SCI D ED230 1,9 CLST E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910110	G7223 SCU D ED230 1,9 CLST E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910080	G7223 SCU D BW230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910070	G7223 SC D ED230 1,9 CLST Front E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910050	G7223 SC D BW230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885110	G7925 SCI XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885100	G7920 SCi A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910520	G7975 SCVi XXL D OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910500	G7970 SCVi D OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910480	G7925 SCI XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910460	G7920 SCi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11746330	H7280BP AB2 EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11746330	H7280BP AB2 EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11746330	H7280BP AB2 EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11746360	H7880BP AB2 GRGR 127/220/60	Heater element Top heat	Lead	7439-92-1
11746360	H7880BP AB2 GRGR 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11746360	H7880BP AB2 GRGR 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11746270	H7880BP AB2 OBSW 127/220/60	Heater element Top heat	Lead	7439-92-1
11746270	H7880BP AB2 OBSW 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11746270	H7880BP AB2 OBSW 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11746300	H7880BP AB2 EDST/CLST 127/220/60	Heater element Top heat	Lead	7439-92-1
11746300	H7880BP AB2 EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11746300	H7880BP AB2 EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11910440	G7695 SCVi XXL D OS/CS230 K2O 1,9AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910430	G7690 SCVi D OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910420	G7665 SCVi XXL D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910410	G7660 SCVi D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12183810	H2465B KW OBSW/EDST-LOOK 220/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11910400	G7615 SCI XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910390	G7610 SCi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910380	G7478 SCVi XXL D OS/CS230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910370	G7473 SCVi D OS/CS230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910360	G7465 SCVi XXL D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910350	G7460 SCVi D OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910340	G7428 SCI XXL D ED230 1,9 CLST AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910330	G7423 SCi D ED230 1,9 CLST AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910320	G7423 SCU D ED230 1,9 CS AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910310	G7423 SCU D BW230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910300	G7423 SC D ED230 1,9 CLST AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910290	G7423 SC D BW230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910280	G7415 SCI XXL D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12183400	H7460BP KW EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12183420	H7240BM KW EDST/CLST 220/50	Heater element Top heat 220-240V	Lead	7439-92-1
12183410	H2890B KW EDST/CLST 220/50	Temperature regul. Sub-assembly	Lead	7439-92-1
12337930	G7180 SCVi D ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11805600	H7880BP USA GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805600	H7880BP USA GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805580	H7880BP USA BRWS 120/240/60	Heater element Top heat	Lead	7439-92-1
11805580	H7880BP USA BRWS 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805580	H7880BP USA BRWS 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805610	H7880BP USA OBSW 120/240/60	Heater element Top heat	Lead	7439-92-1
12338170	G7298 SCVi XXL D ED230 1,9 E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338180	G7380 SCVi D ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338190	G7385 SCVi XXL D ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338420	G7605 SCI XXL D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338480	G7628 SCI XXL D ED230 1,9 CLST AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338360	G7600 SC D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12270200	K7317D EU1	K7317D EU1	Lead	7439-92-1
12270200	K7317D EU1	K7317D EU1	Lead	7439-92-1
12338370	G7600 SC D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338380	G7600 SCU D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338390	G7600 SCU D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338400	G7600 SCi D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12338410	G7600 SCi D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338430	G7623 SC D BW230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338440	G7623 SC D ED230 1,9 CLST AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338450	G7623 SCU D BW230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338460	G7623 SCU D ED230 1,9 CS AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338470	G7623 SCi D ED230 1,9 CLST AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338490	G7650 SCVi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338510	G7673 SCVi D OS230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338500	G7655 SCVi XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12340840	G7678 SCVi XXL D OS230 1,9 AutoDos E	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338560	G7715 SCi XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11805610	H7880BP USA OBSW 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
12338550	G7710 SCi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338570	G7760 SCVi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338580	G7765 SCVi XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11805610	H7880BP USA OBSW 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805590	H7880BP USA EDST/CLST 120/240/60	Heater element Top heat	Lead	7439-92-1
11805590	H7880BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805590	H7880BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805550	H7680BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805550	H7680BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805550	H7680BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11910040	G7205 SCi XXL D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910030	G7200 SCi D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910010	G7200 SCi D OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338150	G7265 SCVi XXL D ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11910020	G7200 SCi D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11909990	G7200 SCU D ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11909980	G7200 SCU D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11909970	G7200 SC D ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11909960	G7200 SC D BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11876270	DGC7470 USA BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876250	DGC7470 USA GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876230	DGC7470 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876210	DGC7670 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876200	DGC7870 USA BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876190	DGC7870 USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876180	DGC7870 USA GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876080	DGC7870 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876050	DGC7875 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11875800	DGC7370 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11875790	DGC7570 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11875780	DGC7770 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11875760	DGC7775 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11877040	DGC7880X USA GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11877030	DGC7870X USA GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876970	DGC7440 USA BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876960	DGC7440 USA GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876950	DGC7440 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876660	DGC7640 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876630	DGC7840 USA BRWS 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876610	DGC7840 USA OBSW 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876600	DGC7840 USA GRGR 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876590	DGC7840 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11876580	DGC7845 USA EDST/CLST 208/240/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11805630	H7880BPX USA GRGR 120/240/60	Heater element Top heat	Lead	7439-92-1
11805630	H7880BPX USA GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805630	H7880BPX USA GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805560	H7780BP USA EDST/CLST 120/240/60	Heater element Top heat	Lead	7439-92-1
11805560	H7780BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805560	H7780BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805600	H7880BP USA GRGR 120/240/60	Heater element Top heat	Lead	7439-92-1
11884660	G7200 SC A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12332990	H2455i XU2/USA OBSW/EDST-LOOK120/208/60	Heater element Bottom heat	Lead	7439-92-1
12346510	PDR516ROP SL EL ANL IG-IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12328420	PDR511COP SL HP ANL IG-IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11886390	G7460 SCVi MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11905980	PDR508HP D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11905970	PDR508HP D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11886380	G7423 SC MER BW230 1,9 AutoD Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11905960	PDR508EL D SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11886370	G7422 SCi MER ED230 1,9 AutoD CLST Selec	Drain pump 220-240V 50HZ	Lead	7439-92-1
11905950	PDR508EL D LW	SMD- Diode STTH1R04A	Lead	7439-92-1
12328430	PDR511COP SL HP ANL IG-IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12109180	DGC7440 HC Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109200	DGC7440 HC Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11886360	G7410 SCi MER ED230 1,9 AutoDos CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886350	G7410 SCi MER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886340	G7410 SC MER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886330	G7278 SCVi XXL MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886320	G7277 SCVi XXL MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886310	G7273 SCVi MER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886290	G7272 SCVi MER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886270	G7255 SCVi XXL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11886260	G7250 SCVi MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886110	G7065 Vi XXL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886120	G7065 SCVi XXL MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12109210	DGC7440 HC Pro C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109230	DGC7440 HCX Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109240	DGC7440 HCX Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11886100	G7060 SCVi MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886080	G7060 Vi MER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886070	G7020 SCi MER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886060	G7020 SCi MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885970	G7020 SC MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886250	G7223 SC MER BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886230	G7222 SCi MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11924600	PDR910 G EU LW E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11886220	G7222 SCU MER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11924590	PDR910 EL EU LW A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11924580	PDR910 EL EU LW E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11886210	G7222 SC MER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12109430	DGC7640 HC Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289750	DGC7440 HC Pro UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289760	DGC7440 HC Pro UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11886430	G7478 SCVi XXL MER OS230 1,9 AutoD Excel	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289780	DGC7440 HC Pro UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289790	DGC7440 HC Pro UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11886420	G7473 SCVi MER OS230 1,9 AutoD Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289800	DGC7440 HCX Pro UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289810	DGC7440 HCX Pro UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11886410	G7472 SCVi MER OS230 1,9 AutoD Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289820	DGC7440 HCX Pro UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289830	DGC7460 HC Pro UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289840	DGC7460 HC Pro UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289850	DGC7460 HC Pro UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289870	DGC7460 HC Pro UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289890	DGC7460 HCX Pro UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289900	DGC7840 HC Pro UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289910	DGC7840 HC Pro UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289920	DGC7840 HC Pro UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289930	DGC7840 HC Pro UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289950	DGC7840 HCX Pro UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289960	DGC7840 HCX Pro UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289970	DGC7840 HCX Pro UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12289990	DGC7860 HC Pro UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12290000	DGC7860 HC Pro UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12290010	DGC7860 HC Pro UA EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12290020	DGC7860 HCX Pro UA BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12290030	DGC7860 HCX Pro UA OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12290040	DGC7860 HCX Pro UA GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12332650	H2455B XU3/USA OBSW/EDST-LOOK120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
12332650	H2455B XU3/USA OBSW/EDST-LOOK120/240/60	Heater element Top heat 230V	Lead	7439-92-1
12332950	H2455E XU3/USA OBSW/EDST-LOOK120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
12332950	H2455E XU3/USA OBSW/EDST-LOOK120/240/60	Heater element Top heat 230V	Lead	7439-92-1
12332970	H2455E XU2/USA OBSW/EDST-LOOK120/208/60	Heater element Top heat 200V	Lead	7439-92-1
12332970	H2455E XU2/USA OBSW/EDST-LOOK120/208/60	Heater element Bottom heat	Lead	7439-92-1
11886400	G7465 SCVi XXL MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12332980	H2455I XU3/USA OBSW/EDST-LOOK120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
12332980	H2455I XU3/USA OBSW/EDST-LOOK120/240/60	Heater element Top heat 230V	Lead	7439-92-1
12332660	H2455B XU2/USA OBSW/EDST-LOOK120/208/60	Heater element Top heat 200V	Lead	7439-92-1
12332660	H2455B XU2/USA OBSW/EDST-LOOK120/208/60	Heater element Bottom heat	Lead	7439-92-1
12332990	H2455I XU2/USA OBSW/EDST-LOOK120/208/60	Heater element Top heat 200V	Lead	7439-92-1
11885090	G7695 SCVi XXL A OS/CS230 K20 1,9AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885080	G7690 SCVi A OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885070	G7665 SCVi XXL A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885050	G7660 SCVi A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885000	G7415 SCi XXL A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884990	G7415 SCi XXL A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885040	G7615 SCi XXL A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885030	G7610 SCi A OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884980	G7410 SCi A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337830	G7130 SCU D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337840	G7130 SCU D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337850	G7130 SCi D BW230 1,9 Auto Dos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337860	G7130 SCi D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884950	G7410 SCi A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337890	G7135 SCi XXL D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337910	G7135 SCi XXL D ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884940	G7410 SCU A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884930	G7410 SCU A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11930430	PDR508EL NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12183810	H2465B KW OBSW/EDST-LOOK 220/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11884920	G7410 SC A ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885020	G7465 SCVi XXL A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885010	G7460 SCVi A OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11930420	PDR508EL NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11930470	PDR508EL DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11884910	G7410 SC A BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922270	PDR508EL F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11922260	PDR508EL F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11930340	PDR508EL B SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11930330	PDR508EL B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11884790	G7255 SCVi XXL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884770	G7250 SCVi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884750	G7205 SCi XXL A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884740	G7205 SCi XXL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884730	G7200 SCi A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884720	G7200 SCi A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884710	G7200 SCi A OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884700	G7200 SCU A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884690	G7200 SCU A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884670	G7200 SC A ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886130	G7200 SCi MER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11924560	PDR910 EL EU SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11924540	PDR910 EL EU SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11927690	PDR510TOP EL EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12109440	DGC7640 HC Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11927680	PDR510TOP EL EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11885960	G7200 SC MER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12109450	DGC7640 HC Pro C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11884650	G7065 SCVi XXL A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884640	G7060 SCVi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884630	G7060 Vi A ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12109460	DGC7660 HC Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109470	DGC7660 HC Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109500	DGC7840 HC Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109510	DGC7840 HC Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109520	DGC7840 HC Pro C CN EDST/CLST 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11930480	PDR508HP DK LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11930450	PDR508HP NL SST	SMD- Diode STTH1R04A	Lead	7439-92-1
12109540	DGC7840 HCX Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11930440	PDR508HP NL LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11922290	PDR508HP F SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11922280	PDR508HP F LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11930380	PDR508HP B SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11930370	PDR508HP B LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11884620	G7025 SCi XXL A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884610	G7025 SCi XXL A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12109550	DGC7840 HCX Pro C CN GRGR 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12109620	DGC7860 HCX Pro C CN OBSW 220/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11884600	G7020 SCi A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
12151380	H2469BP NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
12151380	H2469BP NER OBSW/EDST-LOOK 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11884590	G7020 SCi A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337810	G7130 SC D BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12337820	G7130 SC D ED230 1,9 CLST Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884570	G7020 i A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884560	G7020 SCU A ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884550	G7020 SCU A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11884540	G7020 SC A BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885130	G7975 SCVi XXL A OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885120	G7970 SCVi A OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11105720	H7464BP D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105710	H7464BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105780	H7464BPX D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105740	H7464BPX D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305590	DGC7865 HCX Pro D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105730	H7464BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104270	H7364BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105680	H7460BP D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105670	H7460BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105660	H7460BP D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105790	H7464BPX D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106080	H7860BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305580	DGC7860 HCX Pro D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106040	H7860BP D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106050	H7860BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305570	DGC7845 HCX Pro D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106060	H7860BP D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106100	H7860BPX D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106090	H7860BPX D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11106110	H7860BPX D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105690	H7460BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105870	H7660BP D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105860	H7660BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105850	H7660BP D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105880	H7660BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104250	H7264BP D GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104230	H7264BP D OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104220	H7264BP D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11104260	H7264BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11104050	H7164BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10874260	H7860BP AN7 EDST/CLST 200/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10874670	H7860BPX AN6 GRGR 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
10874650	H7860BP AN6 EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
10874250	H7464BP AN8 EDST/CLST 200/60	SMD- Diode STTH1R04A	Lead	7439-92-1
10874240	H7464BP AN7 EDST/CLST 200/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10874630	H7464BP AN6 EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
10781020	H7860BP AN8 EDST/CLST 200/60	SMD- Diode STTH1R04A	Lead	7439-92-1
10780760	H7464BPX ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780760	H7464BPX ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780760	H7464BPX ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12338780	G7980 SCVi D OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338790	G7985 SCVi XXL D OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12296440	PW6241 EL CN 3N 380-415/50-60	Control electr.unit EW 235-A	Lead	7439-92-1
12296450	PW6241 EL CN 3N 380-415/50-60 MF	Control electr.unit EW 235-A	Lead	7439-92-1
12296480	PW6321 EL CN 3N AC 380-415V 50-60Hz	Control electr.unit EW 235-A	Lead	7439-92-1
12296490	PW6321 EL CN 3N 380-415/50-60 MF	Control electr.unit EW 235-A	Lead	7439-92-1
12292340	KM7174 FR UA 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12292370	KM7464 FR UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12292440	KM7564 FL UA 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12292450	KM7575 FR UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12292450	KM7575 FR UA 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12292470	KM7684 FL UA 230/50	Induction coil G5 Octa OL L100	Lead	7439-92-1
12292470	KM7684 FL UA 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12347600	DGC7440 HCX Pro I OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12347660	DGC7460 HCX Pro I OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12347670	DGC7840 HCX Pro I OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12347680	DGC7860 HCX Pro I OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12343020	DGC7840 HCX Pro IB OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12343040	DGC7860 HCX Pro IB OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12343050	DGC7865 HCX Pro IB OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093630	H7464BPX GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093620	H7464BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093610	H7464BP GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093600	H7464BP GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093820	H7860BPX GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093810	H7860BPX GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093830	H7860BPX GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093790	H7860BP GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305520	DGC7440 HCX Pro D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305530	DGC7445 HCX Pro D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305540	DGC7460 HCX Pro D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305550	DGC7465 HCX Pro D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305560	DGC7840 HCX Pro D OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093780	H7860BP GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093770	H7860BP GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093800	H7860BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11153170	KM7564 FL CH 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10650470	KM7564 FL R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
11153150	KM7564 FR CH 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
10650480	KM7564 FR R01 230/50	Induction coil G5 Octa OL L250	Lead	7439-92-1
12305780	DGC7860 HCX Pro F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305790	DGC7865 HCX Pro F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326550	DGC7440 HCX Pro BNE OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326560	DGC7445 HCX Pro BNE OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326570	DGC7460 HCX Pro BNE OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326580	DGC7465 HCX Pro BNE OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11841950	G7332 SC D BW230 1,9 Referenz	Drain pump 220-240V 50HZ	Lead	7439-92-1
11804710	H7870BMX USA GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804690	H7870BM USA GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804670	H7870BM USA BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804700	H7870BM USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804680	H7870BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804620	H7770BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11841960	G7333 SC D BW230 1,9 GSL 3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11804610	H7670BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804590	H7570BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804580	H7270BM USA GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804530	H7270BM USA BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804570	H7270BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804470	H7170BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
12326590	DGC7840 HCX Pro BNE OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326600	DGC7845 HCX Pro BNE OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11804650	H7840BM USA GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804630	H7840BM USA BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
12326620	DGC7860 HCX Pro BNE OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12326630	DGC7865 HCX Pro BNE OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11804660	H7840BM USA OBSW 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
12317270	DGC7440 HCX Pro NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12317280	DGC7460 HCX Pro NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11804640	H7840BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
12317290	DGC7840 HCX Pro NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12317300	DGC7845 HCX Pro NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11804600	H7640BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12317310	DGC7860 HCX Pro NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12317320	DGC7865 HCX Pro NER OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11804520	H7240BM USA GRGR 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11635931	Power-/Control unit EPL 8630	SMD- Diode STTH1R04A	Lead	7439-92-1
11804480	H7240BM USA BRWS 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11804510	H7240BM USA EDST/CLST 120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11927660	PDR910 EL ANL IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
10780820	H7860BPX ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780820	H7860BPX ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780830	H7860BPX ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780830	H7860BPX ANL BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780870	H7860BP ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780870	H7860BP ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780850	H7860BP ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780850	H7860BP ANL BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780860	H7860BP ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780860	H7860BP ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780790	H7660BP ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780790	H7660BP ANL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
12305650	DGC7440 HCX Pro F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305730	DGC7445 HCX Pro F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305740	DGC7460 HCX Pro F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305750	DGC7465 HCX Pro F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305760	DGC7840 HCX Pro F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12305770	DGC7845 HCX Pro F OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780790	H7660BP ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780750	H7464BP ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780750	H7464BP ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780750	H7464BP ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780740	H7464BP ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780740	H7464BP ANL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780740	H7464BP ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780710	H7460BP ANL BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780710	H7460BP ANL BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780710	H7460BP ANL BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10780770	H7660BP ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10780770	H7660BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10780770	H7660BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10552460	H7460BP ANL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10552460	H7460BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
10552460	H7460BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10400250	H7460BPX ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10400250	H7460BPX ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
10400250	H7460BPX ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
10400280	H7660BP ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
10400280	H7660BP ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
10400280	H7660BP ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12294530	DGC7865 HCX Pro R01 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11111060	H7460BP CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111060	H7460BP CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11111060	H7460BP CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111050	H7460BP CH BRWS 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111050	H7460BP CH BRWS 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11111050	H7460BP CH BRWS 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111080	H7460BP CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111080	H7460BP CH EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11111080	H7460BP CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11121130	H7860BPX SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121120	H7860BPX SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121110	H7860BPX SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121090	H7860BP SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121080	H7860BP SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11121070	H7860BP SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120970	H7660BP SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120960	H7660BP SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120950	H7660BP SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120940	H7464BPX SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120930	H7464BPX SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120920	H7464BPX SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120900	H7464BP SER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120890	H7464BP SER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11120770	H7464BP SER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11136400	H7460BP GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11136410	H7460BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11098740	H7860BP TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11098720	H7460BP TR EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129600	H7860BP IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129590	H7660BP IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129580	H7464BP IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11129570	H7364BP IB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11151030	H7560BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101670	H7860BPX EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101660	H7860BPX EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101650	H7860BP NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11101640	H7860BP EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101630	H7860BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110740	H7860BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110710	H7660BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11805540	H7580BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805540	H7580BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805540	H7580BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805570	H7780BP2 USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805570	H7780BP2 USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805570	H7780BP2 USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805520	H7280BP USA GRGR 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805520	H7280BP USA GRGR 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805520	H7280BP USA GRGR 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805350	H7280BP USA BRWS 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805350	H7280BP USA BRWS 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805350	H7280BP USA BRWS 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805500	H7280BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805500	H7280BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805500	H7280BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805340	H7180BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805340	H7180BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805340	H7180BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805330	H2880BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805330	H2880BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805330	H2880BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11805320	H2780BP USA EDST/CLST 120/240/60	Heater element Hot air 208V	Lead	7439-92-1
11805320	H2780BP USA EDST/CLST 120/240/60	Heater element Top heat 208V	Lead	7439-92-1
11805320	H2780BP USA EDST/CLST 120/240/60	Heater element Bottom heat 208V	Lead	7439-92-1
11934850	PDR944 EL SOM SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11934830	PDR928 EL SOM SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11934820	PDR922 EL SOM SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11934790	PDR918 EL SOM SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11934780	PDR914 EL SOM SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11791750	HR1956-3 LP DF GD USAEDST/CLST120/240/60	Release element 220/240V 50/60HZ	Lead	7439-92-1
11791750	HR1956-3 LP DF GD USAEDST/CLST120/240/60	Heater element Top heat 200-208V	Lead	7439-92-1
11111130	H7660BP CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111130	H7660BP CH GRGR 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11111130	H7660BP CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111140	H7660BP CH EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111140	H7660BP CH EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11111140	H7660BP CH EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11111070	H7460BP CH GRGR 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11111070	H7460BP CH GRGR 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11111070	H7460BP CH GRGR 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11109020	H7860BPX F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11109010	H7860BPX F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11109000	H7860BPX F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108990	H7860BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108980	H7860BP F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108970	H7860BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108960	H7860BP F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108710	H7464BPX F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108700	H7464BPX F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108690	H7464BPX F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108680	H7464BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108670	H7464BP F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108660	H7464BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108650	H7464BP F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108640	H7460BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108630	H7460BP F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108620	H7460BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108610	H7460BP F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108500	H7364BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11183030	H7560BP D EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093510	H7364BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093590	H7464BP GB BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11105700	H7464BP D BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093670	H7660BP GB EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093650	H7464BPX GB GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11093640	H7464BPX GB OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12338590	G7783 SCVi D OS230 1,9 k2o AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338620	G7790 SCVi D OS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12308720	DA2628 UA EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12338600	G7788 SCVi XXL D OS230 1,9 K2O AutoD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338630	G7795 SCVi XXL D OS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338770	G7935 SCi XXL D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12338740	G7930 SCi D OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12294450	DGC7440 HCX Pro R01 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12294460	DGC7445 HCX Pro R01 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12294480	DGC7460 HCX Pro R01 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12294490	DGC7465 HCX Pro R01 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12294500	DGC7840 HCX Pro R01 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12294510	DGC7845 HCX Pro R01 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12294520	DGC7860 HCX Pro R01 OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11110670	H7460BP EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101520	H7660BP NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101510	H7660BP EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110660	H7460BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110690	H7464BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11101500	H7660BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11110680	H7460BP B EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099910	H7464BPX EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099900	H7464BPX EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099890	H7464BP NL EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099880	H7464BP EU1 GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099870	H7464BP EU1 OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11099700	H7364BP EU1 EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130390	H7860BPX NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130380	H7860BPX NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130370	H7860BPX NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130360	H7860BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130340	H7860BP NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130330	H7860BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130320	H7860BP NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130280	H7660BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130270	H7660BP NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130260	H7660BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130250	H7660BP NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130240	H7464BPX NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130230	H7464BPX NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130220	H7464BPX NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130210	H7464BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130200	H7464BP NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130190	H7464BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130180	H7464BP NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130170	H7460BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130160	H7460BP NER GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130150	H7460BP NER OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130140	H7460BP NER BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11130130	H7364BP NER EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108800	H7660BP F EDST/CLST 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108790	H7660BP F GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108780	H7660BP F OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11108770	H7660BP F BRWS 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12295330	H2455-55EP XS2/CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
11870640	G7114 SCi AUS ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870630	G7114 SCU AUS ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11936340	DGC7440X CH OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11870240	G7410 SC GB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870250	G7410 SC GB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870230	G7272 SCVi GB ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870220	G7255 SCVi XXL GB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870610	G7114 SC AUS ED230 1,9 CS Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870210	G7250 SCVi GB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870600	G7114 SC AUS BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870260	G7410 SCi GB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870660	G7164 SCVi AUS ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870270	G7422 SC GB BW230 1,9 AutoDos Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11927230	G7169 SCVi XXL AUS ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870280	G7460 SCVi GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870290	G7465 SCVi XXL GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870300	G7472 SCVi GB OS/SC230 1,9 AutoD Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870310	G7660 SCVi GB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870320	G7975 SCVi XXL GB OS/CS230 1,9 K2O Auto	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887420	G17410 SC CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887430	G17410 SCi CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870030	G7222 SC GB ED230 1,9 CLST Front Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
11869970	G7222 SC GB BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11869910	G7200 SCi GB ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11869830	G7200 SCi GB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11869770	G7200 SC GB ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11868170	G7200 SC GB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887410	G7975 SCVi XXL TR OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887400	G7925 SCi XXL TR OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887390	G7695 SCVi XXL TR OS/CS230 K2O 1,9AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11945040	PDR508HP GB LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11945030	PDR508EL GB LW 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11887380	G7610 SCi TR OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887310	G7410 SCi TR ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887300	G7410 SC TR ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11945110	PDR508EL IRL LW 400V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11788910	H7880BP BR GRGR 127/220/60	Heater element Top heat	Lead	7439-92-1
11788910	H7880BP BR GRGR 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11788910	H7880BP BR GRGR 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11788880	H7880BP BR OBSW 127/220/60	Heater element Top heat	Lead	7439-92-1
11788880	H7880BP BR OBSW 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11788880	H7880BP BR OBSW 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11887440	G17410 SCi CH ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12295130	H2457IP XE1/D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295130	H2457IP XE1/D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11974830	H2861B ANL BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11974830	H2861B ANL BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11974820	H2467B ANL EDST/CLST 230/50 ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11974820	H2467B ANL EDST/CLST 230/50 ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11816600	HR1934-3 LP DF BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11816600	HR1934-3 LP DF BR EDST/CLST 127/220/60	Heater element Top heat 208V	Lead	7439-92-1
11816600	HR1934-3 LP DF BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11782570	H7240BM SA EDST/CLST 220/60	Heater element Top heat 220-240V	Lead	7439-92-1
11782580	H7464BP SA EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11952750	DGC7450 AN2 EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11952750	DGC7450 AN2 EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11952750	DGC7450 AN2 EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11957230	DGC7250 AN2 EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11957230	DGC7250 AN2 EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11957230	DGC7250 AN2 EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11817000	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
11817000	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
11887570	G27975 SCVi XXL CH OS/CS230 1,9k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887560	G17970 SCVi CH OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887550	G27925 SCi XXL CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887540	G27695 SCVi XXL CH OS/CS230 K20 1,9AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887530	G17690 SCVi CH OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887520	G27615 SCi XXL CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887510	G17610 SCi CH OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887630	G27478 SCVi XXL CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887620	G17473 SCVi CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12295150	H2455B XI1/I OBSW/EDST-LOOK 230/50 <3KW	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295150	H2455B XI1/I OBSW/EDST-LOOK 230/50 <3KW	Heater element Top heat 230V	Lead	7439-92-1
11887500	G27465 SCVi XXL CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887490	G17460 SCVi CH OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11911710	G7685 SCVi XXL ANL OS/CS230 1,9 AD FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
11911700	G7680 SCVi ANL OS/CS230 1,9 AutoDos FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
11911730	G7285 SCVi XXL ANL ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
11911720	G7280 SCVi ANL ED230 1,9 FF	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887600	G27428 SCi XXL CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887610	G27428 SCi XXL CH ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887580	G17423 SCi CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887590	G17423 SCi CH ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887480	G27415 SCi XXL CH ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887450	G27415 SCi XXL CH BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885220	G7250 SCVi I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289180	G5540 SC SL I ED230 1,9 CLST Front Act	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288690	G5110 i I ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885200	G7200 SCi I ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885190	G7200 SCi I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885170	G7200 SCU I ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885160	G7200 SCU I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885150	G7200 SC I ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885140	G7200 SC I BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11864240	DA9298W CH BLBO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11911810	G7165 SCVi XXL ANL ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10798890	G7160 SCVi ANL ED230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11911800	G7115 SCi XXL ANL BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10798870	G7110 SCi ANL ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10798860	G7110 SCi ANL BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870900	DA9298W D BLBO 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11979050	PDR910 EL EX LW A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11979040	PDR910 EL EX SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11979030	PDR910 EL EX IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11979020	PDR910 EL EX SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11979010	PDR910 EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11979000	PDR910 EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11978990	PDR510ROP EL EX IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11978970	PDR510ROP EL EX IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11978950	PDR510ROP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11978890	PDR910 EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11978880	PDR910 EL RU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11978870	PDR510ROP EL RU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11978850	PDR510ROP EL RU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11746570	DGC7870 AN6 OBSW 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11746600	DGC7870 AN6 GRGR 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11746580	DGC7870 AN6 EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11451092	Power-/Control unit ELP 7442-A 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11966850	PDR910 EL SOM SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11966870	PDR910 EL SOM SST B03Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11886970	G7975 SCVi XXL OE1 OS/CS230 1,9k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886960	G7970 SCVi OE1 OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288700	G5110 SC I BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288710	G5110 SC I ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886950	G7920 SCi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886930	G7695 SCVi XXL OE1 OS/CS230 K20 1,9AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886900	G7690 SCVi OE1 OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12289190	G5590 SCVi SL I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11788890	H7880BP BR EDST/CLST 127/220/60	Heater element Top heat	Lead	7439-92-1
11788890	H7880BP BR EDST/CLST 127/220/60	Heater element Hot air 208V	Lead	7439-92-1
11788890	H7880BP BR EDST/CLST 127/220/60	Heater element Bottom heat 208V	Lead	7439-92-1
11790770	H7870BM BR GRGR 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11790750	H7870BM BR OBSW 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11790760	H7870BM BR EDST/CLST 127/220/60	Heater element Top heat 200-208V	Lead	7439-92-1
11887290	G7250 SCVi TR ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11945100	PDR508EL IRL LW 230V 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11945090	PDR508HP IRL LW 230V 13A	SMD- Diode STTH1R04A	Lead	7439-92-1
11887280	G7020 SCi TR ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11887260	G7020 SC TR BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870550	G7975 SCVi XXL IB OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870530	G7970 SCVi IB OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870520	G7920 SCi IB OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870510	G7690 SCVi IB OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870500	G7460 SCVi IB OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870490	G7410 SC IB ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870480	G7410 SC IB BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870470	G7255 SCVi XXL IB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870460	G7250 SCVi IB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870450	G7200 SCi IB ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870440	G7200 SCi IB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870430	G7200 SCU IB ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870420	G7200 SC IB ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11870410	G7200 SC IB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11941350	PDR908HP AUS LW 10A	SMD- Diode STTH1R04A	Lead	7439-92-1
11941330	PDR908EL AUS LW 25A	SMD- Diode STTH1R04A	Lead	7439-92-1
11885420	G7975 SCVi XXL I OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885410	G7970 SCVi I OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885400	G7690 SCVi I OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885380	G7660 SCVi I OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885370	G7465 SCVi XXL I OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
10279303	Electronic unit	Electronic unit	Lead	7439-92-1
10279303	Electronic unit	Electronic unit	Lead	7439-92-1
11885350	G7460 SCVi I OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885330	G7410 SCi I ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885310	G7410 SCU I ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885290	G7410 SC I ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885230	G7255 SCVi XXL I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885270	G7273 SCVi I ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11885240	G7272 SCVi I ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289200	G5790 SCVi SL I ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12092180	PW6241 EL NAM IG 3AC 208/240V 60Hz D	Control electr.unit EW 235-A	Lead	7439-92-1
12092240	PW6321 EL NAM SST MF 3AC 440/480V 60Hz Y	Control electr.unit EW 235-A	Lead	7439-92-1
10979291	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
10979291	Heater element Top heat 400V	Heater element Top heat 400V	Lead	7439-92-1
11936430	H7464BPX CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11936430	H7464BPX CH OBSW 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11936430	H7464BPX CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11826160	KM7755 FL ANL 240/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
12092270	PW6321 EL NAM IG 3AC 208/240V 60Hz D	Control electr.unit EW 235-A	Lead	7439-92-1
12066110	PF400 GB LW WB 230V/50Hz	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11826170	KM7745 FL ANL 240/60	Induction coil G5 Octa OL L250	Lead	7439-92-1
11952760	DGC7450-55 AN2 EDST/CLST 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11952760	DGC7450-55 AN2 EDST/CLST 400/N/50	Heater element Bottom heat 400V	Lead	7439-92-1
11952760	DGC7450-55 AN2 EDST/CLST 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
12066140	PF401 GB LW WB 230V/50Hz	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066120	PF401 GB SST WB 230V/50Hz	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066230	PF401 GB SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066160	PF401 GB LW DOS WB 230V/50Hz	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11790110	DG7240 SA EDST/CLST 220/60	SMD- Diode STTH1R04A	Lead	7439-92-1
11848400	PF401 SCVi XXL PL OS3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11863380	PF401 SCi XXL PL ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11863360	PF401 SCi PL ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11848330	PF401 PL ED3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
11863340	PF401 U PL ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
12066130	PF401 GB SST DOS WB 230V/50Hz	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11921940	G7975 SCVi XXL F OS/CS230 1,9 k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12066180	PF402 GB SST WB 230V/50Hz	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066210	PF405 GB SST WB 230V/50Hz	Circulation pump S35 PP (00-53)	Lead	7439-92-1
11863330	PF401 PL ED/BW3N400 7,3	Drain pump 220-240V 50HZ	Lead	7439-92-1
12066250	PF405 GB SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12066220	PF405 GB SST DOS WB 230V/50Hz	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12013020	PDR510TOP EL CN IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
10884758	Power-/Control unit ELP 7482	SMD- Diode STTH1R04A	Lead	7439-92-1
10884649	Power-/Control unit ELP 7202 220-240V	SMD- Diode STTH1R04A	Lead	7439-92-1
11921930	G7970 SCVi F OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921910	G7690 SCVi F OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921920	G7695 SCVi XXL F OS/CS230 K20 1,9AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11780620	G7110 SC AE ED230 1,9 CS Front AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921890	G7665 SCVi XXL F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12011990	PDR944 SI CN SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12011980	PDR944 EL CN SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12294920	H2455E XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12092170	PW6241 EL NAM SST MF 3AC 440/480V 60Hz Y	Control electr.unit EW 235-A	Lead	7439-92-1
11862350	DAS8930 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12146050	H2861-55B CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
11862280	DAS4940 D GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11862220	DAS4640 D GLTR 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12146050	H2861-55B CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12146050	H2861-55B CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
12146130	H2861-55BP CH EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
12146130	H2861-55BP CH EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12146130	H2861-55BP CH EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
12146110	H2861-55BP CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
12146110	H2861-55BP CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11208544	Power-/Control unit ELP 7775 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
12146110	H2861-55BP CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
12146100	H2861-55BP CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
12146100	H2861-55BP CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11862270	DAS4930 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11862200	DAS4630 D OBSW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11862230	DAS4920 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11862180	DAS4620 D EDST 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
12146100	H2861-55BP CH BRWS 400/50	Heater element Top heat 400V	Lead	7439-92-1
12012390	PDR928 EL NAM SST B14YY	SMD- Diode STTH1R04A	Lead	7439-92-1
11962850	G7310 SC ZA BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12298830	PDR944 SI AUS SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12162720	G5110 SC A ED230 1,9 CS Front Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11724000	H2455I AN3 EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11724000	H2455I AN3 EDST/CLST 120/240/60	Heater element Top heat 230V	Lead	7439-92-1
11723980	H2455E AN3 EDST/CLST 120/240/60	Heater element Unterhitze 230-240V	Lead	7439-92-1
11723980	H2455E AN3 EDST/CLST 120/240/60	Heater element Top heat 230V	Lead	7439-92-1
11723990	H2455E ANZ EDST/CLST 120/208/60	Heater element Top heat 200V	Lead	7439-92-1
1198690	PDR908HP S SST	SMD- Diode STTH1R04A	Lead	7439-92-1
11940280	G7060 SCVi GB ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11940270	G7020 SC GB BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11994170	PDR909 EL CP EU SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994210	PDR909 EL CP EU SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994200	PDR909 EL CP EU IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994190	PDR909 EL CP EU SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11994180	PDR909 EL CP EU IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11969170	PDR909 EL CP EU IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11936480	H7440BMX CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11936470	H7440BPX CH OBSW 400/N/50	Heater element Top heat 400V	Lead	7439-92-1
11936470	H7440BPX CH OBSW 400/N/50	Heater element Hot air 400V	Lead	7439-92-1
11723990	H2455E ANZ EDST/CLST 120/208/60	Heater element Bottom heat	Lead	7439-92-1
11921790	G7423 SC F ED230 1,9 AutoD CLST Excellen	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921780	G7423 SC F BW230 1,9 AutoDos Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921760	G7410 SCi F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921750	G7410 SCU F ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921740	G7410 SC F BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921730	G7273 SCVi F ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921720	G7255 SCVi XXL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921710	G7250 SCVi F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921700	G7223 SC F ED230 1,9 CLST Front Excellen	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921690	G7223 SC F BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921680	G7200 SCi F ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921670	G7200 SCi F OS230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11952730	DGC7450 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11952730	DGC7450 ANL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11952730	DGC7450 ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11952740	DGC7450 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11952740	DGC7450 ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11952740	DGC7450 ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11952700	DGC7250 ANL GRGR 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11952700	DGC7250 ANL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11952700	DGC7250 ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11952710	DGC7250 ANL OBSW 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11952710	DGC7250 ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11952710	DGC7250 ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11921660	G7200 SC F ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921530	G7200 SC F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921520	G7065 SCVi XXL F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921440	G7060 SCVi F ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11974880	H2841B ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11974840	H2851BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11974840	H2851BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11974870	H2861BP ANL GRGR 230/50	Heater element Top heat 230V	Lead	7439-92-1
11974870	H2861BP ANL GRGR 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11974860	H2861BP ANL OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11974860	H2861BP ANL OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11921430	G7020 SCi F ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921420	G7020 SCi F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921410	G7020 SC F ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921390	G7020 F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921400	G7020 SC F BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11974850	H2861BP ANL EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
11974850	H2861BP ANL EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11974940	H2861-55BP AN1 EDST/CLST 400/50	Heater element Hot air 400V	Lead	7439-92-1
12294920	H2455E XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12011960	PDR928 SI CN SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12011970	PDR928 EL CN SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12011950	PDR922 SI CN SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12011940	PDR922 EL CN SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12011880	PDR522ROP EL CN IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12011930	PDR918 SI CN SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12011920	PDR918 EL CN SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11921880	G7660 SCVi F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12294960	H2457E XE1/D OBSW/EDST-LOOK 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12294960	H2457E XE1/D OBSW/EDST-LOOK 230/50	Heater element Top heat 230V	Lead	7439-92-1
12011910	PDR914 EL CN SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12011870	PDR514ROP EL CN IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11921870	G7610 SCi F OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12294970	H2457E XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12294970	H2457E XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12294950	H2455I XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12294950	H2455I XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12294980	H2457I XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12294980	H2457I XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12295170	H2455IP XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295170	H2455IP XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
12295160	H2455IP XE1/D BRWS 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295160	H2455IP XE1/D BRWS 230/50	Heater element Top heat 230V	Lead	7439-92-1
11874420	G7110 C SC CN BW220/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12295140	H2457IP XE1/D OBSW 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
12295140	H2457IP XE1/D OBSW 230/50	Heater element Top heat 230V	Lead	7439-92-1
11921860	G7478 SCVi XXL F OS230 1,9 AutoD Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921850	G7473 SCVi F OS230 1,9 AutoDos Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921830	G7465 SCVi XXL F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11921810	G7460 SCVi F OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11974980	H2841B AI1 EDST/CLST 230/50 <3kW	Heater element Top heat 230V	Lead	7439-92-1
11974960	H2465B AI1 EDST/CLST 230/50 <3kW ACTIVE	Heater element Top heat 230V	Lead	7439-92-1
11974960	H2465B AI1 EDST/CLST 230/50 <3kW ACTIVE	Heater element Unterhitze 230-240V	Lead	7439-92-1
11974920	H2465-55B AN1 EDST/CLST 400/50 ACTIVE	Heater element Top heat 400V	Lead	7439-92-1
11974920	H2465-55B AN1 EDST/CLST 400/50 ACTIVE	Heater element Bottom heat 400V	Lead	7439-92-1
11974920	H2465-55B AN1 EDST/CLST 400/50 ACTIVE	Heater element Hot air 400V	Lead	7439-92-1
11974930	H2861-55B AN1 OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
11974930	H2861-55B AN1 OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11974930	H2861-55B AN1 OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
11974940	H2861-55BP AN1 EDST/CLST 400/50	Heater element Top heat 400V	Lead	7439-92-1
11974940	H2861-55BP AN1 EDST/CLST 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11886840	G7610 SCi OE1 OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972510	PDR922 EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972500	PDR922 EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972490	PDR522ROP SI EX IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972470	PDR522ROP G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972460	PDR522ROP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12289070	G5332 SC I ED230 1,9 CLST Front Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972450	PDR522ROP EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972440	PDR522TOP G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12289080	G5332 SCU I ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972430	PDR522TOP EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11973110	PDR944 SI EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12289090	G5333 SC I ED230 1,9 CLST Front Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
11973100	PDR944 SI EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11973090	PDR944 G EX IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12289100	G5333 SCU I BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11973080	PDR944 EL EX SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12289110	G5333 SCU I ED230 1,9 CLST Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11973070	PDR944 EL EX IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11973060	PDR944 EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12289120	G5350 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11973050	PDR944 EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922400	G7200 SCU NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11973040	PDR544ROP SI EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12289130	G5350 Vi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11863140	DAD4840 CH MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11863150	DAD4940 CH MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11923010	G7479 SCVi XXL NER OS230 1,9 AutoD Excel	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922410	G7200 SCi NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972540	PDR922 G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11971810	PDR514TOP EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12288930	G5310 SC I ED230 1,9 CS Front ActivePlu	Drain pump 220-240V 50HZ	Lead	7439-92-1
11959310	PDR514TOP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11973020	PDR544ROP G EX IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11973000	PDR544ROP EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12288940	G5310 SCi I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972990	PDR544ROP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12288950	G5310 SCi I ED230 1,9 CLST Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972980	PDR928 SI EX SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12288960	G5310 SCU I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972970	PDR928 SI EX IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972960	PDR928 G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11922390	G7200 SCU NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972950	PDR928 EL EX SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972940	PDR928 EL EX IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972930	PDR928 EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972920	PDR928 EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972790	PDR528ROP EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972650	PDR528ROP SI EX IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972640	PDR528ROP G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972630	PDR528ROP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972610	PDR922 HP EX SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972600	PDR922 HP EX IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972580	PDR922 SI EX SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12288970	G5310 SCU I ED230 1,9 CLST Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972570	PDR922 SI EX IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972560	PDR922 EL EX SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972550	PDR922 EL EX IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11922990	G7474 SCVi NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12267250	H7860BPX ANL OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11922830	G7202 SCU NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11746810	PG8592 CDN AE-WW-AD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
11922860	G7207 SCU XXL NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922900	G7417 SCU XXL NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922890	G7417 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922880	G7412 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12268130	H7440BMX ANL OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11922870	G7412 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922630	G7415 SCU XXL NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12268120	H7840BMX ANL OBSW/MATT 230/50	Heater element Top heat 220-240V	Lead	7439-92-1
11922620	G7415 SCU XXL NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922590	G7410 SCi NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922570	G7410 SCi NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12092310	PW6321 EH NAM SST MF 2AC 240V 60Hz R	Control electr.unit EW 235-A	Lead	7439-92-1
12128710	H2861B HK EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11922840	G7202 SCU NER ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922850	G7207 SCU XXL NER BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922560	G7410 SCU NER ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11864340	DAD4940 D MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11922530	G7410 SCU NER BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11864370	DAD4840 D MASW 230/50 TLK	SMD- Diode STTH1R04A	Lead	7439-92-1
11922920	G7257 SCVi XXL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922420	G7222 SCU NER BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922910	G7252 SCVi NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922430	G7222 SCU NER ED230 1,9 CLST Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922450	G7255 SCVi XXL NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922440	G7250 SCVi NER ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
12267240	H7840BPX ANL OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11922940	G7279 SCVi XXL NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922930	G7274 SCVi NER ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922820	G7975 SCVi XXL NER OS/CS230 1,9k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289140	G5353 SCVi I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289150	G5355 SCVi XXL I ED230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289160	G5362 SCVi I ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12289170	G5363 SCVi I ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12143270	PPD401 U MAR SST WB	Circulation pump S35 PP (00-53)	Lead	7439-92-1
12295270	H2455E XS2/CH OBSW/EDST-LOOK 400/50	Heater element Hot air 400V	Lead	7439-92-1
12295270	H2455E XS2/CH OBSW/EDST-LOOK 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11922810	G7695 SCVi XXL NER OS/CS230 K20 1,9AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
12295270	H2455E XS2/CH OBSW/EDST-LOOK 400/50	Heater element Top heat 400V	Lead	7439-92-1
12295300	H2455-55B XS2/CH OBSW/EDST-LOOK 400/50	Heater element Hot air 400V	Lead	7439-92-1
12295300	H2455-55B XS2/CH OBSW/EDST-LOOK 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12295300	H2455-55B XS2/CH OBSW/EDST-LOOK 400/50	Heater element Top heat 400V	Lead	7439-92-1
11922800	G7690 SCVi NER OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12303790	G7970 SCVi GB OS/CS230 1,9 k2o AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12295310	H2455-55E XS2/CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
12295310	H2455-55E XS2/CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12295310	H2455-55E XS2/CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
12267260	H7440BPX ANL OBSW/MATT 230/50	Heater element Top heat 230V	Lead	7439-92-1
11922790	G7665 SCVi XXL NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12267270	H7464BPX ANL OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11922780	G7660 SCVi NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922970	G7467 SCVi XXL NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922960	G7462 SCVi NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922770	G7465 SCVi XXL NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922650	G7460 SCVi NER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972360	PDR918 HP EX SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972350	PDR918 HP EX IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972340	PDR918 G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972330	PDR918 EL EX SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972320	PDR918 EL EX IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11746790	PG8582 CDN AE-WW-AD-LD 208V	Circulation pump Mpph01-53/PPS/230V	Lead	7439-92-1
12292900	DGC7465 HCX Pro ANL OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11972310	PDR918 EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972300	PDR918 EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972290	PDR518ROP SI EX IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972280	PDR518ROP G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972270	PDR518ROP EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972260	PDR518ROP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972250	PDR518TOP G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11972230	PDR518TOP EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972220	PDR518TOP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12292890	DGC7445 HCX Pro ANL OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
11972200	PDR914 HP EX SST A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12288720	G5110 SCi I ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972190	PDR914 HP EX IG A01X	SMD- Diode STTH1R04A	Lead	7439-92-1
12288730	G5110 SCU I BW230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288740	G5110 SCU I ED230 1,9 CLST Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886500	G7690 SCVi MER OS/CS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972180	PDR914 G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
12288750	G5132 SC I ED230 1,9 CS Front Select	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288760	G5132 SCU I BW230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288770	G5133 SC I BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12276660	DGC7440 HCX Pro ANL OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12276610	DGC7845 HCX Pro ANL OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12288780	G5133 SC I ED230 1,9 CLST Front Excell	Drain pump 220-240V 50HZ	Lead	7439-92-1
12276600	DGC7840 HCX Pro ANL OBSW/MATT 230/50	SMD- Diode STTH1R04A	Lead	7439-92-1
12295330	H2455-55EP XS2/CH BRWS 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11886440	G7610 SCi MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12295330	H2455-55EP XS2/CH BRWS 400/50	Heater element Hot air 400V	Lead	7439-92-1
12295340	H2455-55EP XS2/CH OBSW 400/50	Heater element Top heat 400V	Lead	7439-92-1
11886450	G7615 SCi XXL MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12295340	H2455-55EP XS2/CH OBSW 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
12295340	H2455-55EP XS2/CH OBSW 400/50	Heater element Hot air 400V	Lead	7439-92-1
11886460	G7660 SCVi MER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12295320	H2455-55EP XS2/CH OBSW/EDST-LOOK 400/50	Heater element Top heat 400V	Lead	7439-92-1
12295320	H2455-55EP XS2/CH OBSW/EDST-LOOK 400/50	Heater element Bottom heat 400V	Lead	7439-92-1
11886480	G7665 SCVi XXL MER OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12295320	H2455-55EP XS2/CH OBSW/EDST-LOOK 400/50	Heater element Hot air 400V	Lead	7439-92-1
12317140	G7110 C SC SG BW230/50 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886820	G7465 SCVi XXL OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886830	G7473 SCVi OE1 OS230 1,9 AutoD Excellenc	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886810	G7460 SCVi OE1 OS/CS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886800	G7415 SCi XXL OE1 ED230 1,9 CS AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886790	G7410 SCi OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886780	G7410 SCi OE1 BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886770	G7410 SC OE1 ED230 1,9 CLST AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886760	G7410 SC OE1 BW230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
11677120	PDR508HP S LW	SMD- Diode STTH1R04A	Lead	7439-92-1
11886740	G7272 SCVi OE1 ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886710	G7255 SCVi XXL OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886700	G7250 SCVi OE1 ED230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886690	G7200 SCi OE1 ED230 1,9 CLST	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886680	G7200 SC OE1 BW230 1,9	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886650	G7200 SC OE1 ED230 1,9 CLST Front	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972400	PDR522TOP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972380	PDR918 SI EX SST E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972370	PDR918 SI EX IG E02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12128710	H2861B HK EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12288830	G5150 SCVi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11500114	Power-/Control unit ELP 7777 120V 60 Hz	SMD- Diode STTH1R04A	Lead	7439-92-1
11922480	G7272 SCVi NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11922500	G7277 SCVi XXL NER ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11972160	PDR914 EL EX SST B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972150	PDR914 EL EX IG B02Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11972140	PDR914 EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11886530	G7925 SCi XXL MER OS230 1,9 AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288840	G5150 Vi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288820	G5133 SCU I ED230 1,9 CS Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288810	G5133 SCU I BW230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12159810	H2761BP B EDST/CLST 230/50	Heater element Top heat 230V	Lead	7439-92-1
12159810	H2761BP B EDST/CLST 230/50	Heater element Unterhitze 230-240V	Lead	7439-92-1
11886510	G7695 SCVi XXL MER OS/CS230 1,9K2O AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
11971820	PDR514ROP EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12288920	G5310 SC I BW230 1,9 Active Plus	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288890	G5163 SCVi I ED230 1,9 Excellence	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288880	G5162 SCVi I ED230 1,9 Selection	Drain pump 220-240V 50HZ	Lead	7439-92-1
11971830	PDR514ROP EL EX SST A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
11971840	PDR514ROP G EX IG E02X	SMD- Diode STTH1R04A	Lead	7439-92-1
11971850	PDR914 EL EX IG A01Z	SMD- Diode STTH1R04A	Lead	7439-92-1
12288870	G5155 SCVi XXL I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886520	G7970 SCVi MER OS/CS230 1,9 K2O AutoDos	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288860	G5153 Vi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
12288850	G5153 SCVi I ED230 1,9 Active	Drain pump 220-240V 50HZ	Lead	7439-92-1
11886550	G7975 SCVi XXL MER OS/CS230 1,9k2o AutoD	Drain pump 220-240V 50HZ	Lead	7439-92-1
8239000	Regulator 230V 50.55021.117/+Z	Regulator 230V 50.55021.117/+Z	Boric acid	10043-35-3
6850923	Regulator 230V 50.55021.155	Regulator 230V 50.55021.155	Boric acid	10043-35-3

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
8239000	Regulator 230V 50.55021.117/+Z	Regulator 230V 50.55021.117/+Z	Boric acid	10043-35-3
8239040	Regulator 230V 50.57021.052	Regulator 230V 50.57021.052	Boric acid	10043-35-3
8230650	Regulator 230V 50.55021.105	Regulator 230V 50.55021.105	Boric acid	10043-35-3
8230650	Regulator 230V 50.55021.105	Regulator 230V 50.55021.105	Boric acid	10043-35-3
7564810	Harness Regulator vormontiert	Regulator 230V 50.57021.155	Boric acid	10043-35-3
8239040	Regulator 230V 50.57021.052	Regulator 230V 50.57021.052	Boric acid	10043-35-3
7564810	Harness Regulator vormontiert	Regulator 230V 50.55021.155	Boric acid	10043-35-3
6980820	CS1122 R01 EDST 230/50	Regulator 230V 50.55021.117/+Z	Boric acid	10043-35-3
6980820	CS1122 R01 EDST 230/50	Regulator 230V 50.57021.052	Boric acid	10043-35-3
6850923	Regulator 230V 50.55021.155	Regulator 230V 50.55021.155	Boric acid	10043-35-3
6850913	Regulator 230V 50.57021.155	Regulator 230V 50.57021.155	Boric acid	10043-35-3
6850913	Regulator 230V 50.57021.155	Regulator 230V 50.57021.155	Boric acid	10043-35-3
11049710	PWM507 DP ZER LW Hygiene	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10878420	PWM908 DP ANL SST -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10878370	PWM908 DV ANL LW -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11114780	PWM907 DP TR SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10878760	PWM908 DV ANL SST -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11114790	PWM908 DP TR LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
12982530	PWM908 DP AUS SST 25A	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11114800	PWM908 DP TR SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11117020	PWM506 DV B LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11103270	PWM508 DV N LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11117030	PWM508 DV B LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11114770	PWM907 DP TR LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11114750	PWM908 DP TR SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11103280	PWM907 DP N LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10823670	PWM906 DP ANL LW -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
12982500	PWM908 DP AUS SST 16A	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10823320	PWM507 DV ANL SST -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11103290	PWM907 DV N LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11050610	PWM907 DV D LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11049770	PWM508 DV D LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11120150	PWM507 DP A LW MH	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11103300	PWM907 DV N SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11049730	PWM507 DP ZER SST Hygiene	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11049700	PWM507 DV D SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11103240	PWM507 DP N LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11169830	PWM507 DV ZER LW Special	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
9348392	Sealing ring Suds container Geh.	Sealing ring Suds container Geh.	Dodecamethylcyclhexasiloxane	540-97-6
9348392	Sealing ring Suds container Geh.	Sealing ring Suds container Geh.	Dodecamethylcyclhexasiloxane	540-97-6
11049740	PWM507 DV ZER SST Hygiene	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
9348392	Sealing ring Suds container Geh.	Sealing ring Suds container Geh.	Dodecamethylcyclhexasiloxane	540-97-6
9348392	Sealing ring Suds container Geh.	Sealing ring Suds container Geh.	Dodecamethylcyclhexasiloxane	540-97-6
11168900	PWM908 DV IRL SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
13083800	DAD6984 XS1/CH MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclhexasiloxane	540-97-6
11121820	PWM507 DP DK LW Hygiene	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11168890	PWM908 DP IRL SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11168820	PWM908 DV IRL SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
13083720	DAD6884 XG1/GB MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclhexasiloxane	540-97-6
11103250	PWM507 DV N LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11168780	PWM908 DP IRL SST	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11154410	PWM907 DV IRL LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
13083780	DAD6984 XG1/GB MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclhexasiloxane	540-97-6
11330440	PW6080Vario XL AV GB OB AC 230V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11154400	PWM907 DV IRL LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11376120	PW5084 XL Mopp AV GB OB 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11154280	PWM507 DP IRL LW	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11154220	PWM506 DV IRL LW Mop Star 60 230V 25A	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11154310	PWM507 DP IRL LW 400V 13A	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11154270	PWM506 DV IRL LW Mop Star 60 230V 13A	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11103210	PWM506 DV N LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11377010	PWT6089Vario XL LP GB OB AC 230V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11748540	PW5105Vario LP GB OB 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11748550	PW5105Vario AV GB OB 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
12199670	PW5082 XL LP GB LW 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
12199680	PW5082 XL AV GB LW 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11205920	PWM906 DP D LW SES ECO EXPRESS	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
13083730	DAD6884 XA1/AUS MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclhexasiloxane	540-97-6
10878320	PWM908 DP ANL LW -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
13083790	DAD6984 XA1/AUS MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclhexasiloxane	540-97-6
10876580	PWM907 DV ANL SST -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10823280	PWM507 DV ANL LW -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
13083750	DAD6884 X C2/CN MASW 220/50 TLK	Seal Built-in frame	Dodecamethylcyclhexasiloxane	540-97-6
10876570	PWM907 DP ANL SST -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
13083810	DAD6984 X C2/CN MASW 220/50 TLK	Seal Built-in frame	Dodecamethylcyclhexasiloxane	540-97-6
10828130	PW5104 Mopp AV GB OB 3N AC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11329970	PW6080Vario XL LP GB ED 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11330000	PW6080Vario XL AV GB ED 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11330070	PW6080Vario XL LP GB OB 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11330280	PW6080Vario XL AV GB OB 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
11330400	PW6080Vario XL LP GB ED AC 230V 50Hz	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10876550	PWM907 DV ANL LW -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10876540	PWM907 DP ANL LW -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6
10823030	PWM507 DP ANL LW -D-	Connection hose Concertina hose	Dodecamethylcyclhexasiloxane	540-97-6

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10823680	PWM906 DV ANL LW -D-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11121850	PWM507 DP FIN LW Hygiene	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11377000	PWT6089Vario XL LP GB ED AC 230V 50Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11049720	PWM507 DV ZER LW Hygiene	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11103310	PWM908 DV N LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11116080	PWM506 DV I SST Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11103320	PWM908 DV N SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050600	PWM907 DP D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10823290	PWM507 DP ANL SST -D-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981360	PWM1900-09 DP ANL LW -CH-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11114740	PWM906 DP TR LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981310	PWM1508 DP ANL LW -EU- MopStar	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981350	PWM1500-08 DP ANL LW -CH-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11049750	PWM506 DV D LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050570	PWM906 DV D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050550	PWM906 DP D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11114510	PWM508 DV TR LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11330420	PW6080Vario XL LP GB OB AC 230V 50Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11114500	PWM507 DP TR SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981320	PWM1509 DV ANL LW -EU- MopStar	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11114490	PWM507 DP TR LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11376920	PWT6089Vario XL LP GB ED 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11114470	PWM506 DV TR SST Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11114460	PWM506 DV TR LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11376950	PWT6089Vario XL LP GB OB 3NAC 400V 50Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
13083760	DAD6884 XR1/OER MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
11330410	PW6080Vario XL AV GB ED AC 230V 50Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
13083820	DAD6984 XR1/OER MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
11088790	PWM908 DV FIN LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088780	PWM908 DP FIN LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088740	PWM906 DV FIN SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088710	PWM906 DP FIN SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088700	PWM906 DV FIN LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088690	PWM906 DP FIN LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088470	PWM507 DV FIN LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088420	PWM507 DP FIN LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11096300	PWM508 DV NL LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087440	PWM908 DV NL SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087430	PWM908 DP NL SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087420	PWM908 DV NL LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087410	PWM908 DP NL LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087400	PWM907 DV NL SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087390	PWM907 DP NL SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087380	PWM907 DV NL LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087370	PWM907 DP NL LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087310	PWM908 DV NL SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
13059120	PWM508 DP AUS LW 16A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
13053670	PWM908 DV AUS SST 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10909250	PWM507 DP ANL LW -D- Hygiene	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10909310	PWM507 DV ANL LW -D- Hygiene	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10909350	PWM507 DP ANL SST -D- Hygiene	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10909360	PWM507 DV ANL SST -D- Hygiene	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10887530	PWM508 DV ANL SST -D- Mopstar 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10887520	PWM508 DV ANL LW -D- Mopstar 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10975470	PWM507 DP ANL LW -CH-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
13072230	PWM906 DP NL LW 230V	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10975480	PWM508 DP ANL LW -CH-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087300	PWM906 DP NL SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087220	PWM507 DV NL SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087210	PWM507 DP NL SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087200	PWM507 DV NL LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11087190	PWM507 DP NL LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094160	PWM907 DV F SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094150	PWM907 DP F SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094140	PWM907 DV F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11116100	PWM507 DV I LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11107350	PWM507 DV I SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11116090	PWM507 DP I LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11107340	PWM507 DP I SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094030	PWM507 DV F SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094020	PWM507 DP F SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094010	PWM507 DV F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11093990	PWM507 DP F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117050	PWM907 DP B LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117060	PWM907 DV B LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117070	PWM907 DP B SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117080	PWM907 DV B SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117190	PWM908 DP B LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117200	PWM908 DV B LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117210	PWM908 DP B SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088530	PWM508 DV FIN LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088140	PWM506 DV FIN LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11093960	PWM506 DV F LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11089390	PWM506 DV DK LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11117220	PWM908 DV B SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117870	PWM507 DP B LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117880	PWM507 DV B LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11107360	PWM907 DP I SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11107370	PWM907 DV I SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11116110	PWM508 DV I SST Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11107380	PWM908 DP I SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11117340	PWM908 DV I SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11049780	PWM508 DV D SST Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11086160	PWM506 DV IB LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11096290	PWM506 DV NL LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094180	PWM908 DV F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094200	PWM908 DV F SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094190	PWM908 DP F SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094170	PWM908 DP F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073220	PWM506 DV S LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088810	PWM908 DV FIN SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11088800	PWM908 DP FIN SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11178640	PWM507 DV S LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11026190	PWM507 DP ANL LW -D- QSR	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050670	PWM908 DV D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11025630	PWM506 DV ANL LW -D- Mopstar 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11025640	PWM506 DV ANL SST -D- Mopstar 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11097750	Connection hose Concertina hose	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11097750	Connection hose Concertina hose	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
13083710	DAD6884 XD1/D MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
13083770	DAD6984 XD1/D MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
11050660	PWM908 DP D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11049650	PWM507 DP D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050650	PWM908 DV D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11049670	PWM507 DV D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11137320	PWM908 DV RU SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11137310	PWM908 DP RU SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11178680	PWM507 DV RU LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050640	PWM908 DP D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11049680	PWM507 DP D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11178660	PWM507 DV DK LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11137300	PWM907 DP RU LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11137280	PWM508 DV RU SST Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11137260	PWM507 DV RU SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11137250	PWM507 DP RU LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050630	PWM907 DV D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11137240	PWM506 DV RU SST Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050620	PWM907 DP D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981270	PWM1508 DP ANL LW -EU-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981280	PWM1508 DP ANL SST -EU-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981290	PWM1908 DP ANL LW -EU-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981300	PWM1909 DV ANL SST -EU-	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12981330	PWM1508 DP ANL LW -EU- Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
9348382	Sealing ring Suds container Geh.	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
13083740	DAD6884 XS1/CH MASW 230/50 TLK	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
9348382	Sealing ring Suds container Geh.	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
9348382	Sealing ring Suds container Geh.	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
9348382	Sealing ring Suds container Geh.	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11114520	PWM508 DV TR SST Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094130	PWM907 DP F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094090	PWM906 DV F SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094070	PWM906 DP F SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094060	PWM906 DV F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11094050	PWM906 DP F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10887940	PWM908 DP ANL SST -MAR- 3AC 230V	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10887930	PWM908 DP ANL LW -MAR- 3AC 230V	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11083010	PWM900-09 DP CH LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11077930	PWM500-09 DP CH LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11077920	PWM500-08 DP CH LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11089430	PWM508 DV DK LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11089150	PWM908 DV DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11089140	PWM908 DP DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11089130	PWM907 DV DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11089120	PWM907 DP DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11089110	PWM906 DV DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11089100	PWM906 DP DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11086820	PWM908 DV IB SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11086810	PWM908 DP IB SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11086590	PWM907 DV IB SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11086580	PWM907 DP IB SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11086550	PWM508 DV IB LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11086320	PWM507 DP IB SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11086280	PWM507 DP IB LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073720	PWM507 DV DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073670	PWM507 DP DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073280	PWM507 DV S LW Hygiene	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073270	PWM908 DV S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073260	PWM907 DV S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11073250	PWM906 DV S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073230	PWM508 DV S LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073210	PWM507 DV S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11073200	PWM507 DP S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10721480	KFN15842D edt/cs EU1	KFN15842D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
10721480	KFN15842D edt/cs EU1	KFN15842D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11050590	PWM906 DV D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11050580	PWM906 DP D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736130	PWM507 DP EXP LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736120	PWM508 DV EXP LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736110	PWM506 DV EXP LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12582780	WEK375WPS I LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11961130	PWM909 EL DP DD GB IG E02X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10622130	KFN28133 D edt/cs EU1	KFN28133 D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
10622450	KFN29132D ws EU1	KFN29132D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
11961090	PWM909 EL DV DD GB SST A01Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11961100	PWM909 EL DV DD GB SST E02Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10622450	KFN29132D ws EU1	KFN29132D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
10622470	KFN29132D edt/cs EU1	KFN29132D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11961120	PWM909 EL DP DD GB SST E02X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11599170	FN12021S EU1	FN12021S EU1	Dodecamethylcyclohexasiloxane	540-97-6
11599170	FN12021S EU1	FN12021S EU1	Dodecamethylcyclohexasiloxane	540-97-6
11961080	PWM909 RH DP DD GB SST A01X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11289940	PWM908 DP AUS SST 16A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11944640	PWM508 DP GB LW 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947050	PWM508 DP B LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11300950	PWM507 DP MAR LW 1N AC 230V 60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11379900	PWM508 DV F LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11394950	PWM507 DP AUS LW Hygiene 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11395020	PWM908 DP AUS LW 16A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11395080	PWM908 DP AUS LW 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947470	PWM508 DP TR LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11390530	PWM908 DP GB SST 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947460	PWM506 DP TR LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11300960	PWM507 DP MAR LW 3 AC 400-480V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11390500	PWM908 DP GB LW 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947450	PWM508 DP S LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947440	PWM506 DP S LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947140	PWM508 DP DK LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947130	PWM506 DP DK LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947040	PWM506 DP B LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11994360	PDW909 EL DP DD GB IG E02X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11994340	PDW909 EL DP DD GB IG A01X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11390330	PWM908 DP GB SST 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11994370	PDW909 EL DP DD GB SST E02X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11994350	PDW909 EL DP DD GB SST A01X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11390320	PWM908 DV GB LW 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11944660	PWM508 DP IRL LW 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11253220	PWM906 DV ZER SST SES LavaPiu	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11253270	PWM908 DV ZER SST SES LavaPiu	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11254700	PWM507 DP UA LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11752540	PWM507 DP GB LW 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10622070	KFN28132 D edt/cs EU1	KFN28132 D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11961070	PWM909 EL DP DD GB SST A01X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11106000	PWM906 DP GB LW 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10622070	KFN28132 D edt/cs EU1	KFN28132 D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
9537800	Fan BG1506 12V	Fan BG1506 12V	Dodecamethylcyclohexasiloxane	540-97-6
11961110	PWM909 EL DV DD GB IG E02Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12582780	WEK375WPS I LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
10622020	KFN28132 D ws EU1	KFN28132 D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
11736260	PWM908 DV EXP SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736250	PWM908 DP EXP SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11254710	PWM507 DP UA SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736240	PWM908 DV EXP LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736230	PWM908 DP EXP LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251390	PWM908 DP MAR SST 2 AC 208-240V 60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251400	PWM906 DP MAR SST 2 AC 208-240V 60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11202630	PWM908 DP CN SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11289930	PWM507 DP AUS LW 16A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11325010	PWM507 DP UA LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736220	PWM907 DV EXP SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736210	PWM907 DP EXP SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736200	PWM907 DV EXP LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736190	PWM907 DP EXP LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736180	PWM906 DV EXP SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736170	PWM906 DP EXP SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736160	PWM906 DV EXP LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736150	PWM906 DP EXP LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12081140	PWM508 DP TR LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12083050	PWM508 DP I LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734090	PWM507 DV EXP SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734080	PWM507 DP EXP SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12082270	PWM506 DP I LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12081110	PWM508 DP I LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
11734070	PWM507 DV EXP LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734060	PWM507 DP EXP LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12080000	PWM508 DP IB LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10622130	KFN28133 D edt/cs EU1	KFN28133 D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
12690260	WWK360WCS TR LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12690260	WWK360WCS TR LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11390310	PWM908 DP GB LW 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11395250	PWM508 DV GB LW Mop Star 80 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11521530	PWM906 DP GB LW 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11588400	PWM507 DV GB LW Hygiene	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12612480	WWK360WCS EU1 LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12612480	WWK360WCS EU1 LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11740390	PWM508 DP S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11740370	PWM506 DP S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736020	PWM508 DV S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11736010	PWM506 DV S LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
9860942	Fan BG1506/RLS100 12V	Fan BG1506/RLS100 12V	Dodecamethylcyclohexasiloxane	540-97-6
11588420	PWM507 DP GB LW Special 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11213680	KFN29162D edt/cs EU1	KFN29162D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11115750	PWM907 DP GB SST 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11213680	KFN29162D edt/cs EU1	KFN29162D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11213670	KFN29162D ws EU1	KFN29162D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
11213670	KFN29162D ws EU1	KFN29162D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
10804910	KFN29142D edt/cs EU1	KFN29142D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11202510	PWM907 DP CN SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11266920	PWM507 DP CN SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10804910	KFN29142D edt/cs EU1	KFN29142D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
10804820	KFN29142D ws EU1	KFN29142D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
10804820	KFN29142D ws EU1	KFN29142D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
10622570	KFN29133D edt/cs EU1	KFN29133D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
10622570	KFN29133D edt/cs EU1	KFN29133D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
10622540	KFN29133D ws EU1	KFN29133D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
11921510	PWM508 DV NL LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11921500	PWM508 DP NL LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11105750	PWM507 DP GB LW 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11105770	PWM507 DP GB SST 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11105830	PWM906 DP GB LW 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11106450	PWM907 DP GB LW 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10622540	KFN29133D ws EU1	KFN29133D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
10622470	KFN29132D edt/cs EU1	KFN29132D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11115710	PWM907 DV GB LW 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11115720	PWM907 DP GB SST 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11106470	PWM907 DP GB LW 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11115740	PWM907 DV GB LW 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947430	PWM508 DP IB LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11435880	PWM508 DV UA SST Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947420	PWM506 DP IB LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947410	PWM508 DP N LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947400	PWM506 DP N LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947380	PWM508 DP NL LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947370	PWM506 DP NL LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947230	PWM506 DP F LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947250	PWM508 DP F LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11395290	PWM508 DV IRL LW Mop Star 80 220-240V 25	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947170	PWM508 DP FIN LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947160	PWM508 DP FIN LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11992790	PWM508 DV FIN LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11992780	PWM508 DP FIN LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947360	PWM508 DP GB LW Mop Star 80 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947350	PWM508 DP GB LW Mop Star 80 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947340	PWM506 DP GB LW Mop Star 60 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11947330	PWM506 DP GB LW Mop Star 60 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11997290	PWM907 DV S SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11905860	PWM508 DP D LW Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11905850	PWM506 DP D LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11477640	PWM507 DV IB LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11477650	PWM507 DV IB SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11202350	PWM508 DV CN SST Mop Star 80	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11267100	PWM506 DV CN SST Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11467860	PWM906 DP MAR RU SST 3 AC 230V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11468020	PWM908 DP MAR RU LW 3 AC 400-480V 50/60H	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11922040	PWM508 DV DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11922030	PWM508 DP DK LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11944580	PWM508 DV N LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11944570	PWM508 DP N LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11921460	PWM508 DV B LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11390520	PWM908 DP GB LW 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11921450	PWM508 DP B LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12618230	W1D BigFoot PWash 15° ICRT WCS 11kg ANL	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11921290	PWM508 DV F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12618230	W1D BigFoot PWash 15° ICRT WCS 11kg ANL	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11921280	PWM508 DP F LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12699110	PWM511MOP EL DV DD GB IG E02Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12699100	PWM509MOP EL DV DD GB IG E02Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12387570	WCK360WCS E LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12389520	WSK363WCS NL LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12389520	WSK363WCS NL LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12389510	WEK375WPS NL LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12389510	WEK375WPS NL LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11178390	PWM507 DP IB LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11169820	PWM507 DP ZER LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11270080	PWM507 DV D LW ISS T	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11270090	PWM507 DP D LW ISS T	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12349590	PWM906 DP INT LW TexLab	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11049760	PWM506 DV D SST Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251280	PWM908 DP MAR LW 3 AC 400-480V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251290	PWM908 DP MAR SST 3 AC 400-480V 50/60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11961050	PWM511 EL DP DD GB IG A01X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251300	PWM906 DP MAR LW 3 AC 400-480V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251310	PWM906 DP MAR SST 3 AC 400-480V 50/60H	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11198540	PWM508 DV AUS LW Mop Star 80 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11203340	PWM507 DP AUS LW 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11204460	PWM908 DP NAM LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11204470	PWM908 DP NAM SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11198770	PWM908 DP AUS SST 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11898860	PWM508 DV D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11198790	PWM908 DV AUS SST 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251340	PWM908 DP MAR LW 3 AC 230V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251350	PWM908 DP MAR SST 3 AC 230V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251370	PWM906 DP MAR LW 3 AC 230V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11251380	PWM906 DP MAR SST 3 AC 230V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11588410	PWM507 DV GB LW Hygiene 400V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11898830	PWM508 DV D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11898800	PWM508 DP D SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10721500	KFN15943D edt/cs EU1	KFN15943D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11252310	PWM906 DP MAR LW 2N AC 400V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12949450	Built-in frame DADX3X0	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
10721500	KFN15943D edt/cs EU1	KFN15943D edt/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
12489940	PWM506 DP DK LW Mop Star 60 10A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12511490	PWM506 DP EXP LW Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11395240	PWM508 DV GB LW Mop Star 80 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11621300	PWM507 DV FIN LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12392790	WSK363WCS GB LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12392790	WSK363WCS GB LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12388870	WEK375WCS FIN LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12388870	WEK375WCS FIN LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12390550	WEK375WPS B LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12390550	WEK375WPS B LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12390540	WCK370WCS B LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12390540	WCK370WCS B LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12402180	WCK360WCS I LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12402180	WCK360WCS I LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12390560	WSK363WCS B LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11805362	Built-in frame DAD4940	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
12390560	WSK363WCS B LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12405090	WCK360WCS F LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12405090	WCK360WCS F LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12392770	WWK360WCS GB LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11567152	Built-in frame DAD4840	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
12392770	WWK360WCS GB LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12390570	WWK360WCS B LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12390570	WWK360WCS B LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12388810	WWK360WCS P LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12388810	WWK360WCS P LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12392780	WEK365WCS GB LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12392780	WEK365WCS GB LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12388860	WEK375WCS NDS LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11961040	PWM511 EL DV DD GB IG A01Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12388860	WEK375WCS NDS LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12387580	WWK360WCS E LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12387580	WWK360WCS E LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12387570	WCK360WCS E LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11898770	PWM508 DP D LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10721540	KFN16947D ed/cs EU1	KFN16947D ed/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
12679430	Built-in frame DADX8X0	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
10721540	KFN16947D ed/cs EU1	KFN16947D ed/cs EU1	Dodecamethylcyclohexasiloxane	540-97-6
11254750	PWM908 DP UA SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12389490	WCK370WCS NL LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
11254760	PWM908 DV UA SST	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11254720	PWM507 DV UA LW Special	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11254730	PWM506 DV UA SST Mop Star 60	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11254740	PWM907 DP UA LW	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11961010	PWM511 EL DV DD GB IG E02Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12389490	WCK370WCS NL LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
9537800	Fan BG1506 12V	Fan BG1506 12V	Dodecamethylcyclohexasiloxane	540-97-6
11689490	PWM507 DP GB LW Special 2N 400V 50Hz 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11961020	PWM511 EL DP DD GB IG E02X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10359670	O-ring 30x3,55	O-ring 30x3,55	Dodecamethylcyclohexasiloxane	540-97-6

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
10359670	O-ring 30x3,55	O-ring 30x3,55	Dodecamethylcyclohexasiloxane	540-97-6
11961030	PWM511MOP RH DV DD GB IG A01Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734980	PWM906 DV ZER LW SES	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734970	PWM906 DP ZER LW SES	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734960	PWM906 DV ZER SST SES	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734950	PWM906 DP ZER SST SES	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734940	PWM907 DV ZER LW SES	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734930	PWM907 DP ZER LW SES	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
7370252	Fan BG2012 230V 50Hz	Fan BG2012 230V 50Hz	Dodecamethylcyclohexasiloxane	540-97-6
11734920	PWM907 DV ZER SST SES	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
7370252	Fan BG2012 230V 50Hz	Fan BG2012 230V 50Hz	Dodecamethylcyclohexasiloxane	540-97-6
11923480	PWM909 EL DV DD GB IG A01Z	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11961060	PWM909 EL DP DD GB IG A01X	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11734910	PWM907 DP ZER SST SES	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
9860942	Fan BG1506/RLS100 12V	Fan BG1506/RLS100 12V	Dodecamethylcyclohexasiloxane	540-97-6
11105630	PWM506 DV GB LW Mop Star 60 230V 25A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11105610	PWM506 DV GB LW Mop Star 60 230V 13A	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10622020	KFN28132 D ws EU1	KFN28132 D ws EU1	Dodecamethylcyclohexasiloxane	540-97-6
11252330	PWM906 DP MAR SST 2N AC 400V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12727330	WWK360WCS CZ LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12727330	WWK360WCS CZ LW PWash&10kg	Sealing ring Suds container Geh.	Dodecamethylcyclohexasiloxane	540-97-6
12707940	PWM907 DV DK LW BL	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
11252200	PWM908 DP MAR LW 2N AC 400V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
12948370	Built-in frame DAD9X0	Seal Built-in frame	Dodecamethylcyclohexasiloxane	540-97-6
11252240	PWM908 DP MAR SST 2N AC 400V 50/60Hz	Connection hose Concertina hose	Dodecamethylcyclohexasiloxane	540-97-6
10721540	KFN16947D ed/cs EU1	KFN16947D ed/cs EU1	Octamethylcyclotetrasiloxane	556-67-2
10721500	KFN15943D edt/cs EU1	KFN15943D edt/cs EU1	Octamethylcyclotetrasiloxane	556-67-2
10721540	KFN16947D ed/cs EU1	KFN16947D ed/cs EU1	Octamethylcyclotetrasiloxane	556-67-2
10721480	KFN15842D edt/cs EU1	KFN15842D edt/cs EU1	Octamethylcyclotetrasiloxane	556-67-2
10721500	KFN15943D edt/cs EU1	KFN15943D edt/cs EU1	Octamethylcyclotetrasiloxane	556-67-2
10721480	KFN15842D edt/cs EU1	KFN15842D edt/cs EU1	Octamethylcyclotetrasiloxane	556-67-2
10499480	H2265E CDN EDST/CLST 240/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10499470	H2265E CDN EDST/CLST 208/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10499490	H2265B CDN EDST/CLST 208/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10599390	H2265B C CN EDST/CLST 220/50 Active	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10585890	H2267B ROK EDST/CLST 220/60 Active	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10874880	H2890B AN6 EDST/CLST 220/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10586690	H2265E D EDST/CLST 230/50 Active	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10250050	H6290B SA EDST/CLST 220/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10585650	H2265B D EDST/CLST 230/50 Active	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10138790	H2561B IB EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10499500	H2265B CDN EDST/CLST 240/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
11146290	H2890B ROK EDST/CLST 220/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
11292890	H2890B TW EDST/CLST 220/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10562790	H2265B TW EDST/CLST 220/60 Active	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10608750	H2265B J EDST/CLST 200/50 Active	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10684730	H2265B SA EDST/CLST 220/60 ACTIVE	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10616380	H2265I CDN EDST/CLST 208/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10616390	H2265I CDN EDST/CLST 240/60	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10109610	H2661-1B D BRWS 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10109600	H2661-1B D OBSW 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10109590	H2661-1B D EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10009380	H2661-1B ANL EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
12183410	H2890B KW EDST/CLST 220/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
12975650	BO8190L XA1/AUS OBSW 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
11127820	H2890B AUS EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
11099480	H2890B NL EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
11119230	H2890B I EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
11110390	H2890B B EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
11093380	H2890B GB EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
11129050	H2890B HK EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
7512511	Temperature regul. Sub-assembly	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
7512511	Temperature regul. Sub-assembly	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
10400200	H2890B ANL EDST/CLST 230/50	Temperature regul. Sub-assembly	HYDROGENATED TERPHENYLS	61788-32-7
12555650	DAH1852 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12285021	LED lamp NV-1200-KWWW	LED lamp NV-1200-KWWW	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12389420	LED lamp NV-900-KWWW-RGB	LED lamp NV-900-KWWW-RGB	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12389420	LED lamp NV-900-KWWW-RGB	LED lamp NV-900-KWWW-RGB	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12389340	LED lamp NV-1200-KWWW-RGB	LED lamp NV-1200-KWWW-RGB	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12533990	DAH2960EXTA D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12533860	DAH1650 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12285021	LED lamp NV-1200-KWWW	LED lamp NV-1200-KWWW	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12591580	DAH2960 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12591570	DAH1950 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12534200	DAH2960 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12533880	DAH1850 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12545640	DAH2960 GB OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12284821	LED lamp NV-900-KWWW	LED lamp NV-900-KWWW	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12284821	LED lamp NV-900-KWWW	LED lamp NV-900-KWWW	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12533900	DAH1950 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12389340	LED lamp NV-1200-KWWW-RGB	LED lamp NV-1200-KWWW-RGB	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12533960	DAH2960 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12591560	DAH1650 UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12533940	DAH2860 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7

Material	Material description	Component	Description of pure substance/pure substance group	CAS No.
12534180	DAH1650 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12533920	DAH2660 D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12534190	DAH1950 CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12342570	DAH2960 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12342510	DAH1950 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12342470	DAH1650 XS1/CH OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12342350	DAH2960 XG1/GB OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12343400	DAH1650 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12343420	DAH1850 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12342160	DAH2960EXTA XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12503241	LED lamp Cornered HV DAH BLACK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12343440	DAH1950 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12503241	LED lamp Cornered HV DAH BLACK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12342000	DAH2960 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12343460	DAH2660 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12341980	DAH2860 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12343480	DAH2860 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12343500	DAH2960 XN1/UA OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12786270	DAH2960 XO1/ROK OBSW 220/60 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12555210	DAH1650 TR OBSW 230/50 TL	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12623210	DAH2960 ROK OBSW 220/60 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12679130	DAH1650 KZ OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12679140	DAH1950 KZ OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12341850	DAH1650 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12341910	DAH2660 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12341870	DAH1850 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12341890	DAH1950 XD1/D OBSW 230/50 TLK	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7
12555220	DAH1950 TR OBSW 230/50 TL	LED lamp Cornered HV DAH BLACK	2,2',6,6'-Tetrabromo-4,4'-isopropylidenediphenol	79-94-7